

RP73D2B332RBTDF

✓ ACTIVE

Holsworthy | Holsworthy RP73


TE Internal #: 3-1879257-8

332 ohm, Thin Film, Precision Resistor, .1 %, 1206, .25 W, ±15 ppm/° C, Solder, 2 Terminations, .55 mm [.022 in] Height, Holsworthy RP73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: Precision Resistor

Element Type: Thin Film

Package Size Code: 1206

Power Rating: .25 W

Resistance Value: 332 Ω

Features

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	1206

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	200 V
Power Rating	.25 W
Resistance Value	332 Ω
Resistance Class	Up to 1kΩ
Passive Component Tolerance	.1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.55 mm[.022 in]
Product Length	3.05 mm[.12 in]
Product Width	1.55 mm[.061 in]



Usage Conditions

Temperature Coefficient	±15 ppm/°C
-------------------------	------------

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

RP73D2B332RBTDF

332 ohm, Thin Film, Precision Resistor, .1 %, 1206, .25 W, ±15 ppm/°C, Solder, 2 Terminations, .55 mm [.022 in] Height, Holsworthy RP73





TE Part # 2-1879279-6

[RP 2A 75K 0.1% 15PPM 1K RL](#)



TE Part # 5-1879743-7

[RP 1J 18R2 0.1% 15PPM CUT LENGTH](#)



TE Part # 2-1879747-4

[RP 1J 110K 0.1% 15PPM CUT LENGTH](#)



TE Part # 5-1879267-0

[RP 2B 1M0 0.1% 15PPM 1K RL](#)



TE Part # 9-1879252-4

[RP 2B 10R 0.1% 15PPM CUT LENGTH](#)

Also in the Series | [Holsworthy RP73](#)



[Surface Mount Resistors\(4227\)](#)

Customers Also Bought



TE Part #1-830611-0

[LGH 1/2 SNGL MLD END](#)



TE Part #9-1625971-5

[HSA25 R01 10%](#)




TE Part #1-1879353-9

[RR02 5% 24K AMMO](#)



TE Part #7-1879354-5

[RR03 5% 390R AMMO](#)



TE Part #7-1879648-1

[H4P 287R 0.5% 100PPM](#)




TE Part #7-2176305-3

[RP 1E 0.1W 604R 0.1% 25PPM 5K RL](#)



TE Part #3-2176307-2


[RP 1E 0.1W 26K1 0.1% 25PPM 5K RL](#)




TE Part #2337238-3

[TACT MINI GW 5.2X5.2X2 160GF](#)





TE Part #3-1437162-8
[FSP-12A-11](#)



TE Part #2-2176392-9
[RQ 1206 261K 0.1% 10PPM 5K RL](#)

Documents

Product Drawings

[RP 2B 332R 0.1% 15PPM 1K RL](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_3-1879257-8_BA1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1879257-8_BA1.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_3-1879257-8_BA1.3d_igs.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[RP73-0915](#)

English

[8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS](#)

English