



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Protective Cover**
Operating Temperature (Max): **175 °C [347 °F]**
Operating Temperature Range: **-65 – 175 °C [-85 – 347 °F]**

Features

Product Type Features

Sealable	Yes
Connector Cover Type	Protective Cover

Body Features

Primary Product Plating Material	Cadmium
Seal Material	Silicone

Mechanical Attachment

Component Retention Feature	Wire Rope with PTFE Coating
-----------------------------	-----------------------------

Housing Features

Compatible With Connector Shape	Circular
---------------------------------	----------

Dimensions

Product Length	127 mm[5 in]
----------------	--------------

Usage Conditions


Operating Temperature (Max)	175 °C[347 °F]
Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]

Operation/Application

Compatible With Connector Shell Size	21
--------------------------------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)





EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Cd (100% in 10563725794) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-D38999-DTS19G
Straight Plug: D38999, 21-39 Insert, Electroless Nickel Plating



TE Part # YDTS24W21-41SAV001
RECP ASSY



TE Part # CAT-D38999-DTS19F
Straight Plug: D38999, 21-35 Insert, Electroless Nickel Plating



TE Part # CAT-D38999-DTS19H
Straight Plug: D38999, 21-41 Insert, Electroless Nickel Plating



TE Part # CAT-D38999-DTS19D
Straight Plug: D38999, 21-11 Insert, Electroless Nickel Plating



TE Part # CAT-D38999-DTS19E
Straight Plug: D38999, 21-16 Insert, Electroless Nickel Plating






Also in the Series

DEUTSCH 38999 Metal Covers



Customers Also Bought



Documents

Product Drawings

DUST COVER ASSEM

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_YDTS32W21NV0010000_1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_YDTS32W21NV0010000_1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_YDTS32W21NV0010000_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[DEUTSCH MIL-DTL-38999 CIRCULAR CONNECTORS](#)

English