



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Protective Cover**
Operating Temperature (Max): **175 °C [347 °F]**
Operating Temperature Range: **-65 – 175 °C [-85 – 347 °F]**

Features

Product Type Features

Sealable	Yes
Connector Cover Type	Protective Cover

Body Features

Primary Product Plating Material	Nickel
Seal Material	Silicone

Mechanical Attachment

Component Retention Feature	Wire Rope with PTFE Coating
-----------------------------	-----------------------------

Housing Features

Compatible With Connector Shape	Circular
---------------------------------	----------

Dimensions

Product Length	127 mm[5 in]
----------------	--------------

Usage Conditions


Operating Temperature (Max)	175 °C[347 °F]
Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]

Operation/Application

Compatible With Connector Shell Size	9
--------------------------------------	---

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # YDTS24F09-98PNV001
RECP ASSY

Also in the Series | [DEUTSCH 38999 Metal Covers](#)



Customers Also Bought



Documents

Product Drawings

DTS CAP ASSY, NICKEL, SIZE 9 RCPT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_YDTS33F09RV0010000_3.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_YDTS33F09RV0010000_3.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_YDTS33F09RV0010000_3.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



[Datasheets & Catalog Pages](#)
[DEUTSCH MIL-DTL-38999 CIRCULAR CONNECTORS](#)
[English](#)