




Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: Pb (13% in 4690948374) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Customers Also Bought



TE Part #170191-3
FF 312 REC 18-14AWG TPBR
REREELING



TE Part #170304-1
250 FASTON,REC.,22-18 AWG,BR



TE Part #172130-6
FF 250 REC HSG 2P NYLON GRAY



TE Part #CAT-T319-CH8172
TH/.025 CONNECTOR SYSTEM,
HOUSING



TE Part #CAT-HPCH5372
High Pin Count Header



TE Part #1-1438356-2
24 WAY ARM PLUG, KEY D NSB



TE Part #1473867-1
040 MLC 8POS CAP OUTER HSG

Documents

- CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_9-175448-1_N.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_9-175448-1_N.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_9-175448-1_N.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_9-175448-1_N3.2d_dxf.zip

English

Customer View Model

ENG_CVM_9-175448-1_N3.3d_igs.zip

English

Customer View Model

ENG_CVM_9-175448-1_N3.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Product Specifications

Application Specification

English

Instruction Sheets

HYBRID I/O CONNECTOR

English

HYBRID I/O CONNECTOR

English

HYBRID I/O CONNECTOR

English

HYBRID I/O CONNECTOR

English