




Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Precision Resistor**
Element Type: **Thin Film**
Power Rating: **1 W**
Resistance Class: **Up to 1kΩ**
Resistance Value: **953 Ω**

Features

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	500 V
Power Rating	1 W
Resistance Class	Up to 1kΩ
Resistance Value	953 Ω
Passive Component Tolerance	.5 %

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	10 x 3.7 mm
------------------------------	-------------



Usage Conditions

Operating Temperature Range	-55 – 155 °C[-67 – 311 °F]
Temperature Coefficient	±100 ppm/°C

Packaging Features

Packaging Method	Bandoliered
------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

H4P953RDZA

953 ohm, Thin Film, Precision Resistor, .5 %, 1 W, ±100 ppm/°C, Axial-Leaded, Copper Termination, 10 x 3.7 mm, Bandoliered, Holsworthy Holco



TE Part # 1879623-8
H4 1K3 0.1% 5PPM

TE Part # 2-1879622-2
H4P 1M0 1% 50PPM

TE Part # 5-1879642-1
H8 5K0 0.1% 25PPM

TE Part # 9-1879664-1
H8 10K 0.1% 15PPM

TE Part # 1879629-8
H4P 127R 0.5% 5PPM

Also in the Series | [Holsworthy Holco](#)

[Through-Hole Resistors\(6370\)](#)

Customers Also Bought

TE Part #1-66399-0
III+ SKT,24-20,TIN ,LP

TE Part #170362-1
UNIV M-N-L SOC. 22-18 AWG

TE Part #213852-1
CPC PLUG ASSEMBLY SIZE 23-19

TE Part #213868-1
23-19 RCPT HSG,REV SEX,CPC

TE Part #641937-1
03P MTA156 HDR ASSY STR W/O#2


TE Part #1614976-1
LR0204 1% 100K

TE Part #1622209-1
LR0204 1% 2K2


TE Part #1622217-1
LR0204 1% 330R

H4P953RDZA

953 ohm, Thin Film, Precision Resistor, .5 %, 1 W, ±100 ppm/°C, Axial-Leaded, Copper Termination, 10 x 3.7 mm, Bandoliered, Holsworthy Holco



TE Part #6-1879627-4
[H4P 4K3 1% 100PPM](#)



TE Part #2-2823088-5
[25P,2MM,BRK HDR,SRVT,2.8,0.76AU, TB](#)

Documents

Product Drawings

[H4P 953R 0.5% 100PPM](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_9-1879648-6_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-1879648-6_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-1879648-6_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[Axial Leaded Precision Resistors - Type HOLCO Series](#)

English

[8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS](#)

English