



Heat Shrink Tubing



Tubing Product Type: **Heat Shrink Tubing**

Primary Product Color: **Clear**

Wall Type: **Single Wall**

Expanded Inside Diameter (Min): **24 mm [.945 in]**

Recovered Inside Diameter (Max): **8 mm [.315 in]**

Features

Product Type Features

Tubing Product Type	Heat Shrink Tubing
Wall Type	Single Wall

Electrical Characteristics

Operating Voltage (Max)	.6 kV
-------------------------	-------

Body Features

Fluid Type	Gasoline, Hydraulic Fluid, Lubricating Oil
Primary Product Color	Clear
Shrink Ratio	3:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Flexible

Dimensions

Recovered Wall Thickness (Nominal)	1 mm[.039 in]
Recovered Wall Thickness (Tolerance)	.2 mm[.008 in]
Expanded Inside Diameter (Min)	24 mm[.945 in]
Recovered Inside Diameter (Max)	8 mm[.315 in]
Tubing Size Range	8 – 24 mm[.315 – .945 in]

Usage Conditions



Shrink Temperature (Min)	80 °C
Tubing Flammability Type	Non-Flame-Retardant
Operating Temperature Range	-40 – 135 °C[-40 – 275 °F]
Recovery Temperature	120 °C

Operation/Application

Mechanical Resistance	Fluids, Mechanical Damage, Strain Relief
-----------------------	--

Product Availability

Applicable Region	Asia, EMEA
-------------------	------------

Packaging Features

Packaging Method	Box
------------------	-----

Other

Meets Low Outgassing Requirements	No
Product Source	Czech Republic

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

CGPT-24/8-X-SP

Heat Shrink Tubing, Clear, 3:1, Single Wall, Shrinks To 8 mm [.315 in], Irradiated Modified Polyolefin, 24 mm [.945 in] Expanded Inside, RAYCHEM CGPT




on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | RAYCHEM CGPT



Heat Shrink Tubing(347)



Orange Heat Shrink Tubing(1)



Power Cable Tubing & Accessories(8)



Single Wall Tubing(346)


Customers Also Bought



TE Part #1074372007
DWTC-8/2-X-STK



TE Part #7474490001
TMS-SCE-1K-1/4-2.0-9



TE Part #131250-000
222K132-25/225-0




TE Part #6893036001
RNF-3000-R-18/6-0



TE Part #NB19914001
VERSAFIT-1/16-0-SP




TE Part #CAT-T3437-R819
RPS Commercial Grade Sleeves



TE Part #5069844021
CGPT-6.4/3.2-0-SP



TE Part #1-2112041-2
26POS, MIXED, TAB HSG, ASSY, SEALED



Documents

Product Drawings

CGPT-24/8-X-SP

English

Datasheets & Catalog Pages

Selecting_Correct_Tubing_1216

English

Application Tooling for Raychem Heat Shrink Product

English

Measuring_Single_Wall_Tubing

English

cgpt-tubing

English

Product Specifications

Quality Specification

English