

ASHD014-1PN-C35-978M

✓ ACTIVE

DEUTSCH | DEUTSCH ASHD

TE Internal #: ASHD014-1PNC35978M

Wire-to-Wire, Circular Connector Receptacle, 1 Position, Shell Size 14, Black Zinc, Aluminum Alloy, Code N, Hard Dielectric/Silicone, DEUTSCH ASHD

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Wire-to-Wire**

Number of Positions: **1**

Shell Plating Material: **Black Zinc**

Shell Base Material: **Aluminum Alloy**

Polarization Code: **N**

Features

Product Type Features

| | |
|-------------------------|-------------------------------|
| Assembly Type | Electrical Connector |
| Connector Product Type | Connector Assembly |
| Connector System | Wire-to-Wire |
| Circular Connector Type | Circular Connector Receptacle |
| Shell Type | Metal |

Configuration Features

| | |
|-----------------------------|----|
| Factory Installed Backshell | No |
| Number of Positions | 1 |
| Contacts Preloaded | No |

Body Features

| | |
|---|--------------------------|
| Feedthrough Type | No |
| Entry Style | Rear Insertion |
| Shell Plating Material | Black Zinc |
| Shell Base Material | Aluminum Alloy |
| Circular Connector Insulation Material Type | Hard Dielectric/Silicone |
| Hermetically Sealed | No |

Contact Features

| | |
|--|--|
| | |
|--|--|



| | |
|---------------------------------|-----|
| Circular Connector Contact Type | Pin |
|---------------------------------|-----|

Mechanical Attachment

| | |
|--------------------------|---------------|
| Panel Mount Feature Type | 2 Hole Flange |
| Mating Retention Type | Bayonet Peg |
| Mating Alignment | With |
| Polarization Code | N |
| Mating Alignment Type | Keyed |
| Mating Retention | With |

Housing Features

| | |
|-------------------------------|----|
| Circular Connector Shell Size | 14 |
|-------------------------------|----|

Dimensions

| | |
|-----------------|---------|
| Assembly Length | 33.5 mm |
|-----------------|---------|

Usage Conditions

| | |
|-----------------------------|----------------------------|
| IP Dust Sealing Level | 6 |
| IP Water Sealing Level | 7 |
| Fluid Resistance | Immersion |
| Operating Temperature Range | -55 – 150 °C[-67 – 302 °F] |

Operation/Application

| | |
|-------------------|------------|
| Durability Rating | 500 Cycles |
|-------------------|------------|

Other

| | |
|-------------------|-----|
| Field Serviceable | Yes |
|-------------------|-----|

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant with Exemptions |
| EU ELV Directive 2000/53/EC | Compliant with Exemptions |
| China RoHS 2 Directive MIIT Order No 32, 2016 | 有害物质含量超出标准 Restricted Substance(s) Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (1.2% in Contact) <small>Article Safe Usage Statements:</small> |



Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

| | |
|---------------------------|--------------------------------------|
| Halogen Content | Not Yet Reviewed for halogen content |
| Solder Process Capability | Reflow solder capable to 245°C |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | DEUTSCH ASHD

Standard Circular Connectors(72)

Customers Also Bought

TE Part #CAT-HST-BSTS
BSTS/BSTS-FR Heat Shrink Tubing

TE Part #358279-000
382C312-50-01-0

TE Part #ZPF000000000007174
983-ORS 08-98 PN

TE Part #ZPF000000000001261
097-0267-16 A1267

TE Part #1616058-6
A703CD (FAA/PMA)=RELAY

TE Part #1617147-5
JMGAP-26P = M39016/17-030P

TE Part #1617807-5
FC-335-SY8= RELAY, 3PST

TE Part #YDTS20Y13-98XNV001
HERM REC

ASHD014-1PN-C35-978M

Wire-to-Wire, Circular Connector Receptacle, 1 Position, Shell Size 14, Black Zinc, Aluminum Alloy, Code N, Hard Dielectric/Silicone, DEUTSCH ASHD



Documents

Datasheets & Catalog Pages

DEUTSCH Autosport Interconnection Solutions

English