



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Wire-to-Wire**  
Number of Positions: **5**  
Shell Plating Material: **Black Zinc**  
Shell Base Material: **Aluminum Alloy**  
Polarization Code: **B**

Features

Product Type Features

Connector Product Type	Connector Assembly
Assembly Type	Electrical Connector
Connector System	Wire-to-Wire
Circular Connector Type	Plug
Shell Type	Metal

Configuration Features

Factory Installed Backshell	No
Number of Positions	5
Contacts Preloaded	No

Body Features

Entry Style	Rear Insertion
Environmental Protection	With
Environmental Protection Type	Sealed
Feedthrough Type	No
Shell Plating Material	Black Zinc
Shell Base Material	Aluminum Alloy
Circular Connector Insulation Material Type	Hard Dielectric/Silicone



Hermetically Sealed	No
---------------------	----

Contact Features

Contact Quantity (Size 22D)	5
Contact Layout Arrangement	3 – 5
Circular Connector Contact Type	Pin

Mechanical Attachment

Mating Retention Type	Coupling Ring
Mating Alignment	With
Polarization Code	B
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features

Circular Connector Shell Size	3
-------------------------------	---

Dimensions

Assembly Length	17.7 mm
-----------------	---------

Usage Conditions

IP Dust Sealing Level	6
IP Water Sealing Level	7
Fluid Resistance	Immersion
Operating Temperature Range	-55 – 170 °C[-67 – 338 °F]

Operation/Application

Durability Rating	500 Cycles
-------------------	------------

Other

Field Serviceable	Yes
-------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)



Candidate List Declared Against: JAN 2024  
(240)  
SVHC > Threshold:  
Pb (1.2% in Contact)

**Article Safe Usage Statements:**  
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # ZPF000000000000867

[PINCE AFM-8](#)

Also in the Series | [DEUTSCH ASU](#)



[Standard Circular Connectors\(84\)](#)

Customers Also Bought

ASU603-05PB-HE

5 Position Circular Connector, Wire-to-Wire, Black Zinc, Aluminum Alloy, B Code, Hard Dielectric/Silicone, 3 Shell Size, Plug, Metal, Pin, DEUTSCH ASU



TE Part #AS618-35PN  
PLUG BOOT TERMIN N TYPE 6



TE Part #ASU603-05PN-HE  
PLUG ASSY ASU 5 WAY



TE Part #ASU003-05SN-HE  
RECEPT ASSY 2 HOLE MTG ASU 5 WAY



TE Part #ASU003-03SN-HE  
RECEPT ASSY 2 HOLE MTG AS 3 WAY



TE Part #ASU603-03PD-HE  
PLUG ASSY AS 3 WAY



TE Part #ASU603-03PN-HE  
PLUG ASSY AS 3 WAY



TE Part #ASU103-05SA-HE  
INLINE RECEPT ASSY ASU 5 WAY



TE Part #ASU603-05PC-HE  
PLUG ASSY ASU 5 WAY



TE Part #ASU003-05SB-HE  
RECEPT ASSY 2 HOLE MTG ASU 5 WAY



TE Part #604984-ZZ  
SOCKET CONTACT #22 AS MODULAR

Documents

Product Drawings  
PLUG ASSY ASU 5 WAY

English

Datasheets & Catalog Pages  
DEUTSCH Autosport Interconnection Solutions

English