

ASU603-05PD-HE

✓ ACTIVE

DEUTSCH | DEUTSCH ASU

TE Internal #: ASU603-05PD-HE

5 Position Circular Connector, Wire-to-Wire, Black Zinc, Aluminum Alloy, D Code, Hard Dielectric/Silicone, 3 Shell Size, Plug, Metal, Pin, DEUTSCH ASU

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Wire-to-Wire**

Number of Positions: **5**

Shell Plating Material: **Black Zinc**

Shell Base Material: **Aluminum Alloy**

Polarization Code: **D**

Features

Product Type Features

| | |
|-------------------------|----------------------|
| Connector Product Type | Connector Assembly |
| Assembly Type | Electrical Connector |
| Connector System | Wire-to-Wire |
| Circular Connector Type | Plug |
| Shell Type | Metal |

Configuration Features

| | |
|-----------------------------|----|
| Factory Installed Backshell | No |
| Number of Positions | 5 |
| Contacts Preloaded | No |

Body Features

| | |
|---|--------------------------|
| Entry Style | Rear Insertion |
| Environmental Protection | With |
| Environmental Protection Type | Sealed |
| Feedthrough Type | No |
| Shell Plating Material | Black Zinc |
| Shell Base Material | Aluminum Alloy |
| Circular Connector Insulation Material Type | Hard Dielectric/Silicone |



| | |
|---------------------|----|
| Hermetically Sealed | No |
|---------------------|----|

Contact Features

| | |
|---------------------------------|-------|
| Contact Quantity (Size 22D) | 5 |
| Contact Layout Arrangement | 3 – 5 |
| Circular Connector Contact Type | Pin |

Mechanical Attachment

| | |
|-----------------------|---------------|
| Mating Retention Type | Coupling Ring |
| Mating Alignment | With |
| Polarization Code | D |
| Mating Alignment Type | Keyed |
| Mating Retention | With |

Housing Features

| | |
|-------------------------------|---|
| Circular Connector Shell Size | 3 |
|-------------------------------|---|

Dimensions

| | |
|-----------------|---------|
| Assembly Length | 17.7 mm |
|-----------------|---------|

Usage Conditions

| | |
|-----------------------------|----------------------------|
| IP Dust Sealing Level | 6 |
| IP Water Sealing Level | 7 |
| Fluid Resistance | Immersion |
| Operating Temperature Range | -55 – 170 °C[-67 – 338 °F] |

Operation/Application

| | |
|-------------------|------------|
| Durability Rating | 500 Cycles |
|-------------------|------------|

Other

| | |
|-------------------|-----|
| Field Serviceable | Yes |
|-------------------|-----|

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant with Exemptions |
| EU ELV Directive 2000/53/EC | Compliant with Exemptions |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2025 (247) |



Candidate List Declared Against: JAN 2024
(240)
SVHC > Threshold:
Pb (1.2% in Contact)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

| | |
|---------------------------|--------------------------------------|
| Halogen Content | Not Yet Reviewed for halogen content |
| Solder Process Capability | Reflow solder capable to 245°C |

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # ZPF000000000000867

[PINCE AFM-8](#)

Also in the Series | [DEUTSCH ASU](#)



[Standard Circular Connectors\(84\)](#)

Customers Also Bought

ASU603-05PD-HE

5 Position Circular Connector, Wire-to-Wire, Black Zinc, Aluminum Alloy, D Code, Hard Dielectric/Silicone, 3 Shell Size, Plug, Metal, Pin, DEUTSCH ASU




TE Part #ASU003-03SN-HE
RECEPT ASSY 2 HOLE MTG AS 3 WAY



TE Part #ASU003-03SE-HE
RECEPT ASSY 2 HOLE MTG AS 3 WAY



TE Part #ASU003-03SA-HE
RECEPT ASSY 2 HOLE MTG AS 3 WAY



TE Part #3160393003
55A1121-24-0/9-9



TE Part #ASU603-03PA-HE
PLUG ASSY AS 3 WAY



TE Part #ASU603-05PC-HE
PLUG ASSY ASU 5 WAY



TE Part #ASU003-05SD-HE
RECEPT ASSY 2 HOLE MTG ASU 5 WAY



TE Part #ASU003-03SB-HE
RECEPT ASSY 2 HOLE MTG AS 3 WAY



TE Part #ASX102-03SB-HE
INLINE REC. ASSEMBLY AS SIZE 2 3 WAY



TE Part #ASU603-05PN-HE
PLUG ASSY ASU 5 WAY

Documents

Product Drawings

PLUG ASSY ASU 5 WAY

English

Datasheets & Catalog Pages

DEUTSCH Autosport Interconnection Solutions

English