



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Wire-to-Wire**

Number of Positions: **3**

Shell Plating Material: **Black Zinc**

Shell Base Material: **Aluminum Alloy**

Polarization Code: **C**

Features

Product Type Features

Connector Product Type	Connector Assembly
Assembly Type	Electrical Connector
Connector System	Wire-to-Wire
Circular Connector Type	Receptacle
Shell Type	Metal

Configuration Features

Factory Installed Backshell	No
Number of Positions	3
Contacts Preloaded	No

Body Features

Entry Style	Rear Insertion
Environmental Protection	With
Environmental Protection Type	Sealed
Feedthrough Type	No
Shell Plating Material	Black Zinc
Shell Base Material	Aluminum Alloy
Circular Connector Insulation Material Type	Hard Dielectric/Silicone



Hermetically Sealed	No
---------------------	----

Contact Features

Contact Quantity (Size 22D)	3
Contact Layout Arrangement	2 – 3
Circular Connector Contact Type	Socket

Mechanical Attachment

Mating Retention Type	Bayonet Peg
Panel Mount Feature Type	2 Hole Flange
Mating Alignment	With
Polarization Code	C
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features

Circular Connector Shell Size	2
-------------------------------	---

Dimensions

Assembly Length	18.4 mm
Wire Size	22 AWG

Usage Conditions

IP Dust Sealing Level	6
IP Water Sealing Level	7
Fluid Resistance	Immersion
Operating Temperature Range	-55 – 170 °C[-67 – 338 °F]

Operation/Application

Durability Rating	500 Cycles
-------------------	------------

Other

Field Serviceable	Yes
-------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025  
(247)

Candidate List Declared Against: JAN 2025  
(247)

SVHC > Threshold:  
Pb (1.2% in Contact)  
Pb (.4% in Shell)

**Article Safe Usage Statements:**  
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # ZPF000000000000867  
[PINCE AFM-8](#)

Also in the Series | [DEUTSCH ASX](#)

[Standard Circular Connectors\(34\)](#)

Customers Also Bought





TE Part #ASX602-03PD-HE  
PLUG ASSY AS SIZE 2 3 WAY



TE Part #ASX002-03SA-HE  
RECEPTACLE ASSY AS SIZE 2 3 WAY

TE Part #YASX602-06PE-HE-R0  
PLUG ASSY. ASX 6 WAY. DESIGN MKII.



TE Part #ASX002-03SD-HE  
RECEPTACLE ASSY AS SIZE 2 3 WAY



TE Part #ASU603-03SB-HE  
PLUG ASSY AS 3 WAY



TE Part #ASX002-03SB-HE  
RECEPTACLE ASSY AS SIZE 2 3 WAY

TE Part #GV-12  
GASKETS FOR SIZE 12 AS CONNECTOR

TE Part #604946-31  
PIN CONTACT.#22. AS MODULAR.

TE Part #605705-31  
CONT PIN

TE Part #ATM396-20  
AS-20 NUT PLATE

Documents

Product Drawings

RECEPTACLE ASSY AS SIZE 2 3 WAY

English

Datasheets & Catalog Pages

DEUTSCH Autosport Interconnection Solutions

English

AS Micro Xtra Lite HE

English