

TAB62635501-040

✓ ACTIVE

TE Internal #: TAB62635501-040
M12 Cable Assembly, 2 Position, Cable Assembly Length 4 m [13.1 ft], Industrial Fieldbus, PROFIBUS, B Code, M12 Plug End A, M12 Socket End B, Shielded
[View on TE.com >](#)



Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > Fieldbus,PROFIBUS M12B2 PUR DragChain DE



Cable Assembly Length: 4 m [13.1 ft]
M8/M12 Application Type: Industrial Fieldbus
Industrial Protocols: PROFIBUS
Number of Positions: 2
Connector & Keying Code: B
[All Fieldbus,PROFIBUS M12B2 PUR DragChain DE \(24\)](#)

Features

Product Type Features

Cable Assembly Type	M12
Cable Assembly (End A)	M12 Plug
Cable Assembly (End B)	M12 Socket

Configuration Features

Number of Positions	2
---------------------	---

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Body Features

Connector Color (End B)	Black
Jacket Material	PUR
Connector Color (End A)	Black
Conductor Material	Copper Alloy
Cable Color	Violet



Connector & Keying Code	B
-------------------------	---

Contact Features

Contact Current Rating (Max)	4 A
------------------------------	-----

Mechanical Attachment

Connector Orientation (End A)	Straight
Connector Orientation (End B)	Right Angle

Housing Features

Housing Material	PA66+25GF
------------------	-----------

Dimensions

Outside Cable Diameter	7.8 mm
Wire Size	24 AWG

Operation/Application

M8/M12 Application Type	Industrial Fieldbus
Shielded	Yes

Industry Standards

IP Rating	IP67
Industrial Protocols	PROFIBUS

Packaging Features

Packaging Method	Bag
Packaging Quantity	5

Other

Cable Assembly Length	4 m[13.1 ft]
Cable Assembly Configuration	Double Ended

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211)



SVHC > Threshold:

Pb (1.9% in Component)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-IN287-SI113G
Fieldbus,PROFIBUS M12B 2p PUR
Drag Chain

Customers Also Bought



TE Part #SL630-C01
5-24VDC,TTL(HI=DRY)OUT



TE Part #86-015G-C
15 PSIG MV PRESSURE SENSOR



TE Part #3-647008-5
05P MTA100 PSTD CONN ASSY LF



TE Part #9-1437621-7
KLN500A1/8=KNOB KNURL W/IND LI



TE Part #2-2172067-2
M8 MALE R/A PNL.3P.PCB (AU)

TE Part #2273099-2
M12 x 1.0 angled socket pigt shld A

TE Part #104505-4
MTE PIN 22-26 AWG PLTD

TE Part #2217000-2
MODEL G II CE TERMINATOR, W /CQM

TE Part #647000-2
02P MTA100 PSTD CONN ASSY SN

TE Part #3-641311-4
04P MTA-100 ASSY TAPE LF

Documents

Product Drawings
M12B2-MS-FR-PUR-4.0M

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_TAB62635501-040_A.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_TAB62635501-040_A.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_TAB62635501-040_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
M8 / M12 Connector System Catalog

Japanese

M8 / M12 Connector System Catalog

English

M8/M12 Cable Assemblies Brochure

English

Product Specifications



Application Specification

English