



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Protective Cover**  
Operating Temperature (Max): **175 °C [ 347 °F ]**  
Operating Temperature Range: **-65 – 175 °C [ -85 – 347 °F ]**

Features

Product Type Features

|                      |                  |
|----------------------|------------------|
| Sealable             | Yes              |
| Connector Cover Type | Protective Cover |

Body Features

|                                  |          |
|----------------------------------|----------|
| Primary Product Plating Material | Cadmium  |
| Seal Material                    | Silicone |

Mechanical Attachment

|                             |                             |
|-----------------------------|-----------------------------|
| Component Retention Feature | Wire Rope with PTFE Coating |
|-----------------------------|-----------------------------|

Housing Features

|                                 |          |
|---------------------------------|----------|
| Compatible With Connector Shape | Circular |
|---------------------------------|----------|

Dimensions

|                |              |
|----------------|--------------|
| Product Length | 127 mm[5 in] |
|----------------|--------------|

Usage Conditions


|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature (Max) | 175 °C[347 °F]             |
| Operating Temperature Range | -65 – 175 °C[-85 – 347 °F] |

Operation/Application

|                                      |    |
|--------------------------------------|----|
| Compatible With Connector Shell Size | 17 |
|--------------------------------------|----|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)





|                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                          |
|-----------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Not Compliant                                                                                                                                                                                                                                                                                                                                                                                                                            |
| EU ELV Directive 2000/53/EC                   | Not Compliant                                                                                                                                                                                                                                                                                                                                                                                                                            |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold                                                                                                                                                                                                                                                                                                                                                                                                     |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>SVHC > Threshold:<br>Cd (100% in 10563731072)<br><b>Article Safe Usage Statements:</b><br>Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content                               | Not Yet Reviewed for halogen content                                                                                                                                                                                                                                                                                                                                                                                                     |
| Solder Process Capability                     | Not reviewed for solder process capability                                                                                                                                                                                                                                                                                                                                                                                               |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



Also in the Series | **DEUTSCH 38999 Metal Covers**



Customers Also Bought



Documents

Product Drawings  
DUST COVER ASSEM

English

CAD Files  
3D PDF

3D





Customer View Model

[ENG\\_CVM\\_CVM\\_YDTS32W17RV0010000\\_2.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_YDTS32W17RV0010000\\_2.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_YDTS32W17RV0010000\\_2.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[DEUTSCH MIL-DTL-38999 CIRCULAR CONNECTORS](#)

English