



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Protective Cover**
Operating Temperature (Max): **175 °C [347 °F]**
Operating Temperature Range: **-65 – 175 °C [-85 – 347 °F]**

Features

Product Type Features

Sealable	Yes
Connector Cover Type	Protective Cover

Body Features

Primary Product Plating Material	Black Zinc-Nickel Alloy
Seal Material	Silicone

Mechanical Attachment

Component Retention Feature	Wire Rope with PTFE Coating
-----------------------------	-----------------------------

Housing Features

Compatible With Connector Shape	Circular
---------------------------------	----------

Dimensions

Product Length	127 mm[5 in]
----------------	--------------

Usage Conditions


Operating Temperature (Max)	175 °C[347 °F]
Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]

Operation/Application

Compatible With Connector Shell Size	15
--------------------------------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)






EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

Also in the Series | **DEUTSCH 38999 Metal Covers**



Connector Caps & Covers(105)

Customers Also Bought



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT



TE Part #CAT-D48-ST273
DEUTSCH Solid Contacts




TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT



TE Part #DT04-2P
REC, 2P, GRY, N



TE Part #DT06-2S
PLG, 2P, GRY, N



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING

Documents

Product Drawings

CAP ASSEMBLY

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_YDTS32Z15NV0010000_2.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_YDTS32Z15NV0010000_2.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_YDTS32Z15NV0010000_2.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



[Datasheets & Catalog Pages](#)
[DEUTSCH MIL-DTL-38999 CIRCULAR CONNECTORS](#)
[English](#)