



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Protective Cover**
Operating Temperature (Max): **175 °C [347 °F]**
Operating Temperature Range: **-65 – 175 °C [-85 – 347 °F]**

Features

Product Type Features

Sealable	Yes
Connector Cover Type	Protective Cover

Body Features

Primary Product Plating Material	Black Zinc-Nickel Alloy
Seal Material	Silicone

Mechanical Attachment

Component Retention Feature	Wire Rope with PTFE Coating
-----------------------------	-----------------------------

Housing Features

Compatible With Connector Shape	Circular
---------------------------------	----------

Dimensions

Product Length	127 mm[5 in]
----------------	--------------

Usage Conditions


Operating Temperature (Max)	175 °C[347 °F]
Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]

Operation/Application

Compatible With Connector Shell Size	15
--------------------------------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)






EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

Also in the Series | **DEUTSCH 38999 Metal Covers**



Connector Caps & Covers(105)

Customers Also Bought



TE Part #YDTS33W23RV0010000
DUST COVER ASSEM




TE Part #HD10-9-1939P
REC, 9P, BLK, N, FLANGE, J1939, TYPE 1




TE Part #740072-000
SO63-3-01



TE Part #100503L
CONT SOC ASSY



TE Part #YDTS33Z15NV0010000
CAP ASSEMBLY



TE Part #811953-000
202D153-12-60-0




TE Part #322242
TERMINAL,SOLIS R 12-10 3/8



TE Part #6485470001
CM-SCE-1/4-4H-9



TE Part #YDTS32W23RV0010000
DUST COVER ASSEM



TE Part #069783M015
NTFR-1/2-0-SP-CS5445

Documents

Product Drawings
CAP ASSEMBLY

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_YDTS32Z15RV0010000_2.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_YDTS32Z15RV0010000_2.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_YDTS32Z15RV0010000_2.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[DEUTSCH MIL-DTL-38999 CIRCULAR CONNECTORS](#)

English