



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Wire-to-Panel**  
Connector Mounting Type: **Panel Mount**  
Number of Positions: **39**  
Sealable: **Yes**  
Connector & Contact Terminates To: **Wire & Cable**

Features

Product Type Features

Prewired	No
Connector Product Type	Connector Assembly
Connector System	Wire-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Circular Connector Receptacle
Shell Type	Square Flange

Configuration Features

Number of Positions	39
Number of Power Positions	0
Number of Signal Positions	39
Contacts Preloaded	No

Electrical Characteristics

Operating Voltage	115 VDC
-------------------	---------

Body Features

Environmental Protection Type	Elastomer Sealed
Primary Product Color	Natural



Shell Plating Material	Black Anodized
Shell Base Material	Aluminum
Circular Connector Insulation Material Type	Thermoset
Hermetically Sealed	No

Contact Features

Contact Current Rating (Max)	7.5 A, 13 A
Reverse Gender	No
Contact Layout Arrangement	20 – 39
Circular Connector Contact Type	Socket

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature Type	Square Flange
Connector Mounting Type	Panel Mount

Housing Features

Circular Connector Shell Size	20
-------------------------------	----

Dimensions

Wire Size	20 – 24 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-65 – 200 °C[-85 – 392 °F]
-----------------------------	----------------------------

Operation/Application

Durability Rating	500 Cycles
Circuit Application	Power, Signal & High Speed Data
Shielded	No

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250)



Candidate List Declared Against: JAN 2025  
(247)  
SVHC > Threshold:  
Pb (1.2% in alloy)

**Article Safe Usage Statements:**  
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 601967-1  
CRIMPING TOOL M22520/1-01

Also in the Series | DEUTSCH FDBA



Standard Circular Connectors(1079)

Customers Also Bought

FDBA 50-20-39 SN-K

Wire-to-Panel, Circular Connector Receptacle, 39 Position, Shell Size 20, Sealable, Wire & Cable, Power, Signal & High Speed Data, DEUTSCH FDBA



TE Part #ZPF000000000011439

[AFMJ 11E 22-03 K](#)

TE Part #ZPF000000000001941

[182-0195-08](#)

TE Part #ZPF000000000011440

[AFMJ 11E 22-04 K](#)

TE Part #ZPF0000000000086226

[DS 07-19 S 261](#)

TE Part #ZPF000000000019140

[FDBA 56-12-10 SN-K](#)

TE Part #ZPF0000000000020144

[FMJ 11E 20-02 G](#)

TE Part #3-1616991-3

[K500B7C02=CONTACTOR SPST NO DB 500 AMP](#)

TE Part #5-2252004-2

[E311AAJ2=EXTERNAL POWER MONITOR](#)

TE Part #ZPF000000000017306

[DTS 26 W 13-35 SA](#)

TE Part #ZPF0000000000100870

[SME 325 B 1 K 6](#)

Documents

[Product Drawings](#)  
[FDBA 50-20-39 SN-K](#)

English

[Datasheets & Catalog Pages](#)  
[DEUTSCH FDBA-HDBA Series](#)

English