TEST REPORT




REPORT NO	58722-3	
OUR JOB NO.	ND 58722	
	·	
CONTRACT		
YOUR P. O. NO.	A02011-2	

RAYCHEM CORPORATION 300 Constitution Drive Menlo Park, California 92024

29 - Page Report

DATE 9 December 1982

ENVIRONMENTAL QUALIFICATION TEST REPORT OF RAYCHEM MOLDED SLEEVE FOR RAYCHEM CORPORATION



STATE OF CALIFORNIA COUNTY OF RIVERSIDE ss. R. C. Sadlier deposes and says: That the information contained in this report is the result of complete and carefully conducted rots and is to the best of his knowledge true and correct in all repects.	DEPARTMENT DYNAMICS DEPT. MGR. J.J. Anderson TEST ENGINEER Luther F. Goad
SUBSCRIBED and sworn to before methis day of December 19 82 Reference State of California	REGISTERED PROFESSIONAL N. Tomusel ENGINEER
W-867A	DCAS_QAR VERIFICATION QUALITY ASSURANCE 2 Housteau L. Housteau

TABLE OF CONTENTS

<u>Section</u>	Title	<u>Page</u>
1.0	SUMMARY	1
2.0	TEST SPECIMEN	2
	2.1 Materials and Construction	2
3.0	TEST PROGRAM	4
	3.1 Test Sequence3.2 Functional Test Procedures3.3 Specimen Preconditioning3.4 LOCA/MSLB Environmental Exposure	4 5 5 7
4.0	TEST RESULTS	11
	4.1 Functional Test Results4.2 LOCA/MSLB Environment4.3 Post LOCA/MSLB Inspection	11 11 12
5.0	CONCLUSIONS	14
	TABLES	17
	APPENDICES	A1 and B1

FIGURES

Figure 1 - Specimen Constructions	3
Figure 2 - Schematic for Energizing Specimens	8
Figure 3 - Diagram of LOCA/MSLB Pressure Vessel and	9
Auxiliary Equipment	
Figure 4 - Temperature and Pressure Profiles for Simulation	10
of LOCA/MSLB Environment	
Figure 5 - Installed Test Specimens After Five Hours Exposure	13
at 177°C (350°F)	

<u>Title</u>

<u>TABLES</u>

Table 1 - Test Specimen Conditioning Summary	17
Table 2 - Summary of Insulation Resistance Measurements	18
Table 3 - Current Monitoring of Test Specimen	19
Table 4 - Post LOCA/MSLB Inspection Summary	20

APPENDICES

Appendix A - Certificate of Radiation Dose	A1
Appendix B - List of Data Acquisition Instruments	B1

1.0 <u>SUMMARY</u>

Six specimens of the Raychem Molded Sleeve were subjected to an environmental qualification type test to demonstrate their capability to maintain functional operability under all service conditions postulated to occur within the containment of nuclear generating stations during the installed life of the product. The qualification program was based upon the methods, procedures and guidelines set forth in IEEE Standards 323-1974¹ and 383-1974² as endorsed by USNRC Regulatory Guides 1.89³ and 1.131⁴ respectively.

The test specimens were exposed to a single environmental profile encompassing temperatures up to 228°C (442°F) that enveloped the conditions produced by main steamline break and loss-of-coolant accidents (MSLB/LOCA), in accordance with the simulated environmental profile preferred by

NUREG-0588⁵ for qualifying equipment located inside containment. A caustic solution was sprayed on the test specimens throughout the environmental exposure to simulate conditions that would occur when containment spray systems actuate. Extremes in power supply voltage ranges were simulated by energizing the test specimens at 1000 volts and 3n amperes.

The effects of installed life were simulated by the accelerated aging of three test specimens to an equivalent service life in excess of 42 years at 90°C (194°F). Accelerated aging was accomplished via thermal exposure at a rate based upon the Arrhenius data documented in Raychem Report EDR-5040.⁶ These specimens were then exposed to gamma radiation at a level to include both the postulated LOCA accident dose and a dose equivalent o an installed assembly containment exposure integrated over a 40-year period. The remaining three specimens received only the postulated accident radiation dose to

simulate beginning of life LOCA/MSLB exposure. The thermally aged specimens received in excess of 2.15 x 10⁸ rads gamma. Thermally unaged specimens received 1.65 x 10⁶ rads gamma.

Acceptance criterion was established as the specimen's ability to maintain rated voltage and current during and after the environmental exposure. Margin was demonstrated by the specimen's ability to pass voltage withstand testing at 2400 Vrms.


Based upon the satisfactory performance of the specimens during this test program, it was concluded that the Raychem molded Sleeve is suitable for use inside the containment of nuclear power generating stations.

The LOCA/MSLB environmental exposure was performed by Wyle Laboratories, Norco, California. Radiation preconditioning of Specimen numbers 4, 5, and 6 and the thermal preconditioning of all specimens was performed at Raychem Corporation, Menlo Park, California. Radiation preconditioning of Specimen numbers 1, 2, and 3 was performed at Isomedix Inc., Parsippany, New Jersey.

- 2.0 <u>Test Specimen</u>
- 2.1 <u>Materials and Construction</u>
- 2.1.1 Each test specimen was constructed of Raychem's nuclear grade extrusion and molding materials taken from standard production. All components conformed to the applicable Raychem Specification Component Drawings referenced in Figure 1.

These Molded Sleeves were designed to seal and insulate configurations having large connector diameters relative to the connecting cable diameters, such as coaxial connections. This configuration was simulated using two single conductor wires and an oversized crimp with an internal spacer.








Figure 1. Specimen Constructions

- 2.1.2 Specimen numbers 1, 2, 3, and 6 were assembled in the "A" configuration shown in Figure 1. Specimen numbers 4 and 5 were assembled in the "B" configuration shown in Figure 1. All specimens were assembled by Raychem personnel using Raychem's standard cable preparation and splice assembly procedures. The cables were cleaned with 1,1,1 Trichloroethane prior to splice assembly and installed using a Raychem FH-2609, LPG portable flame heater.
- 2.1.3 In addition to these six specimens, several other types of products were tested in this program. The other constructions are the subject of separate reports. For clarity of data presentation, the seven constructions reported herein are referenced as specimen numbers 1 through 6. These specimen numbers are crossreferenced with actual Raychem specimen identification numbers in Table 1.

3.0 TEST PROGRAM

3.1 <u>Test Sequence</u>

In conformance with Section 6.3.2 of IEEE Standard 323-1974¹, test specimens were neither modified nor altered after assembly and each specimen was used throughout the entire test sequence. The test sequence comprising this qualification type test is listed below:

<u>Sequence</u>	Test Description
1.	Functional Tests
2.	Specimen Preconditioning
3.	Functional Tests
4.	LOCA/MSLB Environmental Exposure
5.	Functional Tests

3.2 Functional Test Procedures

Functional tests were repeated three times during the test program as shown in Section 3.1. Prior to the performance of each functional testing cycle, all test specimens were immersed in tap water at room temperature for a minimum of 16 hours. Each splice assembly being tested was submerged 12 or more inches below the water's surface during the 16 hour soak. All functional tests were performed with the specimens immersed in the water bath. Test values are summarized in Table 2. Equipment calibration data is provided in Appendix B.

3.2.1 Insulation Resistance (I.R.)

After the 16 hour immersion, while still in the water bath, the I.R. of each specimen was measured. Measurements were made at 500 volts d-c after one minute of electrification. The water bath was used as the ground plane during this test.

3.2.2 Voltage Withstand

After the I.R. of each specimen was measured and while still in the water bath, a 2400 volt a-c voltage withstand test was performed on each test specimen in accordance with ICEA S-61-402, 6.11.2. Using the water bath as ground, the voltage was applied to the conductor in each specimen.

3.3 Specimen Preconditioning

3.3.1 Thermal Aging

Three specimens were thermally aged to simulate a service condition of over 4n years based upon Arrhenius data for Raychem's

Page 6

nuclear grade materials as documented in Raychem Report EDR-5040⁶. These specimens were aged to an equivalent of 42.8 years installed life at 90°C (194°F). The remaining three specimens were not thermally aged, simulating the product at the beginning of installed life. All thermal aging was accomplished at Raychem Corporation. Specimens were situated horizontally in a circulating air oven throughout the aging period. Table 1 presents the aging time and the aging temperature used during specimen conditioning.

3.3.2 Radiation Aging

The radiation dose determined to represent the gamma exposure to installed assemblies within containment over a 40 year period was 5.0×10^7 rads. The postulated accident gamma radiation dose was 1.5×10^8 rads.

Thermally aged specimens were exposed both to the postulated accident dose, plus 10 percent margin, and the dose representing 40 years of installed life totaling 2.15 x 10^8 rads gamma. This radiation aging was performed at Isomedix Inc., Parsippany, New Jersey. The samples simulating the beginning of installed life received only the postulated accident dose plus 10 percent margin for a total dose of 1.65 x 108 rads gamma. This radiation aging was performed at Raychem Corporation, Menlo Park, California.

The actual gamma radiation exposures exceeded the required 2.15 x 10⁸ rad level. Table 1 depicts the air equivalent radiation doses and associated dose rates by specimen number. The radiation source utilized was Co⁶⁰ and the Certificates of Radiation are provided in Appendix A.

3.3.3 Functional Tests

The functional tests were again performed after specimen preconditioning as described in Section 3.2. Test values are listed in Table 2.

3.4 LOCA/MSLB Environmental Exposure

The test specimens were placed horizontally on perforated metal trays inside a pressure vessel. Extension leads were spliced to the test specimen inside the pressure vessel and insulated with Raychem WCSF-N tubing. The extension leads were brought out of the test vessel through penetrations installed in the pressure vessel wall to allow for electrical connection and monitoring. A diagram of the pressure vessel is given in Figure 2. The specimens were energized at 1.0 kV a-c to ground and carried a current of 30 amperes. Current values were sampled throughout the environmental exposure and are presented in Table 3. The voltage energization circuit for each test specimen was separately fused at 1/4 amp. A schematic of the energizing circuit is given in Figure 2.






Figure 2. Test Schematic for Energizing Specimens

A chemical spray solution consisting of 0.28 molar H_3B0_3 (3000 ppm boron), 0.064 molar $Na_2S_2O_3$, buffered with NaOH to a pH of 10.5 at 25°C (77°F) was provided in a separate reservoir. This solution was sprayed through two nozzles from the top of the vessel at a rate in excess of 0.15 gpm/ft² beginning immediately after the second temperature transient and ending upon completion of the 30-day environmental exposure (actual flow was 34 gpm). A diagram of the pressure vessel is given in Figure 3. The temperatures, pressures, and spray duration throughout the test period are given in Figure 4.








Figure 3. LOCA/MSLB Pressure Vessel and Auxiliary Equipment

58722-3

60. 50_





NOTES: (1) Problems encountered with test vessel pressure seals necessitated interrupting the test after 9.0 minutes. Test was resumed at the 177 °C (350 °F) temperature plateau and the chemical spray was initiated.

(2) Problems encountered with the test specimen extension leads and the test vessel pressure seals necessitated interrupting the test after 5 hours. The test was resumed at the 177°C (350°F) temperature plateau to complete the required exposure at this temperature level.

Temperature and Pressure Profiles for Simulation of LOCA/MSLB Environment Figure 4.

4.0 <u>TEST RESULTS</u>

4.1 <u>Functional Test Results</u>

The results of all voltage withstand tests and insulation resistance measurements are listed in Table 2. Test specimen current loading values during the environmental exposure are presented in Table 3. Specimen number 4 was unable to maintain voltage throughout the environmental exposure. This specimen's loss of ability to maintain voltage occurred between the fifth and ninth hour of the LOCA/MSLB exposure. All remaining specimens maintained voltage and current throughout the exposure and passed all functional tests specified in Section 3.1.

4.2 LOCA/MSLB Environment Exposure

The following details of the profile depicted in Figure 4 are noted:

a. The temperature of 204°C (400°F) was not reached in 10 seconds as proposed in Raychem Test Plan No. NPE-TP-81-03.⁸ Attainable rise times were governed by the apparatus selected to encompass the entire scope of the Raychem test plan and precluded meeting the proposed temperature rise time.

However, during the temperature transients, both the peak temperatures and temperature durations exceeded those proposed.

b. Problems encountered with test vessel pressure seals and the test specimen extension leads necessitated interrupting the test after the second temperature transient and again after five hours of specimen exposure at the 177°C (350°F) temperature plateau. During the

interruption at the 177°C (350°F) plateau, the specimens were visually inspected. It was found that a large section of the Steam Diffuser Plate had fallen a distance of approximately three feet from the top of the pressure vessel onto the Raychem test specimens (see Figure 5). Since replacement of the vessel penetration seals was required, this necessitated replacement of test specimen extension leads. The specimens themselves were not modified nor changed in any way. There was no apparent damage to the test specimens from either the impact of the Diffuser Plate upon the test specimens or from the effects of the environmental exposure. However, the visual examination was necessarily cursory because excessive handling and manipulation of specimens was prohibited until completion of the test program.

c. The test specimens were exposed to the LOCA/MSLB environment for 31.3 days rather than the 30 days proposed in Raychem Test Plan No. NPE-TP-81-03.⁸

4.3 Post LOCA/MSLB Inspection

At the conclusion of the environmental exposure, the test vessel was flooded with tap water. The test specimens were then given a voltage withstand test and the insulation resistances were measured. Test values are listed in Table 2. The vessel was then opened and the cause for Specimen number 4 being unable to hold rated voltage throughout the environmental exposure investigated.

At this point, specimen extension wires were severed inside the vessel and the specimens were removed for examination. With the exception of Specimen number 4, all samples were intact with no signs of cracking or splitting. Specimen number 4 exhibited




Figure 5 Installed Test Specimens After Five Hours Exposure at 177° C (350° F). [Note fallen portion of Diffuser Plate in upper right hand corner].

extensive surface tracking (carbonized path formations) and surface erosion (material removal). A circumferential crack approximately 2.5 inches long was observed in the area of the specimen showing the highest degree of tracking. Adjacent to the crack (0.2 inches distant) was a horseshoe-shaped puncture of the material 0.08 inches wide and 0.19 inches long. A summary of these findings is given in Table 4.

5.0 CONCLUSIONS

Six specimens of Raychem's Molded Sleeves were subjected to an environmental qualification type test program designed to simulate the service conditions produced by main steamline break and loss-of-coolant accidents (MSLB/LOCA). The test specimens were exposed to the LOCA/MSLB environmental extremes of temperature, humidity, pressure and chemical spray while electrically energized. These test specimens were conditioned to simulate both the beginning of installed life and over 40 years of installed life. They were exposed to LOCA/MSLB levels of radiation to include both accident dose margin and the postulated containment radiation dose integrated over 40 years of installed life.

Five of the specimens passed all functional tests throughout the entire qualification program, evidencing the configuration's ability to maintain electrical and physical integrity during LOCA/MSLB design basis events occurring both at the beginning and end of power plant life. One of the non-heat aged specimens failed between the fifth and ninth hour of exposure to the environmental profile. Inspection of the failed specimen revealed the failure occurred through the wall of the Raychem Sealing

Page 15

Sleeve and not at the cable-to-sleeve interface. It was concluded that this specimen had been damaged by the impact of the fallen diffusion plate which occurred during the first five hours of the LOCA/MSLB environmental exposure. The failure could not be attributed to either the Raychem splice components or to the splice configuration. All remaining specimens demonstrated performance margin at the conclusion of the test by passing voltage withstand testing.

The results of this comprehensive test program provide reasonable assurance, by type test, that the Raychem Molded Sleeve can perform its intended function of insulating and sealing in the most limiting environment in which it is expected to function. Therefore, it is concluded that the tested configurations are suitable for use on Class IE systems within the containment of nuclear power generating stations.

Page 16

REFERENCES

- 1. IEEE Standard 323-1974, "IEEE Standard for Qualifying IE Equipment for Nuclear Power Generating Stations."
- 2. IEEE Standard 383-1974, "IEEE Standard for Type Test of Class IE Electric Cables, Field Splices, and Connections for Nuclear Power Generating Stations."
- 3. USNRC Regulatory Guide 1.89, "Qualification of Class IE Equipment for Nuclear Power Plants."
- 4. USNRC Regulatory Guide 1.131, "Qualification Tests of Electric Cables and Field Splices for Light-Water-Cooled Nuclear Power Plants."
- 5. NUREG-0588, "Interim Staff Position on Environmental Qualification of Safety-Related Electrical Equipment."
- 6. EDR-5040, Raychem Report "Analysis of Heat Aging Data on -52 Molding Material to Determine Pre-Aging Conditions for Nuclear qualification Testing,"
- 7. ICEA S-61-402, "ICEA/NEMA Standards Publication Thermoplastic-insulated Wire and Cable for the Transmission and Distribution of Electrical Energy."
- 8. NPE-TP-81-03, "Environmental qualification Test Plan of Raychem Nuclear Cable Splice Assemblies."

		È	Thermal Aging ²		Radiatio	Radiation Aging ⁴
Specimen <u>Number</u>	Raychem I.D. ¹ Number	Temperature	Duration	Installed ³ Life Equivalent	Dose (rads)	Rate (rads/hr)
•	10	150°C	916 hrs.	42.8 yrs	2.2 × 10 ⁸	5.7 × 10 ⁵
2.	11	150°C	916 hrs.	42.8 yrs	2.2 × 10 ⁸	5.7×10^{5}
з .	12	155°C	916 hrs.	42.8 yrs	2.2 × 10 ⁸	5.7 × 10 ⁵
4.	501	Unaged	ı	Day 1	1.65 × 10 ⁸	1.0 × 10 ⁶
• 2	502	Unaged	ı	Day 1	1.65 × 10 ⁸	1.0 × 10 ⁶
• 0	503	Unaged	ı	Day 1	1.65 × 10 ⁸	1.0 × 10 ⁶
Notes: (Raychem Specir this report for 	men Identificatior or clarity and eas	n Numbers are se of compreh	Raychem Specimen Identification Numbers are referred to by adjacent Specimen Numbers throughout this report for clarity and ease of comprehension.	acent Specimen	Numbers throughou
	(2) The 916 hour cable.	Thermal Aging exce	eded the req	The 916 hour Thermal Aging exceeded the required aging time to simulate 40-year life for the cable.	simulate 40-y	ear life for the

TABLE 1

- Installed Life Equivalent is based upon Arrhenius data documented in Raychem Report EDR-5040⁶ for continuous conductor temperature of 90°C (194°F). (3)
- (4) All Radiation Aging values are air equivalents of gamma radiation from a Co⁶⁰ source.

58722**-**3 Page 17 TABLE 2 SUMMARY OF INSULATION RESISTANCE MEASUREMENTS

			•		lest Speci	lest Specimen Insulation Resistance (ohms)	on Resistanc	e (ohms)	
Test Conditions	Temperature (°C) (°F)	ature (°F)	Vessel Pressure (psig)	-	2.	3.	4.	5.	6.
Functional Tests Before Conditioning (Note 1)	Ambient	11	1	5.6 × 10 ¹¹	4.5 × 10 ¹¹	3.5 × 10 ¹¹	1.3 × 10 ¹¹	4.2 × 1011	5.0 × 10 ¹¹
Functional lests After Conditioning (Note 1)	Ambient	نى	ı	2.2 × 10 ¹¹	2.2 × 10 ¹¹	2.2 × 10 ¹¹	1.4 × 10 ¹¹	1.3 × 10 ¹¹	2.0 × 10 ¹¹
Functional Tests During LOCA/MSLB	ing LOC/		Exposure						
After 3 hours (Note 2)	177	350	120	1	١	1.0 × 10 ⁸	1.5×10^{8}	4.0 × 10 ⁷	ı
After 9 hours	163	325	74	2.3 × 106	1.8 × 106	1.7 × 10 ⁶	Note 3	2.0 × 10 ⁶	3.0 × 106
After 23 hours	153	307	51	3.5 × 106	2.6 × 106	3.0 × 106	1	3.0 × 106	4.0 × 106
After 82 hours	138	280	28	8.4 × 106	7 . 5 x 106	7.7 × 106	ı	7.6 × 10 ⁶	9.5 × 106
After 132 hours	138	280	28	8.4 × 106	7.8 × 106	8.0 × 106	ı	7.8 × 106	1.0 × 10 ⁷
After 272 hours	111	232	28 (Note 4)	5.2×10^{7}	4.8 × 10 ⁷	3.5×10^7	١	2.3×10^{7}	$3_{*}3 \times 10^{7}$
After 363 hours	111	232	28	4.4 × 10 ⁷	$3_{*}7 \times 10^{7}$	3.0×10^7	I	3.7×10^7	2.7×10^{7}
After 454 hours	111	232	28	5.0 × 10 ⁷	4.2×10^7	3.5×10^7	ı	1.5×10^{7}	2.6×10^7
After 546 hours	111	232	28	5.0 × 107	4.0 × 10 ⁷	3.4×10^7	ı	1.1×10^7	3.2×10^{7}
After 637 hours	111	232	28	5.5 × 107	4.5×10^{7}	3.6 × 10 ⁷	ŀ	1.1×10^{7}	4.0 × 10 ⁷
<pre>lest vessel filled with water (Note 1)</pre>	Ambient	ب	ı	8.2×10^{9}	9.6 × 10 ⁹	1.7 × 10 ¹⁰	F	2.2×10^{7}	1.4×10^{10}
Notes: (1) All spe	All specimens listing	listing	an insulation resistance value also passed voltage withstand testing per section 3.2.2	nce value also	o passed volt	cage withstar	nd testing pe	er section 3.	.2.2
(2) Due to measure	test in Aments c	terrupti ould not	Due to test interruption at this temperature plateau [reference Section 4.2(b)], meaningful Insulation Resistance measurements could not be performed upon all samples.	e plateau [ref 1 samples.	ference Sect.	ion 4.2(b)],	meaningful I	insulation R	ssistance
(3) This te	sst spec	imen cou	This test specimen could not pass functional testing due to extensive surface tracking and erosion attributed to	l testing due	to extensive	e surface tra	acking and er	cosion attrib	outed to

- Ţ • 50 DATC [his test specimen could not pass functional testing due to exter external damage [reference Sections 4.2(b), 4.3, and 5.0]. 3
- lest vessel was externally pressurized with air to maintain a minimum pressure of 28 psig. (4)

I ABLE 3

CURRENT MONITORING OF TEST SAMPLES

DURING LOCA/MSLB ENVIRONMENTAL EXPOSURE

Tack	Tomor		Varcal			Samp le	Sample Number		
Conditions	(, (, (, (, (, (, (, (, (, (, (, (, (, ((.L)	Pressure (psig)	-	2	m	4	5	9
Pre-LOCA/HELB (Note 1)	85	185	I	26	26	26	26	27	27
After 3 hours	177	350	120	30	25	26	Note 2	25	28
After 26 hours	153	307	51	30	25	26	ţ	25	27
After 2 days	138	280	28	30	24	25	I	27	29
After 3 days	138	280	28	30	27	27	I	26	28
After 6 days	138	280	28	29	26	28	i	27	27
After 8 days	111	232	28 (Note 3)	28	26	28	ı	27	28
After 9 days	111	232	28	28	25	26	ı	26	26
After 13 days	111	232	28	30	28	28	ı	26	26.
After 15 days	111	232	28	30	27	27	I	25	27
After 17 days	111	232	28	31	28	27	I	26	29
After 20 days	111	232	28	29	26	26	ı	26	26
After 22 days	111	232	28	29	27	72	ı	25	27
After 24 days	111	232	28	30	26	27	ı	24	26
After 27 days	111	232	28	30	26	28	ı	24	26
After 28 days	111	232	28	29	25	32	r	24	25
After 29 days	111	232	28	30	26	26	ı	26	25
After 30 days	111	232	28	30	27	27	ı	24	25
After 31 days	111	232	28	30	27	26	r	24	26
Notes: (1) Pre-LOCA/HELB current measurements were made during	B curren	t measur	cements were made during		test vessel preheat.	at.			
(2) Current was	terminat	ed on sp	ent was terminated on specimen when the $1/4~\mathrm{amp}$	fuse opened.	ened.				

fest vessel was externally pressurized with air to maintain a minimum pressure of 28 psig.

(3)

TABLE 4	POST LOCA/MSLB INSPECTION SUMMARY	Results of Inspection	Maintained voltage and current throughout environmental exposure. No evidence of cracking or splitting.	Maintained voltage and current throughout environmental exposure. No evidence of cracking or splitting.	Maintained voltage and current throughout environmental exposure. No evidence of cracking or splitting.	Visible burns over 25 percent of the specimen. Electrical stress tracking throughout entire damaged area. Apparent 1/4-inch long puncture parallel to 2-inch long crack.	Maintained voltage and current throughout environmental exposure. No evidence of cracking or splitting.	Maintained voltage and current throughout environmental exposure. No evidence of cracking or splitting.
		Duration of Sample Energization	31 days	31 days	31 days	<3 hours	31 days	31 days
		Specimen Number	1.	2.	ຕໍ	4	ي. م	6.

58722**-**3 Page 20 <u>Appendix A</u>

Certification of Radiation Dose



February 18, 1982

Mr. Joe Connolly Ray Chem Corporation 300 Constitution Drive Menlo Park, California 94025

Dear Mr. Connolly:

This will summarize parameters pertinent to the irradiation of two (2) containers of cable splice samples, as per your Purchase Order #A07349. Specimens were identified as follows:

Group I - R-24593- 165 megarad box

Group II - R-24591 - 215 megarad box

The specimens in Group I were exposed to a Cobalt 60 gamma source for a period of 362 hours at a nominal dose rate of 0.47 megarads per hour. The calculated dose based on dosimetry is 170 megarads. Halfway through the exposure, the specimens were rotated 180 degrees to give a more uniform dose distribution.

The specimens in Group II were exposed to a Cobalt 60 gamma source for a period of 386 hours at a nominal dose rate of 0.57 megarads per hour. The calculated dose based on dosimetry is 220 megarads. Halfway through the exposure, the specimens were rotated 180 degrees to give a more uniform dose distribution.

Dosimetry was performed using Harwell Red 4034 Perspex dosimeters, utilizing a Bausch and Lomb Model 710 spectrophotometer as the readout instrument. This system is calibrated directly with NBS, with the last readout calibration being September 08, 1981. A copy of the dosimetry correlation report is available upon request.

Irradiation was conducted in air at ambient temperature and pressure. Radiant heat from the source heated the specimens somewhat, but the temperature did not exceed 130 degrees F, as indicated by previous measurements on an oil solution in the same relative position. 58722-3 Page A2

Mr. Joe Connolly

-2-

February 18, 1982

Irradiation for Group I was initiated on December 31, 1981, and was completed on January 20, 1982.

Irradiation for Group II was initiated on December 31, 1981 and was completed on January 22, 1982.

Very truly yours,

ISOMEDIX, INC.

wid P. Constantine

David P. Constantine Production Manager

DC/mjb

58722-3 Page A3

IRRADIATION CERTIFICATION

- FACILITY: Raychem Co⁶⁰ Facility
- LOCATION: R&D Building, Menlo Park, CA.
- CUSTOMER: Energy Division of Raychem
- P.O./JOB NUMBER: MRS # 40024
- SAMPLE DESCRIPTION: Cylindrical Dig. 1 to 3 inch length 5 to 8 inches 1982 LOCA/MSLB Test Samples NEIS Samples: 2A1H, 2A2H, 2A3H, 3B1H, 3B2H, 3B3H Coaxial Splice Samples: 501, 502, 503
- RADIATION SOURCE: Co60
- DOSE RATE: 1 M Rad/hr
- CUMULATIVE DOSE: 165 M Rads
- DATE SAMPLES RECEIVED: 08 Jan. 82
- DATE SAMPLES SHIPPED: 15 Jan. 82

CERTIFIED BY:

58722-3 Page A4

GEOMETRY OF SAMPLES AND SOURCE:

Source: Cylindrical 12 Tubes @ 27.5 cm dia.

Samples: Samples were suspended on the outside approx. 4 inches from the Co^{60} .

CALIBRATION CERTIFICATION:

- Dosemeters: FWT-60 Rediochromis dye film manufacture "Par West Technology"
- Calibrated By: National Bureau of Standards Washington, D.C. 20234

Report No.:

Test 533/225797 DB8291046 XRG-136 August 6, 1981 Appendix B

List of Data Acquisition Instruments

	PART NO.				TEST BY	sy G. ADAIR	
	N/S	SEL	<u>SEE REC. INSP.</u>		WITNESS	SS	
WYLE LABORATORIE	: s TEST: -	LOCA			1		
		MODEL		WYLE	CALIBI	CALIBRATION	
EQUIPMENT	MANUFACTURER	NO	RANGE	ö	LAST	DUE	ACCY.
WON	BECKMAN	330	VARIOUS	8892	5-4-81	5-2-82	DATA
RECORDER	КАҮЕ	DR-28	VARIOUS	8750	1-28-82	8-1-82	± 0.05%
DIGITAL THERMOMETER	FLUKE	2160A	-350°F to +752°F	8401	12-7-81	6-13-82	± 2.0°F
DIGITAL THERMOMETER	FLUKE	2160A	-350°F to +752°F	8290	1-26-82	5-30-82	± 2.0°F
DIGITAL THERMOMETER	FLUKE	2160A	-350°F to +752°F	8032	12-29-81	5-2-82	± 2.0°F
A/C D/C HYPOT	ASSOCIATED RESEARCH	4045	0-5K VOLTS	9092	12-11-81	6-13-82	± 2%
RECORDER	HEWLETT PACKARD	7132A	1-500 mV	8674	SYSTE	SYSTEM CALIBRATION	
RECORDER	HEWLETT PACKARD	7132A	1-500 mV	8672	SYSTE	SYSTEM CALIBRATION	
MOV	BECKMAN	330	VARIOUS	8893	7-1-81	7-4-82	DATA
GAUGE	ASHCROFT	7320	0-100 psi	4435	1-22-82	4-25-82	t
X-DUCER	VALIDYNE	DP-15	0-100 psi	19937	2-2-82	8-1-82	+ 1%
X -DUCER	VALIDYNE	DP-15	0-100 psi	32738	2-2-82	8-1-82	+ 1%
MEGOHMMETER	GENERAL Radio	1864	100-500V ₁₃ 0-5 x 10 ¹³ Ω	L99838	12-16-81	6-16-82	± 5%
FLOW GAUGE	BARTON	D4-49053-1	0-80" H ₂ 0	7784	1-11-82	7-18-82	± 0.5%
DIGITAL T/C METER	THERMO	DIGIMITE	0-400°F	7890	2-2-82	6-6-82	LABEL
DMM	BECKMAN	330	0-50 VDC 0-150 ACA	8892	5-4-81	5-2-82	DATA
CURRENT CLAMP	BECKMAN	CT-231	0-150 ACA	9065	10-7-81	7-4-82	LABEL
W614D Q.A. Approval	Where applicable, to the National E the Wyle Laborato	the listed test bureau of Standard bries QA files and	Where applicable, the listed test equipment has been calibrated using standards which are traceable to the National Bureau of Standards. Certificates and reports of all calibrations are retained in the Wyle Laboratories QA files and are available for inspection upon request.	orated using corts of all sction upon r	standards which are calibrations are ret equest.	traceable SHEET ained in	1 ^{OF} 2

58722**-**3 Page B1

RAYCHEM CUSTOMER ____ SPECIMEN

CABLE SPLICE ASSEMBLIES

1-25-82 1 JOB NO. DATE

58722

TEF REC. INSP. G. ADAIR SEE REC. INSP. I. TEST BY G. ADAIR SEE REC. INSP. I. TEST BY G. ADAIR SEE REC. INSP. I. TEST BY G. ADAIR ODEL RANGE WYLE LIDCA 0. 0. 0.200 PSI 30190 2.24-82 5.30-82 F P 0. 0. 0.500 m/ L30107 10-15-81 4-15-82 ± ± 2. 0.500 m/ L30107 10-15-81 4-15-82 ±		CUSTOMER	DMER RAYCHEM	CHEM		DATE	1-25-82	ļ
TEST: IOC TEST: IOC OUMMENT MANUFACTURE MODEL RANGE WYLE LASS CALIBRATION ASNOCIATED ASNOCIATED 2322 0-200 PSI 2-24-82 5-30-82 2 MIGHEOT RESEARCH 1322 0-200 PSI 120106 12-31-81 6-31-82 2 RECIBRICA HOREYMELL 155201212 0-500 mV L30107 10-15-81 4-15-82 2 RECIBRICA HOREYMELL 155201212 0-500 mV L30107 10-15-81 4-15-82 2 RECIBRICA HOREYMELL 155201212 0-500 mV L30107 10-15-81 4-15-82 2 RECIBRICA HOREYMELL 155201212 0-500 mV 10-15-81 4-15-82 2 RECIBRICA HOREYMELL 15520121 0-500 mV 10-15-81 4-15-82 2 RECIBRICA HOREYMELL 155201212 0-500 mV 10-15-81 4-15-82 2		PART		REC. INSP. REC. INSP.		TEST B	(7	
OUTEMENT MANUFACTURER MODEL RANGE WYLE CALIBRATION ASHERDET 2322 0.00 F1 30190 2.24-82 5-30-82 F ASSOCIATED ASSOCIATED ASSOCIATED ASSOCIATED ASSOCIATED 4-15-82 ± ASSOCIATED ASSOCIATED ASSOCIATED ASSOCIATED ASSOCIATED ASSOCIATED 2322 0-500 mV L30106 12-31-81 4-15-82 ± RECORDER HONEYWELL 6922 0-500 mV L30107 10-15-81 4-15-82 ± RECORDER HONEYWELL 6922 0-500 mV L30107 10-15-81 4-15-82 ± RECORDER HONEYWELL 6922 0-500 mV L30107 10-15-81 4-15-82 ± RECORDER HONEYWELL 6922 0-500 mV L30107 10-15-81 4-15-82 ±	WYLE LABORATORI		1007					
Matcher Matcher Mode	EOUIDMENT		MODEL		WYLE NO	1	ATION	
Addition 2322 0-200 53 30.90 2-24-82 5-30-82 MiGHPOT RESCRICH 4030 0-5ky A.C. 130105 12-31-91 6-31-82 RECORDER HONEYMELL 5927 0-500 mV L30107 10-15-81 4-15-82 RECORDER HONEYMELL 6927 6-500 mV L30107 10-15-81 4-15-82 RECORDER HONEYMELL 6927								0.5%
C. HIGHDOT RESCRICH IESTRACH 4030 D-5kV A.C. 130105 12-31-81 6-31-82 ART RECORDER HONEYWELL 5520127 D-500 mV L30107 10-15-81 4-15-82 ART RECORDER HONEYWELL 6327 D-500 mV L30107 10-15-81 4-15-82 ART RECORDER HONEYWELL 6327 D-500 mV L30107 10-15-81 4-15-82 ART RECORDER HONEYWELL 6327 D-500 mV L30107 10-15-81 4-15-82 ART RECORDER HONEYWELL 6327 D-500 mV L30107 10-15-81 4-15-82 ART RECORDER HONEYWELL 6327 D-500 mV L30107 10-15-81 4-15-82 ART RECORDER HONEYWELL 6327 D-500 mV L30107 10-15-81 4-15-82 ART RECORDER HONEYWELL 6327 D-500 mV L30107 10-15-81 4-15-82 ART RECORDER HONEYWELL HONEYWELL HONEYWELL HONEYWELL HONEYWELL ART HERCORDER HONEYW	GAUGE	ASHCROFT	7322	0-200 PSI	30190	2-24-82	5-30-82	FULL SCAL
ART RECORDER HONEYWEIL 154201212 0-500 mV L30107 10-15-81 4-15-82 * Image: Second Se		ASSUCIATED RESEARCH	4030	0-5kV A.C.	L30106	12-31-81	6-31-82	± 0.1%
	CHART RECORDER	HONEYWELL	154201212 6927	0-500 mV	L30107	10-15-81	4-15-82	± 1%

58722-3 Page B2