# **Table of Contents**

KILOVAC WD Series, DIN Rail or Screw Mounted Protective Relays
Introduction
KILOVAC WD25 Paralleling Relays11-3
KILOVAC WD2759 Over/Undervoltage Relays
KILOVAC WD32 Reverse Power Relays11-6, 11-7
KILOVAC WD47 Phase Sequence Relays11-8
KILOVAC WD5051 1Ø and 3Ø Overcurrent Relays
KILOVAC WD810U Over/Underfrequency Relays
Voltage Sensitive Relays
WUV/WOV DC Series
WUV/WOV Series
WUVT/WOVT Series
WOUV DC Series, Over/Undervoltage11-15
WOUVT Series, Over/Undervoltage11-16
250 Series, Over/Undervoltage
D100X Series, Close Differential
D101X Series, 3 Phase Adjustable, Close Differential11-19
Reverse Power Relay
700 Series w/ Adjustable Time Delay11-20
Phase Failure Relay
1000 Series
Phase Sequence Relay
900 Series
Current Balance Relay
WCB Series
Current Sensitive Relays
WC1 & WCT1 Series, Overcurrent
WC3 & WCT3 Series, Overcurrent
Current Differential Relay
WCD Series
Paralleling Relays
1800 Series
Selection Guide
Frequency Sensitive Relays
WOF & WUF Series
WOUF Series, Over/Underfrequency
20-000 Series
25-000 Series
20-050-19 Series (Voltage/Frequency)
Ground Fault Relays
WGD Series — Floating Ground
WC1G Series — Grounded
Additional Relays. 11-35 – 11-43



#### KILOVAC WD Series, DIN Rail or Screw Mounted Protective Relays

#### **Product Facts**

- WD25 Paralleling (Synch Check) Relays
- WD2759 Over/undervoltage Relays
- WD32 Reverse Power Relays
- WD47 Phase Sequence Relays
- WD5051 Single- or Three-Phase Overcurrent Relays
- WD810U Over/ Underfrequency Relays
- File E58048, DIN EN50022-35

Users should thoroughly review the technical data before selecting a product part number. It is recommended that user also seek out the pertinent approvals files of the agencies/laboratories and review them to ensure the product meets the requirements for a given application.



The WD series offers several different models of protective relays in a common package that is suitable for either DIN rail or screw mounting. These flexible, multifunction devices offer user selectable voltages, sense currents and frequencies. Adjustable time delays are standard. This allows a single part number to be suitable for multiple applications, thereby reducing inventory

# Specifications Common to All Models

**Power Consumption** — 2.5VA, maximum.

#### Contact Ratings -

5 amps, resistive, at 120VAC. 5 amps, resistive, at 30VDC.

Isolation from Control to Sense Inputs — 2,500VAC.

#### Mechanical Life —

10 million operations.

**Shock** — 10g.

**Vibration** — 0.062 (1.57) double amplitude at 10-55 Hz.

Terminals — M3.5 screws.

**Maximum Wire Size** — 2 x 24 AWG (2.5mm²) solid to DIN 46288 or 2 x 16 AWG (1.5mm²) stranded w/end sleeves.

Operating Temperature Range  $-40^{\circ}\text{C}$  to  $+60^{\circ}\text{C}$ .

Enclosure — Plastic case (not sealed).

Mounting Options — Snap mounts on standard DIN rail (DIN-EN 50022-35) or panel mounts with M4, M5, #8 or #10 screws.


**Weight** — 14.4 oz. (400g) approximately.


# Installation and Maintenance Information


Installation — To mount the WD series protective relay on a DIN rail, hook the top edge of the cutout on the base of the case over one edge of the DIN rail, then press the opposite side of the cutout containing the release clip over the opposite side of the DIN rail. To remove or reposition the relay, lever the release clip and move the relay as required. WD series relays should be installed in a dry location where the ambient temperature will be within the operating temperature range.

Maintenance — WD series protective relays are solid state devices that require no maintenance. They are not designed to be serviced by the user. Consult KILOVAC customer service at 805-220-2023 if repairs should be necessary.

#### **Outline Dimensions**









# **Protective Relays**

#### KILOVAC WD25 Paralleling Relays

#### **Product Facts**

- Function 25
- ANSI/IEEE C37.90-1978

#### **WD25 Operation**

WD25 paralleling relays are used to ensure that two circuits are synchronized. When voltage, phase relationship and frequency are within the selected synchronizing limits, the output relay will energize. The WD25 paralleling relay allows for a generator to be brought online without damage or system disturbance. WD25 series with a "dead bus" feature will energize for a synchronized condition or an "on line" generator, "dead bus" condition. This "dead bus" feature allows the generator to energize a dead bus. The "double dead bus" feature permits paralleling of two buses when: (a) both the line voltages are equal and in phase, or (b) when either bus is "hot" and the other bus is "dead."

#### **WD25 Specifications**

**Nominal Operating Range** 120, 208, 277 or 480 VAC, selectable.

Maximum Sensing Range -575VAC.

Nominal Frequency Range — 40-400 Hz.

Contact Form — 2 form C (DPDT).

#### **WD25 Calibration**

The calibration marks on the faceplate are provided only as guides. Proper calibration requires using an accurate voltmeter. Use the following procedure to calibrate the WD25:

- 1. Remove the cover.
- 2. Adjust the SYNC VOLTAGE control fully counterclockwise (CCW). Apply nominal voltage to the LINE B (bus) sensing terminals.
- 3. Apply the maximum desired synchronization voltage to the LINE A (generator) terminals. This voltage should be in phase with LINE B (bus) voltage and have the same frequency.
- 4. Slowly adjust the SYNC VOLTAGE control clockwise (CW) until the relay energizes.


#### Sense Voltage

Voltage (nominal)	120	208	277	480
Synch Voltage (% of nom.)	6 - 30	% (≈ 4°- 20°	electrical d	egree)
Dead Bus Voltage (% of nom.)		10 - 70% (	Dead Bus)	


#### **Control Voltage**

Model WD25	-0X1	-0X2	-0X3
Input Voltage (VDC)	18 to 54	13.5 to 32	100 to 200
Input Voltage (VAC)	_	_	100 to 140


#### **WD25 Controls**



#### WD25 Connections




#### **WD25 Typical Hookup**



BI-DIRECTIONAL AC OR DC INPUT

NOTE: For single dead bus option, connect the generator to 1 & 3 and the bus to 5 & 7.

#### **Ordering Information**



- 1 = 18 to 54VDC
- 2 = 13.5 to 32 VDC
- 3 = 100-200VDC or 100-140VAC.

#### Our authorized distributors are more likely to stock these items.

WD25-001 WD25-013



#### **Product Facts**

- Function 27/59
- ANSI/IEEE C37.90-1978

#### KILOVAC WD2759 Over/Undervoltage Relays

#### WD2759 Operation

WD2759 AC voltage sensing relays provide voltage monitoring and protection in AC systems from 50 to 400 Hz. Sensing voltages, number of phases, over and undervoltage setpoint, and time delays are user configured. WD2759 voltage relays operate when the externally adjustable trip point is reached. An external time delay control is provided with an adjustment of .5 to 10 seconds. This time delay may be used to prevent false tripping when there are slight variations in the voltage supply. On overvoltage (OV) the output relay energizes when the input signal exceeds the trip point. On undervoltage (UV) the output relay energizes when the input signal goes below the trip point. A green LED indicates power to the relay. Red LED lights indicate the state of the undervoltage and overvoltage trips.

#### Sense Voltage

Voltage (nominal)	120	208	277	480
UV Adjustment Range	72-120	125-208	166-277	288-480
OV Adjustment Range	120-168	208-291	277-388	480-672

#### **Control Voltage**

Model WD2759	-001	-002	-003
Input Voltage (VDC)	18 to 54	13.5 to 32	100 to 200
Input Voltage (VAC)	_	_	100 to 140

#### **WD2759 Specifications**

**Nominal Operating Range** — 120, 208, 277 or 480 VAC, selectable.

**Maximum Sensing Range** — 700VAC.

**Nominal Frequency Range** — 50-400 Hz.

**Contact Form** — 1 form C (SPDT) for undervoltage and 1 form C (SPDT) for overvoltage.

**Time Delay Adjustment** — 0.5 to 10 sec.

#### WD2759 Calibration

The calibration marks on the faceplate have a maximum error of 10% and are provided only as guides. Proper calibration requires using an accurate voltmeter in parallel with the input signal. Use the following procedure to calibrate your relay.

#### OVER VOLTAGE


- 1. Remove cover.
- 2. Adjust the TRIP SET control fully clockwise (CW) and the TIME DELAY control fully counterclockwise (CCW).
- 3. Apply the desired trip voltage to the relay.
- 4. Slowly adjust the TRIP SET control CCW until the relay trips.

- Remove the applied voltage (do not change the voltage level) and set the TIME DELAY control to the desired time delay.
- 6. Apply the trip voltage to the relay and measure the time to trip.
- Adjust the TIME DELAY and repeat steps 4 and 5 until you have the desired time delay.

#### UNDER VOLTAGE

- 1. Remove cover.
- Adjust the TRIP SET control fully CCW and the TIME DELAY control fully CCW.
- Decrease the applied sensing voltage from the nominal value until the desired tripping voltage is reached.
- 4. Slowly adjust the TRIP SET control CW until the relay trips.
- 5. Set the TIME DELAY control to the desired time delay and apply nominal voltage to the relay.
- Step down the applied voltage from nominal to a level jest below the trip level set in Step 3 and measure the time delay.
- Adjust the TIME DELAY and repeat steps 4 and 5 until the desired time delay is achieved.

#### **Ordering Information**



003 = 100-200VDC or 100-140VAC.

Our authorized distributors are more likely to stock these items.


WD2759-003




# Prote

## KILOVAC WD2759 Over/Undervoltage Relays (Continued)


#### **WD2759 Controls**




#### **WD2759 Connections**



#### WD2759 Typical Hookup





#### **Product Facts**

■ Function 32

#### **KILOVAC WD32 Reverse Power Relays**

#### **WD32 Operation**

WD32 reverse power relays are used to monitor the direction of power from AC generators. This is accomplished by measuring I cos q. If current from the generator is reversed and exceeds the adjustable setting, the relay will trip. A 0.5 to 20 second time delay is provided. A correct setting of the trip point and time delay will prevent motorizing the generator and prevent tripping during transients that occur while synchronizing. A POWER LED indicates the condition of the power supply and a **REVERSE POWER TRIP** LED indicates the output status of the relay.

#### **WD32 Specifications** Nominal Operating Range —

120 to 480 VAC, 1 or 3 phase.

Maximum Sensing Range — 575VAC.

Nominal Sensing Current — 5A. Nominal Frequency Range — WD32-00X — 40-400 Hz.;

WD32-01X --- 60 Hz. Contact Form — 2 form C (DPDT).

Time Delay Adjustment — 0.5 to 20 sec.

Sense Current — Reverse Power Trip: 0.2 to 1.0A (4-20% of nominal sense current).

#### **Control Voltage**

Model WD32	-001	-002	-003
Input Voltage (VDC)	18 to 54	13.5 to 32	100 to 200
Input Voltage (VAC)	_	~	100 to 140


#### **WD32 Calibration**

The calibration marks on the faceplate have a maximum error of 10% and are provided only as guides. Proper calibration requires using an accurate Current Meter in series with the input current. Use the following procedure to calibrate your relay.

#### REVERSE POWER

- 1. Remove cover.
- 2. Adjust the TRIP SET control fully clockwise (CW) and the TIME DELAY control fully counterclockwise (CCW).
- 3. Apply the desired trip current to the relay. NOTE: for the Reverse Power (WD32-00X) a resistive load must be used and for the Reverse kVAR (WD32-01X) an inductive load must
- 4. Slowly adjust the TRIP SET control CCW until the relay trips
- 5. Remove the applied Current and set the TIME DELAY control to the desired time delay.
- 6. Re-apply the Current (10% more than the trip current) to the relay and measure the time to trip.
- 7. Adjust the TIME DELAY and repeat steps 4 and 5 until you have the desired time delay.

#### **Ordering Information**



1 = 18 to 54VDC

2 = 13.5 to 32 VDC

3 = 100-200VDC or 100-140VAC.

Our authorized distributors are more likely to stock these items.


WD32-003 WD32-011




# Protec

## KILOVAC WD32 Reverse Power Relays (Continued)


#### **WD32 Controls**





#### **WD32 Connections**



## WD32 Typical Hookup







#### **KILOVAC WD47 Phase Sequence Relays**

#### **Product Facts**

- Function 47
- ANSI/IEEE C37.90-1978

#### **WD47 Operation**

WD47 phase sequence relays are designed to monitor the correct phase rotation and loss of phase of three phase ac systems from 50 to 400 Hz. An incorrect phase sequence or loss of any phase will cause the WD47 to pickup. When the phase sequence is corrected or the lost phase is restored the contacts dropout. Red LED's light to indicate a fault condition. A green LED indicates power to the relay. The WD47 is often used to detect reverse phase rotation or loss of phase to generators, busses, motors, and transformers.

#### **WD47 Specifications**

Nominal Operating Range -120 to 480 VAC.

Maximum Sensing Range -575VAC.

Nominal Frequency Range — 40-400 Hz.

Contact Form — 2 form C (DPDT).

#### WD47 Calibration


The WD47 has no adjustments and no calibration is necessary. Proper operation may be verified as follows:

- 1. Apply a nominal, three-phase input with the correct phase sequence. The output relay should dropout and the green LED should light.
- 2. Apply a nominal, three-phase input with an incorrect phase sequence. The output relay should pickup and the red LED should light.
- 3. Apply only one or two phases with the correct phase sequence. The output relay should pickup and the red LED should light.


#### **Control Voltage**

Model WD47	-001	-002	-003
Input Voltage (VDC)	18 to 54	13.5 to 32	100 to 200
Input Voltage (VAC)	_	_	100 to 140


#### **WD47 Controls**




#### **WD47 Connections**



#### **WD47 Typical Hookup**



#### **Ordering Information**



Our authorized distributors are more likely to stock these items.

WD47-001

#### **Product Facts**

■ Function 5051

#### KILOVAC WD5051 10 and 30 Overcurrent Relays

#### WD5051 Operation

WD5051 AC current sensing relays provide current monitoring and protection in AC systems from 50 to 400 Hz. Nominal Sensing Current, Instantaneous Over Current setpoint, Time Over Current setpoint, and Time Over Current time delay are user configured. WD5051 current relays operate when the externally adjustable trip point is reached. An external time over current time delay control is provided with an adjustment of .5 to 20 seconds. This time delay may be used to prevent false tripping when there are slight variations in the sensed current. With control power applied, the Instantaneous Over Current (IOC) contacts pick-up when the input signal exceeds the IOC trip setpoint. Similarly, with control power applied, the Time Over Current (TOC) contacts pick-up after the preset time delay when the Sense Current rises above the TOC trip setpoint. The IOC contacts may also be configured to function as an under current relay. A green LED indicates power to the relay. Red LED lights indicate the state of the IOC and TOC trips.

#### Sense Current

Current (nominal)	1	3	6	8
IOC	0.2 to 1.2	0.6 to 3.6	1.2 to 7.2	1.6 to 9.6
TOC	0.2 to 1.2	0.6 to 3.6	1.2 to 7.2	1.6 to 9.6

#### **Control Voltage**

Model WD5051	-001	-002	-003
Input Voltage (VDC)	18 to 54	13.5 to 32	100 to 200
Input Voltage (VAC)	_	_	100 to 140

#### WD5051 Specifications

**Sense Current Full Scale** — 1, 3, 6 or 8A. selectable.

#### Maximum Sensing Current —

10A continuous; 30A for 10 sec.; 60A for 2.5 sec.; 100A for 0.9 sec..

Nominal Frequency Range — 50-400 Hz.

**Contact Form** — 1 form C (SPDT) for IOC and 1 form C (SPDT) for TOC.

**TOC Time Delay Adjustment** — 0.5 to 20 sec.

**IOC Operate Time (max.)** — 0.2 sec.


#### WD5051 Calibration

The calibration marks on the faceplate are provided only as guides. Proper calibration requires using an accurate ammeter in series with the current source. Use the following procedure to calibrate your relay:

#### OVERCURRENT

- 1. Remover the cover.
- Adjust the TRIP SET control fully clockwise (CW) and the TIME DELAY control (TOC only) fully counterclockwise (CCW).
- 3. Apply the desired trip current to the relay.
- 4. Slowly adjust the TRIP SET control CCW until the relay trips.
- Remove the applied current (do not change the current level). Set the TIME DELAY (TOC only) control to the desired time delay.

#### **Ordering Information**



001 = 18 to 54VDC

002 = 13.5 to 32 VDC

003 = 100-200VDC 0r 100-140VAC.


Our authorized distributors are more likely to stock these items.

WD5051-001 WD5051-003 WD5051-3-001




## KILOVAC WD5051 10 and 30 Overcurrent Relays (Continued)

#### WD5051 Controls




#### **WD5051 Connections**

WD5051 Single Phase Model




#### WD5051-3 Three Phase Model



#### WD5051 Typical Hookup

#### WD5051 Single Phase Model



Three Phase Model

Coad

# Control Voltage Model WD81OU -001 -002 -003 Input Voltage (VDC) 18 to 54 13.5 to 32 100 to 200 Input Voltage (VAC) — 100 to 140

60

48-60

60-72

400

360-400

400-480

#### KILOVAC WD810U Over/Underfrequency Relays

#### **Product Facts**

- Function 81 OU
- ANSI/IEEE C37.90-1978

#### **WD810U Operation**

WD81OU frequency relays are used to provide frequency monitoring and protection to generators, buses, power supplies, and other equipment. The relay operates at voltages from 120 to 480 Vac and at nominal frequencies of 50, 60, and 400 Hz. External controls include nominal frequency selection, under frequency (UF) trip set, over frequency (OF) trip set, UF time delay, and OF time delay. A green LED indicates power to the relay. Red LED's indicate the status of the UF and OF trips.

#### **WD810U Specifications**

**Nominal Operating Frequency** — 50, 60 or 400 Hz., selectable.

Maximum Frequency @ 400 Hz. Nominal — 1000 Hz.

Nominal Sensing Voltage — 20-480VAC.

**Maximum Sensing Voltage** — 575VAC.

**Contact Form** — 1 form C (SPDT) for underfrequency and 1 form C (SPDT) for overfrequency.

**Time Delay Adjustment** — 0.5 to 10 sec.

#### **WD810U Calibration**

The calibration marks on the faceplate are provided only as guides. Proper calibration requires using an accurate frequency meter in parallel with the input signal

UNDER FREQUENCY

- 1. Remove the cover.
- Set the SENSE FREQUENCY to the nominal system frequency. Adjust the Under Frequency TRIP SET fully clockwise (CW) and the TIME DELAY control fully counterclockwise (CCW).
- 3. Apply the desired trip frequency to the relay.
- 4. Slowly adjust the TRIP SET control CCW until the relay trips.
- 5. Set the TIME DELAY control to the desired time delay and apply nominal frequency to the relay.
- 6. Step down the applied frequency from nominal to just below the trip level set in Step 4 and measure the time delay.
- Adjust the TIME DELAY and repeat steps 5 and 6 until the desired time delay is set.

OVER FREQUENCY


- Remove the cover.
- Set the SENSE FREQUENCY to the nominal system frequency. Adjust the OF TRIP SET and TIME DELAY controls fully counterclockwise (CCW).
- 3. Apply the desired trip frequency to the relay.
- Slowly adjust the TRIP SET control clockwise (CW) until the relay trips.
- 5. Set the TIME DELAY control to the desired time delay and apply nominal frequency to the relay.
- Step down the applied frequency from nominal to just below the trip level set in Step 4 and measure the time delay.
- Adjust the TIME DELAY and repeat steps 5 and 6 until the desired time delay is set.

Sense Frequency

Frequency (nominal)

UF Adjustment Range

OF Adjustment Range




50


40-50

50-60

#### **WD810U Connections**




#### **WD810U Typical Hookup**



CONTROL BI-DIRECTIONAL AC OR DC INPUT

#### **Ordering Information**



Our authorized distributors are more likely to stock these items.

None at present.

002 = 13.5 to 32 VDC

003 = 100-200VDC or 100-140VAC.



#### **WUV/WOV DC Series**

#### **Product Facts**


■ ANSI/IEEE C37.90-1978

#### **Undervoltage Models**


The relay is energized at normal voltage, N.C. contacts will open and N.O. contacts will close. The relay will de-energize when the voltage drops below the U/V set point.

#### **Overvoltage Models**

The relay is de-energized at normal voltage, N.C. contacts are closed and N.O. contacts are open. The relay will energize, when the voltage rises above the O/V set point.



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.



#### **Product Specifications**

**Nominal Voltage** — 12 VDC to 560 VDC

#### Drop-out Point (u/v models) —

70-100% of nominal voltage, screwdriver adjustable

#### Pick-Up Point (o/v models) —

100-125% of nominal voltage, screwdriver adjustable

**Output Contacts** — One set N.O., One set N.C.

#### Contact Ratings -

5 amp resistive at 120 VAC or 28 VDC

# Operating Temperature Range — $-40^{\circ}\text{C}$ to $+75^{\circ}\text{C}$

**Temperature Effects** — Less than 1% voltage drift over the temperature range

#### Power Consumption —

12 to 60 VDC models — 1 W max. 120 to 305 VDC models — 2 W max. 405 to 470 VDC models — 3 W max. 560 VDC model — 4 W max.

**Time Delay** — A short duration delay is provided to prevent nuisance tripping due to momentary dips or surges in voltage. The drop-out delay, following a voltage fault is 75 to 100 milliseconds.

#### Notes:


- Remove black screws for access to the O/V and U/V trip adjustment.
- Clockwise rotation of the adjustment potentiometer will raise the voltage trip point.
- The adjustments are by means of a single turn potentiometer. Use a small screwdriver and do not force beyond the limit stops.

#### **Ordering Information**


B = 2 Form B Contacts

H = 125 VDC Contacts

P = Transient Protection



#### Time Curves DC Overvoltage Relays



**Transient Protection** — All voltage relays will withstand momentary voltage surges of twice the nominal rated input voltage (standard).

**Option "P"** provides additional transient protection which complies with the requirements of ANSI/IEEE C37.90-1978

#### **WUV/WOV Series**


#### **Product Facts**

- Function 27/59
- ANSI/IEEE C37.90-1978
- **■** UL File No. E58048


■ CSA File No. LR61158



Voltage sensitive relays are available for both AC and DC applications for over/undervoltage protection. Combination over/ undervoltage relays provide bandpass capabilities. AC relays are either single or three-phase type. Three phase models are designed to sense the average of the three phases or the highest single phase. Voltage trip points are screwdriver adjustable, and operation is time-delayed so that momentary voltage transients will not cause nuisance tripping.




Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.



Single Phase

-120

WUV -1



Three Phase

#### **Product Specifications**

**Nominal Voltage** — 120 VAC to 575 VAC

**Phase** — Single or Three

Line Frequency — 50-400 Hz

Pick-up to Drop-out Differential — 2.5% maximum

**Drop-out Point (u/v models)** — 70-100% of nominal voltage,

screwdriver adjustable

Pick-Up Point (o/v models) —
100-125% of nominal voltage.

screwdriver adjustable **Output Contacts** — One set N.O.,

One set N.C.

Contact Ratings —

5 amp resistive at 120 VAC or 28 VDC

Operating Temperature Range —  $-20^{\circ}\text{C}$  to  $+65^{\circ}\text{C}$ 

 ${\bf Power\ Consumption} \ --$ 

2 VA maximum

Time Delay — 150-300 ms (UV Model) Minimum Life — 500,000 operations

#### Notes:

- Remove black screw for access to the voltage trip adjustment.
- Clockwise rotation of the adjustment potentiometer will raise the voltage trip point.

# **Protective Relays**

#### **Ordering Information**

#### Sample Part Number

#### Type:

WUV - Undervoltage WOV - Overvoltage

#### No. Phases

1 = Single

3 = Three

#### Line Voltage VAC

120 416

208 440

220 460

230 480

240 525 380 575


Options

#### P - Transient Protection

A - Two Normally Open Contacts

B - Two Normally Closed Contacts

H - 125VDC, 3A Contacts



**Transient Protection** — All voltage relays will withstand momentary voltage surges of twice the nominal rated input voltage (standard).

**Option "P"** provides additional transient protection which complies with the requirements of ANSI/IEEE C37.90-1978

#### **WUVT/WOVT Series**

#### **Product Facts**

- Function 27/59
- ANSI/IEEE C37.90-1978
- **■** UL File No. E58048
- CSA File No. LR61158




#### **Undervoltage Models**


The relay is energized at normal voltage, N.C. contacts will open and N.O. contacts will close. The relay will de-energize when the voltage drops and remains below the U/V set point for the duration of the set time delay.

#### **Overvoltage Models**

The relay is de-energized at normal voltages, N.C. contacts are closed and N.O. contacts are open. The relay will energize, when the voltage rises and remains above the O/V set point for the duration of the set time delay.



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.




#### **Ordering Information**

B = 2 Form B Contacts

H = 125VDC 3A Contacts

P = Transient Protection



#### **Product Specifications**

**Nominal Voltage** — 100 VAC to 575 VAC

**Phase** — Single or Three

Line Frequency — 50-400 Hz

Pick-up to Drop-out Differential — 1% typical

**Drop-out Point (u/v models)** — 70-100% of nominal voltage, screwdriver adjustable

Pick-Up Point (o/v models) — 100-125% of nominal voltage, screwdriver adjustable

**Output Contacts** — One set N.O., One set N.C.

#### Contact Ratings -

5 amp resistive at 120 VAC or 28 VDC

Operating Temperature Range —  $-40^{\circ}\text{C}$  to  $+70^{\circ}\text{C}$ 

 ${\bf Power\ Consumption}\ --$ 

3 VA maximum

**Time Delay** — 0.5 to 20 seconds, screwdriver adjustable

**Voltage Reset** — The reset is automatic when voltage returns to normal.

#### Notes:

- Remove black screws for access to the voltage and time delay adjustment potentiometer.
- Clockwise rotation of the voltage adjust potentiometer will raise the voltage trip point.
- Clockwise rotation of the time adjust potentiometer will increase the time delay (Pick-up time for O/V models, drop-out time for U/V models).
- The adjustments are single turn potentiometers, use a small screwdriver and do not force beyond the limit stops.
- On U/V models, when the voltage falls to approximately 33% of nominal or below, the relay will drop out in 0.150 to 0.300 seconds, regardless of the time delay setting.

**Transient Protection** — All voltage relays will withstand momentary voltage surges of twice the nominal rated input voltage (standard).

**Option "P"** provides additional transient protection which complies with the requirements of ANSI/IEEE C37.90-1978


# Protective Relays

### WOUV DC Series, Over/Undervoltage


#### **Product Facts**

■ ANSI/IEEE C37.90-1978

The relay will energize at normal voltage conditions. The normally open contacts will close, and the normally closed contacts will open. The relay will de-energize during over or undervoltage conditions. Reset is automatic when the voltage returns to normal.



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.



Single Phase

# Product Specifications Nominal Voltage (±10%) — 12 VDC to 560 VDC

**Drop-out Point (u/v models)** — 70-100% of nominal voltage, screwdriver adjustable

Pick-Up Point (o/v models) — 100-125% of nominal voltage, screwdriver adjustable

**Output Contacts** — One set N.O., One set N.C.

#### Contact Ratings -

5 amp resistive at 120 VAC or 28 VDC

Operating Temperature Range  $-40^{\circ}\text{C}$  to  $+75^{\circ}\text{C}$ 

#### Temperature Effects —

Less than 1% voltage drift over the temperature range.

#### Power Consumption -


12 to 60 VDC models — 1 W max. 120 to 305 VDC models — 2 W max. 405 to 470 VDC models — 3 W max. 560 VDC Model — 4 W max.

**Time Delay** — A short duration delay is provided to prevent nuisance tripping due to momentary dips or surges in voltage. The drop-out delay, following a voltage fault is 75 to 100 milliseconds

#### Notes:

- Remove black screws for access to the O/V and U/V trip adjustment.
- Clockwise rotation of the adjustment potentiometer will raise the voltage trip point.
- The adjustments are by means of a single turn potentiometer. Use a small screwdriver and do not force beyond the limit stops.

#### **Ordering Information**




Blank - Standard

A = 2 Form A Contacts

B = 2 Form B Contacts

H = 125 VDC Contacts

P = Transient Protection



**Transient Protection** — All voltage relays will withstand momentary voltage surges of twice the nominal rated input voltage (standard).

**Option "P"** provides additional transient protection which complies with the requirements of ANSI/IEEE C37.90-1978



#### WOUVT Series, Over/Undervoltage


#### **Product Facts**

- Function 27/59
- ANSI/IEEE C37.90-1978


Voltage sensitive relays are available for both AC and DC applications for overvoltage and undervoltage protection. Combination over/undervoltage relays provide band-pass capabilities. AC relays are either single or three-phase type. Three phase relays are designed to sense the average of the three phases. Voltage trip points are screwdriver adjustable, and operation is time-delayed so that momentary voltage transients will not cause nuisance tripping.

#### Operation

The relay will energize at normal voltage condition. The normally closed contact (Form B) will open and the normally open (Form A) will close. The relay will de-energize after time delay when over or undervoltage condition is reached.



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.



#### **Product Specifications**

**Nominal Voltage** — 120 VAC to 575 VAC

**Phase** — Single or Three

**Line Frequency** — 50-400 Hz

**Type of Sensing** — Average of all three phases

**Undervoltage Trip** — 70-100% of nominal voltage, screwdriver adjustable

**Overvoltage Trip** — 100-125% of nominal voltage, screwdriver adjustable

**Drop-out Time Delay** — 0.5 to 20 seconds, screwdriver adjustable

Pick-up to Drop-out Differential — 2% maximum

Output Contacts — One set N.O., One set N.C.

Contact Ratings — 5 amp resistive at

120 VAC or 28 VDC

Operating Temperature Range —

-40°C to +70°C **Power Consumption** —

4 VA maximum

#### Notes:

- Remove black screw for access to the voltage trip and time delay adjustment potentiometer.
- Clockwise rotation of the voltage adjustment potentiometer will raise the voltage trip point.
- Clockwise rotation of the time adjustment potentiometer will increase the drop-out time delay.


#### **Ordering Information**

A = 2 Form A Contacts

B = 2 Form B Contacts

H = 125 VDC Contacts

P = Transient Protection



**Option "H"** provides for contacts rating of 3 amps @ 125VDC.

**Option "P"** provides additional transient protection which complies with the requirements of ANSI/IEEE C37.90-1978

# Protective Relays

#### 250 Series, Over/Undervoltage


#### **Product Facts**

- Function 27/59
- ANSI/IEEE C37.90-1978


The 250 series relays provide combined Overvoltage and Undervoltage protection in a single compact unit.

Models are available for single phase or three phase applications, and are suitable for either 50 Hz, 60 Hz, or 400 Hz operation. The trip point is adjustable.

A transistorized circuit provides a sharp and accurate response at the preset tripping voltage; unaffected by temperature or frequency variations.



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.



#### **Product Specifications**

**Nominal Voltage** — See Ordering Information

**Undervoltage Trip** — 70-100% of nominal voltage, screwdriver adjustable

**Overvoltage Trip** — 100-125% of nominal voltage, screwdriver adjustable

Pick-up to Drop-out Differential — 3% maximum

**Contact Ratings** — 5 amp resistive at 120 VAC or 28 VDC

**Contact Form** — One set N.O., one set N.C.

Operating Temperature Range — -20°C to +85°C

#### Notes:

 Remove screws for access the overvoltage or undervoltage trip adjustments. Clockwise rotation of the adjustment potentiometer will raise the trip point.

#### **Contact Arrangements**

**NC** — Open at nominal voltage. Closed at Overvoltage and Undervoltage

**NO** — Closed at nominal voltage. Open at Overvoltage and Undervoltage

#### **Ordering Information**

Sample Part Number ► 250X

Model: L-L Volts

250X = 120 VAC, 1 Phase, 50-400 Hz
251X = 120/208 VAC, 3 Phase, 4 Wire, 50-400 Hz
252X = 115 VAC, 3 Phase, 3 Wire, 50-400 Hz
253X\* = 230 VAC, 3 Phase, 3 Wire, 50-400 Hz
254X\* = 380 VAC, 3 Phase, 3 Wire, 50-400 Hz
255X\*= 460 VAC, 3 Phase, 3 Wire, 50-400 Hz
255X\*= 460 VAC, 3 Phase, 3 Wire, 50-400 Hz
256X\* = 575 VAC, 3 Phase, 3 Wire, 50-400 Hz
Mounting

Blank = Stud
X = Flange



<sup>\*</sup> Enclosure height is 3.835"

#### **D100X Series, Close Differential**

#### **Product Facts**

- ANSI/IEEE C37.90-1978
- UL File No. E58048







Close Differential Relays are voltage sensitive. The pick-up and drop-out voltage settings are independently adjustable, which allows precise setting of the differential voltage. This relay is available in a wide range of AC and DC voltages. Their primary application is the sensing and control of transfer switches.

#### Operation

Monitors a single phase AC signal, and is used for undervoltage detection. Has separate pick-up and drop-out voltage settings, providing an adjustable hysteresis.



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.



#### **Product Specifications**

**Nominal Voltage** — AC, Single Phase, see Ordering Information

**Nominal Frequency** — 50 to 400 Hz.

Pick-Up Adjustment Range — 67-100% of nominal voltage

**Drop-Out Adjustment Range** — 67-100% of nominal voltage

Maximum Differential Setting — 33% of nominal voltage

Minimum Differential Setting — 2% of nominal voltage

**Output Contacts** — Form C (SPDT)

**Contact Ratings** — 5 Amp resistive at 120 VAC or 28 VDC

**Operating Temperature Range** — -20°C to +85°C

**Expected Life** — 10 million operations

#### Inverse Time Drop-Out -

The differential relay contains a time delay before operation so that momentary voltage transients do not affect the operation of the relay. The time delay has an inverse time characteristic so that excessive voltage conditions will cause a more rapid drop-out. This time delay is approximately 200mSec. (12 cycles) at the trip settings and decreases to 30 mSec. at approximately 15% beyond the trip settings.

#### Notes

- Remove black nylon protective screws to gain access to the two internal adjustment potentiometers
- 2. Clockwise rotation of the pick-up and drop-out adjustment will raise the voltage trip point.
- 3. The relay contacts are shown in the de-energized state.

#### **Ordering Information**

Sample Part Number ▶	<u>D100X</u>
Model: L-L Volts -	Height
D100X = 120 VAC	2"
D100-6X = 120 VAC, Spike Sup	pression 2"
D100-3X = 208 VAC	3.125"
D100-4X = 240 VAC	3.125"
D100-8X = 277 VAC	3.125"
D100-5X = 480 VAC	3.125"
D100-7X = 510 VAC	3.125"

Surge Withstand Capability is in compliance with the requirements of ANSI/IEEE C37.90B



#### D101X Series, 3 Phase Adjustable, Close Differential

#### **Product Facts**

- ANSI/IEEE C37.90-1978
- UL File No. E58048
- CSA File No. LR61158 (UL)







Close Differential Relays are voltage sensitive. The pick-up and drop-out voltage settings are independently adjustable, which allows precise setting of the differential voltage. This relay is available in a wide range of AC voltages. Their primary application is the sensing and control of transfer switches.

#### Operation

The output contacts will close when the voltage of all three phases is above the pre-set pick-up point, and will open when any one phase drops below its drop-out setting.



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.



# **Ordering Information**

Sample Part Number ▶	<u>D101X</u>
Model: L-L Volts —	
D101X = 120 VAC	
D101-6X = 208 VAC	
D101-4X = 240 VAC	
D101-10X = 380 VAC	
D101-7X = 480 VAC	

Model	Power Consumption Each Phase	H1 (inches)	H2 (inches)
D101X	2 VA max.	2	2 11/16
D101-4X	3 VA max.	3 1/2	4 3/16
D101-6X	3 VA max.	3 1/2	4 3/16
D101-7X	4 VA max.	3 1/2	4 3/16
D101-10X	4 VA max.	3 1/2	4 3/16

**Product Specifications** 

**Nominal Voltage** — AC, Three Phase, see Ordering Information

Nominal Frequency — 50 to 500 Hz.

Pick-Up Adjustment Range —

66-100% of nominal voltage, screwdriver adjustable

Drop-Out Adjustment Range — 66-100% of nominal voltage, screw-

driver adjustable

Output Contacts — SPNO

**Contact Ratings** — 5 amp resistive at 120 VAC or 28 VDC

Operating Temperature Range — -20°C to +85°C

#### Notes:

- 1 Remove screws for access to pick-up and drop-out trip adjustments.
- 2. Clockwise rotation of the pick-up and drop-out adjustment will raise the voltage trip point.




#### 700 Series w/ Adjustable Time Delay

#### **Product Facts**

- Function 32
- ANSI/IEEE C37.90-1978
- **■** UL File No. E58048
- CSA File No. LR61158




Several types of Reverse Power Relays are available including relays sensitive to reverse reactive power (kVAR). KILOVAC is the leading brand of reverse power relays. Our rugged sealed construction provides continuous and reliable operation unaffected by shock, vibration or other severe environments. Reverse Power Relays are used for the protection of generator sets operating in parallel.




Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.

#### Model 710TD

#### Model 720TD (X) thru 724TD (X)



Designed for 120, 220 or 266 volt line to neutral connection



For operation on three phase, three wire

**720TDX** 

#### **Product Specifications**

#### Line Voltage -

Model 710TD — 120 V, 220 V or 266 V, line to neutral

Model 730TD — 120 V, 230 V, 380 V, 460 V, L-L, 3 Phase or 120 V, Single Phase. L-N

All models for three phase, three wire sensing are available, see Ordering Information

Line Frequency — 50-500 Hz.

#### Current Requirements —

0 to 5 amp max direct or from CT with 5 amp secondary

#### Trip Adjustment —

Screwdriver adjustable 4% to 20% (of the 5 amp rating)

**Time Delay Adjustment** — 0.5 to 20 seconds, screwdriver adjustable

**Contact Ratings** — 5 amp resistive at 120 AC or 28 Vdc

#### Power Consumption —

Voltage circuit — 2 VA max. Current circuit — 4 VA max.

Weight — 2.75 lbs. max.

#### Notes:

- Remove screw for access to the pick-up and time delay adjustments.
- Clockwise rotation of the pick-up adjustment will raise the reverse trip point.
- Clockwise rotation of the time adjustment will increase the time delay.
- Polarity of the voltage and the current connections must be observed for true power sensing.
- 5. Interchanging connections on terminals 5 and 6, will cause the output contacts to pick-up on forward power and dropout on no power or reverse power.

#### **Ordering Information**

Sample Part Number

# Type: 710TD = 120V, 220V, 266V line to neutral 720TD = 120V, L-L, 3 Phase 721TD = 230V, L-L, 3 Phase 722TD = 380V, L-L, 3 Phase 723TD = 460V, L-L, 3 Phase 724TD = 575V, L-L, 3 Phase 725TD = 416V, L-L, 3 Phase 730TD = 120 V, 230 V, 380 V, 460 V, L-L, 3 Phase or 120 V, Single Phase, L-N

#### Mounting:

X = Flange Blank - Stud

#### **Options:**

7 = Reverse Inductive, 60 Hz



**■** UL File No. E58048






Phase failure relays protect motors, equipment and personnel from damage or injury caused by open phase, reversed phase sequence, or low voltage in a three phase system. Models are available for 50 and 60 Hz with voltages up to 575 volts. Motor control switchboards are a common application.


#### Operation

The contacts of the relay will close only when it senses normal conditions of three phase power at the proper phase sequence.

The relay contacts will remain in their normally open position (de-energized) when voltage with incorrect phase sequence is applied, one or more phases are open, or at undervoltage condition.



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.



#### **Product Specifications**

**Nominal Voltage** — See Ordering Information

**Voltage Drop-Out** — 75% to 100% of nominal, screwdriver adjustable

Pick-Up to Drop-Out Differential — 3% approx.

Ambient Operating Temperature
— -40°C to +70°C

Temperature Drift —  $\pm 1\%$ 

Time Delay — See Curve

Output Contacts — One set, normally open

Contact Ratings —

10 amp at 28 VDC resistive 10 amp at 230 VAC resistive

#### Notes:


- Remove screw for access to the undervoltage adjustment.
- Clockwise rotation of the adjustment potentiometer will raise the drop-out voltage.

11

**Protective Rela** 

#### **Ordering Information**

Blank - Stud





#### 900 Series


#### **Product Facts**

#### ■ Function 47

Phase sequence relays are designed to monitor the correct phase rotation of a three phase system. Several models are available from 50 Hz, 60 Hz, and 400 Hz with voltages up to 575 volts. High shock relay output and reverse contacts are also available.

#### Operation

The relay remains de-energized when voltage in the proper phase sequence (A, B, C) is applied, the relay is energized when voltage with incorrect sequence (A, C, B) is applied.



#### **Product Specifications**


**Input Voltage** — See Ordering Information

Output Contacts — SPDT


Contact Ratings —

5 amp resistive at 120 Vac or 28 Vdc

Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.



#### **Ordering Information**





**■** UL File No. E58048


■ CSA File No. LR61158




Current Balance Relays are designed to sense unbalanced current flow in a three phase system. The primary application of Current Balance Relays is to protect three phase motors against phase unbalance or phase failure.

#### Operation

With control voltage applied to the relay, the output contacts will energize when the three phase currents are balanced (including zero currents), and will be de-energize by unbalance currents.



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.



#### **Product Specifications**

Line Current — Three Phase, AC current, 50-400 Hz Direct or from

5 amp continuously 20 amp, 30 sec. 200 amp, 0.10 sec.

**Control Voltage** — See Ordering Information

#### Unbalanced Trip Point —

Screwdriver adjustable. Adjustment range in accordance with ordering information. (The unbalanced value is defined as the difference between the highest and the lowest phase current).

#### Drop-Out Time Delay —

0.9 to 1.3 seconds

**Surge Withstand Capability** — In compliance with C37.90B ANSI/IEEE

# Operating Temperature — $-40^{\circ}\text{C}$ to $+70^{\circ}\text{C}$

Burden -

Current input — 5.0 VA, Phase Control voltage — 3.0 VA

#### Contact Ratings -

One set, N.O., One set N.C. 5 amp resistive at 120 VAC or 28 VDC


#### lotes:

- 1. Remove black screw for access to the trip adjustment.
- Clockwise rotation of the adjustment potentiometer will raise the unbalance trip point.
- 3. The output contacts are shown de-energized.

1

**Protective Relays** 

#### **Ordering Information**



A = two normally open contacts B = two normally closed contacts




#### WC1 & WCT1 Series, Overcurrent

#### **Product Facts**


- Function 50/51
- ANSI/IEEE C37.90-1978
- **■** UL File No. E58048
- CSA File No. LR61158



Current sensitive relays are available for single and three phase applications. Voltage controlled overcurrent relays protect generators against fault currents below the full rated value, when the fault produces a voltage drop as in the case of short circuits or grounds. Phase balance relays are available to sense and control unbalanced current flow in three phase systems. Current differential relays operate when the differential between two currents exceeds preset values. Over/under current phase-band relays are also available.



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.



#### Time Delay

#### Standard Time Delay

**(WC1 Series)** — A fixed inverse time delay is incorporated in all overcurrent relays and is represented by the typical curves shown.

#### Adjustable Time Delay

(WCT1 Series) — The time delay is field adjustable. The standard time delay can be increased by any value between 0.5 and 20 seconds.

#### **Product Specifications**

**Line Current** — Single Phase, AC current, 50-400 Hz Direct or from CT

**Control Voltage** — See Ordering Information

**Trip Point** — Screwdriver adjustable. Adjustment range in accordance with ordering information.

**Pick-Up to Drop-Out Differential** — Approximately 0.1 amp.

Overcurrent Allowance —

Maximum of 500% for 0.25 seconds

**Surge Withstand Capability** — In compliance with C37.90B ANSI/IEEE

Operating Temperature  $-40^{\circ}\text{C}$  to  $+70^{\circ}\text{C}$ 

Temperature Drift —  $\pm .05\%$ 

Burden —

Current input — 1.2 VA, Control voltage — 2.5 VA


Contact Ratings —

One set, N.O., One set N.C. 5 amp resistive at 120 VAC or 28 VDC


#### Notes:

- Remove black screws for access to the current pick-up and the time delay adjustment.
- Clockwise rotation of the pick-up adjustment will raise the current trip point.
- Clockwise rotation of the time delay adjustment, (Type WCT1 only) will increase the time delay.

#### **Ordering Information**



Typical Curves (WC1 Series)



See next page for 3-phase types and consult factory for additional models.

B = Two normally closed contacts


#### WC3 & WCT3 Series, Overcurrent

#### **Product Facts**


- Function 50/51
- ANSI/IEEE C37.90-1978
- **■** UL File No. E58048
- CSA File No. LR61158



Current sensitive relays are available for single and three phase applications. Voltage controlled overcurrent relays protect generators against fault currents below the full rated value, when the fault produces a voltage drop as in the case of short circuits or grounds. Phase balance relays are available to sense and control unbalanced current flow in three phase systems. Current differential relays operate when the differential between two currents exceeds preset values. Over/under current phase-band relays are also available.



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.



### Time Delay

### Standard Time Delay

**(WC3 Series)** — A fixed inverse time delay is incorporated in all overcurrent relays and is represented by the typical curves shown.

#### Adjustable Time Delay

(WCT3 Series) — The time delay is field adjustable. The standard time delay can be increased by any value between 0.5 and 20 seconds.

#### **Product Specifications**

**Line Current** — Three Phase, AC current, 50-400 Hz Direct or from CT

**Control Voltage** — See Ordering Information

**Trip Point** — Screwdriver adjustable. Adjustment range in accordance with ordering information.

Pick-Up to Drop-Out Differential — Approximately 0.1 amp

**Overcurrent Allowance** — Maximum of 500% for 0.25 seconds

**Surge Withstand Capability** — In compliance with the requirements of

Operating Temperature — -40°C to +70°C

Temperature Drift —  $\pm 0.05\%$ /°C

Burden –

ANSI/IEEE

Current input — 1.2 VA, Control voltage — 2.5 VA

Contact Ratings -

One set, N.O., One set N.C. 5 amp resistive at 120 VAC or 28VDC


#### Notes:

- Remove black screws for access to the current pick-up and the time delay adjustment.
- Clockwise rotation of the pick-up adjustment will raise the current trip point.
- Clockwise rotation of the time delay adjustment, (Type WCT3 only) will increase the time delay.

**Ordering Information** 

WCT3 -48DC -5 Sample Part Number Type: WC3 = Per Time Curves WCT3 = Adjustable Time Delay Control Voltage (± 15%) -26 DC 48 DC 125 DC 120 AC 230 AC 380 AC 460 AC Trip Adjustment Range 1 = .2 amp - 1 amp5 = 1 amp to 5 amp 10 = 2 amp to 10 amp Other Options

#### Typical Curves (WC3 Series)



See previous page for 1-phase models and consult factory for additional models.

ETE connectivity

A = Two normally open contacts

B = Two normally closed contacts

#### **WCD Series**

#### **Product Facts**


- Function 87
- ANSI/IEEE C37.90-1978

**Current Differential Relays** are used for the protection of transformers, motors and generators, by comparing the magnitude of the current entering and leaving the protected circuit. On a given phase winding, any difference between the two currents will indicate an internal fault; the relay will sense the vectorial difference between the two currents of the protected section and will initiate a quick disconnection of the unit, to prevent disastrous consequences.


The relay may also be used to protect internal faults on transformers, such as: ground faults, shorted winding, leakage between primary and secondary, etc. It will sense and compare primary vs. secondary currents, once the turns ratio has been taken into consideration.

#### Operation

With control voltage applied, the output contacts (shown in the de-energized position) will remain de-energized as long as the difference between the two input currents remains below the preset trip value. The contact will transfer to the energized position when the current difference exceeds the trip value.



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.



#### **Ordering Information**

Sample Part Num	ber <b>&gt;</b>	WCD -230AC -1 -A
Type: ————————————————————————————————————	Differential	
Control Voltage 120AC 208AC 230AC 380AC 416AC 460AC 525AC 575AC	25DC 48DC 125DC	
Trip Adjustmen: .5 = 0.1 amp to 1 = 0.2 amp to 2 = 0.4 amp to Options:	0.5 amp 1 amp	

H = Contacts rated 3 amp at 125 VDC
P = Transient protection is provided in compliance with ANSI/IEEE C37.90-1978

A = Two normally open contacts B = Two normally closed contacts

#### **Product Specifications**

#### Line Current -

Single Phase, AC current, 50-400 Hz Direct or from CT 5 amp continuously 20 amp 30 seconds 200 amp, 0.10 seconds

**Control Voltage** — See Ordering Information

#### Differential Trip Point —

Screwdriver adjustable. See Ordering Information

#### Operating Temperature —

-40°C to +75°C

#### Burden -

Current input — 2.5 VA max. Control voltage DC — 2 W max. AC — 2 VA max.

#### Output Contacts -

One set, N.O., One set N.C.

#### Contact Ratings —

5 amp resistive at 120 VAC or 28 VDC

#### Notes:

- Remove black screws for access to the trip adjustments.
- Clockwise rotation of the adjustment potentiometer will raise the current differential trip point.
- 3. The output contacts are shown de-energized.



#### 1800 Series

#### **Product Facts**

- Function 25
- ANSI/IEEE C37.90-1978
- **■** UL File No. E58048
- CSA File No. LR61158



#### **Application**

These relays are designed for automatic paralleling (synchronizing) of generators. The relays sense the phase angle displacement and the amplitude difference between two voltages and permit paralleling only when both voltages are equal and in phase. A short time delay is provided to assure that the frequencies are essentially the same at the moment of paralleling. The basic series is designed to parallel two or more energized AC generators. The "Dead Bus" type provides paralleling of AC generators to the main bus. They permit electrical connection of an energized generator to an un-energized line (Dead Bus). If the bus is energized, connection of the generator to the bus is permitted only when both are synchronized.


#### Notes

- \*Permits paralleling of two generators only when they are "on-line" and their voltages are equal and in phase (synchronized)
- \*\*Normally used to permit paralleling of a generator to a bus when: (a) both line voltages are equal and in phase, or: (b) when the generator is "on-line" and the bus is "dead"
- \*\*\*Permits paralleling of two power lines (buses) when: (a) both line voltages are equal and in phase, or: (b) when either bus is "hot" and the other bus is "dead"

#### Output Contact Options —

- 1. Two Form A. (Add -A to Model Number)
- 2. Two Form B. (Add -B to Model Number)

Consult factory for additional models.



#### **Product Specifications**

**Sensing Voltage** — 120 V, 230 V, 277 V, 380 V, 460 V, 575 V, & 415 V

**Line Frequency** — 50-500 Hz

#### Pick-Up Adjustment —

External adjustment for field sensing of 10-30% of nominal input voltage. (Vertical voltage differential of 6 to 18 electrical degrees).

**Time Delay** — Fixed @ 60 milliseconds is provided to assure that the frequencies of both input lines are sufficiently close to permit paralleling within the preset window.

#### Output Contacts —

One set N.O., one set N.C. 5 amp resistive at 120 VAC or 28 VDC

Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.

# CONNECTIONS NC NO NC NO LINE 1 LINE 2 FORM B FORM A CONTACTS (GENERATOR) (BUS) CONTACTS CONTACTS

#### A. 3 Phase, 4 Wire System

Connect phase "A" of LINE 1 to terminal 1 Connect phase "A" of LINE 2 to terminal 3 Connect the neutrals to terminals 2 & 4

#### B. 3 Phase, 3 Wire or 1 Phase, 2 Wire System

Connect phase "A" of LINE 1 to terminal 1 Connect phase "B" of LINE 1 to terminal 2 Connect phase "A" of LINE 2 to terminal 3 Connect phase "B" of LINE 2 to terminal 4

#### **Selection Guide (Typical Applications)**

Sensing Voltage	Series 1800* Generator to Generator	Series 1800DB** Generator to Bus	Series 1800DDB*** Bus to Bus
120 Volts	1810X	1810DBX	1810DDBX
230 Volts	1820X	1820DBX	1820DDBX
380 Volts	1830X	1830DBX	1830DDBX
460 Volts	1840X	1840DBX	1840DDBX
575 Volts	1850X	1850DBX	1850DDBX
415 Volts	1860X	1860DBX	1860DDBX
277 Volts	1870X	1870DBX	1870DDBX

		Condition		Series Conf	1800 tacts	Series 1800DB Contacts		Series 1800DDB Contacts		
		Energized	Not Energized	Synch.	N.C.	N.O.	N.C.	N.O.	N.C.	N.O.
	Line 1	Χ			Onen	Class	Close Open	Close	Onen	Close
- 1	Line 2	Х		Yes	Open	Close			Open	
2	Line 1	Х		No	Close	Close Open	Open Close	Open	Close	Open
2	Line 2	Х		No					Ciose	Open
3	Line 1	Χ			Closo	Close Open	Open Open (	Close	Open Close	Closo
3	Line 2		Х		Close			Ciose		Ciose
4	Line 1		Х		Close	Open Close	Class	se Open Cl	Close	Onon
4	Line 2		Х		Close		pen Close		Ciose	Close Open
5	Line 1	-	Х		Close	Onon	Close	Onon	Onon	Close
5	Line 2	Х			– Close	Close Open	Jpen Close	Open	Open	Open Close



#### **WOF & WUF Series**

#### **Product Facts**


- Function 81 O/U
- ANSI/IEEE C37.90-1978
- **■** UL File No. E58048
- CSA File No. LR61158






#### **Application**

The output contacts of frequency relays are energized when the frequency exceeds the adjustable set point. Overfrequency and underfrequency relays are available in 50, 60 and 400Hz. Combination over/ underfrequency "band pass" relays are also available. These are energized at rated frequency and de-energized during overfrequency or underfrequency conditions. Frequency Differential relays are energized above the preset frequency. The pick-up and drop-out frequency settings are independently adjustable.





Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.

#### **Product Specifications**

Nominal Voltage (±20%) — 120, 230, 380 and 460 volts

Nominal Frequencies — 50. 60 and 400 Hz.

**Trip Point** — Screwdriver adjustable. Adjustment range in accordance with ordering information.

Operating Temperature — -20°C to +65°C

**Differential** — The frequency pitch-up to drop-out differential is .5% max

**Voltage Drift** — ± .05% maximum frequency error for input voltage variation of ±10%


Time Delay — See Time versus Frequency curves


Surge Withstand Capability -In compliance with C37.90B ANSI/IEEE

set N.C.

**Contact Ratings** -


5 amp resistive at 120 VAC or 28VDC





#### **Ordering Information**

T = Adjustable



#### **Time Delay**

Standard Time Delay — A minimum, fixed inverse time delay is incorporated in all frequency relays to prevent nuisance tripping and is represented by the typical curves shown above.

Adjustable Time Delay -

If additional time delay is required, a suffix "T" must be added to the part number. This allows the minimum fixed time delay to be field-adjustable up to 20 seconds.

- 1. Remove black screws for access to the frequency and the time adjustments.
- 2. Clockwise rotation of the frequency potentiometer will raise the frequency trip point.
- 3. Clockwise rotation of the time adjustment, option "T" will increase the time for overfrequency relays and dropout time for underfrequency relays.

# Protective Relays

#### **WOUF Series, Over/Underfrequency**

#### **Product Facts**


- Function 81 O/U
- ANSI/IEEE C37.90-1978
- **■** UL File No. E58048
- CSA File No. LR61158




The output contacts of frequency relays are energized when the frequency exceeds the adjustable set point. Overfrequency and underfrequency relays are available in 50, 60 and 400Hz. Combination over/ underfrequency "band pass" relays are also available. These are energized at rated frequency and de-energized during overfrequency or underfrequency conditions. Frequency Differential relays are energized above the preset frequency. The pick-up and drop-out frequency settings are independently adjustable.

#### Operation


The relay will energize at normal frequency; The normally closed contacts will open and the normally open contacts will close. The relay will drop-out after time delay at overfrequency or underfrequency.



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.



#### **Ordering Information**



Consult factory for additional models.

blank = Per Time Curve T = Adjustable

### **Product Specifications**

Nominal Voltage (±20%) — 120, 230, 380 and 460 volts

**Nominal Frequencies** — 50, 60 and 400 Hz.

**Trip Point** — Screwdriver adjustable. Adjustment range in accordance with ordering information.

Operating Temperature —  $-40^{\circ}\text{C}$  to  $+65^{\circ}\text{C}$ 

**Differential** — The frequency pick-up to drop-out differential is .5% max

**Voltage Drift** —  $\pm$  0.05% maximum frequency error for input voltage variation of  $\pm$ 10%

**Time Delay** — See Time versus Frequency curves

Surge Withstand Capability — In compliance with C37-90B ANSI/IEEE

**Output Contacts** — One set N.O., one set N.C.

Contact Ratings —

5 amp resistive at 120 VAC or 28 VDC

#### Notes:


- Remove black screws for access to the frequency and the time adjustments.
- Clockwise rotation of the frequency potentiometer will raise the frequency trip point.
- Clockwise rotation of the time adjustment, option "T" will increase the drop-out time delay.

#### Time Delay

Standard Time Delay — A minimum, fixed inverse time delay is incorporated in all frequency relays to prevent nuisance tripping and is represented by the typical curves shown below.

#### Adjustable Time Delay -

If additional time delay is required, a suffix "T" must be added to the part number. This allows the minimum fixed time delay to be field-adjustable up to 20 seconds.





#### **20-000 Series**

#### **Product Facts**


■ Function 81 0



The output contacts of frequency relays are energized when the frequency exceeds the adjustable set point. Overfrequency and underfrequency relays are available in 50, 60 and 400Hz. Combination over/ underfrequency "band pass" relays are also available. These are energized at rated frequency and de-energized during overfrequency or underfrequency conditions. Frequency Differential relays are energized between the preset frequencies. The pick-up and drop-out frequency settings are independently adjustable.

#### Operation

The normally open contacts close, and the normally closed contacts open, at all frequencies above the set point. The contacts in the connection diagram, are shown in the de-energized position (below the trip set point).



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.

# Product Specifications Input Voltage (±10%) —

120 VAC, Single Phase

Frequencies Range (adjustable) — See Ordering Information

**Differential** — Frequency pick-up to drop-out differential is 1% max

**Temperature Range** — -40°C to +85°C

**Temperature Drift** — ± 1% frequency error over temperature range

**Voltage Error** —  $\pm$  1% for input voltage of 120 VAC  $\pm$  10%


**Contact Ratings** — 5 amp resistive at 120 VAC or 28 VDC

Output Contacts —


One set N.O., one set N.C.

#### Notes:

Remove screw for access to trip adjustment.



#### **Ordering Information**





#### **25-000 Series**


#### **Product Facts**

- Function 81 O/U
- ANSI/IEEE C37.90-1978


The output contacts of frequency relays are energized when the frequency exceeds the adjustable set point. Overfrequency and underfrequency relays are available in 50, 60 and 400Hz. Combination over/ underfrequency "band pass" relays are also available. These are energized at rated frequency and de-energized during overfrequency or underfrequency conditions. Frequency Differential relays are energized above the preset frequency. The pick-up and drop-out frequency settings are independently adjustable.

#### Operation

The normally open contacts close, and the normally closed contacts open, at nominal frequency. The contacts are de-energize at underfrequency, overfrequency or no input voltage.



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.



#### **Product Specifications**

Input Voltage (±10%) — 120 VAC Frequency Range (adjustable) — See Ordering Information

**Trip Points** — Screwdriver adjustable Temperature Range —

-20°C to +85°C **Temperature Drift** — ± 1% frequency error over temperature range

**Voltage Drift** — ± 1% frequency error input voltage variation of ± 10%

**Contact Ratings** — 5 Amp resistive at 120 VAC or 28VDC


Output Contacts -

One set N.O., One set N.C.

- 1. The contacts are shown in the de-energized position.
- 2. Remove screws for access to the underfrequency and overfrequency trip adjustments.

  3. Clockwise rotation of the
- adjustment potentiometer will raise the frequency trip points.

#### **Ordering Information**






### 20-050-19 Series (Voltage/Frequency)

#### **Product Facts**

- Function 27/81
- ANSI/IEEE C37.90-1978
- **■** UL file No. E58048
- CSA file No. LR61158



The output contacts of frequency relays are energized when the frequency exceeds the adjustable set point. Overfrequency and underfrequency relays are available in 50, 60, and 400Hz. Combination over/ underfrequency "band pass" relays are also available. These are energized at rated frequency and de-energized during overfrequency or underfrequency conditions. Frequency Differential relays are energized above the preset frequency. The pick-up and drop-out frequency settings are independently adjustable.



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.

# Product Specifications Nominal Voltage (±20%) — 120 VAC, Single Phase

Nominal Frequency — 60 Hz.

**Voltage Adjustment Range (PU)** — 85 to 120 VAC

Frequency Adjustment Range (PU) — 45 to 60 Hz


Output Contacts —

One set N.O., one set N.C.

**Contact Ratings** — 5 amp resistive at 120 VAC or 28 VDC

#### Notes:

- Remove black screws for access to the voltage and frequency and the time adjustments.
- Clockwise rotation of the voltage adjustment potentiometer will raise the voltage trip point.
- Clockwise rotation of the frequency adjustment will raise the frequency time point.




#### **Ordering Information**

P = Surge Suppression

Sample Part Number ▶	20-050-19X
Type:	
Mounting Options ————————————————————————————————————	
Options:	











**Ground Fault Detectors** are used to sense leakage current to ground in power transformers and generators. They are available for both AC and DC systems. Some generator systems provide auxiliary power outlets for small equipment. TE Connectivity GFD's eliminate personnel risk of accessing these outlets if a ground fault exists. Diesel locomotives and railroad line signal boxes also use GFD's for operational control purposes. The GFD monitors both positive and negative grounds for fault currents and can trigger either notification or system shutdown if these are detected. GFD's are available for both grounded and ungrounded systems.

#### Operation

When the resistance between any phase to ground falls below the set point the relay will energize; The normally closed contacts will open, the normally open contacts will close.



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.



#### **Ordering Information**

Sample Part Number	
--------------------	--

Туре:	Volts L-L	Trip Point Adj. Phase to Ground
115-120AC	115	11-55KΩ
120-120AC	120	12-60K $\Omega$
200-120AC	200	$20$ -100Κ $\Omega$
208-120AC	208	21-105K $\Omega$
220-120AC	220	22-110K $\Omega$
230-120AC	230	23-115KΩ
240-120AC	240	23-115KΩ
380-120AC	380	$38-190$ K $\Omega$
400-120AC	400	$40-200$ Κ $\Omega$
416-120AC	416	42-210KΩ
440-120AC	440	44-220KΩ
460-120AC	460	46-230KΩ
480-120AC	480	48-240KΩ
525-120AC	525	52-260KΩ
575-120AC	575	57-285K $\Omega$
600-120AC	600	60-300Κ $Ω$

WGD-

Sensing Voltage (±10%) — 3 phase, 3-wire. See Ordering Information.

Control Voltage — 120 Volts AC

Contacts Trip Points (sensitivity) — Screwdriver adjustable. See Ordering Information.

**Pick-up Time Delay** — 1.5 seconds approximately

**Contact Ratings** — 5 amp resistive at 120 VAC or 28 VDC

**Operating Temperature** — -40°C to +65°C

#### Temperature Effects -

± 1% over temperature range

#### Power Consumption -

Sensing: —2 mA/Phase Approx., Control — 2VA at 120VAC

#### Surge Withstand Capability —

In accordance with the requirements of ANSI/IEEE

#### Notes:

- Remove screw for access to the pick-up adjustment potentiometer.
- Clockwise rotation of the adjustment potentiometer will raise the relay sensitivity.


#### WC1G Series — Grounded

Ground Fault Detectors are designed to provide very sensitive Ground-Current protection for motor, equipment and personnel from damage or electrical shock. In a ground system, the leakage current is monitored through a toroidal or doughnut current transformer placed around the supply conductors to a motor, transformer, equipment or outlets. Since the sums of the current in a system add to zero, the relay is responsive only to ground-fault current.

#### Operation

The output contacts are shown in de-energized position. They will change state when these conditions are met:

- 1. Control voltage is applied.
- 2. Leakage current exceed the trip setting.



Note: Dimensions in inches. Multiply values by 25.4 for dimensions in mm.

#### **Product Specifications**

**CT Window Diameter** — 1.7 inches (std) or can be specified by customer

**Leakage Current Range** — 10 to 60 mA

**Control Voltage** — See Ordering Information


**Output Contacts** — One set N.C., one set N.O.

**Operating Temperature** — 40°C to +65°C


**Contact Ratings** — 10 amp resistive at 250 Vac, 8 amp. resistive @ 30 Vdc

#### Notes:

- Remove screw for access to the pick-up adjustment potentiometer.
- Clockwise rotation of the adjustment potentiometer will raise the relay sensitivity.



#### **Ordering Information**



# **Additional Relays**

OVERVOLTAGE RELAYS		I 30/60VAC. 400V	Max. Contin., 120V 60Hz Ctrl.
	IGLE PHASE, 50-400 HZ, SPECIALS	300-52X	208VAC, 208-291V, 24VDC Ctrl., 1 N.O.
300X	120VAC		Contact
300HX	120VAC, Similar to 300X, with 125VDC 3A	300-53X	200-480VAC, 200-240V Range
0001170	Contacts	300DC-1X	28VDC, Set at 30V, Curve 1 MIL-STD-704
300S-1X	440VAC, 370-480V Range, Navy High Shock		,
300-2X	120VAC, Set at 132V, .010 Sec.Time Delay		AC, SINGLE PHASE, 400 HZ
300S-2X	120VAC, Navy High Shock	302X	120VAC
300-3X	190VAC, 180-280V Range	302-SX	120VAC, A.E.I Special
300-4X	190VAC, P.U. 264V, D.O. 261V	302-1X	120VAC, 0.3 Sec. T.D.
300-5X	240VAC, 230-360V Range	302-2X	120VAC, 125-175V Range
300-5KX	240VAC, Similar to 300-5X, except 1-10KHz	302-3X	120VAC, 125-150V Range with T.D.
300-6X	230VAC, 230-300V Range	302-4X	120VAC, 125-150V Range, 0.3 Sec. T.D.
300-7X	450VAC, 375-475V Range		
300-8X	120VAC, P.U. 130V, D.O. 125V	AC,	THREE PHASE, 50-400 HZ, SPECIALS
300-9X	120VAC, P.U. 132V, D.O. 126V	301X	120/208VAC4W
300-10X	120VAC, 99-132V Range	301-SX	120/208VAC, 4W, Similar to WOV-3-208 with
300-10HX	120VAC, Sim. to 300-10X, 125VDC 3A		hi-shock
	Contacts	301-HX	120/208VAC, 4W, 125VDC 3A Contacts
300-11X	120VAC, 0.5 Sec. Time Delay	301-1X	240VAC, 4W, 240-330V Range
300-12X	480VAC,480-600V Range	301-2X	220/380VAC, 4W
300-13X	120VAC, 2 N.O. Contacts	301-3X	254/440VAC, 4W, 440-605V Range
300-14X	95VAC, 95-120V Range	301-3HX	277/480VAC, 4W, 125VDC 3A Contacts
300-17X	120VAC, Similar to 300X with Spike	301-4X	127/220VAC, 4W, 220-275V Range
	Suppression	301-4HX	120/208VAC, 4W, 125VDC 3A Contacts
300-18X	120VAC, Differential, 2V Max.	301-5X	380VAC, 4W, 370-460V Range
300-20X	10VAC, 8-12V Range, 120V Transient,	301-6X	380VAC, 4W, 375-528V Range
	120VAC Ctrl.	301-7X	120/208VAC, 4W, 0.022 Sec. T.D.
300-21X	120VAC, 1.5-2.0 Sec. Time Delay	301-8X	120VAC. 3W, 120-150VAC
300-24X	277VAC, 140-320VAC Range	301-9X	240VAC, 3W, 240-300V Range
300-25X	24VAC, 24-30VAC Range	301-11X	120/208VAC, Similar to 301-7X
300-26X	120VAC, 90-150V Range	301-12X	440VAC, 3W
300-27X	120VAC, 105-135VAC Range	301-13SX	120/208VAC, 4W, Hi-Shock, T.D., Solar
300-28X	10VAC, 8-12VAC, 220VAC Transient,	301-15X	120/208VAC, 4W, 140-180V Range
	120VAC Ctrl.	301-16X	254/440VAC, 4W, Sim to 301-3, but 3 XFMS 120VAC, 3W, Sim to 301-13SX except 120V
300-29X	120VAC, 150-180V Range	301-17SX 301-18X	277/480VAC,4W,3 independent adjustments
300-30X	120VAC, 375V Max., 24VDC Control	301-18X	94VAC, 3W, Similar to 301-17SX
300-32X	120VAC, 135-180V Range, 1.5 Sec. Time	301-20SX	86/150VAC, 4W, 90-120V Range, T.D., Solar
200 22V	Delay	301-203X	460VAC, 3W, 125VDC Contacts
300-33X	115/230VAC, DPDT Contacts 230VAC 1A 100VAC, 1.5-2.0 Sec. T.D., 100-120V Range	301-22X	277/480VAC, 4W, 323-425V Range (L-N)
300-34X 300-35X	480VAC, 1.5-2.0 Sec. T.D., 100-120V Range	301-23X	380VAC, 3 or 4W, 0.022 Sec. T.D.
300-35X 300-36X	138VAC, 138-172V Range	301-25X	120/208V, 4W, 2-3 Sec. T.D.
300-30X 300-37X	350VAC, 350-450V Range, 2.0 Sec. T.D., Supp.	301-26X	416VAC, 3 or 4W, 415-520V Range
300-38X	120VAC, 99-132V Range, 125VDC 1A	301-27X	277/480VAC, 4W, 2-3 Sec. T.D.
000 00%	Contacts	301-28X	20.8VAC, 3W, 20-25V Range
300-39X	120VAC, 120-150V Range, 0.3-3.0 Adj. T.D.	301-29X	480VAC, 3 or 4W, Sim. to 301-3X with
300-40X	230VAC, 220-300V Range, 2.0 Sec. T.D.		spike supp.
300-41X	120VAC, 120-165V Range, 1.5 Sec. T.D., Supp.	301-30SX	100VAC, 3W, 100-125V Range, hi-shock
300-42X	120VAC, Similar to 300-39X, but 2 N.O.	301-31X	208-240, 3W, 200-280V Range, 45-65 Hz.
	Contacts	301-32X	400VAC, 3W, 400-500V Range
300-43X	120/240VAC, 140-180V Range, Phase	301-34X	208VAC, 3W, Set 240V, Withstand 600V contin.
	Protection	301-35X	120VAC, 3W, 3-5 Sec. T.D.
300-44X	277VAC, 277-350V Range	301-37X	120VAC, 3W, Sim. to 301-8X with
300-45X	30/60VAC, 277V Continuous, 115VAC Control		spike suppression
300-46X	67VAC, 67-120V Range	301-39X	138/240VAC, 3 or 4W, 2 Sec. T.D.
300-47X	360VAC, 10-64V Range, 0.75-7.5 Sec. T.D.	301-40X	120/208VAC, 4W, Highest of 3, Solar
300-48X	10VAC, 8-21V, 220VAC Transient, 125VDC Ctrl.	301-41SX	450VAC, 3W, Navy Hi-Shock,
300-49X	120VAC, Similar to WOV-1-120,		75VDC 3A Contacts
	but 0.2 Sec. T.D.	301-42X	120VAC, 3W, Highest of 3, 120-150V Range
300-50X	120/240VAC, Highest of 2, 0.5-10 Sec. T.D.	301-45X	120/208VAC, 4W, Highest of 3, Adj. T.D.
	300-51X	301-46X	104VAC, 3W, Similar to WOV-3-104
		l	



301-47X	69/120VAC, 4W, 69-90V Range, 120V (L-N)	360DC-1X	405VDC, 400-470V Range, Spike
	Contin.		Suppression
301-48X	380VAC, 3 or 4W, 380-500V Range	360DC-2X	475VDC, 475-550V Range
301-49X	250VAC, Withstand 520VAC Continuous	360DC-3X	550VDC, 550-600V Range
301-50X	180VAC, 3W, Similar to WOV-3-180	360DC-4X	350VDC, 350-440V Range, Bi-Directional
301-51X	120VAC, 3W, Supp, 10CFR Class1E (Nuclear)	360DC-4HX	350VDC, 350-440V Range, Bi-Directional
301-52X	95VAC, 3W, 95-120V (L-L) Range	370DCX	620VDC, 600-670V Range
301-53X	115/200VAC, Similar to WOV-3-200,	370DC-2X	550VDC, 550-650V Range
	1.0 Sec T.D.	370DC-1X	610VDC, 600-800V Range, 120VAC Control
		370DC-3X	610VDC, 800-1000VDC Range
	AC, THREE PHASE, 400 HZ	370DC-5X	960VDC, 900-1000VDC Range
303X	120/208VAC, 4W		g-
303-1X	115/200VAC, 4W, Highest of 3, T.D.,	AC. SI	NGLE PHASE, 50/60 HZ, SPECIALS
	MIL-E-7894	400X	120VAC
303-1SX	115/200VAC, 3W, High Shock	400HX	120VAC, Sim. to 400X with
303-2X	120/208VAC, 4W, High of 3, T.D., MIL-E-7894		125VDC 3A Contacts
303-3X	120/208VAC, Highest of 3, T.D.	400SX	120VAC, Hi-Shock, 10A Contacts
303-4X	120VAC, 3W, 120-160V Range	400-1X	120VAC, 55-72V Range
303-8X	254/440VAC, 4W	400-1HX	120VAC, Sim. to 400-1X,
303-9X	240/416VAC, 4W	100 11.01	125VDC 3A Contacts
303-10X	120/208VAC, 4W, 168V P.U., Kato	400-S-1	450VAC, 240-350V Range, Hi-Shock, T.D.
303-12X	120/208VAC, 4W, Fast Operating	400-2X	120VAC, 0.017 Sec. T.D.
303-13X	120/208VAC, 4W, 0 deg. C to 90 deg. C	400-S-2	440VAC, 280-420V Range, Hi-Shock, T.D.
303-15X	120/208VAC, Sim. to 303-13X with	400-3X	120VAC, 4.8 Sec. T.D., 80-115V Range
000 107	Latching Circuit	400-S-3	440VAC, 280-420V Range, Hi-Shock, T.D.
303-16X	120/208VAC, 303X with conformal coating	400-4X	240VAC, 170-240V Range
000 TOX	120/200VAO, 000X With Comormal Coating	400-S-4	440VAC, Sim. to 400-2SX, 2-3 Sec. T.D.,
	DC	+00-0-4	D.O. 160V
310DCX	28VDC, 28-36V Range	400-5X	450VAC, 320-450V Range
310DC-HX	28VDC, 28-36V Range, 125VDC 2A Contacts	400-5SX	450VAC, 70-100% Range, Hi-Shock,
310DC-SX	28VDC, 28-36V Range, 2A Contacts,	1 400 30%	10A Contacts
31000-37	High Shock	400-6X	120VAC, 90-123V Range
310DC-2X	28VDC, 28-36V Range, T.D., MIL-E-7894 Fig. 2	400-0X 400-7X	277VAC, 190-290V Range
310DC-2X	28VDC, 35-46V Range, T.D., MIL-E-7894	400-7X 400-8X	120VAC, 55-80V Range
310DC-3X	28VDC, Set 31V, 2 Sec; 40V, 0.2 Sec.	400-8X 400-8SX	120VAC, 55-86V Hange 120VAC, 50-70% Range, Hi-Shock
311DCX	12VDC, 12-16V Range	400-9X	480VAC, 320-480V Range
311DC-1X	12VDC, 12-16V Range, 1V Differential	400-3X 400-10X	120VAC, 1.0 Sec. T.D. with power loss
320DCX	60VDC, 60-85V Range	400-10X 400-11X	480VAC, 1.0 Sec. T.D., 320-480V Range
320DC-HX	60VDC, 60-85V Range, 125VDC 2A Contacts	400-11X 400-12X	120VAC, Similar to 400-10X except 1 N.O.
320DC-1X	35-60VDC, Spike Suppression	100 127	& 1 N.C.
320DC-1X 320DC-2X	55-80VDC, Spike Suppression	400-13X	120VAC, 14-30V Range
320DC-4X	48VDC, 48-70V Range	400-14X	67VAC, 30-67V Range, Suppression
320DC-5X	20-70VDC, 120VAC Control	400-16X	120VAC, 0.6 Sec. T.D., 50-420 Hz
330DCX	120VDC, 120-160V Range	400-10X 400-17X	120VAC, Similar to 400-2 with seismic
330DC-HX	120VDC, 120-160V Range,	400-17X 400-19X	120VAC, 125VDC 2A Contacts, Suppression
000DO 11X	125VDC 2A Contacts	400-20X	208VAC, 24-48V Range
330DC-1X	120VDC, 110-150V Range	400-20X 400-21X	120VAC, 94.8-102V Range, 6 +/-2 Sec. T.D.
330DC-1X	120VDC, 110-130V Hange	400-21X 400-23X	480VAC, 320-480V Range, 2.0 Sec. T.D.
340DCX	240VDC, 240-300V Range	400-23X 400-24X	120VAC, 2.0 Sec. T.D.
340DCA 340DC-HX	240VDC, 240-300V Hange 240VDC, 240-300V Range,	400-24X 400-25X	240/480VAC, 3-30Sec. T.D., Latching
340DO-11X	125VDC 2A Contacts	400-25X 400-26X	480VAC, 160-200V Range
340DC-1SX	200VDC, 240-300V Range, Non-Mag.,	400-20X 400-27X	460VAC, 250-350V Range, 0.3 Sec. T.D.,
340DC-13X		400-277	• • • • • • • • • • • • • • • • • • • •
350DCX	High Shock 305VDC, 280-400V Range	400-28X	Set to 76V 0.5VAC, 0.5-1.0V Range, 115VAC Control
	305VDC, 280-400V Range,	400-28X 400-29X	120VAC, 0.15 Sec. T.D., 10A Contacts
350DC-HX	,	400-29X 400-30X	24VAC, 18-24VAC Adjustable
350DC 16V	125VDC 2A Contacts	l	120VAC, 105-135V Range
350DC-1SX	250VDC, 280-400V Range, Hi-Shock,	400-31X	·
36000	120VAC Control	400-32X	120VAC, 1 Ph. T.D. 0-10 Sec.
360DCX	405VDC, 400-470V Range	400-33X	480VAC, 1 Ph. T.D., 0-10Sec.
360DC-HX	405VDC, 400-470V Range,	400-34X	120VAC, 55-72V Range, 2 N.O. Contacts
	125VDC 2A Contacts	400-35X	120VAC, Similar to 400X, but 2 N.C. Contacts
		I	



400-36X	120VAC, Similar to 400-24X, 1 N.O.,	D100DC-35X	30-40VDC Range, Plug-in,
	1 N.C. Contact		NSN 5945-00-650-8613
400-37X	120VAC, Similar to 400X, with Suppression	D100DC-36X	48VDC, Adjustable 38-48VDC
400-38X	120VAC, 85-120V, 1-20 Sec. T.D.,	D100DC-37X	75VDC, 50-80VDC Range, 0.5A,
	Instant, at 50V		74VDC Contacts
400-38PX	120VAC, Similar to 400-38X with Spike	D100DC-38X	270VDC, 190-270VDC Range, Similar to
	Protection		D100DC-23
400-39X	120VAC, 1.0 Sec. T.D., Transient Protection	D100DC-39X	28VDC, Adjustable 15-30VDC
400-40X	120VAC, 0.083 Sec. T.D.	D100DC-40X	28VDC, Approx. 2.0 Sec T.D.
400-41X	120VAC, Similar to 400X with 2 N.O. Contacts	2.0020 .000	20120, Approxi 210 000 1121
400-43X	240VAC, 120-240V Range	AC. TH	REE PHASE, 50/60 HZ, SPECIALS
400-44X	208VAC, 150-210V Range	401X	120/208VAC, 4W, 85-120V Range
400-47X	380VAC, Fast Operating, 220VAC 5A Contacts	401-HX	120/208VAC, 4W, 125VDC 3A Contacts
400-49X	120VAC, 55-80V Range, 125VDC Contacts	401-1X	240VAC, 4W, 182-244V Range (L-L)
400-50X	480VAC, 320-480V Range,	401-2X	480VAC, 4W, 360-485V Range (L-L)
400-307	125VDC 1A Contacts	401-2X 401-2HX	480VAC, 3 or 4W, 125VDC 3A Contacts
400 51V	120VAC, Sim. to 400-38X with 1-30 Sec. T.D.	401-3X	220VAC, 3W, 160-200V Range (L-L)
400-51X	120VAC, 5iiii. to 400-38X with 1-30 Sec. 1.D.	401-4X	
400-52X		1	380VAC, 4W, 150-220V Range (L-N)
400-53SX	450VAC, 110-300V Range, 120V Control	401-5X	120VAC, 4W, 90-120V Range (L-L)
400-54X	120VAC, Sim. to 400-13X with 1.0 Sec. T.D.	401-6X	120VAC, 3W, 85-120V Range (L-L)
400-55X	208VAC, 125-208V, 24VDC Ctrl.,	401-7X	480VAC, 4W, 332-407V Range (L-L)
	1 N.O. Contact	401-8X	100VAC, 3W, 70-100V Range (L-L)
400-56X	208VAC, 24-48V Range, 2 N.O. Contacts	401-9X	120/208VAC, 4W, Fast Operating
400-57X	120VAC, 25 Hz, 84-120V,	401-9HX	120/208VAC, 4W, 0.02S T.D., 125VDC 3A
	125VDC 3A Contacts		Cont.
400-58X	277VAC, 194-277V Range, 0.020 Sec. T.D.	401-10X	480VAC, 3W, 360-485V Range
400-59X	139VAC, 97-159V Range	401-10HX	480VAC, 3W, 125VDC 3A Contacts
400-60X	240VAC, 84-120V Range	401-11X	240VAC, 3W, 180-240V Range
400-6IPX	120VAC, Similar to WUV-1-120P	401-11HX	240VAC, 3W, 125VDC 3A Contacts
400-62X	120VAC,30-42V Range, 125VDC Contacts	401-12X	120/208VAC, 4W, 1.0 Sec. T.D.
400-63X	120VAC,30-42V Range, 120VAC Contacts	401-12HX	120/208VAC, 4W, 1.0 Sec. T.D.,
			125VDC 3A Contacts
	AC, SINGLE PHASE, 400 HZ	401-13X	380VAC, 3W, 1.0 Sec. T.D.
402X	120VAC	401-14X	480VAC, 4W, 0.5 Sec. T.D.
402-SX	120VAC, Hi-Shock, NSN 5945-00-258-6662	401-15X	120/208VAC, Sim. to 401X with 6" leads
402-1X	240VAC, 170-240V Range		and socket
402-1SX	240VAC, High Shock	401-16X	380VAC, Sim. to 401-4X with 6" leads
402-2X	120VAC, 90-120V Range, 0.3 Sec. T.D.,		and socket
	Set to 96V	401-17SX	120/208VAC, 4W, 10 Sec. T.D., Solar
402-3X	120VAC, Similar to 402-2X with 10A Contact	401-18X	480VAC, 3W, 2.0 Sec. T.D., 90% P.U., 70%
402-4X	120VAC, Similar to 402-2X with 0.15 Sec. T.D.		D.O.
		401-19X	120/208VAC, Sim. to 401X with 2KV Diodes,
AC & DC, S	SINGLE PHASE, CLOSE DIFFERENTIAL		Supp.
D100-10X	120VAC, 50-500Hz, -40 to +75 deg. C	401-20X	69/120VAC, 4W, 25-35V Range, 4KV Diodes,
D100-13X	450VAC, D.O. 60-100%, P.U. 66-100%		Supp.
D100-15X	120VAC, 50-500Hz, 125VDC, 1 Amp Contacts	401-21X	120/208VAC, 4W, 85-120V Range,
D100-16X	208VAC, 50-500Hz, 125VDC, 1 Amp Contacts		0.05 Sec. T.D.
D100-17X	120VAC, 50-500Hz, 450VAC Input Capacitor,	401-22X	480VAC, 3 or 4W, 5.0 Sec. T.D.
	GE	401-23X	120VAC, 3W, 0.05 Sec. T.D.
D100-18X	120VAC, Hi-Shock, D.O. 72-84,	401-24X	120VAC, 3W, 2 N.C. Contacts
	P.U. 102-114 Range	401-25SX	120VAC, 3W, 10Sec. T.D., Solar
D100-19X	120VAC, Hi-Shock, D.O. 80-120,	401-26X	67/115VAC, 4W, Suppression
2.00 .07.	P.U. 80-120 Range	401-28X	120/208VAC, 4W, 60-100V Range, Set at 90V
D100-20X	150VAC, 105-150V Range	401-29X	120VAC, 4W, 90-120V Range, 1.0 Sec. T.D.
D100 20X	60 VDC, 48-55VDC Range, 1.5 Sec. T.D.	401-29HX	69/120VAC, 4W, 1.0 Sec. T.D.,
D100DCX	120VDC, 80-120VDC Adjust, 0.4V Differential	101 2011/	125VDC 3A Contacts
D100DC-15X	60VDC, 40-60VDC Adjust, 0.2V Differential	401-30X	480VAC, 3W, 360-480V Range, 2.0 Sec. T.D.
D100DC-16X	40VDC, 20-40VDC Adjust, 0.2V Differential		125VDC 3A Contacts
D100DC-16X	140VDC, 100-140VDC, 0.4V Differential	401-31SX	94VAC, 3W, 10 Sec. T.D., Solar
D100DC-19X D100DC-22HX	120VDC, 80-120VDC Range,	401-313X 401-33X	480VAC, 4W, 139-231V Range (L-N)
υ ΙΟΟΟΟ <del>-</del> ΖΖΠΛ	120VDC, 80-120VDC Hange,	401-34X	120/208VAC, 4W, 139-231V Hange (L-N)
D100DC-23X	260VDC, 195-260VDC Range	401-34X 401-35X	208VAC, 3W, 0.008 Sec. T.D., 28VDC Control
D 100DO-20A	200 v DO, 100-200 v DO Hallye	401-36X	480VAC, 3W, 0.008 Sec. T.D., 28VDC Control
		1 701-00/	700 VAO, 0VV, 0.000 086. 1.D., 20 VDC COIIIIOI



401-37X	120VAC, 3W, 5.0 Sec. T.D.	403-7SX	480VAC, 3W, T.D., Hi-Shock
401-38X	380VAC, 3W, 0.05 Sec. T.D.	403-10X	120/208VAC, 4W, 10A Contacts
401-39X	480VAC, 4W, 250-550V Range (L-L)	403-11X	480VAC, 4W, 60% to 80% Range
	, ,	l	, ,
401-41X	240/416VAC, 4W, 312-416V Range (L-L)	403-13X	120/208VAC, 4W, 0C to +90C
401-41HX	230/400VAC, 4W, 125VDC 3A Contacts	403-14X	575VAC, 3W, 400-500V Range
401-42X	120/208VAC, 4W, 5.0 Sec. T.D.	403-15X	120/208VAC, Sim. to 403-13X with
401-43SX	480VAC, Sim. to 403-7SX except 60 Hz.		Latching Circuit
401-44X	139/240VAC, 4W, 2.0 Sec. T.D.	403-16X	120/208VAC, Sim. to 403X with Conformal
		400-107	•
401-45X	120VAC, 3W, 85-120V Range (L-L),		Coating
	125VDC Contacts		
401-46X	480VAC, Similar to 401-2X with Suppression	AC TH	REE PHASE, CLOSE DIFFERENTIAL
401-47X	380VAC, 3W, 2.0 Sec. T.D.	D101-3X	Similar to D101X, -55C to +85C
401-48X	208VAC, 3W, 145-208V Range	D101-5X	120VAC, 50-500Hz, Military
		1	
401-49X	20.8VAC, 3W, 15.5-20.8V Range	D101-9X	120VAC, 50-500Hz, 0.5 Sec. T.D.
401-50X	120VAC, 3W, 0-10 Sec. T.D.	D101-11X	120VAC, 50-500Hz, 120-150VAC Adjust,
401-51SX	90/156 VAC, 4W, Similar to 401-17SX		N.C. Cont.
401-52X	480VAC, 3W, Sim. to 401-10X	D101-12X	120VAC, Similar to D101X but
401-53X	120/208VAC, 4W, 1 N.O., 1 N.C.		60-120VAC Range
		D101 10V	S .
401-54X	400VAC, 3W, 300-400V Range	D101-13X	120VAC, Similar to D101X but
401-55X	600VAC, 3W, 480-600V Range		3 N.C. Contacts
401-58X	120/208VAC, Sim. to 401X except	D101-14X	208VAC, Similar to D101-6X but
	2 N.C. Contacts		3 N.C. Contacts
401-59X	220-380VAC, Dual Voltage 220V or 380V	D101-15X	480VAC, 50-500Hz, Spike Suppressors
401-60X	480VAC, 1 N.O., 1 N.C. Contact, 2-3 Sec. T.D.	D101-16X	480VAC, Similar to D101-7X but
		DIGITION	
401-61X	120VAC, 3W, 85-120V Range (L-L),		3 N.C. Contacts
	1.0 Sec. T.D.	D101-17X	120VAC, 0.4A 120VDC Contact,
401-62X	380VAC, 3W, 220VAC 5A Contacts		-20 to +85 deg C
401-63X	120VAC, 3W, Sim. to 401-6X with Suppression	D101-18X	120VAC, Similar to D101X but
401-67X	120/208VAC, 4W, 1.0 Sec. T.D., -55F to +150F		Spike Suppression
		D101 10V	
401-68X	120VAC, 3W, 85-120V Range, 2-3 Sec. T.D.	D101-19X	208VAC, Similar to D101-6X but
401-69X	120/208VAC, 4W, 85-120V Range, Lowest of 3		Spike Suppression
401-70X	133/230VAC, 4W, 99-133V Range, Lowest of 3	D101-20X	240VAC, Similar to D101-4X but
401-71X	220/380VAC, 4W, 154-220V Range, Lowest of 3		Spike Suppression
401-72X	266/460VAC, 4W, 186-266V Range, Lowest of 3	D101-21X	380VAC, Similar to D101-10X but
401-74X	66/115VAC, 4W, 65-75% Adj., Supp.,	5101 21%	Spike Suppression
401-747		D404 04V	
	125VDC Cont.	D101-24X	240VAC, 3 N.C. Contacts
401-75X	115/200VAC, 3W, 65-75% Adj., Suppression	D101-25X	208VAC, 3 N.C. Contacts, Spike Suppression
401-76SX	450VAC, 3W, 382-450V, 0.3-0.5S T.D.,	D101-26X	277VAC, 50-500Hz, 66-100% Adjustable
	Hi-Shock	D101-27X	120VAC, Sim. to D101X, withstand
401-77X	120/208VAC, 4W, 0.5-10 Sec. T.D., Lowest of 3		208V continuous
		D101 00V	
401-79X	480VAC, 3W, 0.2-0.3 Sec. T.D., Suppression	D101-29X	415VAC, 50-500Hz
401-80X	76VAC, 3W, 53-76V Range	D101-30X	380VAC, 50-500Hz, 3 N.C. Contacts
401-81X	120/208VAC, Sim. to 401-12X with	D101-31X	525VAC, Spike Suppression
	48VDC Contacts	D101-32X	120VAC, 50-500Hz, 5 Sec T.D.
401-82X	104VAC, 3W, Similar to WUV-3-104		
401-83SX	120/208VAC, MIL-R-2033A		DC
	·	400DOV	
401-84X	180VAC, 3W, Similar to WUV-3-180	400DCX	120VDC, 85-120V Range
401-85SX	480VAC, Similar to 401-25SX except 480V	400DC-HX	120VDC, 85-120V Range,
401-86SX	380VAC, Similar to 401-25SX except 380V		125VDC 2A Contacts
401-87SX	240VAC, Similar to 401-25SX except 240V	400DC-IX	28VDC, 15-29V Range
401-90X	120/208VAC, 4W, 0.5 Sec. T.D.	400DC-2X	240VDC, 180-220V Range
	480VAC, 3W Fast Oper. 50mS., Suppression	400DC-3X	62.5VDC, 40-65V Range
401-93X	, , , , , , , , , , , , , , , , , , , ,		, 3
401-97X	69/120VAC, Lowest of 3	400DC-4X	305VDC, 200-300V Range
401-98X	480VAC, Sim. to 401TD-9HX with 2.0 Sec. T.D.	400DC-5X	5.6VDC, 4-6V Range, 120VAC Cont
		410DCX	28VDC, 16—29V Range
	AC, THREE PHASE, 400 HZ	410DC-SX	28VDC, 16-29V Range, Hi-Shock, MIL-R-57
403X	120/208VAC, 4W	410DC-1X	28VDC, 15-32V Range, 1.5V Differential
	·	1	
403-1X	115/200VAC, 4W, 35-400mS T.D.	410DC-5X	24VDC, 16-29V Range, Suppression
403-1SX	115VAC, 3W, Hi-Shock	410DCTDX	28VDC, 0.5-20 Sec. T.D.
403-2X	120VAC, 3W	411DCX	12VDC, 9-12 V Range
403-3X	120/208VAC, 4W, 1.0 Sec. T.D.	411DC-1X	15VDC, 11-15V Range
403-4X	254/440VAC, 4W	411DCTDX	12VDC, 0.5-20 Sec. T.D.
403-5X	120/208VAC, 4W, 2 N.C. Contacts	420DCX	60VDC, 40-65V Range
700 OA	120/200 VAO, TVV, 2 IV.O. OUIIIacio	1 -2000	JOVDO, TO JOV Hallye



		_	
420DC-4X	48VDC, 32-48V Range	250-12X	120VAC, Sim. to 250X, MIL-R-5757 2A
420DC-5X	48VDC, 20-48V Range	250-14XAC	67VAC, Sim. to 250-3X with removable cover
420DC-6X	70VDC, 50-70V Range	250-17X	120VAC, Sim. to 250X plus suppression
420DC-8X	32VDC, 33-40V Range (Pick-Up)	250-19X	120VAC, Sim. to 250X with 2 N.O. Contacts
420DC-9X	48VDC, Similar to 420DC-4X with 2 N.O.	250-22X	240VAC, 1-2 Sec. TD on Drop Out
	Contacts	250-23X	120VAC, Sim. to 250X but -40C to +52C
420-470 SUFFIX	SUFFIX: "A" 2 N.O. Contacts	250-27X	139VAC, Same as 250-12X except voltage
	"B" 2 N.C. Contacts	250-28X	138VAC, Same as 250-10X except voltage
430DCX	120VDC, 85-120V Range	250-29HX	120VAC, 50-400Hz., 125VDC 3A Contacts
430DC-HX	120VDC, 85-120V Range,	250-30X	480VAC
	125VDC 3A Contacts	250-31X	240VAC, Fast Trip 25mS
430DC-1X	140VDC, 105-140V Range	250-32HX	480VAC, 100Hz, 1Sec TD,
430DC-2X	140VDC, 105-140V Range, 0.5 Sec. T.D.,		120V 3ADC Contacts
	Suppression	250-33HX	480VAC, 25Hz, 1 Sex TD,
430DC-3X	120VDC, 50-80V Range		120V 3ADC Contacts
430DC-4X	120VDC, 85-120V Range, 0.5 Sec. T.D.,	250-34X	120VAC, 72-120-160V Range, Hi Shock
.0020	Set at 90V	250-35X	230VAC, Sim. to 250-22X, 3.0 Sec. TD
430DC-5X	125VDC, 90-125V Range, Spike Suppression	250-36X	120VAC, 84-120-150V Range, Hi Shock,
430DC-6X	125VDC, 105-140V Range, 3.0-5.0 Sec. T.D.	200 00%	-40C to 70C
430DC-7X	170VDC, 120-170V Range	250-37HX	120VAC, 25 Hz, 1 Sec. TD,
430DC-8X	120VDC, 85-120V Range, 2 N.C. Contacts	250-5711X	120V AG, 23 Hz, 1 Gec. 1D,
		050 200	
430DC-9X 430DC-10X	100VDC, 35-50V Range	250-38X	240VAC, Two N.O. Contacts
	120VDC, 85-120V Range, 2 N.O. Contacts	250-39X	120VAC, Similar to 250X, Range +/- 35%
440DCX	240VDC, 168-240V Range		40 ONO E BUACE 50 400UZ
440DC-HX	240VDC, 168-240V Range,	05407	AC, SINGLE PHASE, 50-400HZ
44000 414	125VDC 3A Contacts	251SX	120/208VAC, Sim. to 251X with Hi Shock
440DC-1X	280VDC, 190-260V Range	251-1X	120/208VAC, 4W, 0.50 Sec. TD
450DCX	305VDC, 230-305V Range		NSN 5895-00-139-0337
450DC-HX	305VDC, 230-305V Range,	251-4X	139/240VAC, 4W
	125VDC 3A Contacts	251-5X	120/208VAC, 4W, Two N.C. Contacts
450DC-1X	305VDC, 230-305V Range,	251-8X	120/208VAC, 4W, 1.2 Sec. TD
	2 N.C. Contacts	251-10X	110/190VAC, 4W
460DCX	405VDC, 315-415V Range	251-13X	120/208VAC, Sim. to 251X except -40C to 52C
460DC-HX	405VDC, 315-415V Range,	251-14X	120/208VAC, 4W, Withstand 220/380V
	125VDC 3A Contacts		Continuous
460DC-1X	405VDC, 300-330V Range	251-15X	120/208VAC, Sim. to 251X with Transient
460DC-3X	405VDC, 300-425V Range		Protection
460DC-4X	432VDC, 275-325V Range	251-16X	120/208VAC, 1.2 Sec. TD, Transient Protection
460DC-5X	470VDC, 300-425V Range	251-17X	120/208VAC, Similar to 251X,
470DC	560VDC, 400-500V Range		208V 7.5A Contacts
470DC-1X	585VDC, 400-500V Range	251-18X	120/208VAC, Highest/Lowest of three,
			TD Adjust 12VDC control
	DC TIME DELAY	251-19X	120/208VAC, Highest/Lowest of three,
420DCTDX	48VDC, 32-48V Range, 0.5-20 Sec. T.D.		TD Adjust 120VAC control
430DCTDX	125VDC, 83-125V Range, 0.5-20 Sec. T.D.	251-20X	120/208VAC, Highest/Lowest of three,
440DCTDX	250VDC, 166-250V Range, 0.5-20 Sec. T.D.		TD Adjust, 24VDC Control
	, , , , , , , , , , , , , , , , , , , ,	251-21X	120/208VAC, Sim. to 251X, 0.5Sec. TD
OVED/UNDEDVO	I TACE DELAVO	251-22X	115/200VAC, Sim. to 251X, 0.75Sec. TD
OVER/UNDERVO		253-HX	230VAC, 3W, 48VDC 3A Contacts
	AC, SINGLE PHASE	253-1X	230VAC, 3W, Spike Suppression
250SX	120VAC, Hi-Shock	253-1HX	230VAC, 3W, Spike Suppression,
250-1X	120VAC, 72-120V, Mil,		125VDC Contacts
	NSN 6125-00-091-0969	253-3X	230VAC, 3W, 1.0 Sec. TD
250-2X	120VAC, 1.2 Sec. Time Delay	253-5X	230VAC, 3/4W, 2 N.C. Contacts, -51C to +71C
250-3X	67VAC, UV 30-67V, OV 67-91V	253-6X	230VAC, 3W, 3.0 Sec. TD
250-4X	26VAC, 28VDC Control, Connector	254-1X	415VAC, 3W, 290-415-519V
250-5X	240VAC, Two N.C. Contacts	1	• •
250-6X	240VAC, One N.O., One N.C. Contact	254-2X	220/380VAC, 4W, 2 N.C. Contacts
250-6HX	240VAC, 120VDC, 3A Contact	254-3X	416VAC, 3/4W, 2 N.C. Contacts, -51C to 71C
250-7X	120VAC, 3 Sec. Time Delay	255-HX	460VAC, 3W, 125VDC 3A Contacts
250-8X	100VAC	255-1X	460VAC, 3/4W, Spike Suppression
250-10X	120VAC, Fast Trip, 25mS	255-2X	480VAC, 3W, High Shock
250-11X	120VAC, Set at 97V and 156V	255-3X	495VAC, 3W, 3.0 Sec. TD
		I	



255-4X	460VAC, 3W, 2 N.O. Contacts,	725TD-14X	415 V, L-L, 50Hz, Reverse Inductive
	EMD # 9333490	726TD-14X	100 V, L-L, 50Hz, Reverse Inductive
255-5X	460VAC, 3W, Sim. to 255-4X, MIL-R-5757,	727TD-14X	185 V, L-L, 50Hz, Reverse Inductive
	10A Relay		
255-6X	460VAC, 3W, EMD# 9337151	DUACE CECHENA	CE DEL AVO
255-7X	460VAC, 3W, Sim. to 255X, Fast operating,	PHASE SEQUEN	
	40mSec.		AC, THREE PHASE
255-8X	480VAC, 3W, 5.0 Sec. fixed TD, 120VAC	900-2PX	208-230VAC, Spike Suppression
	Control	900-4X	208VAC, 50/60 Hz
255-9X	480VAC, 3W, Sim. to 255-8X except +/- 10%	900-5X	120VAC, 50/60Hz
200 071	Setting	900-8X	120VAC, 60 Hz, 125VDC 2A Contacts
		900-10X	120VAC, 60 Hz, Spike Suppression
	AC, SINGLE PHASE, 50-400HZ	901-1X	440VAC, 60 Hz, 5A Contacts
256-1X	600VAC, 3W, 60Hz, 2 N.O. Contacts,	901-5X	575VAC, Porcelain Term., AZ Relay
200 170	EMD Canada	901-6X	460VAC, 60 Hz, Spike Suppression
256-2X	575VAC, 3W, GM# 6964912 Rev. A	901-SX	440VAC, 55-65HZ, HI-Shock
200 2X	37347tG, 344, alviii 3334312 1134.7t	910-1X	220/440VAC, 60 Hz, N.O. Contacts
	DC	910-2X	220/440VAC, 60 Hz, Reversed Contact
250DC-HX	24VDC, 16-24-30V Range, 48VDC 3A Contacts		Operation
250DC-1X	28VDC, MIL Shock and Vibration	910-3X	220/440VAC, 60 Hz, Porcelain Term.,
250DC-1X	26VDC, UV 20-30V, OV 26-36V		Sigma Relay
250DC-2X 250DC-3X	28VDC, 20-28-35V Range, Hi Shock,	920X	380VAC, 50 Hz
250DC-5X	-40C to 70C	920-1X	380VAC, 50 Hz, Mounting per 21-037
250DC-4X	14VDC, Commonwealth Edison	920-2X	380VAC, 50 Hz, Porcelain Terminals,
250DC-4X 250DC-5X	28VDC, Commonwealth Edison		Sigma Relay
251DC-5X	48VDC, Removable Cover	920-3X	416VAC, 50 Hz, 5A Contacts
251DC-1X 251DC-2X	35VDC, UV 23-30V, OV 40-52V	920-5X	220/380VAC, 50 Hz
251DC-2X 251DC-3X		920-6X	440VAC, 50 Hz
	30VDC, UV 21-27V, OV 30-40V 48VDC, 32-48-60V, 48VDC 3A Contacts	930X	208VAC, 400 Hz
251DC-HX		930-1X	208VAC, 400Hz, 2A at 28VDC Contacts,
251DC-4X	60VDC, 45-60-75VDC, 2N.O. 120VAC		Energized A-B-C, 5A
OFODOV	Contacts	930-3X	400VAC, 400Hz
252DCX	120VDC, 85-120-150V Range	930-4X	400VAC, 2 N.C. Contacts, -51C to +71C
252DC-1X	130VDC, 80-130/120-150V Range	931X	120VAC, 400 Hz.
252DC-1HX	125VDC, 85-125/125-160V, 48VDC 3A	932-5X	115/200VAC, 400Hz, 2A Contact, Hi-Shock
05000 01/	Contacts	932-7X	230/400VAC, 400Hz
252DC-2X	130VDC, 80-130/120-150V, Removable Cover		
253DCX	250VDC, 175-250-315VDC Range	PHASE FAILURE	DELAVO
253DC-HX	250VDC, 175-250-315VDC, 48VDC 3A	1	
	Contacts	980X	120VAC, 60 Hz, no T.D. on Starting
		981X	230VAC, 60 Hz, no T.D. on Starting
REVERSE PO	WER RELAYS	982X	460VAC, 60 Hz, no T.D. on Starting
	AC, SINGLE PHASE	983X	380VAC, 60 Hz, no T.D. on Starting
710-HX	120/220/266VAC, 125VDC 3A Control	984X	575VAC, 60 Hz, no T.D. on Starting
710-PX	120/220/266VAC, 0.2-1.0A, Spike Suppression	985X	525VAC, 60 Hz, no T.D. on Starting
710-1X	120/220/266VAC, 125VDC 1/4A Control	40000	400//40, 00 11-
710-3X	120VAC (L-N), 1 Phase, 3-5A	1980X	120VAC, 60 Hz
		1981X	230VAC, 60 Hz
	120/220/266VAC. SINGLE PHASE	1982X	460VAC, 60 Hz
	TIME DELAY	1983X	380VAC, 50 Hz
710TD-1X	0.05-0.25A, 0.5-10 Sec. T.D. with Knobs	1984X	575VAC, 60 Hz
710TD-5X	2 N.O. Contacts	1985X	525VAC, 60 Hz
710TD-7X	60Hz, Reverse Inductive	1986X	415VAC, 50 Hz
710TD-7PX	Similar to 710TD-7X with Suppression	1987X	380VAC, 60 Hz
710TD-8X	Similar to 710TDX with -55F to +150F	SUFFIX:	"-S": Time Delay (0.5 - 30 Sec.)
710TD-9X	Similar to 710TDX with Suppression	1,004,4057	"-3S": Factory Set Time Delay (0-60 Sec.)
710TD-12X	Similar to 710TDX, 125VDC 2A Contacts	1981-1SX	230VAC, Similar to 1981X except 50 Hz
710TD-14X	50Hz, Reverse Inductive	1980-2SX	120VAC, Similar to 1980X except N.C.
720TD-14X	120 V, L-L, 50Hz, Reverse Inductive		Contacts
721TD-14X	230 V, L-L, 50Hz, Reverse Inductive		
722TD-14X	380 V, L-L, 50Hz, Reverse Inductive	1	IREE PHASE, VOLTAGE SENSITIVE
723TD-14X	460 V, L-L, 50Hz, Reverse Inductive	1003X-60HZ	380VAC, Similar to 1003X except 60HZ
724TD-14X	575 V, L-L, 50Hz, Reverse Inductive	1009X	415VAC, 50 Hz
		1010X	208VAC, 50 Hz



1001X-1010X SUFF	FIX "-1": N.C. Contact (example: 1004-1X)	1100TD-9X	24VDC, 0.5-5AAC Range, 0.5-20 Sec. T.D.
	FIX "-2": -53C to +70C, 2% Drift below -20C	1100TD-10X	120VAC, Sim. to WCT1-120AC-5 w/
	FIX "-3": 400Hz, N.O. Contacts		removable cover
	FIX "-T': Spike Suppression	1100TD-11X	120VAC, Sim. to WCT1-120AC-5, 1-5 Min. T.D.
	FIX "-H": 125VDC 3A Contacts	1100TD-11X	
		11001D-12X	120VAC, Sim. to WCT1-120AC-5,
	FIX "-9" 1 N.O. & 1 N.C. Contacts		0.5-5 Sec. T.D.
	FIX "-12": Spike Supp., 125VDC 3A Contacts	OPTION	1: 0.2A to 1.0A Range
1001X-1010X SUF	FIX "-13": 1N.O + 1 N.C. 125VDC 3A Contacts		2.5: 0.5A to 2.5A Range
			5: 1.0A to 5.0A Range
OVERCURRENT F	DEL AVO		10: 2.0A to 10.0A Range
1100X	120VAC, 1-5A Range		AC, THREE PHASE, TIME DELAY
1100-1X	120VAC, 0.5-5A Range, Remote Adjust	1130TDX	120VAC, 1-5A, 0.5-20 Sec. T.D.
1100-2X	120VAC, 0.5-5A Range	1130TD-1X	24VDC, 1-5A, 0.5-20 Sec. T.D.
1100-2SX	120VAC, 0.5-5 A Range, Hi-Shock, 2A Contacts	1130TD-2X	120VAC, 1-5A, 0.5-20 Sec. T.D., Suppression
1100-9X	120VAC, 1-5A, Fast Operating	1130TD-3X	120VAC, 1-5A, 0.5-60 Sec. T.D.,
1100-11X	120VAC, 1-5A, 3% Diff., Suppression 2.5KV	113010-37	2 N.C. Contacts
1100-13X	120VAC, 1-5A, 2 N.C. Contacts	11507	
1100-14X	120VAC, 7-30A, 2 N.C. Contacts	1150X	120VAC, 4.35A, 0.5-5 Sec. T.D.
1100-15X	120VAC, 2-10A, 2 Sec. T.D.	1150-1X	120VAC, 4.26A, 0.5-5 Sec. T.D.
1100-17X	120VAC, 1-5A, 2 Sec. T.D.	1150-2X	120VAC, 3.72A, 0.5-5 Sec. T.D.
1100-18X	120VAC, 0.05-0.15A, 5A Max, 400 Hz	1150-4X	120VAC, 1-5A, (P.G.E.)
1100-19X	24VDC, 1-5A Range	1150-6X	120VAC, 1-5A, 2-3 Sec. T.D. on D.O.
1100-13X 1100-20X	120VAC, 1-5A, Suppression (15 times in-rush)	1150-8X	120VAC,Same as 1150-2X with
			2 N.O. Contacts
1100-21X	74VDC, 7-30A, 50mS T.D., Shock & Vibration	1150-10X	120VAC, 1-5A, 2 Sec. T.D.
1100-22X	120VAC, 1-5A Remote Adjust	1150-10SX	120VAC, 1-5A, 2 Sec. T.D., Hi-Shock
1100-23X	125VDC, 0.25-1.8A, 1 N.O.	1150-11X	120VAC, 2.5-5A, 400Hz, Special T.D. Curve
	125VDC 2A Contact	1150-12X	120VAC, 2.5-5A, 60Hz, Special T.D. Curve
1100-24X	32VDC, 1-5AAC Range	1150-14X	120VAC, 2.5-5A, 400Hz, T.D. Curve, Aux. N.O.
1100-25X	120VAC, 0.25-1.25A	1150-15X	24VDC, 1.2-2.2A, 60Hz, T.D. Curve, (Solar)
1100-26X	120VAC, 0.3-1.5A, Withstand 5A	l	
1100-27X	220VAC, 1-5A Range, 220VAC Contacts	1150-16X	24VDC, 2.5-4.3A, 60Hz, T.D. Curve, (Solar)
1100-32X	120VAC, Undercurrent 1-10A Adj,		VOLTAGE REGERALNIT
	0.2-5 Sec. T.D.		VOLTAGE RESTRAINT
1100-35X	120VAC, 0.1-0.4A Range	1200X	120VAC, 1-5A, 24VDC Control
1100-36X	74VDC, 4-20A, 50mS T.D., Shock & Vibration	1200-1X	120VAC, 1-5A, 12VDC Control
1100-37X	24VDC, 0.1-0.3A Range	1200-4X	120/208VAC, 1-5A, 3 Phase, 24VDC Control
1100-38X	74VDC, Similar to WC1-74DC-5	1200-5X	120VAC, 1-5A, 3 Phase, 24VDC Control
1100 00%	74VD0, 0111111at to VV01-74D0 3	1200-6X	120VAC, 1-5A, 3 Phase, 24VDC Control,
AC SIM	GLE PHASE, ADJ. DIFFERENTIAL		Suppression
•	120VAC, 1-5A Range	1200-7X	120VAC, 1-5A, 1 Phase, 120VAC Control
D1100X		1200-8HX	120VAC, 1-5A, 3 Phase, 125VDC Control
D1100-2X	220VAC, 1-5A Range		DC
D1100-3X	120VAC, 4-12A Range	1100DCX	120VAC, 10-50mV ext. Shunt, 5A Contacts
D1100-4X	230VAC, 4-12A Range	1100DC-1X	230VAC, 0-10VDC ext. Shunt, 5A Contacts
D1100-5X	460VAC, 4-12A Range	1100DC-2X	120VAC, 10-50mV ext. Shunt,
D1100-6X	120VAC, 1-5A Range, 1-2 Sec. T.D.		Transistor Output
D1100-7X	120VAC, 0.7-5A Range,	1100DC-3X	120VAC, 0.2-0.6ADC with 0.125 ohm Shunt
	125VDC 0.5A Contacts	1100DC-4X	28VDC, 10-50mV, Inverter, ext. Shunt,
D1100-8X	120VAC, 5-15A Range	110000-47	2 Sec. T.D.
		1100DC 6V	
AC,	SINGLE PHASE, TIME DELAY	1100DC-6X	125VDC, 10-50mV, Inverter,
1100TDX			
	120VAC, 1-5A Range, 0.5-30 Sec. T.D.	440000 71/	125VDC 3A Contacts
		1100DC-7X	120VAC, 10-50mV, Inverter,
1100TD-HX	120VAC, 1-5A, 0.5-30 Sec. T.D.,		120VAC, 10-50mV, Inverter, 125VDC 3A Contacts
1100TD-HX	120VAC, 1-5A, 0.5-30 Sec. T.D., 125VDC 3A Cont.	1100DC-7X 1100DC-8X	120VAC, 10-50mV, Inverter, 125VDC 3A Contacts 120VAC, isolated outputs
	120VAC, 1-5A, 0.5-30 Sec. T.D., 125VDC 3A Cont. 120VAC, 1-5A Range, 0.5-20 Sec. T.D.,		120VAC, 10-50mV, Inverter, 125VDC 3A Contacts
1100TD-HX 1100TD-SX	120VAC, 1-5A, 0.5-30 Sec. T.D., 125VDC 3A Cont. 120VAC, 1-5A Range, 0.5-20 Sec. T.D., Hi-Shock	1100DC-8X	120VAC, 10-50mV, Inverter, 125VDC 3A Contacts 120VAC, isolated outputs 250VDC, 150mV Shunt, Hi-Shock, +/- 20% Adj.
1100TD-HX 1100TD-SX 1100TD-1X	120VAC, 1-5A, 0.5-30 Sec. T.D., 125VDC 3A Cont. 120VAC, 1-5A Range, 0.5-20 Sec. T.D., Hi-Shock 240VAC, 1-5A Range, 0.5-30 Sec. T.D.	1100DC-8X	120VAC, 10-50mV, Inverter, 125VDC 3A Contacts 120VAC, isolated outputs 250VDC, 150mV Shunt, Hi-Shock, +/- 20% Adj. 120VAC, 50-150mV
1100TD-HX 1100TD-SX 1100TD-1X 1100TD-2X	120VAC, 1-5A, 0.5-30 Sec. T.D., 125VDC 3A Cont. 120VAC, 1-5A Range, 0.5-20 Sec. T.D., Hi-Shock 240VAC, 1-5A Range, 0.5-30 Sec. T.D. 24VDC, 1-5AAC Range, 0.5-30 Sec. T.D.	1100DC-8X 1100DC-9X	120VAC, 10-50mV, Inverter, 125VDC 3A Contacts 120VAC, isolated outputs 250VDC, 150mV Shunt, Hi-Shock, +/- 20% Adj.
1100TD-HX 1100TD-SX 1100TD-1X 1100TD-2X 1100TD-3X	120VAC, 1-5A, 0.5-30 Sec. T.D., 125VDC 3A Cont. 120VAC, 1-5A Range, 0.5-20 Sec. T.D., Hi-Shock 240VAC, 1-5A Range, 0.5-30 Sec. T.D. 24VDC, 1-5AAC Range, 0.5-30 Sec. T.D. 120VAC, 0.5-5A Range, 0.5-30 Sec. T.D.	1100DC-8X 1100DC-9X 1100DC-10X	120VAC, 10-50mV, Inverter, 125VDC 3A Contacts 120VAC, isolated outputs 250VDC, 150mV Shunt, Hi-Shock, +/- 20% Adj. 120VAC, 50-150mV
1100TD-HX 1100TD-SX 1100TD-1X 1100TD-2X 1100TD-3X 1100TD-5X	120VAC, 1-5A, 0.5-30 Sec. T.D., 125VDC 3A Cont. 120VAC, 1-5A Range, 0.5-20 Sec. T.D., Hi-Shock 240VAC, 1-5A Range, 0.5-30 Sec. T.D. 24VDC, 1-5AAC Range, 0.5-30 Sec. T.D. 120VAC, 0.5-5A Range, 0.5-30 Sec. T.D. 120VAC, 0.5-2.5A Range, 0.5-30 Sec. T.D.	1100DC-8X 1100DC-9X 1100DC-10X	120VAC, 10-50mV, Inverter, 125VDC 3A Contacts 120VAC, isolated outputs 250VDC, 150mV Shunt, Hi-Shock, +/- 20% Adj. 120VAC, 50-150mV 220VDC, 5-25mV, 1-25 Sec. T.D., Inverse Current
1100TD-HX 1100TD-SX 1100TD-1X 1100TD-2X 1100TD-3X	120VAC, 1-5A, 0.5-30 Sec. T.D., 125VDC 3A Cont. 120VAC, 1-5A Range, 0.5-20 Sec. T.D., Hi-Shock 240VAC, 1-5A Range, 0.5-30 Sec. T.D. 24VDC, 1-5AAC Range, 0.5-30 Sec. T.D. 120VAC, 0.5-5A Range, 0.5-30 Sec. T.D. 120VAC, 0.5-2.5A Range, 0.5-30 Sec. T.D. 120VAC, 1-5A, 0.2-20 Sec. T.D.	1100DC-8X 1100DC-9X 1100DC-10X 1100DC-11X 1100DC-13X	120VAC, 10-50mV, Inverter, 125VDC 3A Contacts 120VAC, isolated outputs 250VDC, 150mV Shunt, Hi-Shock, +/- 20% Adj. 120VAC, 50-150mV 220VDC, 5-25mV, 1-25 Sec. T.D., Inverse Current 120VAC, 20-35mV, Hi-Shock
1100TD-HX 1100TD-SX 1100TD-1X 1100TD-2X 1100TD-3X 1100TD-5X 1100TD-6X	120VAC, 1-5A, 0.5-30 Sec. T.D., 125VDC 3A Cont. 120VAC, 1-5A Range, 0.5-20 Sec. T.D., Hi-Shock 240VAC, 1-5A Range, 0.5-30 Sec. T.D. 24VDC, 1-5AAC Range, 0.5-30 Sec. T.D. 120VAC, 0.5-5A Range, 0.5-30 Sec. T.D. 120VAC, 0.5-2.5A Range, 0.5-30 Sec. T.D. 120VAC, 1-5A, 0.2-20 Sec. T.D., Manual Reset	1100DC-8X 1100DC-9X 1100DC-10X 1100DC-11X 1100DC-13X 1100DC-15X	120VAC, 10-50mV, Inverter, 125VDC 3A Contacts 120VAC, isolated outputs 250VDC, 150mV Shunt, Hi-Shock, +/- 20% Adj. 120VAC, 50-150mV 220VDC, 5-25mV, 1-25 Sec. T.D., Inverse Current 120VAC, 20-35mV, Hi-Shock 12VDC, 10-50mV, Inverter
1100TD-HX 1100TD-SX 1100TD-1X 1100TD-2X 1100TD-3X 1100TD-5X	120VAC, 1-5A, 0.5-30 Sec. T.D., 125VDC 3A Cont. 120VAC, 1-5A Range, 0.5-20 Sec. T.D., Hi-Shock 240VAC, 1-5A Range, 0.5-30 Sec. T.D. 24VDC, 1-5AAC Range, 0.5-30 Sec. T.D. 120VAC, 0.5-5A Range, 0.5-30 Sec. T.D. 120VAC, 0.5-2.5A Range, 0.5-30 Sec. T.D. 120VAC, 1-5A, 0.2-20 Sec. T.D.	1100DC-8X 1100DC-9X 1100DC-10X 1100DC-11X 1100DC-13X	120VAC, 10-50mV, Inverter, 125VDC 3A Contacts 120VAC, isolated outputs 250VDC, 150mV Shunt, Hi-Shock, +/- 20% Adj. 120VAC, 50-150mV 220VDC, 5-25mV, 1-25 Sec. T.D., Inverse Current 120VAC, 20-35mV, Hi-Shock



IIAII	) ED	וחווי	TIAD	DEL	AVC
UNI	JENU	JUNI	RENT	NEL	AIO

Self Contained CT, 120VAC Control 21-693-1 21-693-2 Self Contained CT, 230VAC Control

#### **CURRENT DIFFERENTIAL**

1350X

1351-4X

1350PX 24VDC, 0.1-0.5A Range, Suppression, 1 N.O. Contact 24VDC, 0.1-0.5A Range, High Shock 1350SX 1350-1X 24VDC, 0.1-0.5A Range, 1 N.C. Contact 48VDC, 0.1-0.5A Range 1350-3X 1351X 120VAC, 0.1-0.5A Range 120VAC, 0.1-0.5A Range, Suppression 1351PX 1351SX 120VAC, 0.1-0.5A Range, High Shock 1351-1X 120VAC, 0.1-0.5A Range, 1 N.C. Contact 120VAC, 2 Sec. T.D. on application of voltage 1351-2X

24VDC, 0.1-0.5A Range

120VAC, 0.1-0.5A Range, Fast, 125VDC Contacts

#### PARALLELING (SYNCHRO-CHECK) RELAYS

1880X 200VAC, 1 N.O. & 1 N.C. Contact 1890X 90VAC, 1 N.O. & N.C. Contact "-A": Two Normally Open Contacts **SUFFIX** "-B": Two Normally Closed Contacts

"-P": Spike Suppression "-7": 0.025 Second Time Delay "-9": 125VDC 2A Contacts "-13": 0.250 Second Time Delay

#### **DEAD BUS TYPE**

1880DBX 200VAC, 1 N.O. & 1 N.C. Contact 1890DBX 90VAC, 1 N.O. & 1 N.C. Contact "-A": 2 Normally Open Contacts SUFFIX "-B": 2 Normally Closed Contacts

"-S": High Shock

"-2": 2 N.O. Contacts, Cond. 5 same as 3

"-3": Condition 1 reversed "-5": 12 deg. to 36 deg. adjustment "-8" 3 Phase, Phase Sequence "-9": 125VDC 2A Contacts

"-12": 25 Hz, 125VDC 3A Contacts

**DOUBLE DEAD BUS (EITHER BUS DEAD)** 

1880DDBX 200VAC, 1 N.O. & 1 N.C. Contact 1890DDBX 90VAC, 1 N.O. & 1 N.C. Contact **SUFFIX** "-A": 2 Normally Open Contacts "-B": 2 Normally Closed Contacts

"-9": 125VDC Contacts; 2A res., 1A ind.

#### **DOUBLE DEAD BUS. UNDERVOLTAGE**

2800-120	120VAC, Ph. Ang. 5-25 deg.,
	UV: 70% D.O. 80% P.U.
2800-208	208VAC, Ph. Ang. 5-25 deg.,
	UV: 70% D.O. 80% P.U.
2800-240	240VAC, Ph. Ang. 5-25 deg.,
	UV: 70% D.O. 80% P.U.
2800-380	380VAC, Ph. Ang. 5-25 deg.,
	UV: 70% D.O. 80% P.U.
2800-416	416VAC, Ph. Ang. 5-25 deg.,
	UV: 70% D.O. 80% P.U.
2800-440	440VAC, Ph. Ang. 5-25 deg.,
	UV: 70% D.O. 80% P.U.

2800-480 480VAC, Ph. Ang. 5-25 deg., UV: 70% D.O. 80% P.U. 2800-600 600VAC, Ph. Ang. 5-25 deg.,

UV: 70% D.O. 80% P.U.

#### PHASE BAND MONITOR

2850X 208/230/460 V, 5-60 deg. Range, 60 Hz 208/240/380/480 V, 5-45 deg. Range, 50/60 Hz 2850-1X

#### **OVERFREQUENCY RELAYS**

WOF-12-100110 120VAC, 100-110 Hz. Range

> SUFFIX "-1": 0.2% Max. Differential "-T": 0.5-20 Sec. Time Delay "-2T": 60 Second Time Delay

"-S": High Shock

23-050X 120VAC. 50-60 Hz 23-060X 120VAC, 60-70 Hz 23-400X 120VAC, 400-450 Hz

#### UNDERFREQUENCY RELAYS

22-050X 120VAC, 50-60 Hz 22-060X 120VAC, 60-70 Hz 22-400X 120VAC, 400-450 Hz

#### FREQUENCY RELAYS (Over or Under)

25-050HX 120VAC, 40-50-60 Hz, 125VDC 3A Contacts 25-050SX 120VAC, 40-50-60 Hz, High Shock 25-050-1X 120VAC, 40-50-60 Hz, 2 N.C. Contacts 25-050-2X 120VAC, 40-50-60 Hz, 1.2 Sec. Time Delay 25-060HX 120VAC, 50-60-70 Hz, 125VDC 3A Contacts 25-060SX 120VAC, 50-60-70 Hz, High Shock

120VAC, 50/60 Hz +/-10% on each Frequency 25-060-1X 120VAC, 50-60-70 Hz, 0.4 Hz Differential 25-060-2X 25-060-3X 120VAC, 50-60-70 Hz, 2 N.C. Contacts 25-060-4X 120VAC, 50-60-70 Hz, 2 N.O. Contacts 25-060-5X 120VAC, 50-60-70 Hz, 2 N.O, 10A MIL-R-5757

25-060-7X 120VAC, EMD #9337150, Set 57.4 &

62.6 +/-0.6 Hz

25-060-8X 120VAC, 50-60-70 Hz, 1 Sec. T.D. 25-060-10X 120VAC, Spike Suppression 104VAC, 50-60-70 Hz 25-060-12X 25-060-14X 240VAC, 50-60-70

Hъ 25-060-18X

120VAC, 50-60-70 Hz, 1 Sec. T.D., Suppression

25-060-19X 120VAC, 50-60-70 Hz, 0.5-10Sec. T.D.,

12VDC Ctrl.

25-060-20X 120VAC, 50-60-70 Hz, 0.5-10Sec. T.D.,

24VDC Ctrl.

25-100X 120VAC, 90-100-110 Hz 25-400X 120VAC, 350-400-450 Hz 25-400-2X 120VAC, 350-400-450 Hz, 220VAC 5A Contacts

25-400-5X 120VAC, 350-400-450 Hz, Suppression 25-025T-1HX 480VAC, 20-25-30 Hz, 0.5-20Sec T.D.,

125VDC 3A Contacts

25-025T-2HX 120VAC, 20-25-30 Hz, 0.5-20Sec. T.D.,

125VDC 3A Contacts

25-100T-1HX 480VAC, 90-100-110 Hz, 0.5-20Sec. T.D.,

125VDC 3A Contacts

20-040-1X 100VAC, 40-50 Hz

120VAC, 40-50 Hz, 1.5-2.0 Sec. T.D. 20-040-2X



20-040-3X	120VAC, 40-50 Hz, 2 N.C. Contacts
20-040-4X	220VAC, 40-50 Hz.
20-050-HX	120VAC, 50-60 Hz, 125VDC 3A Contacts
20-050SX	120VAC, 50-60 Hz, High Shock, MIL-S-901C
20-050-1X	120VAC, 50-60 Hz, 0.2 Sec. T.D.
20-050-2X	120VAC, 45-66 Hz, U.L.
20-050-3X	120VAC, 50-60 Hz, 2000V PIV Diode
20-050-4X	120VAC, 50-60 Hz, 1 Sec. T.D., 0.5% Drift
20-050-8X	120VAC, 57-60 Hz, 0.2 Hz Diff.,
	240V Contacts, FAA
20-050-8PX	120VAC, Similar to 20-050-8X w/
	Spike Suppression
20-050-9X	120VAC, 45-55 Hz
20-050-10X	120VAC, 50-60 Hz, Suppression
20-050-12X	120VAC, 50-60 Hz, 125VDC Contacts
20-050-13X	120VAC, 50-60 Hz, 2 Sec. T.D.
20-050-16X	150VAC, Similar to 20-050-10X except
	Voltage
20-050-19X	120VAC, Volt./Freq., 45-60 Hz, 85-120V
20-050-19PX	120VAC, Similar to 20-050-19X w/
	Suppression
20-050-20X	120VAC, 50-60 Hz, 2 N.C. Contacts
20-050-21X	220VAC, 50-60 Hz
20-050-22X	120VAC, 50-60 Hz, 125VDC Contacts,
	Seismic
20-050-23X	240VAC, Similar to 20-050-19X except Voltage
20-050-23PX	240VAC, Similar to 20-050-23X w/Suppression
20-050-25X	104VAC, 50-60 Hz
20-050-26X	120VAC, 57-60 Hz, Supp., 0.2 Sec. T.D. on
00.050.071/	D.O.
20-050-27X	120VAC, Sim. to 20-050-26X, Operation
00 050 007	Reversed
20-050-28X	120VAC, Sim. to 20-050-2X with Suppression
20-050-29X	120VAC, Sim. to 20-050-19X w/125VDC 2A Contacts
20-050-30X	120VAC, Sim. to 20-050-1X w/125VDC 2A
20-030-30X	Contacts
20-050-31X	200-480VAC, 50-60 Hz Range, 26VDC
20 000 017	Control
20-050-32X	120VAC, Sim. to WUF-12-5060T,
	Operation Rev.
20-060-1X	120VAC, 60-70 Hz, 2000V Diode
20-060-2X	120VAC, 60-63 Hz, 0.2 Hz Diff., 240VAC
<del></del>	Contacts

20-060-2PX	120VAC, Sim. to 20-060-2X w/ Suppression
20-060-4X	120VAC, 65-77 Hz
20-060-5X	120VAC, Jumper, Set at 60 Hz +3% or
	50 Hz +3%
20-060-6X	120VAC, 103-156V Range, 60-70 Hz,
	Set at 70 Hz
20-060-7X	120VAC, 60-63Hz, 0.2 Sec T.D. on P.U.,
	Suppression
20-060-8X	120VAC, 60-70 Hz, Spike Suppression
20-060-9X	120VAC, 60-70 Hz, 0.25 Sec. Inverse T.D.
	on P.U.
20-350X	120VAC, 350-500Hz
20-350SX	120VAC, 350-400Hz, 2 N.C. 2A Contacts,
	Hi-Shock
20-350-2SX	115VAC, 350-400Hz, Hi-Shock
20-350-4X	120VAC, 300-400 Hz
20-400X	120VAC, 400-450 Hz
20-400SX	120VAC, 400-450 Hz, High Shock
20-400-2SX	115VAC, Hi-Shock
20-400-3X	120VAC, 400-450 Hz, 2 N.C. Contacts
20-400-4X	120VAC, 400-500 Hz
,	ADJUSTABLE DIFFERENTIAL
D20-040X	120VAC, 40-50 Hz
D20-050X	120VAC, 50-60 Hz
D20-050-2X	120VAC, P.U. 50-60 Hz, D.O. 40-50 Hz
D	

#### **VOLTAGE UNBALANCE RELAYS**

D20-060X

1500X	120VAC, 3 Phase, 15% - 25% Adjustment
1510X	230VAC, 3 Phase, 15% - 25% Adjustment
1520X	380VAC, 3 Phase, 15% - 25% Adjustment
1530X	460VAC, 3 Phase, 15% - 25% Adjustment
1540X	575VAC, 3 Phase, 15% - 25% Adjustment
1550X	208VAC, 3 Phase, 15% - 25% Adjustment
	SUFFIX "-2": N.C. Contacts (Example: 1500-2X)

120VAC, 60-70 Hz

"-3": 10% - 20% Adjustment "-4": Transient Suppression "-H": 125VDC 3A Contacts



# **Engineering Notes**

