Validation / Qualification Test Report



Q16003

QUALIFICATION ACCORDING TO APTA & AAR

MU27P connector

PRJ-14-000003352

Α	First Edition					2018/04/23	M BOIVIN			
LTR		I		Date	Author					
Арр	roved by	Product Dvl Engineer	Engineering Manager	Manager Product Management						
		M.BONNIN	M.VIMARD	D.BOGAARTS						
Notification to		Product Manager	Manager Operations							
		A. LAGRANGE	M.MEDARD							

THIS IS A CLASS 1 DOCUMENT WHICH IS NONCONFIDENTIAL.

The information contained within this document is the property of TE Connectivity. It is supplied in confidence and the commercial security of the contents must be maintained. It must not be used for any purpose other than that for which it is supplied nor may any information contained in it be disclosed to unauthorised persons. It must not be reproduced in whole or in part without obtaining written permission from TE Connectivity (TE).

While TE has made every reasonable effort to ensure the accuracy of the information in this catalog, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or filtness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

*Trademark. TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks. Other logos, product and/or company names may be trademarks of their respective owners.

Validation / Qualification Test Report



INDEX

1	INT	RODUCTION	3
	1.1	AIM OF THE TESTS	3
	1.2	APPLICABLE DOCUMENTS	3
	1.3	SAMPLING	4
	1.4	TEST SEQUENCE	5
	1.5	SAMPLES IMPLEMENTATION	6
	1.6	SAMPLES WORKING ORDERS	7
	1.7	TESTS DEVICES	8
2	СО	NCLUSION	9
3	AP	PENDICES	11

Validation / Qualification Test Report



1 INTRODUCTION

1.1 AIM OF THE TESTS

The aim of the type tests is to qualify the connector MU27P according to the standard APTA (PR-E-S-001-98, PR-E-RP-019-99, PR-E-RP-002-98) and AAR S512

This connector is designed to be used with a rated voltage of 600V according to the standard EN50124-1/A2 (mated connector), taking into account a pollution degree PD2 and overvoltage category of OV3.

1.2 APPLICABLE DOCUMENTS

Standards:

- EN60068-1: 1995 Environmental tests Part 1: Generality and guidance
- EN60068-2-2/A2: 1995 Environmental tests Part 2: Tests Tests B: Dry heat
- EN60068-2-11: 1999 Environmental tests Part 2: Tests Tests ka: Salt spray
- EN60068-2-14: 2009 Environmental tests Part 4: Tests Tests N: Temperature variation
- EN60068-2-78: 2002 Environmental tests Part 2-78: Tests Test Cab: Continuous damp heat
- EN60529/A1: 2000 Degree of protection provided by enclosures (IP code)
- EN61373: 2000 Railway applications Rolling stock Chocks and vibrations tests
- ISO1431-1: 2012 Rubber, vulcanized or thermoplastic materials Resistance to ozone cracking – Part 1: Tests under static and dynamic stretching
- NF F 61-030: 1992 Railway rolling stock Electrical connectors Generalities
- NF C 93-400 /A1: 1988 Electronic components Connection devices Test procedures and measuring methods – List of tests
- NFC93-422: 1977 Electronic components Connection devices Cylindrical multicontacts connectors - General requirements
- APTA PR-E-S-001-98 Standard for insulation integrity
- APTA PR-E-RP-002-98 Recommended Practice for Wiring of Passenger Equipment
- APTA RP-E-017-99 Recommended Practice for 27-Point Jumper and Receptacle Hardware for Locomotives and Locomotive-Hauled Equipment
- APTA PR-E-RP-019-99 Recommended Practice for 27-Point Jumper and Receptacle Hardware for Locomotives and Locomotive-Hauled Equipment
- AAR-S-512 Locomotives and locomotive interchange equipment

> Assembly drawings (see appendix 2):

- 212075 DEUTSCH: MU CONTROL PLUG
- 211942 DEUTSCH: MU CONTROL RECEPTACLE
- 212093 DEUTSCH: COMMUNICATION PLUG
- 211943 DEUTSCH: COMMUNICATION RECEPTACLE
- 212094_DEUTSCH: TYPICAL AEM-7 PLUG
- 212085_DEUTSCH: TYPICAL AEM-7 RECEPTACLE
- 212095 DEUTSCH: COMMUNICATION COMMUTER PLUG
- 212086_DEUTSCH: COMMUNICATION COMMUTER RECEPTACLE
- 211944_DEUTSCH: DUMMY RECEPTACLE

Rev [A]


Validation / Qualification Test Report


CLASS 1- Public





1.3 SAMPLING


Sample No.	Sample BOM	Quantity per sample	Description	Cables	
1 and 2	27P-REC-1-01 27P-PLU-1-01	1	MU CONTROL RECEPTACLE MU CONTROL PLUG		
3 and 4	27P-REC-2-01 27P-PLU-2-01		COMMUNICATION RECEPTACLE COMMUNICATION PLUG	0 04 5	
5 and 6	27P-REC-3-01 27P-PLU-3-01	1	TYPICAL AEM-7 RECEPTACLE TYPICAL AEM-7 PLUG	See §1.5	
7 and 8	27P-REC-4-01 27P-PLU-4-01	1	COMMUNICATION COMMUTER RECEPTACLE COMMUNICATION COMMUTER PLUG		
9	27P-DUM-Y	1	DUMMY RECEPTACLE	N/A	











Validation / Qualification Test Report



1.4 TEST SEQUENCE

Test sequence is the one described by the NFF61030, added to specific tests from the APTA and AAR standards.

The connectors are successively submitted to the tests corresponding to the groups defined here-after:

Group	Test description	Required by standard	Sample number
	Visual examinations (appearance & marking)	APTA PR-E-RP-019-99	Each sample
	Geometrical checking	APTA PR-E-RP-019-99	1, 9
	Mass checking	AAR S-512	Each sample
	Withstand voltage	APTA PR-E-S-001-98	1 to 8
0	Insulation resistance	APTA PR-E-S-001-98	1 to 8
	Contact resistance	NF F 61-030	2, 3 and 7
	Connector insertion force	APTA PR-E-RP-019-99	1, 3, 5 and 7
	Contact insertion force	APTA PR-E-RP-019-99	1
	Continuous test in damp heat	APTA PR-E-RP-019-99	1
1	Vibration test	NF F 61-030	2
	Resistance to fluids	APTA PR-E-RP-019-99 NF F 61-030	2, 4, 6 and 8
	Rapid variations of temperature	APTA PR-E-RP-002-98	3
2	Mechanical endurance	APTA PR-E-RP-002-98	3
	Jumper head retention	APTA PR-E-RP-019-99	3
	Temperature rise	APTA PR-E-RP-019-99	7
3	Corrosion	NF F 61-030	5
	Shocks	NF F 61-030	5
4	Dry heat	NF F 61-030	7
4	Mechanical resistance to impact (drop test)	NF F 61-030	7
5	Traction test (crimped connection)	NF F 61-030	10 pairs of contacts

Note:

> A full version of this table included severity and checking tests to be performed is in appendix

Rev [A]

Validation / Qualification Test Report



1.5 SAMPLES IMPLEMENTATION

Each sample for testing is a pair of connectors composed of:

- > 1 male receptacle equipped of 27 male contacts caliber 8 with 3 contacts in AWG 10 and 24 contacts in AWG12-14
- 1 female plug equipped of 27 female contacts caliber 8 with 3 contacts in AWG 10 and 24 contacts in AWG12-14

The retention between the plug and the receptacle made by a form in the cover and in the plug.



The contacts and cables used for this qualification are the following:

Cable section	Cable designation	Selector position of the crimping tool
10 AWG (5.27mm ²)	E125352 (P) (UL) BC-5W2 OR MTW OR THHW OR AWM 1011/1015/1230/1335 600V OR 1032 1000V MOISTURE RESISTANT VW-1156016 CSA TEW 105C 600V FT1 OR AWM I A/B 105C 600V FT1	DANIELS CRIMPING HAND CRIMPER HX4
12 AWG (3.31mm ²)	E125352 (P) (UL) BC-5W2 OR MTW OR THHW OR AWM 1011/1015/1230/1335 600V OR 1032 1000V MOISTURE RESISTANT VW-1156016 CSA TEW 105C 600V FT1 OR AWM I A/B 105C 600V FT1	WITH Y543 DIES or DANIELS PNEUMATIC
14 AWG (2.08mm²)	E125352 (P) (UL) BC-5W2 OR MTW OR THHW OR AWM 1011/1015/1230/1335 600V OR 1032 1000V MOISTURE RESISTANT VW-1156016 CSA TEW 105C 600V FT1 OR AWM I A/B 105C 600V FT1	CRIMPER HX23 WITH Y543 DIES

Cable stripping length = 0.54 inches (13,7 mm)

Validation / Qualification Test Report



Receptacle:

	C	RECEPTACLE										
Caliber (mm)	Туре	Type Cable used Reference		IVDE		I Vne Reterence		Reference		Index	No. of contacts	Contact localization in insulator
8	Male contact 10 AWG	10 AWG	YS-UC-211946A-AA1A	С	3	Randomly						
8	Male contact 12-14 AWG	12 AWG	YS-UC-211945A-AA1A	С	12	Randomly						
8	Male contact 12-14 AWG	14 AWG	YS-UC-211945A-AA1A	С	12	Randomly						

Plug:

		RECEPTACLE				
Caliber (mm)	Туре	Cable used	Reference	Index	No. of contacts	Contact localization in insulator
8	Female contact 10 AWG	10 AWG	YS-UC-212073A-AA1A	С	3	Identical to receptacle
8	Female contact 12-14 AWG	12 AWG	YS-UC-212072A-AA1A	С	12	Identical to receptacle
8	Female contact 12-14 AWG	14 AWG	YS-UC-212072A-AA1A	С	12	Identical to receptacle

1.6 SAMPLES WORKING ORDERS

WO No.	DESCRIPTION	CATALOGUE No.			
200215611501	PLUG, MU, CONTROL	27P-PLU-1-01			
200215611503	RECEPTACLE, COMMUNICATION	27P-REC-2-01			
200215611505	200215611505 RECEPTACLE, MU, CONTROL				
200215611506	27P-PLU-2-01				
200215611507	RECEPTACLE, TYPICAL OF AEM-7	27P-REC-3-01			
200215611510	PLUG, TYPICAL AEM-7	27P-PLU-3-01			
200215611511	PLUG, COMMUNICATION COMMUTER	27P-PLU-4-01			
200215611514	RECEPTACLE, COMMUNICATION COMMUTER	27P-REC-4-01			
200215638062	DUMMY RECEPTACLE	27P-DUM-Y			

Rev [A]

Validation / Qualification Test Report



1.7 TESTS DEVICES

		Calibrati	on dates
Description	TE No.	Current	Next
Coating measurement Instrument	6428	2016/07	2017/07
Smart scope MVP 300	6616	2017/11	2018/11
Radius gauge (indicator)	/	/	/
Digital CX1/DX1	5420	2017/06	2018/06
Digital caliper MITUTOYO	6131	2017/10	2018/17
Digital caliper MITUTOYO absolute digimatic	2401	2017/03	2018/03
Scale KERN CXP	5435	2017/01	2018/01
Dielectric strength tester SEFELEC PR 12 PF	1589	2017/03	2018/03
Insulation tester MEGGER BM25	2231	2017/11	2018/11
Ohmmeter MEGGER DLRO600	6701	2017/04	2018/04
Traction / compression machine ADAMEL LHOMARGY DY36	1118	2017/04	2019/04
Climatic chamber CLIMATS 320H60-1-5	1574	2017/06	2018/06
Climatic chamber FRANCE ETUVES XU250	6019	2017/06	2018/06
Climatic chamber CERADEL SNOL 970/350	7292	2017/06	2018/06
Climatic chamber CLIMATS EX5424	6185	2017/06	2018/06
Datalogger AGILENT 34970A	1868	2017/03	2018/03
Current generator ZENONE model GI2000GL	7054	2017/06	2018/06
AC current probe CHAUVIN ARNOUX MA100	7570	2017/03	2018/03
Salt spray chamber DYCOMETAL type SSC-400	7574	2017/05	2018/05
Micro-cuts detection device	7344-0001-03- 002	2017/10	2018/10
Driver station	7161-0001-05- 002	2017/11	2018/11
Sensor signal conditioner model 488C series	7161-0001-26- 001	2016/12	2018/12
Accelerometer	7161-0001-28- 001	2017/10	2018/10
Shower + Flowmeter PIUISI instrument (indicator)	/	/	/
Dust enclosure FLONIC SCHLUMBERGER	D1086002	/	2019/12
Timers QUANTUM	B2040110 B1040111	/	2019/10

CLASS 1- Public



2 CONCLUSION

				Samples No.									
Group	Test description	Standard	Requirements	1	2	3	4	5	6	7	8	9	Compliancy
	Visual examinations	APTA PR-E- RP-019-99	See details on report	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
		APTA PR-E-	211276 Insulator dimensions	✓									
	Dimensions checking	RP-019-99 + AAR S-512	211942 Receptacle dimensions or 211944 Dummy receptacle dimensions	✓								✓	✓
		AAN 3-312	212075 Plug dimensions	✓									
	Mass checking	NF F 61-030	Plug Receptacle	√	√	√	√ ✓	✓	√	√	✓	✓	✓
0	Withstand voltage	APTA PR-E-S-	No disruptive breakdown, nor arcing	✓	✓	✓	✓	✓	✓	✓	✓		✓
	_	001-98	Leakage current ≤ 2 mA (rms value)	✓	✓	✓	✓	✓	✓	✓	✓		Ý
	Insulation resistance	APTA PR-E-S- 001-98	IR ≥ 5 MΩ	✓	✓	✓	✓	✓	✓	✓	✓		✓
	Contact resistance	NF F 61-030	Rc ≤ 0.35 mΩ		✓	✓				✓			✓
	Connector insertion force	APTA PR-E- RP-019-99	195 N < Insertion force < 285 N	✓		✓		✓		✓			✓
	Contact insertion force	APTA PR-E- RP-019-99	2.2 N < Insertion force < 14.5 N	✓									✓
	Continuous damp heat	APTA PR-E-	No defect that would prevent the connector working properly	✓									,
		RP-019-99	Legible marking at the end of the test	✓									✓
			IR ≥ 5 MΩ	✓									
		NF F 61-030	No micro-cuts high than 10 μs		✓								
			No defect, no splitting or fracture or play, no loosing of the locking system		✓								
	Vibrations		195 N < Insertion force < 285 N		✓								✓
1			No water trace on the actives parts		✓								
			No dust trace on the actives parts		✓								
		ADTA DD E DD	No cracking or dissolving of the insulation and the sealing system, no defect that would prevent the connector working properly		✓		✓		✓		✓		
	Resistance to	APTA PR-E-RP- 019-99	The marking shall be legible		✓		✓		✓		✓		✓
	fluids	NF F 61-030	No disruptive breakdown, nor arcing Leakage current ≤ 2 mA (rms value)		✓		✓		✓		✓		·
			IR ≥ 5 MΩ		✓		✓		✓		✓		
	Rapid	4DT4 B2 5 55	The parts shall not have any defect that would prevent them working properly			✓							
2	temperature variation	APTA PR-E-RP- 002-98	The marking shall be legible at the end of the test			✓							✓
	ranation.		IR ≥ 5 MΩ			✓							

Validation / Qualification Test Report



		Mechanical endurance	APTA PR-E-RP- 002-98	No defect that would prevent the connector working properly No splitting or fracture or play in the component parts No loosing of the locking system of the connector 195 N < Insertion force < 285 N Rc ≤ 0.35 mΩ		→				√
		Jumper head retention	APTA PR-E- RP-019-99	No damage on receptacle and plug		✓				✓
		Temperature rise	APTA PR-E- RP-019-99	Method A: ΔT ≤ 50 K @ 30 A (AWG10/12/14) Method B: ΔT ≤ 50 K @ 30 A (AWG10)				√ ✓		✓
	3	Corrosion	NF F 61-030	The parts shall not have any defect that would prevent them working properly The marking shall be legible at the end of the test $IR \geq 5 \text{ M}\Omega$			✓			✓
3	Ĭ	Shocks	NF F 61-030	No defect that would prevent the connector working properly No splitting or fracture or play in the component parts No loosening of the locking system of the connector 195 N < Insertion force < 285 N			√			✓
	4	Dry heat	NF F 61-030	During test after 24h: IR \geq 5 M Ω The parts shall not have any defect that would prevent them working properly Rc \leq 0.35 m Ω IR \geq 5 M Ω				√ √ √		√
	Mechanical resistance to impact	NF F 61-030	No defect of the parts that would harm their satisfactory operation 195 N < Insertion force < 285 N				√		√	

					Sample No.					
Group	Test description	Standard	Requirements	Cable section	1	2	3	4	5	Compliancy
5	Resistance to pulling on the crimping	APTA PR-E-RP- 019-99	F ≥ 180 N	AWG 10	✓	✓	✓	✓	✓	
				AWG 12	✓	✓	✓	✓	✓	✓
		0.000		AWG 14	✓	✓	✓	✓	✓	

✓	Test realized and compliant result
×	Test realized and no compliant result

The results are compliant with the requirements.

Validation / Qualification Test Report



APPENDICES

٩	PPENDIX 1: Type tests synthesis and tests requirements	12
٩	PPENDIX 2: Assembly drawings of the test samples	13
	MU plug control – reference E1894-212075 – revision C	13
	MU receptacle control – reference E1894-211942 – revision C	14
	Plug communication – reference E1894-212093 – revision C	15
	Receptacle communication – reference E1894-211943 – revision C	16
	Typical AEM-7 plug – reference E1894-212094 – revision C	17
	Receptacle typical of AEM-7 plug – reference E1894-212085 – revision C	18
	Communication commuter plug – reference E1894-212095 – revision C	19
	Communication commuter receptacle – reference E1894-212086 – revision C	20
	Dummy receptacle – reference E1894-211944 – revision E	21
Δ	PPENDIX 3: Insulation Coordination	22

Validation / Qualification Test Report



APPENDIX 1: Type tests synthesis and tests requirements


Сколь	Toot description	Severity or conditions	Type tests	Checking tests	No. of the test sample								
Group	Test description				1	2	3	4	5	6	7	8	9
	Visual examination (appearance & marking)	No damage	Х										
	Geometrical checking		Х			-	-	-	-	-	-	-	
	Mass checking	±5%	Х										
0	Withstand voltage	Leakage current ≤2mA	Х										-
U	Insulating resistance	IR ≥5MΩ	X										-
	Contact resistance	Rc≤0.35mΩ	Х		-			-	-	-		-	-
	Connector insertion force	195N <insertion force<285n<="" td=""><td>Х</td><td></td><td></td><td>-</td><td></td><td></td><td></td><td>-</td><td></td><td>-</td><td>-</td></insertion>	Х			-				-		-	-
	Contact insertion force	2.2N <insertion force<14.5n<="" td=""><td>Х</td><td></td><td></td><td>-</td><td>_</td><td>_</td><td>_</td><td>-</td><td>-</td><td>-</td><td>-</td></insertion>	Х			-	_	_	_	-	-	-	-
	Continuous test in damp heat	-	Х			-	-	-	-	-	-	-	-
	Visual examination (appearance & marking)	No damage		X		-	-	-	-	-	-	-	-
	Insulating resistance	IR ≥5MΩ		X		-	-	-	-	-	-	-	-
	Vibration test		Х		-		-	-	-	-	-	-	-
	Visual examination (aspect)	No damage		Х	-	•	-	-	-	-	-	-	-
	Locking test	195N <insertion force<285n<="" td=""><td></td><td>X</td><td>-</td><td>•</td><td>-</td><td>-</td><td>-</td><td>-</td><td>-</td><td>-</td><td>-</td></insertion>		X	-	•	-	-	-	-	-	-	-
- 1	Watertightness IPx4	No water trace on actives parts		X	-		-	-	-	_	-	-	-
	Dust resistance IP5x	No dust trace on actives parts		X	-		-	-	-	-	-	-	-
	Resistance to fluids		X		_		-		-		-		-
	Visual examination (appearance & marking)	No defect – marking visible		Х	_		_		_		_		_
	Withstand voltage	Leakage current ≤2mA		X	_		_				_	•	-
	Insulating resistance	IR ≥5MΩ		X	_						_		_
	Rapid variations of temperature		Х	, , , , , , , , , , , , , , , , , , ,	_	_		-	٠.	-	-	-	-
	Visual examination (appearance & marking)	No defect		X		_		-	_	-	-	-	-
	Insulating resistance	IR ≥5MΩ		X	_	_		_			_	_	_
	Mechanical endurance		X		_	-		_	_	_	_	_	-
2	Visual examination (appearance)	No damage		X		_		-	_	-	-	-	-
_	Locking test	195N <insertion force<285n<="" td=""><td></td><td>X</td><td>_</td><td>_</td><td></td><td>_</td><td>_</td><td>_</td><td>-</td><td>-</td><td>_</td></insertion>		X	_	_		_	_	_	-	-	_
	Contact resistance	Rc≤0.35mΩ		X	-	-		-	_	-	-	-	-
	Jumper head retention		X		_	_		_	-	_	_	-	_
	Visual examination (appearance)	No damage		X	_	_					_	_	_
	Temperature rise	ΔT ≤ 50 K @ 30A	Х	, , , , , , , , , , , , , , , , , , ,	_	_	-	-	_	_		_	-
	Corrosion		X		_	_	_	_			- -	_	_
	Visual examination (appearance & marking)	No damage		X	-	_				_	_	_	_
3	Insulating resistance	IR ≥5MΩ		X	_	_		_				_	_
Ŭ	Shocks		X		-	_		_		_	_	-	_
	Visual examination (appearance)	No damage		X	_	_		_		_	_	_	_
	Locking test	195N <insertion force<285n<="" td=""><td></td><td>X</td><td>_</td><td>_</td><td></td><td>_</td><td></td><td>_</td><td>_</td><td>_</td><td>_</td></insertion>		X	_	_		_		_	_	_	_
	Dry heat		Х	^	_	_	 	 	_			_	
	Visual examination (appearance & marking)	No damage		X	_							-	
	Contact resistance	Rc≤0.35mΩ		X									
4	Insulating resistance	IR ≥5MΩ		X	-	<u> </u>	-			<u> </u>		-	_
	Mechanical resistance to impact (drop test)	II (= OIVILZ	X	^									
	Visual examination (appearance)	No damage		X	-	-		-	-			-	-
	Locking test	195N <insertion force<285n<="" td=""><td></td><td>T X</td><td>-</td><td>-</td><td></td><td></td><td></td><td>-</td><td></td><td></td><td></td></insertion>		T X	-	-				-			
	Looking test	10014/113011101110100/20014		^	-								
5	Traction resistance of the crimped connection	F≥180N	Х				5 pairs	s of contact	s of each o	able sectio	n range		


Test to realized
- Test not to realized



APPENDIX 2: Assembly drawings of the test samples


MU plug control – reference E1894-212075 – revision C








MU receptacle control - reference E1894-211942 - revision C









Plug communication - reference E1894-212093 - revision C






Receptacle communication - reference E1894-211943 - revision C









Typical AEM-7 plug – reference E1894-212094 – revision C






Receptacle typical of AEM-7 plug - reference E1894-212085 - revision C








Communication commuter plug - reference E1894-212095 - revision C








Communication commuter receptacle – reference E1894-212086 – revision C



24 May 2018




Dummy receptacle – reference E1894-211944 – revision E







APPENDIX 3: Insulation Coordination



24 May 2018