Table of Contents

Single Pole, Electrically Held, 1 Amp and Less	1-2 – 1-9
1MA, 1MAD, 1MADD	1-2, 1-3
1MS, 1MSD, 1MSDD	1-4, 1-5
1MAT	1-6, 1-7
1MST	
Double Pole, Electrically Held, 1 Amp and Less	1-10 – 1-35
MA, MAD, MADD	1-10, 1-11
MS, MSD, MSDD	1-12, 1-13
HM, HMD, HS, HSD	1-14, 1-15
MGA, MGAD, MGADD	1-16, 1-17
MGS, MGSD, MGSDD	1-18, 1-19
HC, HCD, HCS, HCSD	1-20, 1-21
MAT	
MST	1-24, 1-25
MGAT	1-26, 1-27
MGST	
SMGA, SMGAD, SMGADD	
SMGS, SMGSD, SMGSDD	
SHC, SHCD, SHCS, SHCSD	
Double Pole, Electrically Held, 2 Amps and Less	1-36 – 1-46
HFW, HMB, HMS	
3SCV	
HFC	
3SBC	
3SCC	
3SAC, 3SAE	
Double Pole, Magnetic Latching, 2 Amps and Less	
LS	•
3SDM	
3SAM	·
Four Pole, Electrically Held, 2 Amps and Less	
SR	•
3SBH	1-55 – 1-57
3SDH	•
Four Pole, Magnetic Latching, 2 Amps and Less	
3SBM	
Six Pole, Electrically Held, 2 Amps and Less	
SS	
Double Pole, Electrically Held, 5 Amps and Less	
HFW4A, HFW5A	
HFC4A, HFC5A	
FW, FW5A, SF, SF5A	
Single Pole, Electrically Held, 10 Amps and Less	
C	
Double Pole, Electrically Held, 10 Amps and Less	
0.7	1_71 1_72




Single Pole, Electrically Held, 1 Amp and Less

1MA, 1MAD, 1MADD

1MA

Standard TO-5 High Performance Relay Qualified to MIL-R-39016/7




Terminal View

Product Facts

- Hermetically sealed
- High shock & vibration ratings
- Spreader pad
- **■** Excellent RF switching

1MAD

Standard TO-5 Diode Suppressed High Performance Relay Qualified to MIL-R-39016/23



Terminal View


Product Facts

- Suppression diode
- Hermetically sealed
- High shock & vibration ratings
- Spreader pad
- **■** Excellent RF switching

1MADD

Standard TO-5 Diode Suppressed/Protected High Performance Relay

Qualified to MIL-R-39016/24



Terminal View

Product Facts

- Suppression & protection diodes
- Hermetically sealed
- High shock & vibration ratings
- Spreader pad
- **■** Excellent RF switching

Electrical Characteristics

Contact Arrangement — 1 Form C (SPDT)

Contact Material -

Stationary — Gold/platinum/palladium/silver alloy (gold plated)

Moveable -

Gold/platinum/palladium/silver alloy (gold plated)

Contact Resistance —

Before Life — 100 milliohms max. (measured @ 10 mA @ 6 Vdc) After Life — 200 milliohms max. (measured @ 1 A @ 28 Vdc)

Mechanical Life Expectancy — 1 million operations

Coil Voltage — 5 to 26.5 Vdc

Coil Power — 512 mW max. @ 25°C

Duty Cycle — Continuous


Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity -


100 mW max. @ 25°C

Contact Load	Туре	Operations MINd.
1.0 A @ 28 Vdc	Resistive	100,000
250 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive (case not grounded)	100,000
100 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.2 A @ 28 Vdc	Inductive (0.32 Henry)	100,000
0.1 A @ 28 Vdc	Lamp	100,000
30 μA @ 50 mVdc	Low Level	1,000,000
0.1 A @ 28 Vdc	Intermediate Current	50,000





1MA/1MAD/1MADD Enclosure



1MA/1MAD/1MADD Header

1MA, 1MAD, 1MADD

(Continued)

Operating Characteristics

Timing —

Operate Time — 2.0 ms max.
Release Time —
1MA — 2.0 ms max.
1MAD/1MADD — 4.0 ms max.
(suppression diode, suppression/steering diodes)

Contact Bounce — 1.5 ms max
Dielectric Withstanding Voltage —

Between Open Contacts — 500 Vrms 60 Hz Between Adjacent Contacts — 500 Vrms 60 Hz Between Contacts & Coil — 500 Vrms 60 Hz

Insulation Resistance —

10,000 megohms @ 500 Vdc 1,000 megohms @ 500 Vdc (coil to case @ +125°C)

Environmental Characteristics

Temperature Range —

-65°C to +125°C

Weight —

0.08 oz. (2.27 grms) 0.09 oz. (2.52 grms) with spreader pad

attache

Vibration Resistance —

30 G's, 10 to 3,000 Hz

Shock Resistance -

75 G's, 6 ± 1 ms max.


QPL Approval -

MIL-R-39016/7 (J1MA) MIL-R-39016/23 (J1MAD) MIL-R-39016/24 (J1MADD)

Semiconductor Characteristics

Diode -

100 Vdc peak inverse voltage (PIV) 1.0 Vdc max. transient voltage



Spreader & Mounting Pads

Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C (Note 1)	Coil Circuit Current mA (Max.) (Note 1&2)	Coil Circuit Current mA (Min.) (Note 1&2)	Pickup Voltage Vdc (Max.) @ 25°C (Note 2)	Base Turn On Current mA (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C (Note 2)	Base Turn On Current mA (Max.) @ 125°C	Drop-Out Voltage Vdc (Min.) @ 25°C (Note 2)	Drop-Out Voltage Vdc (Min.) @ -65°C (Note 2)	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
1MA/MAD												
5.0	63	n/a	n/a	2.8	n/a	3.7	n/a	0.23	0.15	397	6.0	5
6.0	125	n/a	n/a	3.5	n/a	4.5	n/a	0.28	0.18	288	8.0	6
9.0	280	n/a	n/a	5.3	n/a	6.8	n/a	0.54	0.35	289	12.0	9
12.0	500	n/a	n/a	7.0	n/a	9.0	n/a	0.63	0.40	288	16.0	12
18.0	1,130	n/a	n/a	10.5	n/a	13.5	n/a	0.91	0.58	287	24.0	18
26.5	2,000	n/a	n/a	14.2	n/a	18.0	n/a	1.37	0.89	351	32.0	26
1MADD												
5.0	50	100.0	72.7	3.5	n/a	4.5	n/a	0.23	0.15	500	6.0	5
6.0	98	62.4	46.3	4.1	n/a	5.5	n/a	0.28	0.18	367	8.0	6
9.0	280	33.7	25.9	6.3	n/a	7.8	n/a	0.54	0.35	289	12.0	9
12.0	500	25.6	20.0	8.0	n/a	10.0	n/a	0.63	0.40	288	16.0	12
18.0	1,130	17.2	13.6	11.6	n/a	14.5	n/a	0.91	0.58	287	24.0	18
26.5	2,000	14.4	11.5	15.4	n/a	19.0	n/a	1.37	0.89	351	32.0	26

Notes: 1. Coil resistance not directly measurable. Coil current should be within limits shown when tested at nominal voltage at 25°C for 5 seconds max. 2. Set base current at 3 mA to 15 mA during measurements.

Ordering Instructions

Specifying a Part Number Example*:	<u>Type</u>	<u>Terminal</u>	<u>Diodes</u>	<u>Coils</u>	Spreader/Mounting Pads
	1MA	С	D	-26	S


^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.



1MS, 1MSD, 1MSDD

1MS

Sensitive TO-5 High Performance Relay Qualified to MIL-R-39016/10



Terminal View


Product Facts

- Hermetically sealed
- High shock & vibration ratings
- Spreader pad
- **■** Excellent RF switching

1MSD

Sensitive TO-5
Diode Suppressed
High Performance Relay
Ouglified to

Qualified to MIL-R-39016/25



Terminal View


Product Facts

- Suppression diode
- Hermetically sealed
- High shock & vibration ratings
- Spreader pad
- **■** Excellent RF switching

1MSDD

Sensitive TO-5 Diode Suppressed/Protected High Performance Relay

Qualified to MIL-R-39016/26



Terminal View

Product Facts

- Suppression & protection diodes
- Hermetically sealed
- High shock & vibration ratings
- Spreader pad
- **■** Excellent RF switching

Electrical Characteristics Contact Arrangement —

1 Form C (SPDT)

Contact Material -

Stationary — Gold/platinum/palladium/silver alloy (gold plated)

Moveable —

Gold/platinum/palladium/silver alloy (gold plated)

Contact Resistance —

Before Life — 100 milliohms max. (measured @ 10 mA @ 6 Vdc) After Life — 200 milliohms max. (measured @ 1 A @ 28 Vdc)

Mechanical Life Expectancy — 1 million operations

Coil Voltage — 5 to 40 Vdc

Coil Power — 506 mW max. @ 25° C


Duty Cycle — Continuous

Pick-up Voltage — Approximately 50% of nominal coil voltage


Pick-up Sensitivity – 40 mW max. @ 25°C

Contact Load	Туре	Operations MINd.
1.0 A @ 28 Vdc	Resistive	100,000
250 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive (case not grounded)	100,000
100 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.2 A @ 28 Vdc	Inductive (0.32 Henry)	100,000
0.1 A @ 28 Vdc	Lamp	100,000
30 μA @ 50 mVdc	Low Level	1,000,000
0.1 A @ 28 Vdc	Intermediate Current	50,000





1MS/1MSD/1MSDD Enclosure



1MS/1MSD/1MSDD Header



1MS, 1MSD, 1MSDD

(Continued)

Operating Characteristics

Timing —

Operate Time — 4.0 ms max.
Release Time —
1MS — 2.5 ms max.
1MSD/1MSDD — 7.5 ms max.
(suppression diode, suppression/steering diodes)

Contact Bounce — 1.5 ms max
Dielectric Withstanding Voltage —

Between Open Contacts — 500 Vrms 60 Hz Between Adjacent Contacts — 500 Vrms 60 Hz Between Contacts & Coil — 500 Vrms 60 Hz

Insulation Resistance —

10,000 megohms @ 500 Vdc 1,000 megohms @ 500 Vdc (coil to case @ +125°C)

Environmental Characteristics

Temperature Range —

-65°C to +125°C

Weight —

0.10 oz. (2.84 grms)

0.11 oz. (3.09 grms) with spreader pad attached

Vibration Resistance —

30 G's, 10 to 3,000 Hz

Shock Resistance -

75 G's, 6 ± 1 ms max.

QPL Approval -


MIL-R-39016/10 (J1MS) MIL-R-39016/25 (J1MSD)

MIL-R-39016/26 (J1MSDD)

Semiconductor Characteristics

Diode -

100 Vdc peak inverse voltage (PIV) 1.0 Vdc max. transient voltage



Spreader & Mounting Pads

Coil Data

Guii Data												
Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C (Note 1)	Coil Circuit Current mA (Max.) (Note 1&2)	Coil Circuit Current mA (MINd) (Note 1&2)	Pickup Voltage Vdc (Max.) @ 25°C (Note 2)	Base Turn On Current mA (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C (Note 2)	Base Turn On Current mA (Max.) @ 125°C	Drop-Out Voltage Vdc (MINd) @ 25°C (Note 2)	Drop-Out Voltage Vdc (MINd) @ -65°C (Note 2)	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
1MS/MSD												
5.0	125	n/a	n/a	2.8	n/a	3.7	n/a	0.23	0.15	200	8.0	5
6.0	255	n/a	n/a	3.5	n/a	4.5	n/a	0.28	0.18	141	11.0	6
9.0	630	n/a	n/a	5.3	n/a	6.8	n/a	0.54	0.35	129	12.0	9
12.0	1,025	n/a	n/a	7.0	n/a	9.0	n/a	0.63	0.40	140	22.0	12
18.0	2,300	n/a	n/a	10.5	n/a	13.5	n/a	0.91	0.59	141	24.0	18
26.5	4,000	n/a	n/a	14.2	n/a	18.0	n/a	1.37	0.89	176	45.0	26
32.0	6,500	n/a	n/a	18.7	n/a	24.0	n/a	1.59	1.0	158	57.0	32
40.0	11,000	n/a	n/a	23.3	n/a	30.0	n/a	2.0	1.3	145	75.0	40
1MSDD												
5.0	100	50.0	36.3	3.5	n/a	4.5	n/a	0.23	0.15	250	8.0	5
6.0	200	30.6	22.7	4.1	n/a	5.5	n/a	0.28	0.18	180	11.0	6
9.0	630	15.0	11.5	6.3	n/a	7.8	n/a	0.54	0.35	129	16.0	9
12.0	1,025	12.5	9.7	8.0	n/a	10.0	n/a	0.63	0.40	140	22.0	12
18.0	2,300	8.5	6.7	11.6	n/a	14.5	n/a	0.91	0.58	141	33.0	18
26.5	4,000	7.2	5.7	15.4	n/a	19.0	n/a	1.37	0.89	176	45.0	26
32.0	6,500	5.4	4.3	17.0	n/a	21.0	n/a	1.5	0.95	158	57.0	32
40.0	11,000	4.0	3.2	22.0	n/a	27.0	n/a	2.0	1.28	145	75.0	40

Notes: 1. Coil resistance not directly measurable. Coil current should be within limits shown when tested at nominal voltage at 25°C for 5 seconds max.

Ordering Instructions

Specifying a Part Number Example:	<u>Type</u>	<u>Terminal</u>	<u>Diodes</u>	<u>Coils</u>	Spreader/Mounting Pads
	1MS	С	D	-26	S

^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.




^{2.} Set base current at 3 mA to 15 mA during measurements.

1MAT

1MAT

Standard TO-5 **Diode Suppressed/ Transistor Driven High Performance Relay**

> Qualified to MIL-R-28776/5



Terminal View

Product Facts

- **■** Transistor driver & suppression diode
- Hermetically sealed
- High shock & vibration ratings
- Spreader pad
- **■** Excellent RF switching

Electrical Characteristics

Contact Arrangement — 1 Form C (SPDT)

Contact Material —

Stationary -Gold/platinum/palladium/silver alloy (gold plated)

Moveable -

Gold/platinum/palladium/silver alloy (gold plated)

Contact Resistance —

Before Life — 100 milliohms max. (measured @ 10 mA @ 6 Vdc) After Life — 200 milliohms max. (measured @ 1 A @ 28 Vdc)

Mechanical Life Expectancy —

1 million operations

Coil Voltage - 5 to 26.5 Vdc


Coil Power — 512 mW max. @ 25°C

Duty Cycle — Continuous

Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity -100 mW max. @ 25°C

Contact Load	Туре	Operations MINd.
1.0 A @ 28 Vdc	Resistive	100,000
250 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive (case not grounded)	100,000
100 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.2 A @ 28 Vdc	Inductive (0.32 Henry)	100,000
0.1 A @ 28 Vdc	Lamp	100,000
30 μA @ 50 mVdc	Low Level	1,000,000
0.1 A @ 28 Vdc	Intermediate Current	50,000



1MAT Enclosure



1MAT (Continued)

Operating Characteristics

Timing —

Operate Time — 2.0 ms max. Release Time — 4.0 ms max.

Contact Bounce — 1.5 ms max Dielectric Withstanding Voltage —

Between Open Contacts — 500 Vrms 60 Hz Between Adjacent Contacts — 500 Vrms 60 Hz Between Contacts & Coil — 500 Vrms 60 Hz

Insulation Resistance —

10,000 megohms @ 500 Vdc 1,000 megohms @ 500 Vdc (coil to case @ +125°C)

Environmental Characteristics

Temperature Range —

-65°C to +125°C

Weight -

0.08 oz. (2.27 grms) 0.09 oz. (2.52 grms) with spreader pad

Vibration Resistance —

30 G's, 10 to 3,000 Hz

Shock Resistance –

75 G's, 6 ± 1 ms max.

QPL Approval -

MIL-R-28776/5 (J1MAT)


Semiconductor Characteristics

Diode -

100 Vdc peak inverse voltage (PIV) 1.0 Vdc max. transient voltage

Transistor —

0.3 Vdc MINd. base turn off voltage; 6.0 Vdc min. emitter-base breakdown voltage (BV $_{EBO}$) @ 25°C; 80.0 Vdc min. collector-base breakdown voltage (BV $_{CBO}$) @ 25°C & I $_{C}$ =100 μ A



Spreader & Mounting Pads

Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C (Note 1)	Coil Circuit Current mA (Max.) (Note 1&2)	Coil Circuit Current mA (MINd) (Note 1&2)	Pickup Voltage Vdc (Max.) @ 25°C (Note 2)	Base Turn On Current mA (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C (Note 2)	Base Turn On Current mA (Max.) @ 125°C	Drop-Out Voltage Vdc (MINd) @ 25°C (Note 2)	Drop-Out Voltage Vdc (MINd) @ -65°C (Note 2)	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
1MAT												
5.0	63	89.6	66.6	3.0	0.60	3.9	2.38	0.24	0.15	397	5.8	5
6.0	125	55.5	42.0	3.8	0.42	5.2	1.60	0.31	0.18	288	8.0	6
9.0	280	38.1	28.0	5.6	0.27	7.8	1.07	0.47	0.35	289	12.0	9
12.0	500	28.1	20.9	7.2	0.21	10.0	0.80	0.62	0.40	288	16.0	12
18.0	1,130	18.8	13.8	10.7	0.12	14.5	0.53	0.94	0.58	287	24.0	18
26.5	2,000	15.5	11.5	14.4	0.10	19.0	0.40	1.25	0.89	351	32.0	26

Notes: 1. Coil resistance not directly measurable. Coil current should be within limits shown when tested at nominal voltage at 25°C for 5 seconds max.

Ordering Instructions

Specifying a Part Number Example:	<u>Type</u>	<u>Terminal</u>	<u>Diodes</u>	<u>Coils</u>	Spreader/Mounting Pads
	1MA	С	Т	-26	S

^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.




^{2.} Set base current at 3 mA to 15 mA during measurements.

1MST

1MST

Sensitive TO-5 **Diode Suppressed/ Transistor Driven High Performance Relay** Qualified to MIL-R-28776/4



Terminal View

Product Facts

- Transistor driver & suppression diode
- Hermetically sealed
- High shock & vibration ratings
- Spreader pad
- **■** Excellent RF switching

Electrical Characteristics

Contact Arrangement — 1 Form C (SPDT)

Contact Material —

Stationary -

Gold/platinum/palladium/silver alloy (gold plated)

Moveable -

Gold/platinum/palladium/silver alloy (gold plated)

Contact Resistance —

Before Life — 100 milliohms max. (measured @ 10 mA @ 6 Vdc) After Life — 200 milliohms max. (measured @ 1 A @ 28 Vdc)

Mechanical Life Expectancy —

1 million operations

Coil Voltage - 5 to 40 Vdc

Coil Power — 506 mW max. @ 25°C


Duty Cycle — Continuous


Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity -40 mW max. @ 25°C

1.0 A @ 28 Vdc	Resistive	100,000
250 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive (case not grounded)	100,000
100 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.2 A @ 28 Vdc	Inductive (0.32 Henry)	100,000
0.1 A @ 28 Vdc	Lamp	100,000
30 μA @ 50 mVdc	Low Level	1,000,000
0.1 A @ 28 Vdc	Intermediate Current	50,000







1MST Enclosure



1MST (Continued)

Operating Characteristics

Timing — Operate Time —

3.5 ms max. Release Time — 7.5 ms max.

Contact Bounce — 1.5 ms max

Dielectric Withstanding Voltage —

Between Open Contacts — 500 Vrms 60 Hz Between Adjacent Contacts — 500 Vrms 60 Hz Between Contacts & Coil — 500 Vrms 60 Hz

Insulation Resistance —

10,000 megohms @ 500 Vdc 1,000 megohms @ 500 Vdc (coil to case @ +125°C)

Environmental Characteristics

Temperature Range — -65°C to +125°C

Weight —

0.10 oz. (2.84 grms)

0.11 oz. (3.09 grms) with spreader pad attached

Vibration Resistance —

30 G's, 10 to 3,000 Hz

Shock Resistance – 75 G's, 6 ±1 ms max.

QPL Approval —

MIL-R-28776/4 (J1MST)


Semiconductor Characteristics

Diode -

100 Vdc peak inverse voltage (PIV) 1.0 Vdc max. transient voltage

Transistor —

0.3 Vdc min. base turn off voltage; 6.0 Vdc min. emitter-base breakdown voltage (BV_{EBO}) @ 25°C; 80.0 Vdc min. collector-base breakdown voltage (BV_{CBO}) @ 25°C & I_C=100 μA



Spreader & Mounting Pads

Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C (Note 1)	Coil Circuit Current mA (Max.) (Note 1&2)	Coil Circuit Current mA (Min.) (Note 1&2)	Pickup Voltage Vdc (Max.) @ 25°C (Note 2)	Base Turn On Current mA (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C (Note 2)	Base Turn On Current mA (Max.) @ 125°C	Drop-Out Voltage Vdc (Min.) @ 25°C (Note 2)	Drop-Out Voltage Vdc (Min.) @ -65°C (Note 2)	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
1MST												
5.0	125	47.8	34.7	2.6	0.28	3.6	1.20	0.22	0.15	200	8.0	5
6.0	255	27.7	21.2	3.5	0.20	4.8	0.78	0.28	0.18	141	11.0	6
9.0	630	16.8	11.8	5.4	0.13	7.8	0.48	0.54	0.35	129	16.0	9
12.0	1,025	13.6	10.1	6.6	0.10	10.0	0.39	0.63	0.41	140	22.0	12
18.0	2,300	9.1	6.7	9.8	0.07	14.5	0.26	0.91	0.58	141	33.0	18
26.5	4,000	7.7	5.7	12.8	0.05	19.0	0.20	1.37	0.89	176	45.0	26
32.0	6,500	5.8	4.2	18.7	0.04	24.0	0.16	1.60	1.00	158	57.0	32
40.0	11,000	4.3	3.1	23.3	0.03	30.0	0.13	2.10	1.30	145	75.0	40

Notes: 1. Coil resistance not directly measurable. Coil current should be within limits shown when tested at nominal voltage at 25°C for 5 seconds max.

Ordering Instructions

Specifying a Part Number Example:	<u>Type</u>	<u>Terminal</u>	<u>Diodes</u>	<u>Coils</u>	Spreader/Mounting Pads
	1MS	С	Т	-26	S

^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.



^{2.} Set base current at 3 mA to 15 mA during measurements.

Double Pole, Electrically Held, 1 Amp and Less

MA, MAD, MADD

MA

Standard TO-5 High Performance Relay Qualified to MIL-R-39016/9



Terminal View

Product Facts

- Hermetically sealed
- High shock & vibration ratings
- **■** Spreader pads
- **■** Excellent RF switching

MAD

Standard TO-5 Diode Suppressed High Performance Relay Qualified to MIL-R-39016/15



Terminal View


Product Facts

- Suppression diode
- Hermetically sealed
- High shock & vibration ratings
- Spreader pads
- **■** Excellent RF switching

MADD

Standard TO-5 Diode Suppressed/Protected High Performance Relay

Qualified to MIL-R-39016/20



Terminal View

Product Facts

- Suppression & protection diodes
- Hermetically sealed
- High shock & vibration ratings
- Spreader pads
- **■** Excellent RF switching

Electrical Characteristics Contact Arrangement —

2 Form C (DPDT)

Contact Material -

Stationary — Gold/platinum/palladium/silver alloy (gold plated)

Moveable — Gold/platinum/palladium/silver alloy

Contact Resistance —

Before Life — 100 milliohms max. (measured @ 10 mA @ 6 Vdc) After Life — 200 milliohms max. (measured @ 1 A @ 28 Vdc)

Mechanical Life Expectancy —

1 million operations

Coil Voltage -

(gold plated)

5 to 30 Vdc (MA/MAD) 5 to 26.5 Vdc (MADD)

Coil Power — 675 mW max. @ 25°C


Duty Cycle — Continuous

Pick-up Voltage — Approximately 50% of nominal coil voltage


Pick-up Sensitivity — 130 mW max. @ 25°C

Contact Load	Туре	Operations Min.
1.0 A @ 28 Vdc	Resistive	100,000
250 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive (case not grounded)	100,000
100 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.2 A @ 28 Vdc	Inductive (0.32 Henry)	100,000
0.1 A @ 28 Vdc	Lamp	100,000
30 μA @ 50 mVdc	Low Level	1,000,000
0.1 A @ 28 Vdc	Intermediate Current	50,000





Enclosure





MA, MAD, MADD (Continued)

Operating Characteristics

Timing –

Operate Time — 2.0 ms max.
Release Time —
MA — 1.5 ms max.
MAD/MADD — 4.0 ms max.
(suppression diode, suppression/
steering diodes)

Contact Bounce — 1.5 ms max
Dielectric Withstanding Voltage —

Between Open Contacts — 500 Vrms 60 Hz Between Adjacent Contacts — 500 Vrms 60 Hz Between Contacts & Coil — 500 Vrms 60 Hz

Insulation Resistance —

10,000 megohms min. @ 500 Vdc 1,000 megohms @ 500 Vdc (coil to case @ +125°C)

Environmental Characteristics

Temperature Range — -65°C to +125°C

Weight —

0.09 oz. (2.55 grms)

0.10 oz. (2.80 grms) with spreader pad attached

Vibration Resistance —

30 G's, 10 to 3,000 Hz

Shock Resistance –

75 G's, 6 ± 1 ms max.


QPL Approval — MIL-R-39016/9 (JMA)

MIL-R-39016/15 (JMAD) MIL-R-39016/20 (JMADD)

Semiconductor Characteristics

Diode -

100 Vdc peak inverse voltage (PIV) 1.0 Vdc max. transient voltage



Spreader & Mounting Pads



Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C (Note 1)	Coil Circuit Current mA (Max.) (Note 1&2)	Coil Circuit Current mA (Min.) (Note 1&2)	Pickup Voltage Vdc (Max.) @ 25°C (Note 2)	Base Turn On Current mA (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C (Note 2)	Base Turn On Current mA (Max.) @ 125°C	Drop-Out Voltage Vdc (Min.) @ 25°C (Note 2)	Drop-Out Voltage Vdc (Min.) @ -65°C (Note 2)	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
MA/MAD												
5.0	50	n/a	n/a	2.7	n/a	3.5	n/a	0.22	0.14	500	5.8	5
6.0	98	n/a	n/a	3.5	n/a	4.5	n/a	0.28	0.18	367	8.0	6
9.0	220	n/a	n/a	5.3	n/a	6.8	n/a	0.54	0.35	368	12.0	9
12.0	390	n/a	n/a	7.0	n/a	9.0	n/a	0.63	0.41	369	16.0	12
18.0	880	n/a	n/a	10.5	n/a	13.5	n/a	0.91	0.59	368	24.0	18
26.5	1,560	n/a	n/a	14.2	n/a	18.0	n/a	1.37	0.89	450	32.0	26
30.0	2,500	n/a	n/a	17.7	n/a	22.0	n/a	1.50	1.00	360	36.0	30
MADD												
5.0	39	128.2	93.2	3.2	n/a	4.0	n/a	0.6	0.6	641	5.8	5
6.0	78	78.3	58.3	4.0	n/a	5.0	n/a	0.7	0.7	462	8.0	6
9.0	220	42.9	33.0	6.3	n/a	7.8	n/a	0.9	0.8	368	12.0	9
12.0	390	32.8	25.6	8.0	n/a	10.0	n/a	1.1	0.9	369	16.0	12
18.0	880	22.1	17.5	11.5	n/a	14.5	n/a	1.4	1.1	368	24.0	18
26.5	1,560	18.5	14.8	15.2	n/a	19.0	n/a	1.8	1.4	450	32.0	26

Notes: 1. Coil resistance not directly measurable. Coil current should be within limits shown when tested at nominal voltage at 25°C for 5 seconds max.

Ordering Instructions

Specifying a Part Number Example:	<u>Type</u>	<u>Terminal</u>	<u>Diodes</u>	Ground Pins	<u>Coils</u>	Spreader/Mounting Pads
	MA	С	D	G	-26	S

^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.



^{2.} Set base current at 3 mA to 15 mA during measurements.

MS, MSD, MSDD

MS

Sensitive TO-5 High Performance Relay Qualified to MIL-R-39016/11



Terminal View

A3 🔾 L

Product Facts

- Suppression diode
- Hermetically sealed
- High shock & vibration ratings
- Spreader pads
- **■** Excellent RF switching

MSD

Sensitive TO-5
Diode Suppressed
High Performance Relay
Ouglified to

Qualified to MIL-R-39016/16



Terminal View

Product Facts

- Suppression & protection diodes
- Hermetically sealed
- High shock & vibration ratings

MSDD Sensitive TO-5 Diode

Suppressed/Protected

High Performance Relay

Qualified to

MIL-R-39016/21

Terminal View

- Spreader pads
- **■** Excellent RF switching

Product Facts

- **■** Hermetically sealed
- High shock & vibration ratings
- **■** Spreader pads
- **■** Excellent RF switching

Contact Ratings

Contact Load	Туре	Operations Min.
1.0 A @ 28 Vdc	Resistive	100,000
250 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive (case not grounded)	100,000
100 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.2 A @ 28 Vdc	Inductive (0.32 Henry)	100,000
0.1 A @ 28 Vdc	Lamp	100,000
30 μA @ 50 mVdc	Low Level	1,000,000
0.1 A @ 28 Vdc	Intermediate Current	50,000

Electrical Characteristics Contact Arrangement —

2 Form C (DPDT)

Contact Material -

Stationary — Gold/platinum/palladium/silver alloy (gold plated)

Moveable -

Gold/platinum/palladium/silver alloy (gold plated)

Contact Resistance —

Before Life — 100 milliohms max. (measured @ 10 mA @ 6 Vdc) After Life — 200 milliohms max. (measured @ 1 A @ 28 Vdc)

Mechanical Life Expectancy — 1 million operations


Coil Voltage — 5 to 48 Vdc

Coil Power — 565 mW max. @ 25°C


Duty Cycle — Continuous

Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity – 60 mW max. @ 25°C



Enclosure





MS, MSD, MSDD (Continued)

Operating Characteristics

Timing —

Operate Time — 4.0 ms max.
Release Time —
MS — 2.0 ms max.
MSD/MSDD — 7.5 ms max.
(suppression diode, suppression/
steering diodes)

Contact Bounce — 1.5 ms max
Dielectric Withstanding Voltage –

Between Open Contacts — 500 Vrms 60 Hz Between Adjacent Contacts — 500 Vrms 60 Hz Between Contacts & Coil — 500 Vrms 60 Hz

Insulation Resistance —

10,000 megohms min. @ 500 Vdc 1,000 megohms @ 500 Vdc (coil to case @ +125°C)

Environmental Characteristics Temperature Range —

-65°C to +125°C

Weight —

0.12 oz. (3.40 grms)

0.13 oz. (3.45 grms) with spreader pad attached

Vibration Resistance —

30 G's, 10 to 3,000 Hz

Shock Resistance –

75 G's, 6 ±1 ms max.


QPL Approval -

MIL-R-39016/11 (JMS) MIL-R-39016/16 (JMSD) MIL-R-39016/21 (JMSDD)

Semiconductor Characteristics

Diode -

100 Vdc peak inverse voltage (PIV) 1.0 Vdc max. transient voltage



Spreader & Mounting Pads

Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C (Note 1)	Coil Circuit Current mA (Max.) (Note 1&2)	Coil Circuit Current mA (Min.) (Note 1&2)	Pickup Voltage Vdc (Max.) @ 25°C (Note 2)	Base Turn On Current mA (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C (Note 2)	Base Turn On Current mA (Max.) @ 125°C	Drop-Out Voltage Vdc (Min.) @ 25°C (Note 2)	Drop-Out Voltage Vdc (Min.) @ -65°C (Note 2)	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
MS/MSD												
5.0	100	n/a	n/a	2.6	n/a	3.5	n/a	0.23	0.12	250	7.5	5
6.0	200	n/a	n/a	3.4	n/a	4.5	n/a	0.28	0.18	180	10.0	6
9.0	400	n/a	n/a	4.85	n/a	6.8	n/a	0.55	0.35	203	15.0	9
12.0	850	n/a	n/a	7.0	n/a	9.0	n/a	0.64	0.41	169	20.0	12
18.0	1,600	n/a	n/a	9.8	n/a	13.5	n/a	0.92	0.59	203	30.0	18
26.5	3,300	n/a	n/a	14.0	n/a	18.0	n/a	1.4	0.89	213	40.0	26
36.0	6,500	n/a	n/a	20.0	n/a	27.0	n/a	1.8	1.25	199	57.0	36
48.0	11,000	n/a	n/a	25.8	n/a	36.0	n/a	2.4	1.60	209	75.0	48
MSDD												
5.0	64	78.1	56.8	2.9	n/a	3.7	n/a	0.8	0.7	391	7.0	5
6.0	125	48.9	36.3	4.0	n/a	4.8	n/a	0.9	0.8	288	10.0	6
9.0	400	23.6	18.1	6.1	n/a	8.0	n/a	1.1	0.9	203	15.0	9
12.0	850	15.0	11.7	7.8	n/a	11.0	n/a	1.3	1.0	169	20.0	12
18.0	1,600	12.2	9.6	11.3	n/a	14.5	n/a	1.5	1.1	203	30.0	18
26.5	3,300	8.8	7.0	15.2	n/a	19.0	n/a	1.7	1.3	213	40.0	26
36.0	6,500	6.1	4.9	21.7	n/a	27.2	n/a	2.3	1.7	199	57.0	36
48.0	11,000	4.8	3.9	27.8	n/a	34.8	n/a	2.8	2.0	209	75.0	48

Notes: 1. Coil resistance not directly measurable. Coil current should be within limits shown when tested at nominal voltage at 25°C for 5 seconds max. 2. Set base current at 3 mA to 15 mA during measurements.

Ordering Instructions

Catalog-selected Relays: The catalog number is derived by choosing the proper CODE for each of the relay characteristics in the order in which the codes are listed.

Specifying a Part Number Example:TypeTerminalDiodesGround PinsCoilsSpreader/Mounting PadsMSCDG-26S

^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.



HM, HMD, HS, HSD



HM, HS Standard / Sensitive TO-5 Commercial Relay



Terminal View

Product Facts

- **■** Hermetically sealed
- Spreader Pads
- **■** Excellent RF switching

HMD, HSD

Standard / Sensitive TO-5 Diode Suppressed Commercial Relay



Terminal View

Product Facts

- **■** Suppression Diode
- Hermetically sealed
- **■** Spreader Pads
- **■** Excellent RF switching

Electrical Characteristics

Contact Arrangement –

2 Form C (DPDT)

Contact Material —

Stationary —

Gold/platinum/palladium/silver alloy (gold plated)

Moveable -

Gold/platinum/palladium/silver alloy (gold plated)

Contact Resistance —

Before Life — 100 milliohms max. (measured @ 10 mA @ 6 Vdc) After Life — 200 milliohms max. (measured @ 1 A @ 28 Vdc)

Mechanical Life Expectancy — 1 million operations

Electrical Characteristics

Coil Voltage -

5 to 30 Vdc (HM/HMD) 5 to 48 Vdc (HS/HSD)

Coil Power -


HM/HMD — 675 mW max. @ 25°C HS/HSD — 565 mW max. @ 25°C

Duty Cycle — Continuous

Pick-up Voltage — Approximately 70% of nominal coil voltage

Pick-up Sensitivity -

HM/HMD — 180 mW max. @ 25°C HS/HSD — 90 mW max. @ 25°C



Header

Contact Load	Туре	Operations Min.
1.0 A @ 28 Vdc	Resistive	100,000
250 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive (Case not grounded)	100,000
100 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.2 A @ 28 Vdc	Inductive (0.32 Henry)	100,000
0.1 A @ 28 Vdc	Lamp	100,000
30 μA @ 50 mVdc	Low Level	1,000,000



HM, HMD, HS, HSD

(Continued)

Operating Characteristics

Timing -

Operate Time -

HM/HMD — 4.0 ms max.

HS/HSD — 6.0 ms max.

Release Time -

HM — 3.0 ms max.

HS — 3.0 ms max.

HMD — 6.0 ms max. (suppression diode)

HSD — 7.5 ms max.

(suppression diode)

Dielectric Withstanding Voltage —

Between Open Contacts

350 Vrms 60 Hz

Between Adjacent Contacts —

350 Vrms 60 Hz

Between Contacts & Coil -

350 Vrms 60 Hz

Insulation Resistance —

1,000 megohms @ 500 Vdc

Environmental Characteristics

Temperature Range

-55°C to +85°C

Weight -

HM/HMD —

0.09 oz. (2.55 gms)

0.099 oz. (2.80 gms) w/ spreader pad

HS/HSD -

0.12 oz. (3.40 gms)

0.129 oz. (3.45 gms) w/ spreader pad

Vibration Resistance

10 G's, 10 to 500 Hz

Shock Resistance —

30 G's, 6 ±1 ms


Semiconductor Characteristics

Diode -

100 Vdc peak inverse voltage (PIV) 1.0 Vdc max. transient voltage


Standard Coil Data

	Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±20% @ 25°C	Pickup Voltage Vdc (max.) @ 25°C	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
HM/HMD	5.0	50	3.6	500	5.8	5
	6.0	98	4.2	367	8.0	6
	9.0	220	6.5	368	12.0	9
	12.0	390	8.4	369	16.0	12
	18.0	880	13.0	368	24.0	18
	26.5	1,560	17.0	450	32.0	26
	30.0	2,500	22.0	360	36.0	30
HS/HSD	5.0	100	3.5	250	7.5	5
	6.0	200	4.5	180	10.0	6
	9.0	400	6.8	203	15.0	9
	12.0	850	9.0	169	20.0	12
	18.0	1,600	13.5	203	30.0	18
	26.5	3,300	18.0	213	40.0	26
	36.0	6,500	24.0	199	57.0	36
	48.0	11,000	32.0	209	75.0	48





HS/HSD Enclosure



Spreader and Mounting Pads

Ordering Instructions

Catalog-selected Relays: The catalog number is derived by choosing the proper CODE for each of the relay characteristics in the order in which the codes are listed.

Spreader/Mounting Pads **Specifying a Part Number Example: Diodes Ground Pin Coils Terminals Type** HM D Χ 3 -26 В



MGA, MGAD, MGADD

MGA

Standard .100 Grid High Performance Relay Qualified to MIL-R-39016/17



Terminal View

- Hermetically sealed
- High shock & vibration ratings
- **■** Mounting pads

Product Facts

■ Excellent RF switching

MGAD

Standard .100 Grid Diode Suppressed High Performance Relay

Qualified to MIL-R-39016/18



Terminal View


Product Facts

- Suppression diode
- Hermetically sealed
- High shock & vibration ratings
- Mounting pads
- **■** Excellent RF switching

MGADD

Standard .100 Grid Diode Suppressed/Protected High Performance Relay

Qualified to MIL-R-39016/19



Terminal View

Product Facts

- Suppression & protection diodes
- Hermetically sealed
- High shock & vibration ratings
- Mounting pads
- **■** Excellent RF switching

Electrical Characteristics

Contact Arrangement —

2 Form C (DPDT)

Contact Material —

Stationary — Gold/platinum/palladium/silver (gold plated)

Moveable —

Gold/platinum/palladium/silver (gold plated)

Contact Resistance —

Before Life — 100 milliohms max. (measured @ 10 mA @ 6 Vdc) After Life — 200 milliohms max. (measured @ 1 A @ 28 Vdc)

Mechanical Life Expectancy — 1 million operations

Coil Voltage — 5 to 26.5 Vdc

Duty Cycle — Continuous


Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity — 130 mW max. @ 25°C


Contact Load	Туре	Operations Min.
1.0 A @ 28 Vdc	Resistive	100,000
250 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive (case not grounded)	100,000
100 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.2 A @ 28 Vdc	Inductive (0.32 Henry)	100,000
0.1 A @ 28 Vdc	Lamp	100,000
30 μA @ 50 mVdc	Low Level	1,000,000
0.1 A @ 28 Vdc	Intermediate Current	50,000



MGA



MGA/MGAD/MGADD Enclosure



MGA/MGAD/MGADD Header

MGA, MGAD, MGADD

(Continued)

Operating Characteristics

Timing -

Operate Time — 2.0 ms max.
Release Time —
MGA — 1.5 ms max.
MGAD/MGADD — 4.0 ms max.
(suppression diode, protection/
suppression diodes)

Contact Bounce — 1.5 ms max. Dielectric Withstanding Voltage

— Between Open Contacts — 500 Vrms 60 Hz Between Adjacent Contacts — 500 Vrms 60 Hz Between Contacts & Coil — 500 Vrms 60 Hz

Insulation Resistance —

10,000 megohms min. @ 500 Vdc 1,000 megohms @ 500 Vdc (coil to case @ +125°C)

Environmental Characteristics

Temperature Range —

-65°C to +125°C

Weight —

0.09 oz. (2.55 gms) 0.129 oz. (3.45 gms) w/ mounting pad

Vibration Resistance —

30 G's, 10 to 3,000 Hz

Shock Resistance -

75 G's, 6 ± 1 ms max.

QPL Approval -


MIL-R-39016/17 (JMGA) MIL-R-39016/18 (JMGAD) MIL-R-39016/19 (JMGADD)

Semiconductor Characteristics

Diode -

100 Vdc peak inverse voltage (PIV) 1.0 Vdc max. transient voltage

.014 ±.003 (0.36) ↑



MGA/MGAD/MGADD Mounting Pad

Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C (Note)	Coil Circuit Current mA (Max.) (Note)	Coil Circuit Current mA (Min.) (Note)	Pickup Voltage Vdc (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C	Drop-Out Voltage Vdc (Min.) @ 25°C	Drop-Out Voltage Vdc (Min.) @ -65°C	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
MGA/MGAD										
5.0	50	n/a	n/a	2.7	3.5	0.22	0.14	500	5.8	5
6.0	98	n/a	n/a	3.5	4.5	0.28	0.18	367	8.0	6
9.0	220	n/a	n/a	5.3	6.8	0.54	0.35	368	12.0	9
12.0	390	n/a	n/a	7.0	9.0	0.63	0.41	369	16.0	12
18.0	880	n/a	n/a	10.5	13.5	0.91	0.59	368	24.0	18
26.5	1,560	n/a	n/a	14.2	18.0	1.37	0.89	450	32.0	26
MGADD										
5.0	39	128.2	93.2	3.2	4.0	0.6	0.6	641	5.8	5
6.0	78	78.3	58.3	4.0	5.0	0.7	0.7	462	8.0	6
9.0	220	42.9	33.0	6.3	7.8	0.9	0.8	368	12.0	9
12.0	390	32.8	25.6	8.0	10.0	1.1	0.9	369	16.0	12
18.0	880	22.1	17.5	11.5	14.5	1.4	1.1	368	24.0	18
26.5	1,560	18.5	14.8	15.2	19.0	1.8	1.4	450	32.0	26

Note: Coil resistance not directly measurable. Coil current should be within limits shown when tested at nominal voltage at 25°C for 5 seconds max.

Ordering Instructions

Specifying a Part Number Example:	<u>Type</u>	<u>Terminals</u>	<u>Diodes</u>	Ground Pins	<u>Coils</u>	Mounting Pads
	MGA	С	D	G	-26	W

^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.



MGS, MGSD, MGSDD

MGS

Sensitive .100 Grid High Performance Relay Qualified to MIL-R-39016/41



Terminal View

Product Facts

- Hermetically sealed
- High shock & vibration ratings
- **■** Mounting pads

Contact Ratings

■ Excellent RF switching

MGSD

Sensitive .100 Grid Diode Suppressed High Performance Relay Qualified to

MIL-R-39016/42



Terminal View


Product Facts

- Suppression diode
- Hermetically sealed
- High shock & vibration ratings
- Mounting pads
- **■** Excellent RF switching

MGSDD

Sensitive .100 Grid Diode Suppressed/Protected High Performance Relay

Qualified to MIL-R-39016/43



Terminal View

Product Facts

- Suppression & protection diodes
- Hermetically sealed
- High shock & vibration ratings
- Mounting pads
- **■** Excellent RF switching

Operations Contact Type Load Min. 1.0 A @ 28 Vdc Resistive 100,000 250 mA @ 115 Vac, 60 Hz & 400 Hz Resistive (case not grounded) 100,000 100 mA @ 115 Vac, 60 Hz & 400 Hz Resistive 100,000 0.2 A @ 28 Vdc Inductive (0.32 Henry) 100,000 0.1 A @ 28 Vdc Lamp 100,000 30 μA @ 50 mVdc Low Level 1,000,000 0.1 A @ 28 Vdc Intermediate Current 50,000

Electrical Characteristics Contact Arrangement —

2 Form C (DPDT)

Contact Material —

Stationary — Gold/platinum/palladium/silver (gold plated)

Moveable —

Gold/platinum/palladium/silver (gold plated)

Contact Resistance —

Before Life — 100 milliohms max. (measured @ 10 mA @ 6 Vdc) After Life — 200 milliohms max. (measured @ 1 A @ 28 Vdc)

Mechanical Life Expectancy — 1 million operations

Coil Voltage — 5 to 48 Vdc

Coil Power — 565 mW max. @ 25°C

Duty Cycle — Continuous

Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity —

60 mW max. @ 25°C



- 375 (9.40) SQ MAX + 035 ± 035 (0.98)

- 1 - 1 - 100 (2.54)

GROUND PIN + 100 (0PTIONAL)
(2.54) + 100 (2.54) + 100

MGS/MGSD/MGSDD Enclosure

MGS/MGSD/MGSDD Header

Semiconductor Characteristics

100 Vdc peak inverse voltage (PIV)

1.0 Vdc max. transient voltage

Diode -

Double Pole, Electrically Held, 1 Amp and Less (Continued)

MGS, MGSD, MGSDD

(Continued)

Operating Characteristics

Timing -

Operate Time — 4.0 ms max.
Release Time —
MGS — 2.0 ms max.
MGSD/MGSDD — 7.5 ms max.
(suppression diode, protection/
suppression diodes)

Contact Bounce — 1.5 ms max.

Dielectric Withstanding Voltage— Between Open Contacts — 500 Vrms 60 Hz

Between Adjacent Contacts — 500 Vrms 60 Hz Between Contacts & Coil — 500 Vrms 60 Hz

Insulation Resistance —

10,000 megohms min. @ 500 Vdc 1,000 megohms @ 500 Vdc (coil to case @ +125°C)

Environmental Characteristics

Temperature Range —

-65°C to +125°C

Weight —

0.09 oz. (2.55 gms) 0.129 oz. (3.45 gms) w/ mounting pad

Vibration Resistance —


30 G's, 10 to 3,000 Hz


Shock Resistance -

75 G's, 6 ± 1 ms max.

QPL Approval -

MIL-R-39016/41 (JMGS) MIL-R-39016/42 (JMGSD) MIL-R-39016/43 (JMGSDD)





MGS/MGSD/MGSDD Mounting Pad

Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C (Note)	Coil Circuit Current mA (Max.) (Note)	Coil Circuit Current mA (Min.) (Note)	Pickup Voltage Vdc (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C	Drop-Out Voltage Vdc (Min.) @ 25°C	Drop-Out Voltage Vdc (Min.) @ -65°C	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
MGS/MGSD										
5.0	100	n/a	n/a	2.6	3.5	0.23	0.12	250	7.5	5
6.0	200	n/a	n/a	3.4	4.5	0.28	0.18	180	10.0	6
9.0	400	n/a	n/a	4.85	6.8	0.55	0.35	203	15.0	9
12.0	800	n/a	n/a	7.0	9.0	0.64	0.41	180	20.0	12
18.0	1,600	n/a	n/a	9.8	13.5	0.92	0.59	203	30.0	18
26.5	3,200	n/a	n/a	14.0	18.0	1.4	0.89	219	40.0	26
36.0	6,500	n/a	n/a	20.0	27.0	1.8	1.25	199	57.0	36
48.0	11,000	n/a	n/a	25.8	36.0	2.4	1.60	209	75.0	48
MGSDD										
5.0	64	78.1	56.8	2.9	3.7	0.8	0.7	391	7.5	5
6.0	125	48.9	36.3	4.0	4.8	0.9	0.8	288	10.0	6
9.0	400	23.6	18.1	6.1	8.0	1.1	0.9	203	15.0	9
12.0	800	16.0	12.5	7.8	11.0	1.3	1.0	180	20.0	12
18.0	1,600	12.2	9.6	11.3	14.5	1.5	1.1	203	30.0	18
26.5	3,200	9.0	7.2	15.2	19.0	1.7	1.3	219	40.0	26
36.0	6,500	6.1	4.9	21.7	27.2	2.3	1.7	199	57.0	36
48.0	11,000	4.8	3.9	27.8	34.8	2.8	2.0	209	75.0	48

Note: Coil resistance not directly measurable. Coil current should be within limits shown when tested at nominal voltage at 25°C for 5 seconds max.

Ordering Instructions

Specifying a Part Number Example:	<u>Type</u>	<u>Terminals</u>	<u>Diodes</u>	Ground Pins	<u>Coils</u>	Mounting Pads
	MGS	С	D	G	-26	W

^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.



HC, HCD, HCS, HCSD



HC, HCS

Standard / Sensitive .100 Grid Commercial Relay

Standard / Sensitive .100 Grid Diode Suppressed Commercial Relay



Terminal View



HCD, HCSD

Terminal View

Product Facts

- **■** Hermetically sealed
- **■** Mounting pads
- **■** Excellent RF switching

Product Facts

- Suppression diode
- **■** Hermetically sealed
- **■** Mounting pads
- **■** Excellent RF switching

Electrical Characteristics

Contact Arrangement —

2 Form C (DPDT)

Contact Material —

Stationary —

Gold/platinum/palladium/silver alloy (gold plated)

Moveable -

Gold/platinum/palladium/silver alloy (gold plated)

Contact Resistance —

Before Life — 100 milliohms max. (measured @ 10 mA @ 6 Vdc) After Life — 200 milliohms max. (measured @ 1 A @ 28 Vdc)

Mechanical Life Expectancy —

1 million operations

Coil Voltage —

5 to 26.5 Vdc (HC/HCD) 5 to 48 Vdc (HCS/HCSD)

Coil Power -


HC/HCD — 660 mW max. @ 25° C HCS/HCSD — 565 mW max. @ 25° C

Duty Cycle — Continuous


Pick-up Voltage — Approximately 70% of nominal coil voltage

Pick-up Sensitivity -

HC/HCD — 180 mW max. @ 25°C HCS/HCSD — 90 mW max. @ 25°C



Header



Mounting Pad

Contact Load	Туре	Operations Min.
1.0 A @ 28 Vdc	Resistive	100,000
250 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive (Case not grounded)	100,000
100 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.2 A @ 28 Vdc	Inductive (0.32 Henry)	100,000
0.1 A @ 28 Vdc	Lamp	100,000
30 µA @ 50 mVdc	Low Level	1 000 000



HC, HCD, HCS, HCSD

(Continued)

Operating Characteristics

Timing -Operate Time -HC/HCD — 4.0 ms max. HCS/HCSD — 6.0 ms max. Release Time — HC — 3.0 ms max. HCS — 3.0 ms max. HCD — 6.0 ms max.

(suppression diode) HCSD — 7.5 ms max. (suppression diode)

Dielectric Withstanding Voltage —

350 Vrms 60 Hz Between Adjacent Contacts — 350 Vrms 60 Hz

Insulation Resistance — 1,000 megohms @ 500 Vdc

Between Open Contacts -

Between Contacts & Coil -350 Vrms 60 Hz

Environmental Characteristics

Temperature Range -

-55°C to +85°C

Weight -

HC/HCD — 0.09 oz. (2.55 gms) HCS/HCSD 0.15 oz. (4.30 gms)

Vibration Resistance — 10 G's, 10 to 500 Hz

Shock Resistance —


30 G's, 6 ±1 ms

Semiconductor Characteristics

Diode -

100 Vdc peak inverse voltage (PIV) 1.0 Vdc max. transient voltage

Standard Coil Data Pickup Voltage Vdc (Max.) @ 25°C Nom. Coil Coil Resistance Nom. Coil Power Max. Coil Voltage Coil in Ohms ±20% @ 25°C (mW) @ 25°C Voltage Desig. (Vdc) HC/HCD 391 5.8 5.0 64 3.8 5 6.0 98 4.9 367 8.0 6 9.0 220 7.0 368 12.0 9 12.0 400 9.0 360 16.0 12 14.0 368 24.0 18.0 880 18 26.5 1,600 18.0 439 32.0 26 HCS/HCSD 250 5.0 100 3.5 7.5 5 200 4.5 180 10.0 6 6.0 9.0 400 6.8 203 15.0 9 180 12.0 800 9.0 20.0 12 1,600 203 18 18.0 13.5 30.0 26.5 3,200 18.0 219 26 40.0 36.0 6,500 24.0 199 57.0 36 48.0 11,000 32.0 209 75.0 48



Ordering Instructions


Specifying a Part Number Example:	<u>Type</u>	<u>Diodes</u>	<u>Ground Pin</u>	Mounting Pads	<u>Coils</u>	<u>Terminals</u>
	HC	D	Χ	3	-26	В



MAT

MAT

Standard TO-5
Diode Suppressed/
Transistor Driven
High Performance Relay
Qualified to MIL-R-28776/1



Terminal View

Product Facts

- Transistor driver & suppression diode
- Hermetically sealed
- High shock & vibration ratings
- Spreader pads
- **■** Excellent RF switching

Electrical Characteristics

Contact Arrangement — 2 Form C (DPDT)

Contact Material -

Stationary — Gold/platinum/palladium/silver alloy (gold plated)

Moveable –

Gold/platinum/palladium/silver alloy (gold plated)

Contact Resistance —

Before Life — 100 milliohms max. (measured @ 10 mA @ 6 Vdc) After Life — 200 milliohms max. (measured @ 1 A @ 28 Vdc)

Mechanical Life Expectancy —

1 million operations **Coil Voltage** — 5 to 26.5 Vdc

Coil Power — 675 mW max. @ 25°C

Duty Cycle — Continuous


Pick-up Voltage — Approximately 50% of nominal coil voltage


Pick-up Sensitivity -

130 mW max. @ 25°C

Contact Load	Туре	Operations Min.
1.0 A @ 28 Vdc	Resistive	100,000
250 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive (case not grounded)	100,000
100 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.2 A @ 28 Vdc	Inductive (0.32 Henry)	100,000
0.1 A @ 28 Vdc	Lamp	100,000
30 μA @ 50 mVdc	Low Level	1,000,000
0.1 A @ 28 Vdc	Intermediate Current	50,000







Enclosure



MAT (Continued)

Operating Characteristics

Timing —

Operate Time — 2.0 ms max. Release Time — 7.5 ms max. Contact Bounce — 1.5 ms max

Dielectric Withstanding Voltage —

Between Open Contacts 500 Vrms 60 Hz Between Adjacent Contacts — 500 Vrms 60 Hz Between Contacts & Coil -500 Vrms 60 Hz

Insulation Resistance —

10,000 megohms @ 500 Vdc 1,000 megohms @ 500 Vdc (coil to case @ +125°C)

Environmental Characteristics

Temperature Range —

-65°C to +125°C

Weight -

0.09 oz. (2.55 arms) 0.10 oz. (2.80 grms) with spreader pad

Vibration Resistance — 30 G's, 10 to 3,000 Hz

Shock Resistance -

75 G's, 6 ±1 ms max.

QPL Approval -

MIL-R-28776/1 (JMAT)


Semiconductor Characteristics

Diode -

100 Vdc peak inverse voltage (PIV) 1.0 Vdc max. transient voltage

Transistor -

0.3 Vdc min. base turn off voltage; 6.0 Vdc min. emitter-base breakdown voltage (BV_{FBO}) @ 25°C; 80.0 Vdc min. collector-base breakdown voltage (BV $_{\text{CBO}})$ @ 25°C & I $_{\text{C}}\text{=}100~\mu\text{A}$



Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C (Note 1)	Coil Circuit Current mA (Max.) (Note 1&2)	Coil Circuit Current mA (Min.) (Note 1&2)	Pickup Voltage Vdc (Max.) @ 25°C (Note 2)	Base Turn On Current mA (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C (Note 2)	Base Turn On Current mA (Max.) @ 125°C	Drop-Out Voltage Vdc (Min.) @ 25°C (Note 2)	Drop-Out Voltage Vdc (Min.) @ -65°C (Note 2)	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
MAT												
5.0	50	112.1	82.2	2.7	0.75	3.5	3.00	0.22	0.14	500	5.8	5
6.0	98	69.9	52.9	3.5	0.55	4.5	2.04	0.28	0.18	367	8.0	6
9.0	220	47.4	35.3	5.3	0.36	6.8	1.36	0.54	0.35	368	12.0	9
12.0	390	35.8	26.6	7.0	0.27	9.0	1.03	0.63	0.41	369	16.0	12
18.0	880	24.0	17.9	10.5	0.16	13.5	0.68	0.91	0.59	368	24.0	18
26.5	1,560	19.8	14.7	14.2	0.13	18.0	0.50	1.37	0.89	450	32.0	26

Notes: 1. Coil resistance not directly measurable. Coil current should be within limits shown when tested at nominal voltage at 25°C for 5 seconds max. 2. Set base current at 3 mA to 15 mA during measurements.

Ordering Instructions

Specifying a Part Number Example:	<u>Type</u>	<u>Terminal</u>	<u>Diodes</u>	Ground Pins	<u>Coils</u>	Spreader/Mounting Pads
	MA	С	Т	G	-26	S


^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.



MST

MST

Sensitive TO-5
Diode Suppressed/
Transistor Driven
High Performance Relay
Qualified to MIL-R-28776/3



Terminal View

Product Facts

- Transistor driver & suppression diode
- Hermetically sealed
- High shock & vibration ratings
- Spreader pads
- **■** Excellent RF switching

Electrical Characteristics

Contact Arrangement — 2 Form C (DPDT)

Contact Material –

Stationary —

Gold/platinum/palladium/silver alloy (gold plated)

Moveable -

Gold/platinum/palladium/silver alloy (gold plated)

Contact Resistance —

Before Life — 100 milliohms max. (measured @ 10 mA @ 6 Vdc) After Life — 200 milliohms max. (measured @ 1 A @ 28 Vdc)

Mechanical Life Expectancy — 1 million operations

Coil Voltage — 5 to 48 Vdc


Coil Power — 565 mW max. @ 25°C


Duty Cycle — Continuous

Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity - 60 mW max. @ 25°C

Contact Load	Туре	Operations Min.
1.0 A @ 28 Vdc	Resistive	100,000
250 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive (case not grounded)	100,000
100 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.2 A @ 28 Vdc	Inductive (0.32 Henry)	100,000
0.1 A @ 28 Vdc	Lamp	100,000
30 μA @ 50 mVdc	Low Level	1,000,000
0.1 A @ 28 Vdc	Intermediate Current	50,000





Enclosure



MST (Continued)

Operating Characteristics

Timing –

Operate Time — 4.0 ms max.
Release Time — 7.5 ms max.

Contact Bounce — 1.5 ms max

Dielectric Withstanding Voltage —

Between Open Contacts — 500 Vrms 60 Hz Between Adjacent Contacts — 500 Vrms 60 Hz Between Contacts & Coil — 500 Vrms 60 Hz

Insulation Resistance —

10,000 megohms min. @ 500 Vdc 1,000 megohms @ 500 Vdc (coil to case @ +125°C)

Environmental Characteristics

Temperature Range —

-65°C to +125°C

Weight —

0.12 oz. (3.40 grms) 0.13 oz. (3.45 grms) with spreader pad

attache

Vibration Resistance —

30 G's, 10 to 3,000 Hz

Shock Resistance –

75 G's, 6 ± 1 ms max.

QPL Approval -

MIL-R-28776/3 (JMST)


Semiconductor Characteristics

Diode -

100 Vdc peak inverse voltage (PIV) 1.0 Vdc max. transient voltage

Transistor —

0.3 Vdc min. base turn off voltage; 6.0 Vdc min. emitter-base breakdown voltage (BV $_{\rm EBO}$) @ 25°C; 80.0 Vdc min. collector-base breakdown voltage (BV $_{\rm CBO}$) @ 25°C & I $_{\rm C}$ =100 $\mu{\rm A}$



Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C (Note 1)	Coil Circuit Current mA (Max.) (Note 1&2)	Coil Circuit Current mA (Min.) (Note 1&2)	Pickup Voltage Vdc (Max.) @ 25°C (Note 2)	Base Turn On Current mA (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C (Note 2)	Base Turn On Current mA (Max.) @ 125°C	Drop-Out Voltage Vdc (Min.) @ 25°C (Note 2)	Drop-Out Voltage Vdc (Min.) @ -65°C (Note 2)	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
MST												
5.0	100	59.3	43.5	2.8	0.37	3.6	1.50	0.22	0.14	250	7.0	5
6.0	200	35.4	26.4	3.8	0.25	4.8	1.00	0.28	0.18	180	10.0	6
9.0	400	25.8	19.7	5.2	0.18	7.8	0.75	0.54	0.35	203	15.0	9
12.0	850	16.7	12.2	7.4	0.12	11.0	0.47	0.63	0.41	169	20.0	12
18.0	1,600	13.1	9.7	10.0	0.09	14.5	0.38	0.91	0.59	203	30.0	18
26.5	3,300	9.5	6.9	14.2	0.06	19.0	0.24	1.37	0.89	213	40.0	26
36.0	6,500	6.4	4.8	20.0	0.034	27.0	0.17	1.80	1.25	199	57.0	36
48.0	11,000	5.1	3.7	25.8	0.026	36.0	0.13	2.40	1.60	209	75.0	48

Notes: 1. Coil resistance not directly measurable. Coil current should be within limits shown when tested at nominal voltage at 25°C for 5 seconds max. 2. Set base current at 3 mA to 15 mA during measurements.

Ordering Instructions

Specifying a Part Number Example:	<u>Type</u>	<u>Terminal</u>	<u>Diodes</u>	Ground Pins	<u>Coils</u>	Spreader/Mounting Pads
	MS	С	Т	G	-26	S

^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.




MGAT

MGAT

Standard .100 Grid Diode Suppressed/MOSFET Driven High Performance Relay

Qualified to MIL-R-28776/6



Terminal View

Product Facts

- MOSFET driver, zener & suppression diodes
- **■** Hermetically sealed
- High shock & vibration ratings
- **■** Mounting pads
- **■** Excellent RF switching

Electrical Characteristics

Contact Arrangement —

2 Form C (DPDT)

Contact Material —

Stationary — Gold/platinum/palladium/silver

(gold plated) Moveable —

Gold/platinum/palladium/silver (gold plated)

Contact Resistance —

Before Life — 100 milliohms max. (measured @ 10 mA @ 6 Vdc) After Life — 200 milliohms max. (measured @ 1 A @ 28 Vdc)

Mechanical Life Expectancy — 1 million operations

Coil Voltage — 5 to 26.5 Vdc


Duty Cycle — Continuous


Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity — 130 mW max. @ 25°C

Contact Ratings

Contact Load	Туре	Operations Min.		
1.0 A @ 28 Vdc	Resistive	100,000		
250 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive (case not grounded)	100,000		
100 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000		
0.2 A @ 28 Vdc	Inductive (0.32 Henry)	100,000		
0.1 A @ 28 Vdc	Lamp	100,000		
30 μA @ 50 mVdc	Low Level	1,000,000		
0.1 A @ 28 Vdc	Intermediate Current	50,000		





GROUND PIN (0PTIONAL) 100 (2.54) WGAT Header

.375 (9.40) MAX

.031 ± .003 (0.79)



MGAT (Continued)

Operating Characteristics

Timing —

Operate Time — 2.0 ms max. **Contact Bounce** — 1.5 ms max.

Dielectric Withstanding Voltage

— Between Open Contacts — 500 Vrms 60 Hz Between Adiacent Contacts —

500 Vrms 60 Hz Between Contacts & Coil — 500 Vrms 60 Hz

Insulation Resistance —

10,000 megohms min. @ 500 Vdc 1,000 megohms @ 500 Vdc (coil to case @ +125°C)

Environmental Characteristics

Temperature Range —

-65°C to +125°C

Weight -

0.09 oz. (2.55 gms)

0.129 oz. (3.45 gms) w/ mounting pad attached

Vibration Resistance —

30 G's, 10 to 3,000 Hz

Shock Resistance -

75 G's, 6 ± 1 ms max.

QPL Approval -

MIL-R-28776/6 (JMGAT)

Semiconductor Characteristics

${\rm Diode}\,-$


100 Vdc peak inverse voltage (PIV) 1.0 Vdc max. transient voltage

Zener Diode -

20 Vdc ±3 Vdc over temperature range

MOSFET —

0.5 Vdc min. gate turn-off voltage 4.3 Vdc max. gate turn-on voltage



Coil Data

oon Data										
Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C (Note)	Coil Circuit Current mA (Max.) (Note)	Coil Circuit Current mA (Min.) (Note)	Pickup Voltage Vdc (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C	Drop-Out Voltage Vdc (Min.) @ 25°C	Drop-Out Voltage Vdc (Min.) @ -65°C	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
MGAT										
5.0	39	132.3	96.5	2.9	3.5	0.23	0.13	641	5.8	5
6.0	78	83.9	60.3	3.5	4.5	0.32	0.18	462	8.0	6
9.0	220	47.1	33.1	5.3	6.8	0.48	0.27	368	12.0	9
12.0	390	36.1	24.9	7.1	9.0	0.65	0.36	369	16.0	12
18.0	880	24.1	16.1	10.6	13.5	0.97	0.54	368	24.0	18
26.5	1,560	19.9	12.9	14.2	18.0	1.30	0.72	450	32.0	26

Note: Coil resistance not directly measurable. Coil current should be within limits shown when tested at nominal voltage at 25°C for 5 seconds max.

Ordering Instructions

Specifying a Part Number Example:	<u>Type</u>	<u>Terminals</u>	<u>Diodes</u>	Ground Pins	<u>Coils</u>	Mounting Pads
	MGA	С	Т	G	-26	W

^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.




MGST

MGST

Sensitive .100 Grid Diode Suppressed/MOSFET Driven High Performance Relay

Qualified to MIL-R-28776/7



Terminal View

Product Facts

- MOSFET driver, zener & suppression diodes
- **■** Hermetically sealed
- High shock & vibration ratings
- **■** Mounting pads
- **■** Excellent RF switching

Electrical Characteristics

Contact Arrangement —

2 Form C (DPDT)

Contact Material —

Stationary — Gold/platinum/palladium/silver

(gold plated) Moveable —

Gold/platinum/palladium/silver (gold plated)

Contact Resistance —

Before Life — 100 milliohms max. (measured @ 10 mA @ 6 Vdc) After Life — 200 milliohms max. (measured @ 1 A @ 28 Vdc)

Mechanical Life Expectancy — 1 million operations

Coil Voltage — 5 to 26.5 Vdc

 $\textbf{Coil Power} - 565 \text{ mW max.} @ 25^{\circ}\text{C}$


Duty Cycle — Continuous


Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity — 60 mW max. @ 25°C

Contact Load	Туре	Operations Min.
1.0 A @ 28 Vdc	Resistive	100,000
250 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive (case not grounded)	100,000
100 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.2 A @ 28 Vdc	Inductive (0.32 Henry)	100,000
0.1 A @ 28 Vdc	Lamp	100,000
30 μA @ 50 mVdc	Low Level	1,000,000
0.1 A @ 28 Vdc	Intermediate Current	50,000







MGST Header

MGST (Continued)

Operating Characteristics

Timing —

Operate Time — 4.0 ms max. Release Time — 7.5 ms max. Contact Bounce — 1.5 ms max.

Dielectric Withstanding Voltage

– Between Open Contacts -500 Vrms 60 Hz Between Adjacent Contacts — 500 Vrms 60 Hz Between Contacts & Coil -500 Vrms 60 Hz

Insulation Resistance —

10,000 megohms min. @ 500 Vdc 1,000 megohms @ 500 Vdc (coil to case @ +125°C)

Environmental Characteristics

Temperature Range —

-65°C to +125°C

Weight —

0.09 oz. (2.55 ams)

0.129 oz. (3.45 gms) w/ mounting pad

Vibration Resistance —

30 G's, 10 to 3,000 Hz

Shock Resistance —

75 G's, 6 ±1 ms max.

QPL Approval -

MIL-R-28776/7 (JMGST)

Semiconductor Characteristics

Diode -


100 Vdc peak inverse voltage (PIV) 1.0 Vdc max. transient voltage

Zener Diode -

20 Vdc ±3 Vdc over temperature range

MOSFET —

0.5 Vdc min. gate turn off voltage 4.3 Vdc max. gate turn on voltage



Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C (Note)	Coil Circuit Current mA (Max.) (Note)	Coil Circuit Current mA (Min.) (Note)	Pickup Voltage Vdc (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C	Drop-Out Voltage Vdc (Min.) @ 25°C	Drop-Out Voltage Vdc (Min.) @ -65°C	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
MGST										
5.0	100	56.0	43.0	2.9	4.0	0.23	0.13	250	5.6	5
6.0	200	33.0	27.0	3.5	4.9	0.32	0.18	180	8.0	6
9.0	400	26.4	17.8	5.3	7.3	0.48	0.27	203	12.0	9
12.0	800	17.7	11.3	7.1	9.8	0.65	0.36	180	16.0	12
18.0	1,600	13.8	8.4	10.6	14.6	0.97	0.54	203	24.0	18
26.5	3,200	10.2	5.8	14.2	19.5	1.30	0.72	219	32.0	26

Note: Coil resistance not directly measurable. Coil current should be within limits shown when tested at nominal voltage at 25°C for 5 seconds max.

Ordering Instructions

Specifying a Part Number Example:	<u>Type</u>	<u>Terminals</u>	<u>Diodes</u>	Ground Pins	<u>Coils</u>	Mounting Pads
	MGS	С	Т	G	-26	W

^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.



SMGA, SMGAD, SMGADD

SMGA

Standard .100 Grid Surface Mount High Performance Relay

Designed to MIL-R-39016/17



Terminal View

Product Facts

- **■** Hermetically sealed
- High shock & vibration ratings
- Surface mount leads
- **■** Excellent RF switching

SMGAD

Standard .100 Grid Diode Suppressed Surface Mount High Performance Relay

Designed to MIL-R-39016/18



Terminal View

Product Facts

- Suppression diode
- Hermetically sealed
- High shock & vibration ratings
- Surface mount leads
- **■** Excellent RF switching

SMGADD

Standard .100 Grid Diode Suppressed/Protected Surface Mount High Performance Relay

Designed to MIL-R-39016/19



Terminal View

Product Facts

- Suppression & protection diodes
- Hermetically sealed
- High shock & vibration ratings
- Surface mount leads
- **■** Excellent RF switching

Electrical Characteristics Contact Arrangement —

2 Form C (DPDT)

Contact Material -

Stationary — Gold/platinum/palladium/silver (gold plated)

Moveable —

Gold/platinum/palladium/silver (gold plated)

Contact Resistance —

Before Life — 100 milliohms max. (measured @ 10 mA @ 6 Vdc) After Life — 200 milliohms max. (measured @ 1 A @ 28 Vdc)

Mechanical Life Expectancy — 1 million operations

Coil Voltage — 5 to 26.5 Vdc


Duty Cycle — Continuous


Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity — 130 mW max. @ 25°C

Contact Load	Туре	Operations Min.
1.0 A @ 28 Vdc	Resistive	100,000
250 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive (case not grounded)	100,000
100 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.2 A @ 28 Vdc	Inductive (0.32 Henry)	100,000
0.1 A @ 28 Vdc	Lamp	100,000
30 μA @ 50 mVdc	Low Level	1,000,000
0.1 A @ 28 Vdc	Intermediate Current	50,000







Enclosure

Header

SMGA, SMGAD, SMGADD

(Continued)

Operating Characteristics

Timing -

Operate Time — 2.0 ms max.
Release Time —
SMGA — 1.5 ms max.
SMGAD/SMGADD — 4.0 ms max.
(suppression diode, protection/
suppression diodes)

Contact Bounce — 1.5 ms max.

Dielectric Withstanding Voltage

— Between Open Contacts — 500 Vrms 60 Hz Between Adjacent Contacts — 500 Vrms 60 Hz Between Contacts & Coil — 500 Vrms 60 Hz

Insulation Resistance —

10,000 megohms min. @ 500 Vdc 1,000 megohms @ 500 Vdc (coil to case @ +125°C)

Environmental Characteristics

Temperature Range —

-65°C to +125°C

Weight —

0.09 oz. (2.55 gms)

Vibration Resistance — 30 G's, 10 to 3,000 Hz


Shock Resistance -

75 G's, 6 ±1 ms max.

Semiconductor Characteristics

Diode —

100 Vdc peak inverse voltage (PIV) 1.0 Vdc max. transient voltage



Recommended Solder Pad Layout

Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C (Note)	Coil Circuit Current mA (Max.) (Note)	Coil Circuit Current mA (Min.) (Note)	Pickup Voltage Vdc (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C	Drop-Out Voltage Vdc (Min.) @ 25°C	Drop-Out Voltage Vdc (Min.) @ -65°C	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
SMGA/SMG	AD									
5.0	50	n/a	n/a	2.7	3.5	0.22	0.14	500	5.8	5
6.0	98	n/a	n/a	3.5	4.5	0.28	0.18	367	8.0	6
9.0	220	n/a	n/a	5.3	6.8	0.54	0.35	368	12.0	9
12.0	390	n/a	n/a	7.0	9.0	0.63	0.41	369	16.0	12
18.0	880	n/a	n/a	10.5	13.5	0.91	0.59	368	24.0	18
26.5	1,560	n/a	n/a	14.2	18.0	1.37	0.89	450	32.0	26
SMGADD										
5.0	39	128.2	93.2	3.2	4.0	0.6	0.6	641	5.8	5
6.0	78	78.3	58.3	4.0	5.0	0.7	0.7	462	8.0	6
9.0	220	42.9	33.0	6.3	7.8	0.9	0.8	368	12.0	9
12.0	390	32.8	25.6	8.0	10.0	1.1	0.9	369	16.0	12
18.0	880	22.1	17.5	11.5	14.5	1.4	1.1	368	24.0	18
26.5	1,560	18.5	14.8	15.2	19.0	1.8	1.4	450	32.0	26

Note: Coil resistance not directly measurable. Coil current should be within limits shown when tested at nominal voltage at 25°C for 5 seconds max.

Ordering Instructions

Specifying a Part Number Example:	<u>Type</u>	<u>Diode</u>	<u>Coils</u>
	SMGA	D	-26



SMGS, SMGSD, SMGSDD

SMGS

Sensitive .100 Grid Surface Mount High Performance Relay

> Designed to MIL-R-39016/41



Terminal View

Product Facts

- **■** Hermetically sealed
- High shock & vibration ratings
- Surface mount leads
- **■** Excellent RF switching

SMGSD

Sensitive .100 Grid Diode Suppressed Surface Mount High Performance Relay

Designed to MIL-R-39016/42



Terminal View

Product Facts

- Suppression diode
- Hermetically sealed
- High shock & vibration ratings
- Surface mount leads
- **■** Excellent RF switching

SMGSDD

Sensitive .100 Grid Diode Suppressed/Protected Surface Mount High Performance Relay

Designed to MIL-R-39016/43



Terminal View

Product Facts

- Suppression & protection diodes
- Hermetically sealed
- High shock & vibration ratings
- Surface mount leads
- **■** Excellent RF switching

Electrical Characteristics Contact Arrangement —

2 Form C (DPDT)

Contact Material —

Stationary — Gold/platinum/palladium/silver (gold plated)

Moveable — Gold/platinum/palladium/silver (gold plated)

Contact Resistance —

Before Life — 100 milliohms max. (measured @ 10 mA @ 6 Vdc) After Life — 200 milliohms max. (measured @ 1 A @ 28 Vdc)

Mechanical Life Expectancy — 1 million operations

Coil Voltage — 5 to 48 Vdc

Coil Power — 565 mW max. @ 25°C


Duty Cycle — Continuous

Pick-up Voltage — Approximately 50% of nominal coil voltage


Pick-up Sensitivity — 130 mW max. @ 25°C

Contact Load	Туре	Operations Min.
1.0 A @ 28 Vdc	Resistive	100,000
250 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive (case not grounded)	100,000
100 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.2 A @ 28 Vdc	Inductive (0.32 Henry)	100,000
0.1 A @ 28 Vdc	Lamp	100,000
30 μA @ 50 mVdc	Low Level	1,000,000
0.1 A @ 28 Vdc	Intermediate Current	50,000





Enclosure



Header

SMGS, SMGSD, SMGSDD

(Continued)

Operating Characteristics

Timing —

Operate Time — 4.0 ms max.
Release Time —
SMGS — 2.0 ms max.
SMGSD/SMGSDD — 7.5 ms max.
(suppression diode, protection/
suppression diodes)

Contact Bounce — 1.5 ms max. Dielectric Withstanding Voltage

— Between Open Contacts — 500 Vrms 60 Hz Between Adjacent Contacts — 500 Vrms 60 Hz Between Contacts & Coil — 500 Vrms 60 Hz

Insulation Resistance —

10,000 megohms min. @ 500 Vdc 1,000 megohms @ 500 Vdc (coil to case @ +125°C)

Environmental Characteristics

Temperature Range —

-65°C to +125°C

Weight —

0.09 oz. (2.55 gms)

Vibration Resistance —

30 G's, 10 to 3,000 Hz


Shock Resistance -

75 G's, 6 ±1 ms max.

Semiconductor Characteristics

Diode —

100 Vdc peak inverse voltage (PIV) 1.0 Vdc max. transient voltage



Recommended Solder Pad Layout

Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C (Note)	Coil Circuit Current mA (Max.) (Note)	Coil Circuit Current mA (Min.) (Note)	Pickup Voltage Vdc (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C	Drop-Out Voltage Vdc (Min.) @ 25°C	Drop-Out Voltage Vdc (Min.) @ -65°C	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
SMGS/SMG	SD									
5.0	100	n/a	n/a	2.6	3.5	0.23	0.12	250	7.5	5
6.0	200	n/a	n/a	3.4	4.5	0.28	0.18	180	10.0	6
9.0	400	n/a	n/a	4.85	6.8	0.55	0.35	203	15.0	9
12.0	800	n/a	n/a	7.0	9.0	0.64	0.41	180	20.0	12
18.0	1,600	n/a	n/a	9.8	13.5	0.92	0.59	203	30.0	18
26.5	3,200	n/a	n/a	14.0	18.0	1.4	0.89	219	40.0	26
36.0	6,500	n/a	n/a	20.0	27.0	1.8	1.25	199	57.0	36
48.0	11,000	n/a	n/a	25.8	36.0	2.4	1.60	209	75.0	48
SMGSDD										
5.0	64	78.1	56.8	2.9	3.7	0.8	0.7	391	7.5	5
6.0	125	48.9	36.3	4.0	4.8	0.9	0.8	288	10.0	6
9.0	400	23.6	18.1	6.1	8.0	1.1	0.9	203	15.0	9
12.0	800	16.0	12.5	7.8	11.0	1.3	1.0	180	20.0	12
18.0	1,600	12.2	9.6	11.3	14.5	1.5	1.1	203	30.0	18
26.5	3,200	9.0	7.2	15.2	19.0	1.7	1.3	219	40.0	26
36.0	6,500	6.1	4.9	21.7	27.2	2.3	1.7	199	57.0	36
48.0	11,000	4.8	3.9	27.8	34.8	2.8	2.0	209	75.0	48

Note: Coil resistance not directly measurable. Coil current should be within limits shown when tested at nominal voltage at 25°C for 5 seconds max.

Ordering Instructions

Specifying a Part Number Example:	<u>Type</u>	<u>Diode</u>	<u>Coils</u>
	SMGS	D	-26



SHC, SHCD, SHCS, SHCSD



SHC, SHCS

Standard / Sensitive .100 Grid Surface Mount Commercial Relay



Terminal View

Product Facts

- Hermetically sealed
- **■** Excellent RF switching

SHCD, SHCSD

Standard / Sensitive .100 Grid Surface Mount Diode Suppressed Commercial Relay



Terminal View

Product Facts

- Suppression Diode
- Hermetically sealed
- **■** Excellent RF switching

Electrical Characteristics

Contact Arrangement —

2 Form C (DPDT)

Contact Material —

Stationary — Gold/platinum/palladium/silver alloy

(gold plated) Moveable —

Gold/platinum/palladium/silver alloy (gold plated)

Contact Resistance —

Before Life — 100 milliohms max. (measured @ 10 mA @ 6 Vdc) After Life — 200 milliohms max. (measured @ 1 A @ 28 Vdc)

Mechanical Life Expectancy —

1 million operations

Coil Voltage —

5 to 26.5 Vdc (SHC/SHCD) 5 to 48 Vdc (SHCS/SHCSD)

Coil Power -

SHC/SHCD — 660 mW max. @ 25° C SHCS/SHCSD — 565 mW max. @ 25° C

Duty Cycle — Continuous

Pick-up Voltage — Approximately 70% of nominal coil voltage

Pick-up Sensitivity -

SHC/SHCD — 180 mW max. @ 25°C SHCS/SHCSD — 90 mW max. @ 25°C

Contact Load	Туре	Operations Min.
1.0 A @ 28 Vdc	Resistive	100,000
250 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive (Case not grounded)	100,000
100 mA @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.2 A @ 28 Vdc	Inductive (0.32 Henry)	100,000
0.1 A @ 28 Vdc	Lamp	100,000
30 μA @ 50 mVdc	Low Level	1,000,000



SHC, SHCD, SHCS, SHCSD

(Continued)

Operating Characteristics

Timing —
Operate Time —
SHC/SHCD — 4.0 ms max.
SHCS/SHCSD — 6.0 ms max.
Release Time —
SHC — 3.0 ms max.
SHCS — 3.0 ms max.
SHCD — 6.0 ms max.
(suppression diode)
SHCSD — 7.5 ms max.

Dielectric Withstanding Voltage —

Between Open Contacts —
350 Vrms 60 Hz
Between Adjacent Contacts —
350 Vrms 60 Hz
Between Contacts & Coil —
350 Vrms 60 Hz

Insulation Resistance —

(suppression diode)

1,000 megohms @ 500 Vdc

Environmental Characteristics

Temperature Range — -55°C to +85°C

Weight —

SHC/SHCD — 0.09 oz. (2.55 gms) SHCS/SHCSD — 0.15 oz. (4.30 gms)

Vibration Resistance -

10 G's, 10 to 500 Hz

Shock Resistance —

 $30 \text{ G's}, 6 \pm 1 \text{ ms}$


Semiconductor Characteristics

Diode –


100 Vdc peak inverse voltage (PIV) 1.0 Vdc max. transient voltage

Standard Coil Data


	Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±20% @ 25°C	Pickup Voltage Vdc (Max.) @ 25°C	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
SHC/SHCD	5.0	64	3.8	391	5.8	5
	6.0	98	4.9	367	8.0	6
	9.0	220	7.0	368	12.0	9
	12.0	400	9.0	360	16.0	12
	18.0	880	14.0	368	24.0	18
	26.5	1,600	18.0	439	32.0	26
SHCS/SHCSD	5.0	100	3.5	250	7.5	5
	6.0	200	4.5	180	10.0	6
	9.0	400	6.8	203	15.0	9
	12.0	800	9.0	180	20.0	12
	18.0	1,600	13.5	203	30.0	18
	26.5	3,200	18.0	219	40.0	26
	36.0	6,500	24.0	199	57.0	36
	48.0	11,000	32.0	209	75.0	48




SHC/SHCD Enclosure



SHC/SHCD/SHCS/SHCSD Header



SHCS/SHCSD Enclosure



Recommended Solder Pad Layout

Ordering Instructions

Catalog-selected Relays: The catalog number is derived by choosing the proper CODE for each of the relay characteristics in the order in which the codes are listed.

Specifying a Part Number Example:TypeDiodesCoilsSHCD-26




Double Pole, Electrically Held, 2 Amps and Less

HFW, HMB, HMS

HFW

Standard Half Size High Performance Relay Qualified to MIL-R-39016/6





Terminal View


Product Facts

- Hermetically sealed
- Up to 2 amps switching
- High shock & vibration ratings
- Optional terminals & mounting styles
- **■** Excellent RF switching

HMB

Bifilar Half Size High Performance Relay Qualified to MIL-R-39016/22





Terminal View


Product Facts

- **■** Hermetically sealed
- Up to 2 amps switching
- High shock & vibration ratings
- Optional terminals & mounting styles
- **■** Excellent RF switching

HMS

Sensitive Half Size High Performance Relay Qualified to MIL-R-39016/44





Terminal View

Product Facts

- Hermetically sealed
- Up to 2 amps switching
- High shock & vibration ratings
- Optional terminals & mounting styles
- **■** Excellent RF switching

Electrical Characteristics Contact Arrangement —

2 Form C (DPDT)

Contact Material —

Stationary —
Hardened silver alloy
Moveable —
Cold plated bardened silv

Gold plated hardened silver alloy

Contact Resistance -

Before Life — 50 milliohms max. (measured at 10 mA @ 6 Vdc) After Life — 100 milliohms max. (measured @ 2 A @ 28 Vdc)

Mechanical Life Expectancy —

50 million operations

Coil Voltage -

5 to 48 Vdc (HFW) 6 to 26.5 Vdc (HMB) 5 to 36 Vdc (HMS)

Coil Power — 1.4 watts max. @ 25°C

Duty Cycle — Continuous

Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity @ 25°C —

145 to 260 mW (HFW) 325 mW (HMB) 100 to 125 mW (HMS)

Contact Ratings

Contact Load	Туре	Operations Min.
2 A @ 28 Vdc	Resistive	100,000
0.75 A @ 28 Vdc	Inductive (200mH)	100,000
0.1 A @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.3 A @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.1 A @ 28 Vdc	Intermediate	50,000
0.160 A @ 28 Vdc	Lamp	100,000
30 μA @ 50 mVdc	Low Level	1,000,000

RF Performance

Frequency (MHz)	RF Losses (dB)	VSWR	Isolation (dB)
100	0.1	1.17:1	40
500	0.3	1.19:1	28
1000	0.4	1.19:1	23



HFW, HMB, HMS (Continued)

Operating Characteristics

Timing — Operate Time -

4.0 ms max. (HFW)

5.0 ms max. (HMB) 6.0 ms max. (HMS)

Release Time -

4.0 ms max. (HFW)

5.0 ms max. (HMB/HMS)

Contact Bounce — 2.0 ms max.

Dielectric Withstanding Voltage

 Between Open Contacts – 500 Vrms 60 Hz

Between Adjacent Contacts —

1000 Vrms 60 Hz

Between Contacts & Coil -

1000 Vrms 60 Hz

Terminals

Insulation Resistance —

10,000 megohms min. @ 500 Vdc

Environmental Characteristics

Temperature Range —

-65°C to +125°C

Weight — 0.46 oz. (13 gms max.)

Vibration Resistance — HFW/HMB/

HMS -

Standard — 20 G's, 10 to 2,000 Hz

HFW/HMB -

QPL - 30 G's, 10 to 3,000 Hz

HMS -

QPL - 20 G's, 10 to 2,500 Hz


Shock Resistance —

100 G's, 6 ±1 ms 50 G's, 11 ±1 ms (HMS)

QPL Approval -


MIL-R-39016/6 (HFW)


MIL-R-39016/22 (HMB) MIL-R-39016/44 (HMS)




.410 MAX

(10.41)









1.320 MAX (33.53) .410 MAX (10.41) 31 I≪-.810 MAX (20.57)→ .410 MAX (10.41) **V** .120 ±.002 (3.05 ±.05) O (E O .250 ±.010 1.062 (26.97) $(6.35 \pm .25)$ 1.078 (27.38)

Mounting Styles

Standard Coil Data

	Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C	Pickup Voltage Vdc (Max.) @ 25°C	Pickup Voltage Vdc (Min.) @ 125°C	Drop-out Voltage Vdc (Min.) @ 25°C	Drop-out Voltage Vdc (Min.) @ -65°C	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
HFW	5.0	27	2.7	3.8	0.29	0.21	926	6.0	L
	6.0	40	3.2	4.5	0.35	0.25	900	7.5	F
	12.0	160	6.4	9.0	0.7	0.5	900	15.0	G
	26.5	700	13.5	18.0	1.5	1.0	1003	32.0	K
HMB	6.0	40	3.6	4.8	0.35	0.25	900	7.5	F
	12.0	160	7.2	9.6	0.7	0.5	900	15.0	G
	26.5	700	15.0	20.0	1.5	1.0	1003	32.0	K
HMS	5.0	47	2.2	3.2	0.21	0.12	532	7.0	S001
	6.0	75	2.75	4.0	0.27	0.17	480	9.0	S002
	12.0	310	5.6	8.0	0.55	0.35	465	20.0	S003
	26.5	1,030	11.4	16.5	1.1	0.7	682	35.0	S004
	30.0	1,620	14.3	21.0	1.4	0.9	556	44.0	S005
	36.0	2,640	18.0	26.0	1.8	1.1	491	56.0	S006
Other	6-8	60	3.5	4.85	0.35	0.22	817	9.0	Α
(avail. for HFW	12-15	320	6.8	9.42	0.68	0.44	570	21.0	В
relays only)	18.0	520	9.5	13.16	0.95	0.62	623	27.0	J
	26.5-32	1,250	14.0	19.4	1.5	0.98	684	42.0	D
	40.0	2,700	21.3	29.5	2.1	1.37	593	61.0	Н
	48.0	3,500	25.5	35.3	2.5	1.63	658	70.0	Е

Specifying a Part Number Example:	<u>Type</u>	<u>Terminals</u>	<u>Mountings</u>	<u>Coils</u>	<u>Features</u>
	HFW	12	30	K	00 (n/a HMS)


^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.



Long-life Half size Industrial Relay Type 3SCV (2PDT)

Product Facts

- 100,000,000 operations at low-level
- Hermetic seal



The 3SCV is an exceptionally long life relay for low level applications which is designed for industrial applications such as business machines and computer peripheral equipment. The design is such that the phenomenon of sticking contacts is all but eliminated. Because of its low contact resistance and its ability to handle overloads the 3SCV relay is well suited for applications which have previously required reed devices.

Electrical Characteristics

Contacts — 2 Form C

Contact Resistance —

0.050 ohms; 0.100 ohms after life test

Life — 10⁵-2A 28 volts DC, 115 volts AC (not grounded, resistive)

Low-level — 100,000,000 operations — 50 µA at 50 mV Peak AC or DC

Sensitivity — 340 mW

Operating Characteristics

Operate Time — 6 ms max.

Release Time — 4 ms max.

Contact Bounce — 2 ms max.

 $\textbf{Enclosure} \longrightarrow \textbf{All welded, hermetically}$

sealed **Terminals** — Weldable and solderable

Dielectric Strength — 500 volts rms

Insulation Resistance — 1,000 megohm min.

Environmental Characteristics

Weight — 0.30 oz.

Vibration — 10G, 10-2000 Hz

Shock — 50 G 6ms, 1/2 sine

Temperature — -14°C to +125°C


See page 1-39 for Mounting Forms, Terminals and Circuit Diagrams.

Coil Table (All Values DC)* 340 mW Sensitivity: (Code 1)

			Voltage Calibrated, Co			
Coil	Out Deviates as	0	Maximum	Release Voltage Range at 25C		
Code Letter	Coil Resistance at 25C (ohms)	Suggested Source	Operate Volts	Hange	at 25C	
Letter	at 250 (011113)	Volts†	at 25C	Max	Min	
A	47 ± 10%	4.8-7	3.9	2.7	.43	
В	75 ± 10%	6.1-9	4.9	3.4	.5	
0	120 ± 10%	7.7-12	6.3	4.4	.69	
D	180 ± 10%	9.5-15	7.7	5.4	.85	
E	310 ± 10%	12.5-20	10.1	7.0	1.1	
F	440 ± 10%	15.0-23	12.0	8.4	1.3	
Н	700 ± 10%	20.0-30	15.5	10.9	1.7	
K	1030 ± 10%	24.0-35	18.5	12.9	2.0	
L	1620 ± 10%	30.0-44	23.1	16.2	2.5	
M	2640 ± 10%	39.0-56	29.5	20.68	3.2	


Ordering Instructions

Catalog-selected Relays: The catalog number is derived by choosing the proper CODE for each of the six relay characteristics in the order in which the codes are listed. **Example:** The relay selected in this example is a 2PDT half size relay, voltage calibrated, two-hole side bracket mounting, solder hook header, 700 ohms coil resistance, and 340 mW sensitivity. By choosing the proper code for each of these relay characteristics, the catalog number is identified as 3SCV5042H1. The letter R following sensitivity code indicates relay received 5000 operation misstest. Ex. 3SCV5042H1R.







Mounting Forms (3SCV)




Header and Connection Diagrams





Header Types


Туре	Z Dim.	Header Code
Solder hook	0.16	2
Straight pin (socket or PCB type)	0.19	4





HFC Commercial/Industrial Half Size Relay





Terminal View

Electrical Characteristics Contact Arrangement —

2 Form C (DPDT)

Contact Material -

Stationary

Bifurcated hardened silver alloy Moveable

Gold plated hardened alloy

Contact Resistance Before Life — 50 milliohms max. (measured at 10 mA @ 6 Vdc) After Life — 100 milliohms max. (measured @ 2 A @ 28 Vdc)

Mechanical Life Expectancy — 10 million operations

Coil Voltage — 5 to 26.5 Vdc

Coil Power — 1.4 watts max. @ 25°C

Duty Cycle — Continuous

Pick-up Voltage — Approximately 60% of nominal coil voltage

Pick-up Sensitivity — 360 mW

Operating Characteristics

Timing -

Operate Time — 6.0 ms max. Release Time — 6.0 ms max.

Dielectric Withstanding Voltage

Between Open Contacts -350 Vrms 60 Hz

Between Adjacent Contacts -

500 Vrms 60 Hz Between Contacts and Coil -

500 Vrms 60 Hz Insulation Resistance -

1,000 megohms min @ 500 Vdc **Environmental Characteristics**

Temperature Range —

-55°C to +85°C

Weight — 0.46 oz. (13 gms) max.

Vibration Resistance -10 G's, 10 to 500 Hz

Shock Resistance — 30 G's, 6 ±1 ms


Product Facts


- **■** Hermetically sealed
- Up to 2 amps switching
- **■** Economical configuration
- Optional terminals & mounting styles


Contact Ratings

Contact Load	Туре	Operations Min.	
2 A @ 28 Vdc	Resistive	100,000	
0.75 A @ 28 Vdc	Inductive (200 mH)	100,000	
0.3 A @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000	

.410 MAX (10.41) 01 -.810 MAX (20.57)→ 410 MAX (10.41)








Mounting Styles

Standard Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ± 20% @ 25°C	Pickup Voltage Vdc (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 85°C	Nom. Coil Power (W) @ 25°C	Max. Coil Voltage	Coil Desig.
5.0	27	3.0	3.7	.92	6.0	L
6.0	40	3.6	4.5	.90	7.5	F
12.0	160	7.2	8.9	.90	15.0	G
26.5	700	16.0	19.7	1.00	32.0	K



Ordering Instructions


Catalog-selected Relays: The catalog number is derived by choosing the proper CODE for each of the six relay characteristics in the order in which the codes are listed.

Specifying a Part Number Example: Terminals Mountings Coils Features Type HFC 12 30 Κ 00

.150 Grid-space Relays Type 3SBC (2PDT) Standard 135 mW 2PDT 50 mW (Form AB) 1 PNC-1 PNO

Product Facts

- Low profile... only 0.32 inches high
- Internal diode for coil transient suppression and transistor driven models available
- Qualified to MIL-R-39016/13
- RF designs available



The .150 Grid-space relay — only 0.32 inches high — saves space in electronic packaging. The pin spacing allows you to insert the relay with no intermediate pin spreaders as well as meet applicable military specifications.

Electrical Characteristics Contact Ratings —

DC resistive — 2 amps at 28 volts (50,000 operations)

1 Amp @ 28 V (100,000 operations) DC inductive — 0.5 amps at 28 volts, 200 mH

AC resistive — 0.5 amps at 115 volts AC — 0.125 amps at 115 volts (case grounded)

Low-level — 50 μA at 50 mV Peak AC or DC

Contact Resistance —

 $0.050\ \text{ohms}\ \text{max.};\, 0.150\ \text{ohms}\ \text{after}$ life test

Life — 100,000 operations at rated loads listed; 1,000,000 operations at low-level loads

Operating Characteristics

Operate Time — 4 ms max. **Release Time** — 4 ms max.

Contact Bounce — 1.5 ms

Dielectric Strength —

500 volts rms at sea level; 350 volts rms at 70,000 feet and above

Insulation Resistance — 1,000 megohm min. over temperature range

Environmental Characteristics

Vibration — 30G, to 3000 Hz

Shock — 100 G at 11 ms

Temperature — -65° C to $+125^{\circ}$ C

See page 1-44 for Mounting Forms, Terminals and Circuit Diagrams.

Coil Table Type 3SBC (All Values DC)*2PDT, 135 mW Sensitivity: (Code 1)

			Voltage	Calibrated		Current Calibrated, Code 6			
Coil	Coil Resistance	Suggested	Max. Operate	Release Voltage Range @ 25C		Max. Continuous	Max. Operate	Release Current Range @ 25C (mA)	
Code Letter	@ 25C (ohms)	Source Volts†	Volts @ 25C	Max.	Min.	Current @ 125C (mA)	Current @ 25C (mA)	Max.	Min.
Α	44 ± 10%	3.5-6.2	2.4	1.45	0.26	87.0	54.5	32.7	6.00
В	56 ± 10%	4.0-7.0	2.7	1.6	0.3	77.0	48.3	28.6	5.30
D	140 ± 10%	6.4-12.0	4.4	2.6	0.5	50.3	31.4	18.5	3.60
Е	210 ± 10%	8.0-16.0	5.4	3.2	0.6	40.0	25.7	15.4	2.80
L	650 ± 10%	13.6-24.0	9.5	5.6	1.0	22.9	14.3	8.6	1.54
K	1350 ± 10%	20.0-35.0	13.5	8.1	1.5	15.5	10.0	6.0	1.10
N	2245 ± 10%	26.0-46.0	17.1	10.5	1.9	12.0	7.6	4.7	0.84

Coil-Data (All Values DC)* Type 3SBC Form AB 50 mW Sensitivity non mil spec: (Code 2)

			Voltage	Calibrated		Current Calibrated, Code 6			
Coil	Coil Resistance	Suggested	Max. Operate	Release Voltage Range @ 25C		Max. Continuous	Max. Operate	Release Current Range @ 25C (mA)	
Code Letter	@ 25C (ohms)	Source Volts†	Volts @ 25C	Max.	Min.	Current @ 125C (mA)	Current @ 25C (mA)	Max.	Min.
В	56 ± 10%	2.6-7.0	1.8	1.1	0.16	46.5	29.1	18.2	3.30
С	85 ± 10%	3.3-9.5	2.3	1.4	0.20	38.7	24.2	15.1	2.70
D	140 ± 10%	4.3-12.0	2.9	1.8	0.27	30.4	19.0	11.9	2.10
E	210 ± 10%	5.3-14.0	3.6	2.2	0.33	24.8	15.5	9.7	1.75
F	360 ± 10%	6.7-19.0	4.5	2.8	0.41	18.9	11.8	7.2	1.30
G	510 ± 10%	8.2-23.0	5.6	3.5	0.51	15.8	9.9	6.2	1.10
Н	775 ± 10%	10.0-26.0	6.8	4.2	0.62	12.8	8.0	5.0	0.90
K	1350 ± 10%	13.2-35.0	9.0	5.6	0.82	9.8	6.1	3.8	0.68
N	2245 ± 10%	16.8-46.0	11.4	7.1	1.00	7.4	4.6	2.9	0.52

^{*}Values listed are factory test and inspection data. User should allow for meter variations.

‡Applicable over the operating temperature range in circulating air.

See Page 1-42 for ordering instructions.

^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.




[†]At nominal resistance plus 10%.

.150 Grid-space Hybrid Relays Single Diode, Dual Diode Type 3SBC (2PDT) 135 mW

Product Facts

- Low profile... only 0.32 inches high
- 50 milliwatt forms available
- Qualified to MIL-R-39016/37
- Qualified to MIL-R-39016/38
- RF designs available



The hybrid .150 Grid-space relay — only 0.32 inches high — saves space in electronic packaging. The pin spacing allows you to insert the relay with no intermediate pin spreader.

Electrical Characteristics Contact Ratings —

DC resistive — 2 amps at 28 volts (50,000 operations)

1 Amp @ 28 V (100,000 operations) DC inductive — 0.5 amps at 28 volts, 200 mH

AC resistive — 0.5 amps at 115 volts AC — 0.125 amps at 115 volts (case grounded)

Low-level — 50 µA at 50 mV Peak AC or DC

Contact Resistance —

0.050 ohms max.; 0.150 ohms after life test

Life — 100,000 operations at rated loads listed; 1,000,000 operations at low-level loads

Operating Characteristics

Operate Time — 4 ms max.

Release Time — 6 ms max.

Contact Bounce — 1.5 ms

Dielectric Strength (Note 1) —

500 volts rms at sea level;

350 volts rms at 70,000 feet and above

Insulation Resistance (Note 1) — 1,000 megohm min. over temperature

Environmental Characteristics

Vibration — 30G, to 3000 Hz

Shock — 100 G at 11 ms

Temperature — -65°C to +125°C

Semiconductor Characteristics at 25°C

Diode -

Max. Negative Transient — 1.0 volt Breakdown Voltage — 100 VDC @ 10 μA Max. Leakage Current — 1 μA @ 50 VDC

See page 1-44 for Mounting Forms, Terminals and Circuit Diagrams.

Coil Table Single Diode (All Values DC)*(2DPT), 135 mW Sensitivity: (Code 5)

		·									
		L\	Voltage Calibrated, Code 5				Current Calibrated, Code 6				
Coil Code	Coil Resistance @ 25C	Suggested Source	Max. Operate Volts	Release Voltage Range @ 25C		Max. Contin- uous Current	Max. Operate Current @	Release Current Range @ 25C (mA			
Letter	_etter (ohms)	Volts† volts @ 25C		Max.	Min.	@ 125C (mA)	25C (mA)	Max.	Min.		
Α	44 ± 10%	3.5- 6.2	2.4	1.45	0.26	87.0	54.5	32.7	6.00		
В	56 ± 10%	4.0- 7.0	2.7	1.6	0.3	77.0	48.3	28.6	5.30		
D	140 ± 10%	6.4-12.0	4.4	2.6	0.5	50.3	31.4	18.5	3.60		
E	210 ± 10%	8.0-16.0	5.4	3.2	0.6	40.0	25.7	15.4	2.80		
L	650 ± 10%	13.6-24.0	9.5	5.6	1.0	22.9	14.3	8.6	1.54		
K	1350 ± 10%	20.0-35.0	13.5	8.1	1.5	15.5	10.0	6.0	1.10		
N	2245 ± 10%	26.0-46.0	17.1	10.5	1.9	12.0	7.6	4.7	0.84		


Coil Table Dual Diode (All Values DC)*(2DPT), 135 mW Sensitivity: (Code 6)

	**								
Α	44 ± 10%	3.9- 7.0	3.4	2.0	0.37	98.2	77.3	45.5	8.4
В	56 ± 10%	4.6- 8.0	3.7	2.2	0.41	89.8	66.1	39.3	7.1
D	140 ± 10%	7.8-12.0	5.4	3.2	0.6	52.4	38.6	22.9	4.3
E	210 ± 10%	9.3-16.0	6.4	3.8	0.7	41.4	30.5	18.1	3.3
L	650 ± 10%	15.0-24.0	10.5	6.2	1.1	23.6	16.2	9.5	1.7
K	1350 ± 10%	21.0-35.0	14.5	8.7	1.6	16.0	10.7	6.4	1.2
N	2245 ± 10%	27.0-46.0	18.1	10.9	2.0	12.1	8.1	4.9	0.9

Ordering Instructions

Example: The relay selected in the example is a FORM AB .150-grid relay, current calibrated, end bracket mounting with 0.13-inch solder hook header, 210 ohms coil resistance, and 50 mW sensitivity. By choosing the proper code for each of these relay characteristics, the catalog number is 3SBC6131E2. The letter R following sensitivity code indicates relay received 5000 operation miss-test. Ex. 3SBC6131E2R.

Note: Relays specified by catalog numbers (per above directions) are general use items controlled by catalog specifications. Relays to be controlled by customer drawings — or relays having requirements not covered in this publication — will be assigned special catalog numbers upon request.



^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.



.150 Grid-space Long-life Relays Type 3SCC (2PDT) 170 mW

Product Facts

- 100,000,000 operations low-level signal loads
- RF designs available
- Low profile 0.32 height
- Hermetic seal
- High reliability
- **■** Performance tested



The .150 Grid relay, the smallest (.320 inches high) 2 Amp rated relay available in commercial and military qualified models, is now available in the long life version. Capable of over 100.000.000 mechanical operations at low level and signal load, the .150 Grid relay provides the simplicity of relays for circuit design, the low circuit resistance of precious metal contact systems, and the long life processing that has made CII relays the standard for quality and reliability.

Electrical Characteristics Contact Ratings —

DC resistive — 2 amps at 28 volts (50,000 operations)

1 Amp @ 28 V (100,000 operations) DC inductive — 0.5 amps at 28 volts, 200 mH

AC resistive — 0.5 amps at 115 volts AC — 0.125 amps at 115 volts (case grounded)

Low-level — 50 µA at 50 mV Peak AC or DC

Contact Resistance —

0.050 ohms max.; 0.150 ohms after life test

Life — 100,000 operations at rated loads listed; 1,000,000 operations at low-level loads

Operating Characteristics

Operate Time — 4 ms max. **Release Time** — 4 ms max.

Contact Bounce — 1.5 ms

Dielectric Strength —

500 volts rms at sea level; 350 volts rms at 70,000 feet and above

Insulation Resistance — 1,000 megohm min. over temperature range

Environmental Characteristics

Vibration — 30G, to 3000 Hz

Shock — 100 G at 11 ms

Temperature — -40° C to $+125^{\circ}$ C

See page 1-44 for Mounting Forms, Terminals and Circuit Diagrams.

Coil Table Type 3SCC (All Values DC)* 2 PDT Relay - 170mW Sensitivity: (Code 1)


		Vo	Itage Calibra	ted, Code	5		Current Calibrate	d, Code 6	
Coil Code	Coil Resistance @ 25C	Suggested Source	Max. Operate Volts	ı	Voltage @ 25C	Max. Contin- uous Current	Max. Operate Current @	Release Current Range @ 25C (mA)	
Letter	(ohms)	Volts†	@25C	Max.	Min.	@ 125C (mA)	25C (mA)	Max.	Min.
Α	44 ± 10%	3.5- 6.2	2.7	1.45	0.26	87.0	61.4	32.7	6.00
В	$56\pm10\%$	4.0- 7.0	3.1	1.6	0.3	77.0	55.4	28.6	5.30
D	$140 \pm 10\%$	6.4-12.0	4.9	2.6	0.5	50.3	35.0	18.5	3.60
E	$210\pm10\%$	8.0-16.0	5.9	3.2	0.6	40.0	28.0	15.4	2.80
L	650 ± 10%	13.6-24.0	10.5	5.6	1.0	22.9	16.2	8.6	1.54
К	$1350\pm10\%$	20.0-35.0	15.1	8.1	1.5	15.5	11.2	6.0	1.10
N	2245 ± 10%	26.0-46.0	19.5	10.5	1.9	12.0	8.7	4.7	0.84

^{*}Values listed are factory test and inspection data. User should allow for meter variations.

Ordering Instructions

Example: The relay selected in the example is a 2PDT .150-grid relay, current calibrated, end bracket mounting with 0.13-inch solder hook header, 210 ohms coil resistance, and 175 mW sensitivity. By choosing the proper code for each of these relay characteristics, the catalog number is 3SCC6131E1. The letter R following sensitivity code indicates relay received 5000 operation miss-test. Ex. 3SCC6131E1R.

Note: Relays specified by catalog numbers (per above directions) are general use items controlled by catalog specifications. Relays to be controlled by customer drawings — or relays having requirements not covered in this publication — will be assigned special catalog numbers upon request.







[†]Applicable over the operating temperature range in circulating air.

Mounting Forms (3SBC, 3SCC)


(Vibration note with each form is acceleration from 55 to 3000 Hz)





All dimensions in inches

	TOLERANCES (Unless otherwise specified)					
Hundredths	± 0.020					
Thousandths	± 0.005					



No Mount

Mounting Code	Vibration
00	30g

^{*}Assumes relay held securely by potting or other means

End Bracket


Mounting Code	Vibration
13	30a

Side Bracket


Mounting Code	Vibration
25	30a


Header and Connection Diagrams


Header Types Z **HEADER** TYPE DIMENSION CODE Solder hook 0.13 Straight pin 8 0.12 Straight pin 0.19 4 Straight pin 0.25 5



.020 dia







Crystal-Can Relays Type 3SAE (2PDT)

Product Facts

- Small lightweight crystal-can type
- 0.25 cubic inch, 0.60 ounces
- Power or low-level switching
- 20G to 2000 Hz vibration capability



The TE Connectivity line of crystal-can relays is backed by years of experience and millions of relays operating in the field.

Electrical Characteristics Contact Ratings —

DC resistive — 2 amps at 28 volts DC inductive — 1 amp at 28 volts, L/R < .025 Low-level — 50 μ A at 50 mV Peak AC or DC AC resistive — 1.0 amp at 115 volts, case not grounded AC resistive — 0.25 amps at 115 volts, case grounded

Contact Resistance —

0.050 ohms max. initial; 0.100 ohms max. after life test **Life** — 100,000 operations at rated

load; 1,000,000 at low-level

Operating Characteristics

Operate Time — 6 ms max. **Release Time** — 5 ms max.

Contact Bounce — 2.5 ms

Dielectric Strength —

1,000 volts rms at sea level; 700 volts rms across contact gaps; 350 volts rms at 70,000 feet

Insulation Resistance -

1,000 megohm min. except coil to case 500 min. at 125°C

Environmental Characteristics

Vibration — Depends upon mounting forms

Shock — 50 G at 11 ms

Temperature — -65°C to +125°C

See page 1-46 for Mounting Forms, Terminals and Circuit Diagrams.

Coil Table (All Values DC)* Type 3SAE 330 mW Sensitivity: (Code 1)


	Voltage Calibrated, CODE: 5				
Coil Code Letter	Coil Resistance	Suggested Maximum Release Source Operate at 2		Voltage 25C	
	at 25C (Ohms)	Volts†	Voits at 25C	Max	Min
A B C D	22 ± 10% 34 ± 10% 53 ± 10% 92 ± 10%	3.9- 5.9 4.8- 7.4 6.2- 9.2 8.0-12.0	2.7 3.3 4.2 5.4	1.4 1.7 2.2 2.8	0.29 0.36 0.46 0.60
E F H K	$\begin{array}{c} 146 \pm 10\% \\ 215 \pm 10\% \\ 342 \pm 10\% \\ 552 \pm 10\% \end{array}$	10.2-15.0 12.3-18.5 15.4-23.0 20.0-29.5	6.9 8.3 10.4 13.5	3.6 4.3 5.4 7.0	0.76 0.92 1.16 1.50
L M P	814 ± 10% 1180 ± 10% 1278 ± 15% 1800 ± 15%	25.0-36.0 30.0-43.0 31.0-41.5 38.0-49.0	16.9 20.5 21.3 25.8	8.8 10.6 11.0 13.3	1.88 2.28 2.36 2.86
R S T V	2530 ± 15% 2950 ± 15% 5000 ± 20% 5170 ± 20%	43.0-58.5 50.0-63.0 62.0-75.0 68.0-76.0	29.0 34.0 41.8 46.0	15.0 17.5 21.6 25.4	3.22 3.77 4.64 5.12

^{*}Values listed are factory test and inspection values. User should allow for meter variations.

Ordering Instructions

Example: The relay selected in this example is a 2PDT crystal-can relay, voltage calibrated, two-hole side bracket mounting solder hook header, 552 ohms coil resistance, and 330 mW sensitivity. By choos-

ing the proper code for each of these relay characteristics, the catalog number is identified as 3SAE5041K1. The letter R following sensitivity code indicates relay received 5000 operation miss-test. Ex. 3SAE5041K1R.





[†]Applicable over the operating temperature range in circulating air.

Mounting Forms (3SAE)

(Vibration note with each form is acceleration from 55 to 2000 Hz)


All dimensions in inches

TOLERANCES (unless otherwise specified)			
Hundredths ±0.020			
Thousandths	±0.005		

No Mount


Mounting	A Dim.	Vibra-	Relay
Code	(Max)	tion*	Type
00	0.875	20g	3SAE


* Assumes relay securely held by potting or other means.



Flange Mount, 2 in-line holes


Mount- ing Code	A Dim. (Max)	X Dim.	Vibra- tion	Relay Type
13	0.875	0.125	15g	3SAE
14	0.875	0.375	20g	3SAE






Four-hole Flange


Mount- ing Code	A Dim. (Max)	X Dim.	Vibra- tion	Relay Type
01	0.875	0.125	15g	3SAE
02	0.875	0.375	20g	3SAE




Two-hole Side Bracket

Mounting	A Dim.	Vibra-	Relay
Code	(Max)	tion	Type
04	0.875	20g	3SAE






Header and Connection Diagrams



Header Types

Туре	Z Dim.	Header Code
Solder hook	0.19	2
Straight pin (socket or PCB type)	0.19	4
Straight pin	2.99	8



CODES: 4, 8

LS


Double Pole, Magnetic Latching, 2 Amps and Less


Magnetic Latching Half Size High Performance Relay DESIGNED to

LS









Terminal View

Standard Schematic Contacts will switch from the indicated position when either coil is energized with polarity as shown.

MIL-R-39016/45 SCHEMATIC Contacts will switch from the indicated position when either coil is energized with polarity as shown.

Product Facts

- Hermetically sealed
- Up to 2 amps switching
- High shock & vibration ratings
- Optional terminals & mounting styles
- Latching design

Electrical Characteristics Contact Arrangement —

2 Form C (DPDT)

Contact Material —

Stationary —
Gold plated hardened silver alloy
Moveable —

Gold plated hardened silver alloy

Contact Resistance —

Before Life — 50 milliohms max. (measured at 10 mA @ 6 Vdc) After Life — 100 milliohms max. (measured @ 2 A @ 28 Vdc)

Mechanical Life Expectancy —

1 million operations min.

Coil Voltage — 5 to 48 Vdc

Coil Power — 1.0 watts max. **Duty Cycle** — Continuous

Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity — 170 mW

Contact Ratings

Contact Load	Туре	Operations Min.
2 A @ 28 Vdc	Resistive	100,000
0.3 A @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.75 A @ 28 Vdc	Inductive (200mH)	100,000
0.1 A @ 28 Vdc	Intermediate	50,000
0.160 A @ 28 Vdc	Lamp	100,000
30 μA @ 50 mVdc	Low Level	1,000,000

RF Performance

Frequency (MHz)	RF Losses (dB)	VSWR	Isolation (dB)
100	0.1	1.15:1	38
500	0.3	1.19:1	31
1000	0.6	1.32:1	45



LS (Continued)

Operating Characteristics

Timing —

Set-Reset Time — 5.0 ms max.

Contact Bounce —

2.0 ms max.

${\bf Dielectric\ With standing\ Voltage--}$

Between Open Contacts — 500 Vrms 60 Hz

Between Adjacent Contacts — 1000 Vrms 60 Hz

Between Contacts and Coil — 1000 Vrms 60 Hz

Insulation Resistance —

10,000 megohms min. @ 500 Vdc

Environmental Characteristics

 ${\bf Temperature\ Range--}$

-65°C to +125°C

Weight — .46 oz (13 gms) max.

Vibration Resistance -


Standard — 20 G's, 10 to 2,000 Hz QPL Equiv. — 30 G's, 10 to 2,500 Hz


Shock Resistance —

100 G's, 6 ± 1 ms


QPL Equivalent —

MIL-R-39016/45





LS Terminals



Standard Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C	Pickup Voltage Vdc (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C	Pickup Voltage Vdc (Min.) @ 25°C	Pickup Voltage Vdc (Min.) @ -65°C	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
5.0	45	2.7	3.8	1.6	1.0	556	6.7	5
6.0	63	3.25	4.5	2.0	1.3	571	8.0	6
12.0	254	6.5	9.0	4.0	2.6	567	16.0	12
26.5	1,000	13.0	18.0	8.0	5.2	702	32.0	24
48.0	3,800	26.0	36.0	16.0	10.4	606	64.0	48

Ordering Instructions

Catalog-selected Relays: The catalog number is derived by choosing the proper CODE for each of the six relay characteristics in the order in which the codes are listed.


Specifying a Part Number Example:	<u>Type</u>	<u>Mountings</u>	Contacts	<u>Coils</u>	<u>Terminals</u>
	LS	RW-	2C-	24	R



Magnetic Latching, Grid Space, Relay Type 3SDM (2PDT)

Product Facts

- Suitable for pulse operation
- No hang up feature
- MIL-R-39016 type
- Special contact and coil wiring available



This magnetic latching relay maintains the high reliability attributes of the aerospace proven CII 3SAM relay family. By reducing the size of the coil and maintaining the contact system of the 3SAM, we can now offer a smaller 2 amp rated magnetic latching relay. The pulse operation can provide multiple hundred thousand operations in power saving circuits. The on or off

circuits are maintained using no power until there is a need to switch the contacts. Suitable for matrix switches or relay trees, these versatile relays have contact systems capable of reliability switching high power or very low level signals in the same package. The relay's unique circuit prevents it from ever hanging up in an off-center or neutral position.

Electrical Characteristics Contact Ratings —

DC resistive — 2 amps at 28 volts Low-level — 50 µA at 50 mV DC or peak AC

Contact Resistance —

0.050 ohms initial; 0.100 ohms after life test (High level) 0.150 ohms after life test (Low level)

Life -

100,000 operations at rated load; 1,000,000 operations at low-level

Operating Characteristics

Operate Time — 4 ms Reset Time — 4 ms Contact Bounce — 2 ms

Dielectric Strength —

1,000 volts at sea level; 500 volts across contact gap and 500 volts coil to case

Insulation Resistance —


1,000 megohms min.


Environmental Characteristics


Vibration —

Sine — 30G; 55 to 3000 Hz Random — 0.4 G^2/Hz ; 100 to 1,000 Hz **Shock** — 150 G at 11 ms, half-sine

Temperature — -65°C to +125°C











Mounting Forms (3SDM)




Header:

Type	Z	Header
	Dimensions	Code
Straight Pin (socket or PCB Type)	0.19 +/020	4
Solder Hook	0.16 +/020	2








Sensitivity and Modification: 290 mW Sensitivity

Sensitivity Code	Modification (see connection diagrams at right)
1	No Diode
5	Single Diode

(Terminal View) (+ on blue bead closes as shown)



SCHEMATIC DIAGRAM TERMINAL VIEW CODE 1




SCHEMATIC DIAGRAM TERMINAL VIEW WITH DIODE CODE 5

Ordering Instructions

Type 3SDM relays can be ordered by specifying the correct catalog number. This number is derived by choosing the proper CODE for each of the six relay characteristics in the order in which the codes are listed in the example. The letter R following the sensitivity code indicates relay received 5,000 operations miss-test. **Example:** The relay selected is a 2PDT magnetic-latching relay, voltage calibrated, 2-hole end bracket mount, solder hook header, 500 ohm coil, and 290 mW sensitivity. **3SDM5132H1**

Relay Characteristic Catalog Number




CII Low Signal Relays

Double Pole, Magnetic Latching, 2 Amps and Less (Continued)

Magnetic Latching, Grid-space, Relays Type 3SAM (2PDT)

Product Facts

- Special shock designs up to 700 G, 1 ms
- Suitable for pulse operation
- No hang up feature on low power pulses
- Qualified to MIL-R-39016/32
- Special wiring is available



This relay has "memory" in that the contact positions do not change when coil power is removed. Switching is accomplished by applying power to the applicable coil (dual coil) or with the applicable polarity (single coil). The low switching power requirements are further enhanced by its ability to operate from capacitor discharge or other pulses or through its own contacts for batteries or similarly limited supplies.

Electrical Characteristics Contact Ratings —

DC resistive — 2 amps at 28 volts DC inductive — 0.5 amps at 28 volts, 200 mH

AC resistive — 1 amp at 115 volts (single coil), case not grounded AC resistive — 0.25 amps at 115 volts (dual coil), case not grounded Low-level — 50 μA at 50 mV Peak AC or DC

Contact Resistance —

0.050 ohms initial; 0.100 ohms after life test

Life -

100,000 operations at rated load; 1,000,000 at low-level

Operating Characteristics

Operate Time — 4 ms

Release Time — 4 ms

Contact Bounce — 2 ms

Dielectric Strength —

1,000 volts rms at sea level; 700 volts rms across contact gap

Insulation Resistance — 1,000 megohm min.

Environmental Characteristics

Vibration — 30 G, to 3,000 Hz

Shock — 150 G at 11 ms

Temperature — -65° C to $+125^{\circ}$ C

See page 1-52 for Mounting Forms, Terminals and Circuit Diagrams.

Coil Table (All Values DC) Single Coil 50 mW Sensitivity: (Code: 1)

	Curre	Current Calibrated, CODE: 6			
Coil Code Letter	Coil Resistance @25C (Ohms)	Max Operate and Reset Current (mA) ‡	Suggested Source Voltage†		
A B C D	16.4 ± 10% 40 ± 10% 96 ± 10% 164 ± 10%	55.2 35.3 22.8 17.4	1.8-4.8 2.7-7.5 4.2-11.0 5.5-15.0		
E F H K	$260 \pm 10\%$ $400 \pm 10\%$ $600 \pm 10\%$ $960 \pm 10\%$	13.9 11.2 9.2 7.2	7.0-19.0 8.5-23.0 11.0-29.0 13.0-37.0		
L M N P Fr	$1350 \pm 10\%$ $1950 \pm 10\%$ $3000 \pm 15\%$ $4800 \pm 15\%$ $8200 \pm 20\%$	6.1 5.1 4.1 3.3 2.5	16.0-43.0 19.0-52.0 25.0-64.0 32.0-81.0 43.0-99.0		

- † Applicable over the operating temperature range in circulating air.
- ‡ Initial or inspection value. Allow 20% increase in value of maximum pickup during rated life.

Coil Table (All Values DC) Dual Coil 75 mW Sensitivity: (Code: 2)

	Currer	Current Calibrated, CODE: 6			
Coil Code Letter	Coil Resistance @25C For Each Coil (Ohms)	Max‡ Operate Current For Each Coil (mA)	Suggested Source Voltage For Each Coil†		
A B C D	$8.2 \pm 10\% \ 20 \pm 10\% \ 48 \pm 10\% \ 82 \pm 10\%$	95.8 61.2 39.5 30.2	1.5-2.6 2.3-4.1 3.6-6.3 4.7-8.3		
EFHK	$130 \pm 10\% \ 200 \pm 10\% \ 300 \pm 10\% \ 480 \pm 10\%$	24.0 19.4 15.8 12.5	6.0-10.0 7.4-13.0 9.0-16.0 12.0-20.0		
L M N P R	$\begin{array}{c} 675 \pm 10\% \\ 975 \pm 10\% \\ 1500 \pm 15\% \\ 2400 \pm 15\% \\ 4100 \pm 20\% \end{array}$	10.6 8.8 7.1 5.6 4.3	14.0-24.0 16.0-29.0 21.0-35.0 27.0-44.0 37.0-55.0		

- † Applicable over the operating temperature range in circulating air.
- ‡ Initial or inspection value. Allow 20% increase in value of maximum pickup during rated life.

Ordering Instructions

Example: The relay selected in this example is a 2PDT magnetic latching relay, current calibrated, fourhole end bracket mounting, solder hook header, 1500 ohms coil resistance, and 75 mW sensitivity. By choosing the proper code for each

of these relay characteristics, the catalog number is identified as 3SAM6014N2. The letter R following sensitivity code indicates relay received 5000 operation miss-test. Ex. 3SAM6014N2R.

Relay	Catalog No.					
Characteristic	3SAM	6	01	4	Ν	2
Type		†	†	†	†	1
Calibration						-
Mounting						
Header						
Coil Resistance						
Sensitivity						

^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.




Mounting Forms (3SAM)

(Vibration note with each form is acceleration from 55 to 3000 Hz)

No Mount

Mounting Code	Vibration*
00	30g

Assumes relay se-curely held by pot-ting or other means.




Two-hole End Bracket

Mounting Code

13

14

15



Side Studs

.120 DIA

900 MAX

Mounting Code	X Dim.	Vibra- tion
07	0.250	30g
08	0.375	30g


1.330 MAX


1.078


Dual Coil

⊕ 400 MAX

800 MAX







Four-hole Side Bracket

Mounting Code	Vibration
06	30g

All dimensions in inches

TOLERANCES (unless otherwise specified)			
Hundredths	±0.020		
Thousandths	±0.005		

Top Studs

Mounting Code

10

11

X Dim.


0.250

0.375

Vibra-tion


30g

30g



Four-hole **End Bracket**

Mounting Code	X Dim.	Vibra- tion
01	0.125	30 g
02	0.250	30 g
03	0.450	30 g



Header and Connection Diagrams

X Dim.

0.125

0.250

0.450


Single Coil (Terminal View)


30**g**


30g


30**g**

(+ on blue bead closes as shown)










Header Types

Type	Z	Header Code		
Туре	Dimension	Single	Dual	
Solder hook	0.16	1	4	
Straight pin (socket or PCB type)	0.19	2	5	




CODES: 2, 5

Four Pole, Electrically Held, 2 Amps and Less

SR

SR **Four Pole Half Size High Performance Relay Qualified to** MIL-R-39016/40





Terminal View

Product Facts

- Hermetically sealed
- Up to 2 amps switching
- High shock & vibration ratings
- Optional terminals & mounting styles
- 4 form C Hi-density design

Electrical Characteristics

Contact Arrangement —

4 Form C (4PDT)

Contact Material —

Stationary -

Gold plated hardened silver alloy Moveable —

Gold plated hardened silver alloy

Contact Resistance —

Before Life — 50 milliohms max. (measured at 10 mA @ 6 Vdc) After Life — 100 milliohms max. (measured @ 2 A @ 28 Vdc)

Mechanical Life Expectancy —

1 million operations min.

Coil Voltage — 6 to 26.5 Vdc

Coil Power — 2.6 watts max. @ 25°C

Duty Cycle — Continuous

Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity — 475 mW

Contact Ratings

Contact Load	Туре	Operations Min.
2 A @ 28 Vdc	Resistive	100,000
0.3 A @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.75 A @ 28 Vdc	Inductive (200mH)	100,000
0.1 A @ 28 Vdc	Intermediate	50,000
0.2 A @ 28 Vdc	Lamp	100,000
10 μA @ 50 mV	Low Level	1,000,000



SR (Continued)

Operating Characteristics

Timing — Operate Time — 5.0 ms max. Release Time — 5.0 ms max.

Contact Bounce — 5 ms max

 ${\bf Dielectric\ With standing\ Voltage--}$

Between Open Contacts -350 Vrms 60 Hz

Between Adjacent Contacts — 500 Vrms 60 Hz

Between Contacts & Coil -500 Vrms 60 Hz

Insulation Resistance —

1,000 megohms min. @ 500 Vdc

Environmental Characteristics

Temperature Range —

-65°C to +125°C

Weight -


0.28 oz. (7.8 grms)

Vibration Resistance -15 G's, 10 to 2,000 Hz


Shock Resistance -

100 G's, 6 ± 1 ms

QPL Approval -MIL-R-39016/40



SR Terminals



Standard Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C	Pickup Voltage Vdc (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C	Drop-out Voltage Vdc (Min.) @ 25°C	Drop-out Voltage Vdc (Min.) @ -65°C	Nom. Coil Power (W) @ 25°C	Max. Coil Voltage	Coil Desig.
5.0	20	2.75	3.8	0.35	0.23	1.25	6.0	5
6.0	25	3.5	4.5	0.45	0.3	1.44	8.0	6
12.0	100	6.5	9.0	0.9	0.6	1.44	15.0	12
26.5	390	14.0	18.0	1.8	1.2	1.8	32.0	24

Specifying a Part Number Example:	<u>Type</u>	Mountings	Contacts	<u>Coils</u>	<u>Terminals</u>
	SR	BW-	4C-	24	В


^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.



.150 Grid-space Relays Type 3SBH (4PDT)

Product Facts

- Low profile... only 0.32 inches high
- Long life version available
- Qualified to MIL-R-39016/14



This .150 four pole double throw Grid-space relay is the companion to the two pole 3SBC type shown on page 1-41. It also features the same .150 inch pin spacing that allows you to insert the relay with no intermediate pin spreaders. There is adequate clearance for conductors to reach all pins. It is a very compact 4 pole double throw 2 ampere relay.

Electrical Characteristics Contact Ratings —

DC resistive — 2 amps at 28 volts DC inductive — 0.5 amps at 28 volts, 200 mH

AC resistive — 0.5 amps at 115 volts, 400 or 60 Hz (enclosure isolated from ground, or enclosure and movable contact at same potential)

AC — 0.125 amps at 115 volts (enclosure at line potential with respect

to movable contact) Low-level — low-level operation at 50 millivolts, 30 µA, 33 ohm miss level

Contact Resistance -

0.050 ohms max.; 0.150 ohms after life test

Life –

100,000 operations at rated loads listed; 1,000,000 operations at low-level loads

Operating Characteristics

Operate Time — 4 ms max.

Release Time — 4 ms max. **Contact Bounce** — 1.5 ms

Dielectric Strength —

500 volts rms at sea level; 350 volts rms at 70,000 feet

Insulation Resistance —

1,000 megohms min. over temperature

Environmental Characteristics

Vibration — 30 G, to 3,000 Hz

Shock — 100 G at 11 ms

Temperature — -65°C to +125°C

See page 1-57 for Mounting Forms, Terminals and Circuit Diagrams.

Coil Table (All Values DC)* Type 3SBH, 4 Pole Relay — 250 mW Sensitivity: (Code 1)


	SENSITIVITY CODE: 1							
			Voltage Calibrated, C	ode: 5				
Coil Code	Coil Resistance	Suggested Source	Maximum Operate	Release Range				
Letter	at 25C ohms	Volts†	Volts at 25C	Max.	Min.			
B D E G H K N	$28 \pm 10\%$ $73 \pm 10\%$ $115 \pm 10\%$ $280 \pm 10\%$ $430 \pm 10\%$ $720 \pm 10\%$ $1040 \pm 10\%$	4.0- 7.0 6.0-11.0 8.0-14.0 12 -22.0 15 -26.0 20 -35.0 26 -46.0	2.7 4.2 5.4 8.4 10.3 13.5 17.5	1.6 2.5 3.2 5.0 6.0 8.1 10.5	0.3 0.4 0.6 0.8 1.0 1.5			

^{*}Values listed are factory test and inspection values. User should allow for meter variations.

Ordering Instructions

Catalog-selected Relays: The catalog number is derived by choosing the proper CODE for each of the six relay characteristics in the order in which the codes are listed.

Example: The relay selected in this example is a 4PDT .150-grid relay, voltage calibrated, end bracket mounting, 0.13 inch solder hook header, 720 ohms coil resistance, and 250 mW sensitivity. By choosing the proper code for each of these relay characteristics, the catalog number is identified as 3SBH5131K1. The letter R following sensitivity code indicates relay received 5000 operation miss-test. Ex. 3SBH5131K1R.



^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.




[†]Applicable over the operating temperature range in circulating air.

.150 Grid-space Hybrid Relays Type 3SBH (4PDT)

Product Facts

- Low profile... only 0.32 inches high
- Long life version available
- Qualified to MIL-R-39016/53 & 54



The 4PDT .150 Grid-space hybrid relays are advanced designs of the standard high reliability 4PDT .150 Grid-space relays. In the single diode version, the relay coilback electromotive force is suppressed to prevent circuit/component damage. With the dual diode version, a steering diode is added to the coil circuit, along with the suppression diode. This

steering diode prevents operation of the relay by reverse polarity voltages and protects the suppression diode. The single diode version is qualified to MIL-R-39016/53 and the dual diode is qualified to MIL-R-39016/54.

Electrical Characteristics Contact Ratings —

DC resistive — 2 amps at 28 volts
DC inductive — 0.5 amps at 28 volts,
200 mH
AC resistive — 0.5 amps at 115 volts,
400 or 60 Hz (enclosure isolated from

ground, or enclosure and movable contact at same potential)
AC — 0.125 amps at 115 volts (enclosure at line potential with respect to movable contact)

Low-level — 50 µÅ at 50mV

Contact Resistance -

0.050 ohms max.; 0.150 ohms after life test

Life — 100,000 operations at rated loads listed; 1,000,000 operations at low-level loads

Operating Characteristics

Operate Time — 4 ms max.

Release Time — 6 ms max.

Contact Bounce — 2.0 ms

Dielectric Strength (Note 1) —

500 volts rms at sea level; 350 volts rms at 70,000 feet

Insulation Resistance (Note 1) — 1,000 megohms min. over temperature

Semiconductor Characteristics at 25°C

Max. Negative Transient — 1 volt Breakdown Voltage — 100 Vdc @ 10 µA min.

Max. Leakage Current — 1 uA @ 50 Vdc

Note 1: Tests for dielectric withstanding voltage and insulation resistance should be made with "coil terminals" shorted together to avoid unnecessary electrical stress to semiconductor elements.

See page 1-57 for Mounting Forms, Terminals and Circuit Diagrams.

Coil Table (All Values DC)* Type 3SBH, 4 Pole Relay — 250 mW Sensitivity: (Code 5 single diode, Code 6 dual diodes)

Single Diode)	SENSITIVITY C	ODE: 5		
			Voltage Calibrated,	Code: 5	
Coil Code	Coil Resistance	Suggested Source	Maximum Operate		Voltage at 25C
Letter	at 25C ohms	Volts†	Volts at 25C	Max.	Min.
B D E G H K N	$28 \pm 10\%$ $73 \pm 10\%$ $115 \pm 10\%$ $280 \pm 10\%$ $430 \pm 10\%$ $720 \pm 10\%$ $1040 \pm 10\%$	4.0- 7.0 6.0-11.0 8.0-14.0 12 -22.0 15 -26.0 20 -35.0 26 -46.0	2.7 4.2 5.4 8.4 10.3 13.5 17.5	1.6 2.5 3.2 5.0 6.0 8.1 10.5	0.3 0.4 0.6 0.8 1.0 1.5
Dual Diode		SENSITIVITY CO	ODE: 6	•	
B D E G H K N	$28 \pm 10\%$ $73 \pm 10\%$ $115 \pm 10\%$ $280 \pm 10\%$ $430 \pm 10\%$ $720 \pm 10\%$ $1040 \pm 10\%$	4.0- 7.0 6.0-11.0 8.0-14.0 12.0-22.0 15 -26.0 20 -35.0 26 -46.0	3.7 5.2 6.4 9.4 11.3 14.5 18.1	2.3 3.2 3.9 5.7 6.7 8.8 11.1	0.5 0.6 0.8 1.0 1.2 1.7 2.1

^{*}Values listed are factory test and inspection values. User should allow for meter variations.

[†]Applicable over the operating temperature range in circulating air.

Header Types

Туре


Solder hook

Straight pin

Straight pin socket or PCB type)

Straight pin

Four Pole, Electrically Held, 2 Amps and Less (Continued)



Header and Connection Diagrams

Z Dimension

0.13


0.19

0.25

Header Code

8


4



Ordering Instructions

Catalog-selected Relays: The catalog number is derived by choosing the proper CODE for each of the six relay characteristics in the order in which the codes are listed.

Example: The relay selected in this example is a 4PDT .150-grid relay, voltage calibrated, end bracket mounting, 0.13 inch solder hook header, 720 ohms coil resistance, and 250 mW sensitivity. By choosing the proper code for each of these relay characteristics, the catalog number is identified as 3SBH5131K5. The letter R following sensitivity code indicates relay received 5000 operation miss-test. Ex. 3SBH5131K5R.




^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.



Long-life .150 Grid-space Relays 100,000,000 Operations At Low Levels Type 3SDH (4PDT)

Product Facts

- Long life at low level or signal loads
- Low profile... only 0.32 inches high



The 3SDH relay is designed for 100,000,000 operations at low levels. It is a four pole double throw Grid-space relay. The 0.150 inch pin spacing allows the user to insert the relay with no intermediate pin spreaders. There is adequate clearance for conductor to reach all pins.

Electrical Characteristics Contact Ratings —

Contact Natings—

DC resistive — 2 amps at 28 volts, (DC 100,000 operations)

DC inductive — 0.3 amp at 28 volts, (L/R not greater than 0.008)

AC resistive — 0.5 amp at 115 volts, 400 or 60 Hz (enclosure isolated from ground, or enclosure and movable contact at same potential)

AC resistive — 0.125 amp at 115 volts (enclosure at line potential with respect to movable contact)

Low-level — 50 µÅ at 50 mV Peak AC or DC

Contact Resistance —

0.050 ohms max.; 0.150 ohms after life test

Life — 100,000 operations at rated loads listed; 100,000,000 operations at low-level loads

Operating Characteristics Operate Time @ +25°C —

4 ms max.

Release Time @ +25°C — 4 ms max.

Contact Bounce @ +25°C — 1.5 ms **Dielectric Strength** —

500 volts rms at sea level; 350 volts rms at 70,000 feet

Insulation Resistance —

1,000 megohms min. over temperature

Environmental Characteristics

Vibration — 30 G, to 3,000 Hz

Shock — 100 G at 11 ms

Temperature — -40° C to $+125^{\circ}$ C

See page 1-59 for Mounting Forms, Terminals and Circuit Diagrams.

Coil Table (All Values DC)*Type 3SDH, 4 Pole Relay—210mW Sensitivity: (Code 1)

	SENSITIVITY CODE: 1						
			Voltage Calibrated, Co	ode: 5			
Coil Code	Coil Resistance	Suggested Source	Maximum Operate		Voltage at 25C		
Letter	at 25C ohms	Volts†	Volts at 25C	Max.	Min.		
В	28 ± 10%	4.0- 7.0	3.0	1.6	0.3		
D E	73 ± 10% 115 ± 10%	6.0-11.0 8.0-14.0	4.8 5.9	2.5 3.2	0.4 0.6		
G H	280 ± 10% 430 ± 10%	12 -22.0 15 -26.0	9.3 11.5	5.0 6.0	0.8 1.0		
K	$720 \pm 10\%$	20 -35.0	14.9	8.1	1.5		
N	1040 ± 10%	26 -46.0	17.9	10.5	1.9		

^{*}Values listed are factory test and inspection values. User should allow for meter variations.



[†]Applicable over the operating temperature range in circulating air.

Header Types

Туре


Solder hook

Straight pin

Straight pin socket or PCB type)

Straight pin

Four Pole, Electrically Held, 2 Amps and Less (Continued)



Header and Connection Diagrams

Z Dimension

0.13

0.19


0.25

Header Code

8


4

5



Ordering Instructions

Catalog-selected Relays: The catalog number is derived by choosing the proper CODE for each of the six relay characteristics in the order in which the codes are listed. **Example:** The relay selected in this example is a 4PDT .150-grid relay, voltage calibrated, end bracket mounting, 0.13 inch solder hook header, 720 ohms coil resistance, and 210 mW sensitivity. By choosing the proper code for each of these relay characteristics, the catalog number is identified as 3SDH5131K1. The letter R following sensitivity code indicates relay received 5000 operation miss-test. Ex. 3SDH5131K1R.






Four Pole, Magnetic Latching, 2 Amps and Less

.150 Grid-space Magnetic Latching Relays Type 3SBM (4PDT)

Product Facts

- Low profile... only 0.32 inches high
- Internal diode for coil transient suppression available
- Qualified to MIL-R-39016/31



The Type 3SBM relay adds magnetic latching capability to the popular and growing family of .150-grid relays. This relay has memory in that the contact positions do not change when coil power is removed. Switching is accomplished by applying power to the applicable coil (dual coil) or with the applicable polarity (single coil). The low switching power requirements are further enhanced by its ability to operate from capacitor discharge or other pulses or through its own contacts from batteries or similarly limited supplies.

Electrical Characteristics Operate Sensitivity—

Single-coil form, 100 mW, Dual-coil form, 180 mW

Contact Arrangement— 4-pole double-throw (4C)

7-poic dodbic-tillow (4c

Contact Ratings -

DC resistive — 2 amps at 28 volts DC inductive — 0.5 amp at 28 volts, 200 mH

AC resistive — 0.5 amp at 115 volts (enclosure isolated from ground, or enclosure and movable contact at same potential)

AC — 0.125 amp at 115 volts (enclosure at line potential with respect to movable contact)

Low-level — 50 µÅ at 50 mV Peak AC or DC

Contact Resistance —

0.050 ohms max.; 0.150 ohms after life tests

Life -

100,000 operations at rated loads listed; 1,000,000 operations at low-level loads

Operating Characteristics

Operate Time — 4 ms max.

 $\textbf{Release Time} - 4 \ \text{ms max}.$

 $\textbf{Contact Bounce} - 1.5 \ \text{ms}$

Dielectric Strength -

500 volts rms at sea level; 350 volts rms at 70,000 feet and above

Insulation Resistance —

1,000 megohms min. over temperature

Environmental Characteristics

Vibration — 30 G, 55 to 3,000 Hz

Shock — 150 G at 11 ms

Temperature — -65°C to +125°C

See page 1-62 for Mounting Forms, Terminals and Circuit Diagrams.

Coil Table (All Values DC)*

		SINGLE COIL, SENSITIVITY 1, (100 mW)				
١	Coil	Coil	Maximum Set-Reset Values		C	
	Code Letter			Calibration Code 6 Current (mA)	Suggested Source Volts‡	
ĺ	N	57	2.4	42	3.6- 8.5	
١	R	256	5.1	20	7.6–18	
I	Τ	830	9.1	11	14-32	
ı	V	1700	13.0	7.7	20-46	
	W	3250	18.0	5.5	28–63	

	DUAL (COIL, SENSITIVITY	7 CODE 2, (180 i	n₩)	
Coil	Ceil	Maximum Set	Suggested		
Code Letter	Resistance @ 25C (Ohms) ± 10%	Calibration Code 5 Voltage (Volts)	Calibration Code 6 Current (mA)	Source Volts‡	
Н	10	1.4	135	2.0- 3.7	
N	37	2.6	70	3.8- 7.2	
R	145	5.2	35	7.6–14.5	
Т	450	9.0	20	14-25	
V	975	13.5	13.5	20–35	
W	2140	20.0	9.2	30–54	

^{*}Values listed are factory test and inspection values. User should allow for meter variations. †Applicable over the operating temperature range in circulating air.

Ordering Instructions

Type 3SBM relays can be ordered by specifying the correct catalog number. This number is derived by choosing the proper CODE for each of the six relay characteristics in the order in which the codes are listed. **Example:** The relay selected in this example is a dual coil, current calibrated, four-hole end bracket mounting, solder hook header, 37 ohms coil resistance, and 180 mW sensitivity. By choosing the proper code for each of these relay characteristics, the catalog number is identified as 3SBM6131N2. The letter R following sensitivity code indicates relay received 5000 operation miss-test. Ex. 3SBM6131N2R.

Relay Characteristic Catalog No.						
	3SBM	6	13	1	Ν	2
Type_		Ť	t	t	1	1
Calibr	ation	╛				
Moun	ting					
Heade	r					
Coil F	Resistance	e				
Sensit	ivity					


^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.



.150 Grid-space Hybrid Magnetic Latching Relays Single Diode, Dual Diode Type 3SBM (4PDT)

Product Facts

- Low profile... only 0.32 inches high
- Suitable for pulse operation
- Qualified to MIL-R-39016/35
- Qualified to MIL-R-39016/36



The dual coil version of the 3SBM magnetic latching relay is now available with coil transient suppression with or without blocking diodes for reverse polarity protection. This hybrid magnetic latching relay is an addition to the growing family of .150 grid relays. The diode method is employed to limit the back EMF generated when the coil circuit is opened in order to protect other circuit components such as semiconductors. The contact load capabilities of the 3SBM as well as the memory feature of the latching function are both maintained.

Electrical Characteristics

Contact Arrangement— 4-pole double-throw (4C)

Operate Sensitivity—

Single-coil form, 100 mW, Dual-coil form, 180 mW per coil

Contact Ratings –

DC resistive — 2 amps at 28 volts DC inductive — 0.5 amp at 28 volts, 200 mH

AC resistive — 0.5 amp at 115 volts (enclosure isolated from ground, or enclosure and movable contact at same notential)

AC — 0.125 amp at 115 volts (enclosure at line potential with respect to movable contact) Low-level — 50 µA at 50 mV

Low-level — 50 µA at 50 m\ Peak AC or DC

Contact Resistance —

0.050 ohms max.; 0.150 ohms after life test

Life — 100,000 operations at rated loads listed; 1,000,000 operations at low-level loads

Operating Characteristics Operate Time — 4 ms max.

Release Time — 4 ms max.

Contact Bounce — 4 ms max

Dielectric Strength (Note 1) —

500 volts rms at sea level; 350 volts rms at 70,000 feet and above

Insulation Resistance (Note 1) — 1,000 megohms min. over temperature

Environmental Characteristics

Vibration — 30 G, 55 to 3,000 Hz

Shock — 150 G at 11 ms

Temperature — -65°C to +125°C

Semiconductor Characteristics at 25°C

Max. Negative Transient — 1 volt Breakdown Voltage — 100 Vdc min.

Max. Leakage Current — 1 μA @ 50 Vdc

Note 1: Tests for dielectric withstanding voltage and insulation resistance should be made with "coil terminals" shorted together to avoid unnecessary electrical stress to semiconductor elements.

See page 1-62 for Mounting Forms, Terminals and Circuit Diagrams.

Coil Table Single Diode (All Values DC)*

	Dual Coil, Sensitivity Code 5 (180 mW)						
Coil Code Letter	Coil Resistance @ 25C (ohms) ± 10%	MAX. SET—RE Calibration Code 5 Voltage (Volts)	Suggested Source Volts†				
H N R T V	10 37 145 450 975 2140	1.4 2.6 5.2 9.0 13.5 20.0	135 70 35 20 3.5 9.2	2.0- 3.7 3.8- 7.2 7.6-14.5 14-25 20-35 30-54			

Coil Table Dual Diode (All Values DC)*

	Dual Co	il, Sensitivity C	ode 6 (180 mV	V)
Coil	Coil	MAX. SET—RE	SET VALUES	Suggested
Code Letter	Resistance @ 25C (ohms) ± 10%**	Calibration Code 5 Voltage (Volts)	Calibration Code 6 Current (mA)	Source Volts†
H N R T V	10 37 145 450 975 2140	2.4 3.6 6.2 10.0 14.5 21.0	135 70 35 20 13.5 9.2	2.6- 4.1 3.8- 7.2 7.6-14.5 14.0-25.0 20.0-35.0 30.0-45.0

^{*}Values listed are factory test and inspection values. User should allow for meter variations.

Note: See page 1-60 for ordering instructions.

^{*} The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.




[†]Applicable over the operating temperature range in circulating air.

^{**}Coil resistance cannot be measured by conventional bridge.

Mounting Forms (3SBM)

(Vibration note with each form is acceleration from 55 to 3000 Hz)



No Mount

Mounting Code	Vibration*
00	30g

^{*}Assumes relay held securely by potting or other means.

.610 max .096 dia. .096 dia. .094 ±.010

Vibration

30g

ALL DIMENSIONS IN INCHES

TOLERANCES Unless otherwise specified:					
Uniess otherwise	specified:				
Hundredths ± 0.020					
Thousandths ± 0.005					

Header and Connection Diagrams

Dual Coil


When the SET coil is pulsed with plus polarity on the blue bead, the movable contacts take the position shown in the connection diagram. The contacts are transferred when the RESET coil is pulsed with plus polarity on the reset terminal. A new pulse of the SET coil with plus polarity on the blue bead will transfer the contacts back.

The contacts can also be transferred by applying a pulse of opposite polarity to the coil previously pulsed. However, this method requires slightly more power than the more normal form of operation described in the previous paragraph.

CODE: 1 -.020 dia z ± .020

Mounting Code

13




CODE 1 blue beed 40 50 + 6 07 30 0|4 08 20 |30 99


(Terminal numbers for reference only)


Header Types


71		
Туре	Z Dimension	Header Code
Solder Hook	0.13	1
Straight Pin	0.12	8
Straight Pin (socket or PCB type)	0.19	4
Straight Pin	0.25	5

Terminal numbers for reference only











Six Pole, Electrically Held, 2 Amps and Less


SS

SS

Six Pole Half Size **High Performance Relay**

> Designed to MIL-R-39016





Terminal View

Product Facts

- Hermetically sealed
- Up to 2 amps switching
- High shock & vibration ratings
- Optional terminals & mounting styles
- 6 form C Hi-density design

Electrical Characteristics

Contact Arrangement —

6 Form C (6PDT)

Contact Material —

Stationary

Gold plated hardened silver alloy Moveable —

Gold plated hardened silver alloy

Contact Resistance —

Before Life — 50 milliohms max. (measured at 10 mA @ 6 Vdc) After Life — 100 milliohms max. (measured @ 2 A @ 28 Vdc)

Mechanical Life Expectancy —

1 million operations min.

Coil Voltage — 5 to 26.5 Vdc

Coil Power — 2.6 watts max. @ 25°C

Duty Cycle — Continuous

Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity — 475 mW

Contact Ratings

Туре	Operations Min.
Resistive	100,000
Resistive	100,000
Inductive (200mH)	100,000
Intermediate	50,000
Lamp	100,000
Low Level	1,000,000
	Resistive Resistive Inductive (200mH) Intermediate Lamp



SS (Continued)

Operating Characteristics

Timing — Operate Time — 5.0 ms max. Release Time — 5.0 ms max.

Contact Bounce — 5.0 ms max

Dielectric Withstanding Voltage —

Between Open Contacts — 350 Vrms 60 Hz

Between Adjacent Contacts — 500 Vrms 60 Hz

Between Contacts & Coil -500 Vrms 60 Hz

Insulation Resistance —

1,000 megohms min. @ 500 Vdc

Environmental Characteristics

Temperature Range —

-65°C to +125°C

Weight -

0.28 oz. (7.8 grms)


Vibration Resistance — 15 G's, 10 to 2,000 Hz

Shock Resistance -


100 G's, 6 ± 1 ms

QPL Equivalent -

MIL-R-39016



SS Terminals



Standard Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C	Pickup Voltage Vdc (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C	Drop-out Voltage Vdc (Min.) @ 25°C	Drop-out Voltage Vdc (Min.) @ -65°C	Nom. Coil Power (W) @ 25°C	Max. Coil Voltage	Coil Desig.
5.0	20	2.75	3.8	0.35	0.23	1.25	6.0	5
6.0	25	3.5	4.5	0.45	0.3	1.44	8.0	6
12.0	100	6.5	9.0	0.9	0.6	1.44	15.0	12
26.5	390	14.0	18.0	1.8	1.2	1.8	32.0	24

Mountings Specifying a Part Number Example: Type Contacts Coils **Terminals** SS BW-6C-24 В




Double Pole, Electrically Held, 5 Amps and Less

HFW4A, HFW5A

HFW4A, HFW5A Standard Half Size High Performance Relay Designed to MIL-R-39016/6





Terminal View

Product Facts

- Hermetically sealed
- Up to 5 amps switching
- High shock & vibration ratings
- Optional terminals & mounting styles
- **■** Excellent RF switching

Electrical Characteristics Contact Arrangement —

2 Form C (DPDT)

Contact Material —

Stationary — Hardened silver alloy Moveable — Gold plated hardened silver alloy

Contact Resistance —

Before Life — 50 milliohms max. (measured at 10 mA @ 6 Vdc) After Life — 100 milliohms max. (measured @ 2 A @ 28 Vdc)

Mechanical Life Expectancy —

50 million operations

Coil Voltage -

5 to 48 Vdc (HFW4A) 5 to 26.5 Vdc (HFW5A)

Coil Power — 1.4 watts max. @ 25°C

Duty Cycle — Continuous

Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity @ 25°C — 145 to 260 mW

Contact Ratings

Contact Load	Туре	Operations Min.
4 A @ 28 Vdc (HFW4A)	Resistive	100,000
5 A @ 28 Vdc (HFW5A)	Resistive	100,000
0.75 A @ 28 Vdc	Inductive (200mH)	100,000
0.1 A @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.3 A @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000
0.1 A @ 28 Vdc	Intermediate	50,000
0.160 A @ 28 Vdc	Lamp	100,000
30 μA @ 50 mVdc	Low Level	1,000,000

RF Performance

Frequency (MHz)	RF Losses (dB)	VSWR	Isolation (dB)
100	0.1	1.17:1	40
500	0.3	1.19:1	28
1000	0.4	1.19:1	23



HFW4A, HFW5A (Continued)

Operating Characteristics

Timing —

Operate Time — 4.0 ms max. Release Time — 4.0 ms max.

Contact Bounce — 2.0 ms max.

Dielectric Withstanding Voltage

– Between Open Contacts – 500 Vrms 60 Hz Between Adjacent Contacts — 1000 Vrms 60 Hz Between Contacts & Coil -1000 Vrms 60 Hz

Insulation Resistance —

10,000 megohms min. @ 500 Vdc

Environmental Characteristics

Temperature Range —


-65°C to +125°C


Weight — 0.46 oz. (13 gms max.)


Vibration Resistance —


20 G's, 10 to 2,000 Hz

Shock Resistance — 100 G's, 6 ±1 ms









Mounting Styles

Standard Coil Data


	Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C	Pickup Voltage Vdc (Max.) @ 25°C	Pickup Voltage Vdc (Min.) @ 125°C	Drop-out Voltage Vdc (Min.) @ 25°C	Drop-out Voltage Vdc (Min.) @ -65°C	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.
HFW4A/HFW5A	5.0	27	2.7	3.8	0.29	0.21	926	6.0	L
	6.0	40	3.2	4.5	0.35	0.25	900	7.5	F
	12.0	160	6.4	9.0	0.7	0.5	900	15.0	G
	26.5	700	13.5	18.0	1.5	1.0	1003	32.0	K
Other	6-8	60	3.5	4.85	0.35	0.22	817	9.0	Α
(avail. for	12-15	320	6.8	9.42	0.68	0.44	570	21.0	В
HFW4A	18.0	520	9.5	13.16	0.95	0.62	623	27.0	J
relays only)	26.5-32	1,250	14.0	19.4	1.5	0.98	684	42.0	D
	40.0	2,700	21.3	29.5	2.1	1.37	593	61.0	Н
	48.0	3,500	25.5	35.3	2.5	1.63	658	70.0	E

Specifying a Part Number Example: Type Terminals Mountings Coils **Features** HFW5A 12 30 Κ 00



HFC4A, HFC5A Commercial/Industrial Half Size Relay





Terminal View

Electrical Characteristics

Contact Arrangement —

2 Form C (DPDT)

Contact Material -

Stationary Bifurcated hardened silver alloy Moveable

Gold plated hardened alloy

Contact Resistance

Before Life — 50 milliohms max. (measured at 10 mA @ 6 Vdc) After Life — 100 milliohms max. (measured @ 2 A @ 28 Vdc)

Mechanical Life Expectancy — 10 million operations

Coil Voltage — 5 to 26.5 Vdc

Coil Power — 1.4 watts max. @ 25°C

Duty Cycle — Continuous

Pick-up Voltage — Approximately 60% of nominal coil voltage

Pick-up Sensitivity — 360 mW

Operating Characteristics

Timing -

Operate Time — 6.0 ms max. Release Time — 6.0 ms max.

Dielectric Withstanding Voltage

- Between Open Contacts -350 Vrms 60 Hz

Between Adiacent Contacts -500 Vrms 60 Hz

Between Contacts and Coil -500 Vrms 60 Hz

Insulation Resistance —

1,000 megohms min @ 500 Vdc

Environmental Characteristics Temperature Range -

-55°C to +85°C

Weight — 0.46 oz. (13 gms) max. Vibration Resistance —


10 G's, 10 to 500 Hz Shock Resistance — 30 G's. 6 ±1 ms

Product Facts

- **■** Hermetically sealed
- Up to 5 amps switching
- **■** Economical configuration
- Optional terminals & mounting styles


Contact Ratings


	Contact Load	Туре	Operations Min.
HFC4A	4 A @ 28 Vdc	Resistive	100,000
HFC5A	5 A @ 28 Vdc	Resistive	100,000
	0.75 A @ 28 Vdc	Inductive (200 mH)	100,000
	0.3 A @ 115 Vac, 60 Hz & 400 Hz	Resistive	100,000



Standard Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ± 20% @ 25°C	Pickup Voltage Vdc (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 85°C	Nom. Coil Power (W) @ 25°C	Max. Coil Voltage	Coil Desig.
5.0	27	3.0	3.7	.92	6.0	L
6.0	40	3.6	4.5	.90	7.5	F
12.0	160	7.2	8.9	.90	15.0	G
26.5	700	16.0	19.7	1.00	32.0	K





Mounting Styles

11

.190 MAX (4.83)

.030 +.008 -.006 (.76 +.003 -.002)

030 RAD



RLUE READ

.200 (5.08)

Terminals

 Θ

 $\Theta \Theta \Theta$

.400 (10.16)

_ .600 _ (15.24)



© BLUE BEAD

.200 (5.08)

0 0 0 →1 - .400 → (10.16)

⊚ (6

12


______ .187 ±.020

 $(4.75 \pm .51)$

.030 +.008 -.006 (.76 +.003 -.002)

FW, FW5A, SF, SF5A Two Pole Full Size Crystal-Can Relay FW Qualified to MIL-R-5757/10





Terminal View

Product Facts

- Hermetically sealed
- Up to 5 amps switching
- High shock & vibration ratings
- Optional terminals & mounting options
- **■** Excellent RF switching

Electrical Characteristics Contact Arrangement —

2 Form C

Contact Material —

Stationary —

Bifurcated hardened silver alloy Moveable —

Gold plated hardened alloy

Contact Resistance

Before Life — 50 milliohms max. (measured at 10 mA @ 6 Vdc) After Life — 100 milliohms max. (measured @ 2 mA @ 28 Vdc)

Mechanical Life Expectancy — 50 million operations

Coil Voltage -

6.3 to 110 Vdc (FW, FWSA) 1.8 to 40 Vdc (SF) 2.8 to 40 Vdc (SFSA)

Coil Power — 1.5 watts max. @ 25°C

Duty Cycle — Continuous

Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity -250 mW (FW, FWSA) 40 mW (SF) 80 mW (SF5A)

Operating Characteristics

Operate Time -

15 ms max. (SF) 5 ms (FW, FWSA)) 6 ms max. (MIL-R-5757/10)

Release Time -

10 ms max. (SF) 5 ms max. (FW, FWSA) 6 ms max. (MIL-R-5757/10)

Contact Bounce — 2 ms max.

Dielectric Withstanding Voltage

— Between Open Contacts — 500 Vrms 60 Hz Between Adjacent Contacts — 1,000 Vrms 60 Hz Between Contacts and Coil —

1,000 Vrms 60 Hz

Insulation Resistance — 10,000 megohms min @ 500 Vdc

Environmental Characteristics

Temperature Range —

-65°C to +125°C

Weight -

0.6 oz. max. (FW, FWSA) 0.7 oz. max. (SF 6) 1.1 oz. max. (SF/SF 5A)

Vibration Resistance —

Standard —

20 G's, 10 to 2000 Hz (FW, FWSA) 15 G's, 10 to 2000 Hz (SF) QPL —

20 G's, 10 to 2000 Hz


Shock Resistance —


100 G's, 6 ±1 ms

QPL Approval — MIL-R-5757/10 (FW only)


${\bf QPL} \; {\bf Equivalent} \, - \,$

MIL-R-5757/13 (SF only)





2



3

Terminals

RF Performance

Frequency (MHz)	RF Losses (dB)	VSWR	Isolation (dB)
100	0.1	1.17:1	40
250	0.2	1.18:1	33
500	0.3	1.19:1	28
750	0.4	1.19:1	25
1,000	0.4	1.19:1	23

Contact Ratings

Contact Load	Туре	Operations Min.
5 A @ 28 Vdc (FW5A/SF5A)	Resistive	100,000
3 A @ 28 Vdc (FW)	Resistive	100,000
2 A @ 28 Vdc (SF)	Resistive	100,000
1 A @ 115 Vac, 60 Hz & 400 Hz (FW)	Resistive	100,000
0.3 A @ 115 Vac, 60 Hz & 400 Hz (SF)	Resistive	100,000
1 A @ 28 Vdc	Inductive (200 mH)	100,000
0.1 A @ 28 Vdc	Lamp	100,000
10 μA @ 50 mVdc	Low Level	1,000,000
75 WATTS @ 50 MHz (FW)	RF	10,000,000

FW, FWSA Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C	Pickup Voltage Vdc (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C	Drop-out Voltage Vdc (Min.) @ 25°C	Drop-out Voltage Vdc (Min.) @ -65°C	Nom. Coil Power (W) @ 25°C	Max. Coil Voltage	Coil Desig.
6.3	35	3.2	4.4	0.35	0.23	1.13	7.9	Α
12.6	200	6.8	9.4	0.74	0.49	.79	15.8	D
17.6	340	8.9	12.3	0.97	0.64	.91	22.0	E
26.5	675	13.5	18.7	1.47	0.96	1.04	33.1	G
32.0	975	15.5	21.5	1.69	1.1	1.05	40.0	Н
48.0	2,450	25.0	34.7	2.73	1.8	.94	60.0	L
56.0	3,150	30.0	41.6	3.27	2.1	1.90	70.0	M
75.0	5,000	38.0	52.7	4.14	2.7	1.13	93.8	N
110.0	9,100	51.0	70.7	5.56	3.6	1.33	137.5	R


SF5/SF6 Coil Data

Nom. Coil Voltage (Vdc)	Nom. Current (mA)	Coil Resistance in Ohms ± 10% @ 25°C	Pickup Current (mA) @ 25°C	Nom. Coil Power (mW) @ 25°C	Coil Desig.
1.8	90.0	20	45.0	162	Α
9.0	18.0	500	9.0	162	E
12.6	12.6	1,000	6.5	159	F
16.5	11.0	1,500	5.2	182	G
18.0	9.0	2,000	4.5	162	Н
20.0	8.0	2,500	4.0	160	J
26.5	5.3	5,000	2.8	140	W
36.0	4.5	8,000	2.3	162	L
40.0	4.0	10,000	2.0	160	Υ

SF5A Coil Data

Nom. Coil Voltage (Vdc)	Nom. Current (mA)	Coil Resistance in Ohms ± 10% @ 25°C	Pickup Current (mA) @ 25°C	Nom. Coil Power (mW) @ 25°C	Coil Desig.
2.8	140.0	20	65.0	392	Α
4.0	80.0	50	41.6	320	В
12.0	24.0	500	12.5	288	E
18.0	18.0	1,000	9.3	324	F
26.5	10.6	2,500	5.6	281	J
40.0	8.0	5,000	4.0	320	W

NOTE: FW/FW5A = .875 (22.23) Max. SF6 = .900 (22.86) Max. SF5/SF5A5 = 1.281 (32.54) Max.




Specifying a Part Number Example:	<u>Type</u>	<u>Series</u>	Terminals	<u>Mountings</u>	<u>Coils</u>	<u>Features</u>
	FW	1	1	20	G	00
	SF	5	1	20	W	00
	SF5A	5	1	20	W	00
	SF	6	1	20	W	00



Single Pole, Electrically Held, 10 Amps and Less

C Single Pole, Half Size **High Performance Relay**





Terminal View

Product Facts

- Hermetically sealed
- Up to 10 amps switching
- High shock & vibration ratings
- Optional terminals & mounting styles

Electrical Characteristics Contact Arrangement —

1 Form C (SPDT)

Contact Material -

Stationary — Hardened silver allov Moveable — Hardened silver alloy

Contact Resistance —

Before Life — 50 Milliohms max. (measured at 10 mA @ 6 Vdc) After Life — 100 Milliohms max. (measured @ 1 A @28 Vdc)

Contact Rating –

Contact Load — 10 A 28 Vdc Type — Resistive Operations min. 50,000

Mechanical Life Expectancy — 1 million operations min.

Coil Voltage — 6 to 26.5 Vdc

Coil Power — 1.4 watts max. @ 25°C

Duty Cycle — Continuous

Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity — 260 mW

Operational Characteristics

Operate Time — 5.0 ms max. Release Time — 5.0 ms max.

Contact Bounce — 5.0 ms max.

Dielectric Withstanding Voltage

Between Open Contacts -500 Vrms 60 Hz Between Adjacent Contacts —

1000 Vrms 60 Hz

Between Contacts and Coils -1000 Vrms 60 Hz

Insulation Resistance —

1,000 megohms min. @ 500 Vdc

Environmental Characteristics


Temperature Range — -65°C to +125°C


Weight — 0.28 oz. (8 grams) max.

Vibration Resistance — 20 G's, 10 to 2,000 Hz

Shock Resistance — 100 G's, 6 ±1 ms

Designed To - MIL-R-39016





Standard Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C	Pickup Voltage Vdc (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C	Drop-out Voltage Vdc (Min.) @ 25°C	Drop-out Voltage Vdc (Min.) @ -65°C	Nom. Coil Power (W) @ 25°C	Max. Coil Voltage	Coil Desig.
6.0	40	3.5	4.5	0.45	0.3	.9	8.0	6
12.0	160	6.5	9.0	0.9	0.6	.9	15.0	12
26.5	700	14.0	18.0	1.8	1.2	1.0	32.0	24

Specifying a Part Number Example: Contacts Coils Terminals Type Mountings С BW-1C-24 В

Double Pole, Electrically Held, 10 Amps and Less

07

Two Pole 10 Amp **High Performance Relay**

Qualified to MIL-R-5757/23 MS 27245 & MS 27247

Product Facts

- Hermetically sealed
- Up to 10 amps switching
- High shock & vibration ratings
- Optional terminals & mounting styles
- DC, AC & diode-suppressed

Electrical Characteristics Contact Arrangement —

2 Form C (DPDT)

Contact Material -

Stationary — Silver cadmium oxide Moveable — Silver cadmium oxide

Contact Resistance -

Before Life — 10 milliohms max. After life — 20 milliohms max. (Measured at 10 A @ 28 Vdc)

Mechanical Life Expectancy -1 million operations

Coil Voltage — 6 to 120 Vdc, 115 Vac Coil Power — 4.3 watts max. @ 25°C

Duty Cycle — Continuous

Pick-up Voltage — Approximately 50% of nominal coil voltage

Pick-up Sensitivity — 565 mW

Operating Characteristics

Operate Time — Std — 10 ms max.

QPL - 15 ms max.

AC Coil - 15 ms max.

Release Time -

Std — 10 ms max. QPL — 15 ms max. AC Coil - 20 ms max.

Contact Bounce -

Std — 5 ms max. (N.O. and N.C.) QPL — 2 ms max. (N.O.)

QPL - 5 ms max. (N.C.)

Dielectric Withstanding Voltage

 Between Open Contacts – 500 Vrms 60 Hz

Between Adjacent Contacts — 1000 Vrms 60 Hz

Between Contacts and Coil -1000 Vrms 60 Hz

Insulation Resistance —

1,000 megohms min. @ 500 Vdc

Environmental Characteristics

Temperature Range — -65°C TO +125°C

Weight — 1.3 oz (37 gms) max.

Vibration Resistance —

Standard — 30 G's, 10 to 2.000 Hz QPL — 20 G's, 10 to 2,000 Hz

Shock Resistance -

100 G's, 6 ±1 ms

QPL Approval -


MIL-R-5757/23 MS 27245 MS 27247

Contact Ratings


Contact Load	Туре	Operations Min.
10 A @ 28 Vdc	Resistive	100,000
3 A @ 115 V, 60 Hz	Resistive	50,000
5 A @ 115 V, 400 Hz	Resistive	50,000
6 A @ 28 Vdc	Inductive	50,000
2 A @ 115 V, 60 Hz	Inductive	50,000
2.5 A @ 115 V, 400 Hz	Inductive	50,000
1 A @ 28 Vdc	Lamp	50,000
0.5 A @ 115 V, 60 Hz	Lamp	50,000
0.8 A @ 115 V, 400 Hz	Lamp	50,000
3 A @ 28 Vdc	Motor	50,000
1.5 A @ 115 V, 60 Hz	Motor	50,000
3 A @ 115 V, 400 Hz	Motor	50,000

^{*}All ratings grounded case








Terminal View




Terminal View











Terminals





Coil Data

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C	Pickup Voltage Vdc (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C	Drop-out Voltage Vdc (Min.) @ 25°C	Drop-out Voltage Vdc (Min.) @ -65°C	Nom. Coil Power (mW) @ 25°C	Max. Coil Voltage	Coil Desig.	Environmental
6.0	19	3.6	4.5	0.4	0.25	1.89	9.0	AA	Temperature
12.0	75	7.2	9.0	0.9	0.5	1.92	16.0	AB	-55°C to +85°C
26.5	300	14.4	18.0	1.8	1.0	2.34	32.0	AC	Vibration
48.0	1,200	29.0	36.0	3.6	2.0	1.92	52.0	AD	20G's, 10 to 2,000Hz
120.0	7,600	72.0	90.0	9.0	5.0	1.89	122.0	AE	Shock
115 Vac 400 Hz	1,200	72.0	90.0	10.0	5.0	n/a	n/a	AR	50G's, 11ms
115 Vac 60-400 Hz	7,600	72.0	90.0	10.0	5.0	n/a	n/a	AS	
6.0	19	3.3	4.5	0.4	0.25	1.89	9.0	BA	Temperature
12.0	75	6.5	9.0	0.9	0.5	1.92	16.0	BB	-65°C to +125°C
26.5	300	13.0	18.0	1.8	1.0	2.34	32.0	BC	Vibration
48.0	1,200	26.0	36.0	3.6	2.0	1.92	52.0	BD	20G's, 10 to 2,000Hz
120.0	7,600	66.0	90.0	9.0	5.0	1.89	122.0	BE	Shock
115 Vac 400 Hz	1,200	75.0	90.0	10.0	5.0	n/a	n/a	BR	50G's, 11ms
115 Vac 60-400 Hz	7,600	75.0	90.0	10.0	5.0	n/a	n/a	BS	
6.0	19	3.7	5.0	0.4	0.25	1.89	9.0	CA	Temperature
12.0	75	7.4	10.0	0.9	0.5	1.92	16.0	СВ	-65°C to +125°C
26.5	300	14.7	20.0	1.8	1.0	2.34	32.0	CC	Vibration
48.0	1,200	29.4	40.0	3.6	2.0	1.92	52.0	CD	30G's, 10 to 2,000Hz
120.0	7,600	74.0	100.0	9.0	5.0	1.89	122.0	CE	Shock
115 Vac 400 Hz	1,200	80.0	100.0	10.0	5.0	n/a	n/a	CR	100G's, 6ms
115 Vac 60-400 Hz	7,600	80.0	100.0	10.0	5.0	n/a	n/a	CS	



В * The part number example shown on this page is for catalog items. For a list of specific QPL part numbers, please see the index in Section 15.

3

B07

1

2

BC