




# WIREWOUND ANTI-SURGE RESISTORS

---

## Type EP Series


TE Connectivity is pleased to offer this wire wound axial leaded resistor. Robustly manufactured with high quality materials this resistor offers flame proof coating, and is designed and tested to withstand power surges of up to 12KV. In line with our commitment to increasing power to size ratio we are now also able to offer this series in extra-small size.

## CHARACTERISTICS - ELECTRICAL

|                  | Type    | Rated Power at 70° C | Max. Working Voltage | Max. Overload Voltage | Dielectric Withstanding Voltage | Resistance Range | Operating Temp. Range |
|------------------|---------|----------------------|----------------------|-----------------------|---------------------------------|------------------|-----------------------|
| NORMAL SIZE      | EP05W   | 1/2W (0.50W)         | 500 V                | 1,000 V               | 350 V                           | 10Ω - 560Ω       | -55°C - +155°C        |
|                  | EP1W    | 1W                   | 500 V                | 1,000 V               | 500 V                           | 10Ω - 1KΩ        |                       |
|                  | EP2W    | 2W                   | 500 V                | 1,000 V               | 500 V                           | 10Ω - 2KΩ        |                       |
|                  | EP3W    | 3W                   | 500 V                | 1,000 V               | 500 V                           | 10Ω - 3KΩ        |                       |
|                  | EP5W    | 5W                   | 500 V                | 1,000 V               | 500 V                           | 10Ω - 5KΩ        |                       |
|                  | EP7W    | 7W                   | 500 V                | 1,000 V               | 500 V                           | 10Ω - 6KΩ        |                       |
|                  | EP8W    | 8W                   | 500 V                | 1,000 V               | 500 V                           | 10Ω - 10KΩ       |                       |
|                  | EP9W    | 9W                   | 500 V                | 1,000 V               | 500 V                           | 10Ω - 15KΩ       |                       |
| SMALL SIZE       | EP1WS   | 1W                   | 500 V                | 1,000 V               | 350 V                           | 10Ω - 560Ω       | -55°C - +155°C        |
|                  | EP2WS   | 2W                   | 500 V                | 1,000 V               | 500 V                           | 10Ω - 1KΩ        |                       |
|                  | EP3WS   | 3W                   | 500 V                | 1,000 V               | 500 V                           | 10Ω - 2KΩ        |                       |
|                  | EP5WS   | 5W                   | 500 V                | 1,000 V               | 500 V                           | 10Ω - 3KΩ        |                       |
|                  | EP7WS   | 7W                   | 500 V                | 1,000 V               | 500 V                           | 10Ω - 5KΩ        |                       |
|                  | EP8WS   | 8W                   | 500 V                | 1,000 V               | 500 V                           | 10Ω - 6KΩ        |                       |
|                  | EP9WS   | 9W                   | 500 V                | 1,000 V               | 500 V                           | 10Ω - 10KΩ       |                       |
|                  | EP10WS  | 10W                  | 500 V                | 1,000 V               | 500 V                           | 10Ω - 15KΩ       |                       |
| EXTRA SMALL SIZE | EP1WSSS | 1W                   | 500 V                | 1,000 V               | 350 V                           | 1Ω - 560Ω        | -55°C - +155°C        |
|                  | EP1WSS  | 1W                   | 500 V                | 1,000 V               | 350 V                           | 1Ω - 750Ω        |                       |
|                  | EP2WSS  | 2W                   | 500 V                | 1,000 V               | 350 V                           | 1Ω - 910Ω        |                       |
|                  | EP3WSS  | 3W                   | 500 V                | 1,000 V               | 500 V                           | 1Ω - 2.2KΩ       |                       |
|                  | EP4WSS  | 4W                   | 500 V                | 1,000 V               | 500 V                           | 1Ω - 2.2KΩ       |                       |
|                  | EP10WSS | 10W                  | 500 V                | 1,000 V               | 500 V                           | 1Ω - 10KΩ        |                       |

## DERATING CURVE


For resistors operated in ambient temperatures above 70°C, power rating must be derated in accordance with this curve.




## SURGE RATING

|                  | Type    | Low Resistance Range | Maximum Surge Voltage | Medium resistance range | Maximum Surge Voltage | High Resistance Range | Maximum Surge Voltage |
|------------------|---------|----------------------|-----------------------|-------------------------|-----------------------|-----------------------|-----------------------|
| NORMAL SIZE      | EP05W   | 10Ω - 40Ω            | 3KV                   | 43Ω - 240Ω              | 4KV                   | 270Ω - 560Ω           | 4KV                   |
|                  | EP1W    | 10Ω - 50Ω            | 4KV                   | 51Ω - 240 Ω             | 5KV                   | 270Ω - 1kΩ            | 5KV                   |
|                  | EP2W    | 10Ω - 100Ω           | 5KV                   | 110Ω - 240Ω             | 6KV                   | 270Ω - 2kΩ            | 6KV                   |
|                  | EP3W    | 10Ω - 100Ω           | 7KV                   | 110Ω - 680Ω             | 8KV                   | 750Ω - 3kΩ            | 8KV                   |
|                  | EP5W    | 10Ω - 160Ω           | 8KV                   | 180Ω - 680Ω             | 9KV                   | 750Ω - 5kΩ            | 9KV                   |
|                  | EP7W    | 10Ω - 160Ω           | 9KV                   | 180Ω - 680Ω             | 10KV                  | 750Ω - 6kΩ            | 10KV                  |
|                  | EP8W    | 10Ω - 160Ω           | 10KV                  | 180Ω - 680Ω             | 11KV                  | 750Ω - 10kΩ           | 11KV                  |
|                  | EP9W    | 10Ω - 160Ω           | 10KV                  | 180Ω - 680Ω             | 11KV                  | 750Ω - 15kΩ           | 12KV                  |
| SMALL SIZE       | EP1WS   | 10Ω - 40Ω            | 3KV                   | 43Ω - 240Ω              | 4KV                   | 270Ω - 560Ω           | 4KV                   |
|                  | EP2WS   | 10Ω - 50Ω            | 4KV                   | 51Ω - 240 Ω             | 5KV                   | 270Ω - 1kΩ            | 5KV                   |
|                  | EP3WS   | 10Ω - 100Ω           | 5KV                   | 110Ω - 240Ω             | 6KV                   | 270Ω - 2kΩ            | 6KV                   |
|                  | EP5WS   | 10Ω - 100Ω           | 7KV                   | 110Ω - 680Ω             | 8KV                   | 750Ω - 3kΩ            | 8KV                   |
|                  | EP7WS   | 10Ω - 160Ω           | 8KV                   | 180Ω - 680Ω             | 9KV                   | 750Ω - 5kΩ            | 9KV                   |
|                  | EP8WS   | 10Ω - 160Ω           | 9KV                   | 180Ω - 680Ω             | 10KV                  | 750Ω - 6kΩ            | 10KV                  |
|                  | EP9WS   | 10Ω - 160Ω           | 10KV                  | 180Ω - 680Ω             | 11KV                  | 750Ω - 10kΩ           | 11KV                  |
|                  | EP10WS  | 10Ω - 160Ω           | 10KV                  | 180Ω - 680Ω             | 11KV                  | 750Ω - 15kΩ           | 12KV                  |
| EXTRA SMALL SIZE | EP1WSSS | 1Ω - 40Ω             | 1.5KV                 | 43Ω - 240Ω              | 2KV                   | 270Ω - 560Ω           | 2.5KV                 |
|                  | EP1WSS  | 1Ω - 40Ω             | 1.8KV                 | 43Ω - 240Ω              | 3KV                   | 270Ω - 750Ω           | 4KV                   |
|                  | EP2WSS  | 1Ω - 40Ω             | 2KV                   | 43Ω - 240Ω              | 3KV                   | 270Ω - 910Ω           | 4KV                   |
|                  | EP3WSS  | 1Ω - 100Ω            | 3KV                   | 110Ω - 240Ω             | 4KV                   | 270Ω - 2k2Ω           | 5KV                   |
|                  | EP4WSS  | 1Ω - 100Ω            | 4KV                   | 110Ω - 240Ω             | 5KV                   | 270Ω - 2k2Ω           | 6KV                   |
|                  | EP10WSS | 1Ω - 160Ω            | 9KV                   | 180Ω - 680Ω             | 10KV                  | 750Ω - 10kΩ           | 10KV                  |


## SURGE WAVEFORM (1.2 / 50 μS)



## 1.2 / 50 $\mu$ S VOLTAGE CAPABILITY




## CONSTRUCTION



| No. | Name            | Material                                          |
|-----|-----------------|---------------------------------------------------|
| 1   | Basic Body      | Rod Type Ceramics                                 |
| 2   | Resistance Wire | Resistance Wire Alloy                             |
| 3   | End Cap         | Steel (Tin plated iron surface)                   |
| 4   | Lead Wire       | Annealed copper wire coated with tin              |
| 5   | Joint           | By welding                                        |
| 6   | Coating         | Insulated & Non-Flame paint (colour: Light Green) |
| 7   | Colour Code     | Non-Flame epoxy resin                             |

## DIMENSIONS AND RESISTANCE RANGE




| Type    | Power Rating at 70°C | Dimensions (mm) |           |              |           |
|---------|----------------------|-----------------|-----------|--------------|-----------|
|         |                      | $D \pm 1$       | $L \pm 1$ | $d \pm 0.05$ | $H \pm 3$ |
| EP05W   | 1/2W (0.50W)         | 3.5             | 10.0      | 0.54         | 28        |
| EP1W    | 1W                   | 5.0             | 12.0      | 0.70         | 28        |
| EP2W    | 2W                   | 5.5             | 16.0      | 0.70         | 28        |
| EP3W    | 3W                   | 6.5             | 17.5      | 0.75         | 28        |
| EP5W    | 5W                   | 8.5             | 25.0      | 0.75         | 38        |
| EP7W    | 7W                   | 8.5             | 30.0      | 0.75         | 38        |
| EP8W    | 8W                   | 8.5             | 40.0      | 0.75         | 38        |
| EP9W    | 9W                   | 8.5             | 53.0      | 0.75         | 38        |
| EP1WS   | 1W-S                 | 3.5             | 10.0      | 0.54         | 28        |
| EP2WS   | 2W-S                 | 5.0             | 12.0      | 0.70         | 28        |
| EP3WS   | 3W-S                 | 5.5             | 16.0      | 0.70         | 28        |
| EP5WS   | 5W-S                 | 6.5             | 17.5      | 0.75         | 28        |
| EP7WS   | 7W-S                 | 8.5             | 25.0      | 0.75         | 38        |
| EP8WS   | 8W-S                 | 8.5             | 30.0      | 0.75         | 38        |
| EP9WS   | 9W-S                 | 8.5             | 40.0      | 0.75         | 38        |
| EP10WS  | 10W-S                | 8.5             | 53.0      | 0.75         | 38        |
| EP1WSSS | 1W-SSS               | 2.5             | 6.8       | 0.54         | 28        |
| EP1WSS  | 1W-SS                | 3.0             | 9.0       | 0.54         | 28        |
| EP2WSS  | 2W-SS                | 3.5             | 9.5       | 0.54         | 28        |
| EP3WSS  | 3W-SS                | 5.0             | 11.5      | 0.70         | 28        |
| EP4WSS  | 4W-SS                | 5.5             | 15.5      | 0.70         | 28        |
| EP10WSS | 10W-SS               | 8.5             | 39.5      | 0.75         | 38        |


## PERFORMANCE SPECIFICATION

| Characteristics              | Limits                                                                                                         | Test Methods (JIS C 5201-1)                                                                                                                                                                                                                                                                                                                                                                                                               |      |             |      |   |                 |         |   |            |              |   |                  |        |   |            |              |
|------------------------------|----------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------|-------------|------|---|-----------------|---------|---|------------|--------------|---|------------------|--------|---|------------|--------------|
| DC. resistance               | Must be within the specified tolerance                                                                         | The limit of error of measuring apparatus shall not exceed allowable range or 5% of resistance tolerance.                                                                                                                                                                                                                                                                                                                                 |      |             |      |   |                 |         |   |            |              |   |                  |        |   |            |              |
| Temperature coefficient      | $<20\Omega : \pm 400 \text{ PPM}/^{\circ}\text{C}$<br>$\geq 20\Omega : \pm 300 \text{ PPM}/^{\circ}\text{C}$   | Natural resistance change per temp. degree centigrade.<br>$\frac{R2-R1}{R1(t2-t1)} \times 10^6 \text{ (PPM}/^{\circ}\text{C})$ (R1: Resistance value at room temperature (t1)<br>R2: Resistance value at room temp. plus 100 °C (t2)<br>(Sub-clause 4.8)                                                                                                                                                                                  |      |             |      |   |                 |         |   |            |              |   |                  |        |   |            |              |
| Short time overload          | Resistance change rate is $\pm (2\% + 0.05\Omega)$ Max. with no evidence of mechanical damage                  | Permanent resistance change after application of a potential of 2.5 times RCWV for 5 seconds.<br>(Sub-clause 4.13)                                                                                                                                                                                                                                                                                                                        |      |             |      |   |                 |         |   |            |              |   |                  |        |   |            |              |
| Terminal Strength            | No evidence of mechanical damage                                                                               | <b>Direct load:</b><br>Resistance to a 2.5 kgs direct load for 10 secs. In the direction of the axis of the terminal leads<br><b>Twist test:</b><br>Terminal leads shall be bent through 90° at a point of about 6mm from the body of the resistor and shall be rotated through 360° about the original axis of the bent terminal in alternating direction for a total of 3 rotations<br>(Sub-clause 4.16)                                |      |             |      |   |                 |         |   |            |              |   |                  |        |   |            |              |
| Solderability                | 95% coverage Min.                                                                                              | The area covered with a new, smooth, clean, shiny and continuous surface free from concentrated pinholes.<br>Test temp. of solder 245°C $\pm$ 3°C<br>Dwell time in solder : 2 ~ 3 seconds<br>(Sub-clause 4.17)                                                                                                                                                                                                                            |      |             |      |   |                 |         |   |            |              |   |                  |        |   |            |              |
| Soldering temp. reference    | Electrical characteristics shall be satisfied. Without distinct deformation in appearance. (95% coverage Min.) | The leads immersed into solder bath to 3.2 to 4.8 mm. from the body. Permanent resistance change shall be checked.<br><u>Wave soldering conditions: (2 cycles Max.)</u><br>Pre-heat : 100 ~ 120 °C, 30 $\pm$ 5 sec.<br>Suggestion solder temp.: 235 ~ 255 °C, 10 sec. (Max.)<br>Peak temp.: 260 °C<br><u>Hand soldering condition:</u><br>Hand soldering bit temp.: 380 $\pm$ 10 °C<br>Dwell time in solder : 3 +1/-0 sec.                |      |             |      |   |                 |         |   |            |              |   |                  |        |   |            |              |
| Resistance to soldering heat | Resistance change rate is $\pm (1\% + 0.05\Omega)$ Max. with no evidence of mechanical damage.                 | Permanent resistance change when leads immersed to 3.2 to 4.8 mm from the body in 350°C $\pm$ 10 °C solder for 3 $\pm$ 0.5 seconds.<br>(Sub-clause 4.18)                                                                                                                                                                                                                                                                                  |      |             |      |   |                 |         |   |            |              |   |                  |        |   |            |              |
| Temperature cycling          | Resistance change rate is $\pm (2\% + 0.05\Omega)$ Max. with no evidence of mechanical damage                  | Resistance change after continuous 100 cycles for duty shown below: <table> <tr> <th>Step</th><th>Temperature</th><th>Time</th></tr> <tr> <td>1</td><td>-55°C <math>\pm</math> 3°C</td><td>30 mins</td></tr> <tr> <td>2</td><td>Room temp.</td><td>10 ~ 15 mins</td></tr> <tr> <td>3</td><td>+155°C <math>\pm</math> 2°C</td><td>30mins</td></tr> <tr> <td>4</td><td>Room temp.</td><td>10 ~ 15 mins</td></tr> </table> (Sub-clause 4.19) | Step | Temperature | Time | 1 | -55°C $\pm$ 3°C | 30 mins | 2 | Room temp. | 10 ~ 15 mins | 3 | +155°C $\pm$ 2°C | 30mins | 4 | Room temp. | 10 ~ 15 mins |
| Step                         | Temperature                                                                                                    | Time                                                                                                                                                                                                                                                                                                                                                                                                                                      |      |             |      |   |                 |         |   |            |              |   |                  |        |   |            |              |
| 1                            | -55°C $\pm$ 3°C                                                                                                | 30 mins                                                                                                                                                                                                                                                                                                                                                                                                                                   |      |             |      |   |                 |         |   |            |              |   |                  |        |   |            |              |
| 2                            | Room temp.                                                                                                     | 10 ~ 15 mins                                                                                                                                                                                                                                                                                                                                                                                                                              |      |             |      |   |                 |         |   |            |              |   |                  |        |   |            |              |
| 3                            | +155°C $\pm$ 2°C                                                                                               | 30mins                                                                                                                                                                                                                                                                                                                                                                                                                                    |      |             |      |   |                 |         |   |            |              |   |                  |        |   |            |              |
| 4                            | Room temp.                                                                                                     | 10 ~ 15 mins                                                                                                                                                                                                                                                                                                                                                                                                                              |      |             |      |   |                 |         |   |            |              |   |                  |        |   |            |              |

## PERFORMANCE SPECIFICATION (CONTINUED)

| Characteristics                                                                    | Limits                                                                                        | Test Methods (JIS C 5201-1)                                                                                                                                                                                        |
|------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Vibration                                                                          | Resistance change rate is $\pm (1\% + 0.05\Omega)$ Max.                                       | 55Hz, 3 planes 2hrs each<br>Total amplitude = 1.5mm<br>(Sub-clause 4.22)                                                                                                                                           |
| Load life in humidity                                                              | Resistance change rate is $\pm (5\% + 0.05\Omega)$ Max. with no evidence of mechanical damage | Resistance change after 1000 hrs (1.5 hrs "on", 0.5 hr "off") at RCWV in a humidity test chamber controlled at $40^{\circ}\text{C} \pm 2^{\circ}\text{C}$ and 90 to 95% relative humidity<br>(Sub-clause 4.24.2.1) |
| Load life                                                                          | Resistance change rate is $\pm (5\% + 0.05\Omega)$ Max. with no evidence of mechanical damage | Permanent resistance change after 1000 hrs operating at RCWV with duty cycle of (1.5 hours "on", 0.5 hour "off") at $70^{\circ}\text{C} \pm 2^{\circ}\text{C}$ ambient<br>(Sub-clause 4.25.1)                      |
| Resistance to solvent                                                              | No deterioration of protective coatings and markings                                          | Specimens shall be immersed in a bath of Isopropyl alcohol completely for 3 minutes with ultrasonic<br>(Sub-clause 4.30)                                                                                           |
| Surge immunity test<br>(Resistor stand alone-Not sync to phase angle and polarity) | Resistance change rate is $\pm (5\% + 0.05\Omega)$ Max.                                       | <div>Refer to IEC61000-4-5</div>  <div>1.2μsec rising time and<br/>50μsec discharge;<br/>10 cycles every 1 minute</div>          |
|                                                                                    |                                                                                               | <div>Max Surge Voltage</div> <div>Refer to surge rating chart.</div>                                                                                                                                               |


## PAINTING METHOD



Welding point, terminal and lead wire, is permissible to be exposed without the outer coated cover. The extent should be within  $\frac{1}{2}$  of the angle.


## MARKING

For EP Normal Size 1/2W, 1W, 2W, 3W and EP Small Size 1WS, 2WS, 3WS, 5WS and EP Extra Small Size 1WSSS, 1WSS, 2WSS, 3WSS. Resistors shall be marked with colour coding in accordance with JIS C 0802.



For EP Normal Size 5W, 7W, 8W 9W and EP Small Size 7WS, 8WS, 9WS, 10WS and EP Extra Small Size 10WSS. Resistors will be marked with:

1. Power Rating,
2. Nominal Resistance
3. Resistance Tolerance Code.



## LABEL

Label shall be marked with the following items:

1. Type and style
2. Resistance Tolerance
3. Nominal Resistance
4. Quantity
5. PPM
6. Lot Number


Example:

| TYCO PN | 2176082-7       |      |          |
|---------|-----------------|------|----------|
| DESC    | EP 3W (S)       | ± 5% | 100R     |
| QTY     | 1,000           | PCS. | PPM: 300 |
| LOT     | SAMPLE          |      |          |
| REF     | RoHS 2011/65/EU |      |          |




## PACKAGING

Tape dimensions (mm)



|                  |         | STYLE | $O \pm 1$ | $P$          | $L1-L2$<br>MAX. | $T \pm 1$ | $Z$<br>MAX. | $R$ | $T \pm 1$ | $S$<br>MAX. |
|------------------|---------|-------|-----------|--------------|-----------------|-----------|-------------|-----|-----------|-------------|
| NORMAL SIZE      | EP05W   | PT-52 | 52        | $5 \pm 0.3$  | 1               | 6         | 1           | 0   | 4         | 0.5         |
|                  | EP1W    | PT-52 | 52        | $5 \pm 0.3$  | 1               | 6         | 1           | 0   | 4         | 0.5         |
|                  | EP2W    | PT-64 | 64        | $10 \pm 0.5$ | 1               | 6         | 1           | 0   | 5         | 0.5         |
|                  | EP3W    | PT-64 | 64        | $10 \pm 0.5$ | 1               | 6         | 1           | 0   | 6         | 0.5         |
| SMALL SIZE       | EP1WS   | PT-52 | 52        | $5 \pm 0.3$  | 1               | 6         | 1           | 0   | 4         | 0.5         |
|                  | EP2WS   | PT-52 | 52        | $5 \pm 0.3$  | 1               | 6         | 1           | 0   | 4         | 0.5         |
|                  | EP3WS   | PT-64 | 64        | $10 \pm 0.5$ | 1               | 6         | 1           | 0   | 5         | 0.5         |
|                  | EP5WS   | PT-64 | 64        | $10 \pm 0.5$ | 1               | 6         | 1           | 0   | 6         | 0.5         |
| EXTRA SMALL SIZE | EP1WSSS | PT-52 | 52        | $5 \pm 0.3$  | 1               | 6         | 1           | 0   | 4         | 0.5         |
|                  | EP1WSS  | PT-52 | 52        | $5 \pm 0.3$  | 1               | 6         | 1           | 0   | 4         | 0.5         |
|                  | EP2WSS  | PT-52 | 52        | $5 \pm 0.5$  | 1               | 6         | 1           | 0   | 4         | 0.5         |
|                  | EP3WSS  | PT-64 | 64        | $10 \pm 0.5$ | 1               | 6         | 1           | 0   | 6         | 0.5         |
|                  | EP4WSS  | PT-64 | 64        | $10 \pm 0.5$ | 1               | 6         | 1           | 0   | 6         | 0.5         |


TAPE IN BOX PACKAGING (MM)



Bandoliers may also be  
contained in a cardboard  
box ("Ammopack")


|                  |         | Style | C ± 5 | A ± 5 | B ± 5 | Quantity Per Box (pcs.) |
|------------------|---------|-------|-------|-------|-------|-------------------------|
| NORMAL SIZE      | EP05W   | PT-52 | 260   | 85    | 70    | 1000                    |
|                  | EP1W    | PT-52 | 262   | 86    | 80    | 1000                    |
|                  | EP2W    | PT-64 | 262   | 92    | 108   | 1000                    |
|                  | EP3W    | PT-64 | 256   | 92    | 80    | 500                     |
| SMALL SIZE       | EP1WS   | PT-52 | 260   | 85    | 70    | 1000                    |
|                  | EP2WS   | PT-52 | 262   | 86    | 80    | 1000                    |
|                  | EP3WS   | PT-64 | 262   | 92    | 108   | 1000                    |
|                  | EP5WS   | PT-64 | 256   | 92    | 80    | 500                     |
| EXTRA SMALL SIZE | EP1WSSS | PT-52 | 260   | 85    | 70    | 1000                    |
|                  | EP1WSS  | PT-52 | 260   | 85    | 70    | 1000                    |
|                  | EP2WSS  | PT-52 | 262   | 86    | 80    | 1000                    |
|                  | EP3WSS  | PT-64 | 262   | 86    | 80    | 1000                    |
|                  | EP4WSS  | PT-64 | 262   | 86    | 80    | 1000                    |

## TAPE ON REEL PACKAGING (MM)




|                  |         | Style | A (Across Flanges) | Quantity Per Reel |
|------------------|---------|-------|--------------------|-------------------|
| NORMAL SIZE      | EP05W   | PT-52 | 73 ± 2             | 2500              |
|                  | EP1W    | PT-52 | 73 ± 2             | 2500              |
|                  | EP2W    | PT-64 | 81 ± 5             | 1000              |
|                  | EP3W    | PT-64 | 81 ± 5             | 500               |
| SMALL SIZE       | EP1WS   | PT-52 | 73 ± 2             | 2500              |
|                  | EP2WS   | PT-52 | 73 ± 2             | 2500              |
|                  | EP3WS   | PT-64 | 81 ± 5             | 1000              |
|                  | EP5WS   | PT-64 | 81 ± 5             | 500               |
| EXTRA SMALL SIZE | EP1WSSS | PT-52 | 73 ± 2             | 2500              |
|                  | EP1WSS  | PT-52 | 73 ± 2             | 2500              |
|                  | EP2WSS  | PT-52 | 73 ± 2             | 2500              |
|                  | EP3WSS  | PT-64 | 81 ± 5             | 1000              |
|                  | EP4WSS  | PT-64 | 81 ± 5             | 1000              |

BULK IN BOX (IN PLASTIC BAG) (MM)




|                  |         | $c \pm 5$ | $A \pm 5$ | $B \pm 5$ | Quantity Per Bag/Box (pcs.) |
|------------------|---------|-----------|-----------|-----------|-----------------------------|
| NORMAL SIZE      | EP05W   | 155       | 95        | 53        | 100 / 1000                  |
|                  | EP1W    | 155       | 95        | 53        | 100 / 500                   |
|                  | EP2W    | 155       | 95        | 53        | 100 / 500                   |
|                  | EP3W    | 155       | 95        | 53        | 100 / 400                   |
| SMALL SIZE       | EP1WS   | 155       | 95        | 53        | 100 / 1000                  |
|                  | EP2WS   | 155       | 95        | 53        | 100 / 500                   |
|                  | EP3WS   | 155       | 95        | 53        | 100 / 500                   |
|                  | EP5WS   | 155       | 95        | 53        | 100 / 400                   |
| EXTRA SMALL SIZE | EP1WSSS | 155       | 95        | 53        | 100 / 1000                  |
|                  | EP1WSS  | 155       | 95        | 53        | 100 / 1000                  |
|                  | EP2WSS  | 155       | 95        | 53        | 100 / 1000                  |
|                  | EP3WSS  | 155       | 95        | 53        | 100 / 1000                  |
|                  | EP4WSS  | 155       | 95        | 53        | 100 / 500                   |

BULK IN PLASTIC CASE PACKAGING (MM)



|             |       | $c \pm 5$ | $A \pm 5$ | $B \pm 5$ | Quantity Per cage/Box (pcs.) |
|-------------|-------|-----------|-----------|-----------|------------------------------|
| NORMAL SIZE | EP5W  | 36        | 20        | 8         | 100 / 1000                   |
| SMALL SIZE  | EP7WS | 36        | 20        | 8         | 100 / 1000                   |

## BULK IN INNER BOX PACKAGING (IN PLASTIC BAG) (MM)



|                        |         | Quantity / Bag<br>(pcs.) | Quantity Inner<br>Box (pcs.) | Quantity Carton<br>(pcs.) | Carton Box Size L<br>x W x H (± 5) |
|------------------------|---------|--------------------------|------------------------------|---------------------------|------------------------------------|
| NORMAL<br>SIZE         | EP7W    | 10                       | 250                          | 1000                      | 520 x 220 x 250                    |
|                        | EP8W    | 10                       | 250                          | 1000                      | 520 x 220 x 250                    |
|                        | EP9W    | 10                       | 250                          | 1000                      | 520 x 220 x 250                    |
| SMALL<br>SIZE          | EP8WS   | 10                       | 250                          | 1000                      | 520 x 220 x 250                    |
|                        | EP9WS   | 10                       | 250                          | 1000                      | 520 x 220 x 250                    |
|                        | EP10WS  | 10                       | 250                          | 1000                      | 520 x 220 x 250                    |
| EXTRA<br>SMALL<br>SIZE | EP10WSS | 10                       | 250                          | 1000                      | 215 x 520 x 250                    |

## ENVIRONMENTAL RELATED SUBSTANCE

This product complies to EU RoHS directive, EU PAHs directive, EU PFOS directive and halogen free.

Ozone layer depleting substances.

Ozone depleting substances are not used in our manufacturing process of this product.

This product is not manufactured using Chloro fluorocarbons (CFGs), Hydrochlorofluorocarbons (HCFCs), Hydrobromofluorocarbons (HBFCs) or other ozone depleting substances in any phase of the manufacturing process.

---

## STORAGE CONDITIONS (MSL1)

The performance of these products, including the solderability, is guaranteed for a year from the date of arrival at your company, provided that they remain packed as they were when delivered and stored at a temperature of  $25^{\circ}\text{C} \pm 10^{\circ}\text{C}$  and a relative humidity of  $60\%\text{RH} \pm 10\%\text{RH}$ , chemical and dust free atmosphere.

Even within the above guarantee periods, do not store these products in the following conditions.

Otherwise, their electrical performance and/or solderability may be deteriorated, and the packaging materials (e.g. taping materials) may be deformed or deteriorated, resulting in mounting failures.

1. In salty air or in air with a high concentration of corrosive gas, such as  $\text{Cl}_2$ ,  $\text{H}_2\text{S}$ ,  $\text{NH}_3$ ,  $\text{SO}_2$ , or  $\text{NO}_2$
2. In direct sunlight

## HOW TO ORDER

| EP          | 3W                                                                                                               | 200R                                                           | J                                                                     |                                                       |
|-------------|------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------|-----------------------------------------------------------------------|-------------------------------------------------------|
| Common Part | Power Rating                                                                                                     | Nominal Resistance                                             | Resistance Tolerance                                                  | Packaging                                             |
| EP          | 05W = 1/2W<br>1W = 1W<br>1WS = 1W-S<br>1WSS = 1W-SS<br>1WSSS = 1W-SSS<br>As per Electrical Characteristics chart | 10 $\Omega$ – 10R<br><br>1K $\Omega$ – 1K0<br>(1000 $\Omega$ ) | F = $\pm 1$<br><br>G = $\pm 2$<br><br>J = $\pm 5$<br><br>K = $\pm 10$ | - Tape/Box<br><br>TR - Tape/Reel<br><br>BB - Bulk/Box |

\*Preferred range is E24 resistances at 5% Tolerance with Tape/Box packaging.

---

## About TE

While TE has made every reasonable effort to ensure the accuracy of the information in this data sheet, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this data sheet are for reference purposes only and are subject to change without notice. Specifications are subject to

## Connect With Us

We make it easy to connect with our experts and are ready to provide all the support you need. Visit [te.com/support](https://te.com/support) to chat with a Product Information Specialist.

## te.com

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2023 TE Connectivity. All Rights Reserved.

04/23