



SEE NOTE 4 ↔
 SEE NOTE 1 ↔
 SEE NOTE 3 ↔
 SEE NOTE 2 ↔

ITEM	PART/DRG NO	QTY	DESCRIPTION
1	01-803-0016	2	ENGRAVING LABEL - WHITE/BLACK/WHITE - 80x35mm
2	01-807-0118	1	SINGLE SIDED FOAM TAPE - 10mm x 2mm x 25m REEL (FOR APPROX REQUIRED LENGTH, SEE NOTE)
3	01-807-0371	1	LINK BOX ENCLOSURE COVER 2-WAY (MK2 & MK3 LINKBOX)
4	01-807-0433	1	2-WAY LINK BOX ENCLOSURE SET - MK2 & MK3 LINKBOX (UR3030TMB)
5	BAH-018070591	1	RECYCLED LDPE 2 WAY LINK BOX BASE PAD : 500mm X 500mm X 12mm THICK
6	BAH-018110107	1	2-WAY VAC-FORMED DIVING BELL - MK3 LINKBOX
7	BAH-018110111	1	2-WAY DIVING BELL LOCKING BAR - MK3 LINKBOX
8	BAH-018110113	1	ADJUSTMENT LOCKING COLLAR - MK3 LINKBOX
9	BAH-018110138	2	LABEL - YELLOW / BLACK - 80 x 35 x 0.06mm "LID ARROWS THIS WAY"
10	BAH-018110161	2	LIFTING HANDLE FOR MK3 LINKBOX DIVING BELL
11	BAH-018110178	2	PRE-CAST MK3 LINKBOX 3-CORE STRAIGHT JOINT UPPER HOUSING
12	BAH-018110179	2	PRE-CAST MK3 LINKBOX 3-CORE STRAIGHT JOINT LOWER HOUSING
13	BAH-028110181	1	300mm ² 2-WAY 3-CORE PRE-CAST LINKBOX BODY BUILD - STANDARD UK VERSION
14	BAH-028110195	1	2-WAY PRE-CAST LINK / ACCESSORY TOOLBOX ASSEMBLY - MK3 LINKBOX



- NOTES :
- ADD 15mm LONG BEAD OF LOCTITE 595 SUPERFIX CLEAR SILICONE (AVANTE PART 9A430) TO LOWER THREADED AREA OF LOCKING BAR PRIOR TO ASSEMBLY WITH LOCKING COLLAR. ONCE ADJUSTED WITH LOCKING BAR FITTED TO ENCLOSURE AND LOCKING COLLAR JUST MAKING CONTACT WITH DIVING BELL, ALLOW SILICONE TO CURE.
 - LIFTING HANDLES ARE TO BE ATTACHED TO DIVING BELL USING SOLVENT CEMENT (AVANTE PART 0A529).
 - LABELS TO BE STUCK TO ENCLOSURE MIDDLE OR TOP RING AS SHOWN ON OPPOSITE FACES IN LINE WITH ENCLOSURE CUT-OUT.
 - SINGLE SIDED FOAM TAPE TO BE APPLIED TO FLANGES OF STRAIGHT JOINT LOWER HOUSING. LENGTH REQUIRED APPROX 2600mm



Material	VARIES	Part Description	- IF IN DOUBT ASK - DO NOT SCALE -
Finish	VARIES	300mm ² 2-WAY 3-CORE PRE-CAST MK3 LINKBOX	
Tolerances (UOS)	N/A	- STANDARD UK VERSION	
B&H Short Desc.	1712/UK		

F	BAH-018070591 (x1) WAS BAH-018070426 (x1)	BH-01155	24/03/16
E	NOTE 3 REVISED TO CLARIFY LABEL POSITION	BH-01018	28/07/14
D	REMOVED BAH-038070347 (x2), BAH-018000626 (x2), BAH-018110109 (x1), BAH-018110114 (x1), BAH-018070410 (x6) AND REPLACED WITH BAH-028110195 (x1)	BH-01011	14/07/14
	BAH-018070410 (x6) ADDED	BH-01012	
C	BAH-038070347 QTY 2 WAS QTY 4	BH-00965	05/02/14
B	PICTORIAL CHANGES ONLY	BH-00919	12/09/13
A	FIRST ISSUE (WAS D154-000 REV X3)	BH-00866	06/03/13
Revision	Description	Name/DMR	Date
Design/Drawn	D M EATON	Date	29-Aug-12
Scale (UOS)	1:10	Part Weight	
TCPN	EE8506-000	Drawing/Part No	BAH-028110182
		Drawing Type	CUSTOMER
		Rev	F